




GREENLEE®
A Textron Company

MADE FOR THE TRADE!™



BIT,STEP 32,5MM (PKGD)

Kwik Stepper® Step Bits

Cat No: 36022

UPC No: 783310360223

Description

- Unique split-tip design penetrates through steel faster
- Resists walking or skidding, even on round surfaces
- Balanced, double-flute construction requires less pressure, does the work for you
- Designed and manufactured in USA.

Specifications

- Capacity : Cut Up Through 3/8 IN (9.500 MM) Mild Steel, Copper, Brass, Aluminum, Wood, Plastic and Laminates
- Hole Size : 0.638 IN (16.200 MM), 0.803 IN (20.400 MM), 1 IN (25.400 MM), 1.280 IN (32.500 MM)
- ISO : 16, 20, 25, 32
- Maximum Material Thickness : 1/4 IN (6.400 MM)
- Minimum Chuck Size : 3/8 IN (9.500 MM)
- Overall Length : 3-7/8 IN (85.700 MM)
- Sub Brand : Kwik Stepper