




Wiha Dynamic Series Screwdrivers - Slotted & Phillips




Rotating cap prevents user discomfort and blisters - even at high pressure and high torque

Allows rapid rotation

Blade CVM steel, hardened, hard chromed

Ergonomic Handle shape for user comfort




510 90 Set 5 Pc. Slotted & Phillips, Wiha-Dynamic Handle

Item	↓	⊕	—	—	⊕	—	—	↶	↷
No.	mm	Inch	mm	Inch	Size	mm	Inch	lbs.	pkg.
510 90	3.0	.118	80	3.1	0	60	2.3	.68	1
	4.0	.157	100	3.9	1	80	3.1		
	5.5	.216	125	4.9					



510 Slotted Screwdriver, With Wiha-Dynamic Handle

Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Dynamic-handle high quality plastic.

Item	↓	⊕	—	—	⊕	—	—	↶	↷	
No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
510 20	2.0	.08	65	2.5	0.4	.02	165	6.5	.04	10
510 25	2.5	.10	75	3.0	0.4	.02	175	6.9	.04	10
510 30	3.0	.12	80	3.1	0.5	.02	180	7.1	.05	10
510 35	3.5	.14	100	3.9	0.6	.02	205	8.1	.07	10
510 40	4.0	.16	100	3.9	0.8	.03	205	8.1	.08	10
510 55	5.5	.22	125	5.0	1.0	.04	236	9.3	.14	10
510 65	6.5	.26	150	5.9	1.2	.05	267	10.5	.20	10
510 80	8.0	.32	175	7.0	1.2	.05	267	11.6	.29	10

510 92 Set 4 Pc. Slotted, Wiha-Dynamic Handle

Item	↓	⊕	—	—	↓	⊕	—	—	↶	↷
No.	mm	mm	Inch		mm	mm	Inch		pkg.	lbs.
510 92	2.0	65	2.5		5.5	125	5.0		1	.58
	3.0	80	3.1		6.5	150	6.0			



511 Phillips Screwdriver, With Wiha-Dynamic Handle

Item	⊕	—	—	⊕	⊕	—	—	↶	↷
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
511 05	0	60	2.4	3.0	1/8	160	6.3	.05	10
511 10	1	80	3.1	4.5	3/16	191	7.5	.11	10
511 20	2	100	3.9	6.0	1/4	217	8.5	.17	10



510 99 Set 11 Pc. Slotted & Phillips, Wiha-Dynamic Handle

Item	↓	⊕	—	—	⊕	—	—	↶	↷
No.	mm	Inch	mm	Inch	Size	mm	Inch	lbs.	pkg.
510 99	2.0	.078	65	2.5	0	60	2.3	1.3	1
	2.5	.098	75	3.0	1	80	3.1		
	3.0	.118	80	3.1	2	100	4.0		
	3.5	.139	100	3.9					
	4.0	.157	100	3.9					
	5.5	.216	125	5.0					
	6.5	.255	150	5.9					
	8.0	.315	175	7.0					