




Rating	20A 277VAC, 1HP 277VAC 1/2HP 125VAC  10(4)A 250V~25T85 	Mounting Hole	Circuit
Contact Resistance	50m ohm Max		
Insulation Resistance	DC 500V 100M ohm Min		
Dielectric Strength	AC 1500V 1 minute		
Operation Temperature	0°C~85°C		
Switch Function	3P SPDT ON-ON		

Waterproof: IP56



RoHS Compliant

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 2/03/09

Rev. 1

Unit: mm

Checked By: GG

Title: TOGGLE SWITCH

CW P/N: GTS447C301HR