








PC board drilling dimensions(after plating)
(thickness ≤ 3.20±0.30mm)



SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	TIN LEAD	TIN LEAD	TIN LEAD	TIN LEAD	LEAD FREE	LEAD FREE	LEAD FREE
09	30.81	24.99	16.96	16.79	10.96	D09P91C4P V00	D09P91C6P V00	D09P91C8P V00	D09P91C8P V00LF	D09P91C4P V00LF	D09P91C6P V00LF	D09P91C8P V00LF
15	39.14	33.32	25.18	25.12	19.18	D15P91C4P V00	D15P91C6P V00	D15P91C8P V00	D15P91C8P V00LF	D15P91C4P V00LF	D15P91C6P V00LF	D15P91C8P V00LF
25	53.03	47.04	39.12	38.84	33.12	D25P91C4P V00	D25P91C6P V00	D25P91C8P V00	D25P91C8P V00LF	D25P91C4P V00LF	D25P91C6P V00LF	D25P91C8P V00LF
37	69.32	63.50	55.68	55.30	49.68	D37P91C4P V00	D37P91C6P V00	D37P91C8P V00	D37P91C8P V00LF	D37P91C4P V00LF	D37P91C6P V00LF	D37P91C8P V00LF
				gold flash			0.76» gold		1.25» gold		gold flash	

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0001

European Views

www.fciconnect.com				surface	ISO 1302	tolerance std	ISO 406 ISO 1101	projection	mm
				TOLERANCES UNLESS OTHERWISE SPECIFIED					
Dr	PESSON	1992-09-15	ANGULAR	0.X		±0.1	size	A3	Scale
Eng	PESSON	1992-09-15		0.XX		±0.1			2
H	LS05-004	LMA	2004/12/31	0.XXX		±0.1	ECN	109-0268	
J	LS06-0097	LGO	2006/07/29	Product family		D-SUB	Spec ref	-	
K	LS06-0140	LGO	2006/09/22						
L	109-0268	NG	2009-11-24						
	-	-	-						
	-	-	-						
	-	-	-						

FCI		MALE CONNECTOR DELTA D		C01-8646-0112		Rev.
EUROPE STRAIGHT PRESS-FIT						L
catalog no				CUSTOMER		sheet 1 of 1

