

NYS231BG-LL

3 pole 3.5 mm plug, black metal handle, gold plated contacts, up to 8 mm cable diameter



Technical Information

Product

Title NYS231BG-LL

Electrical

Dielectric strength	0.5 kVdc
Insulation resistance	$\geq 1 \text{ G}\Omega$
Rated current	depends on mated connector
Contact resistance	depends on mated connector

Mechanical

Cable O.D.	8 mm
Lifetime	1000 mating cycles

Environmental

Flammability	Complies with IEC 68-2-20
Temperature range	-25 °C to +70 °C