

HC-M-KV-M25(14-21)

Order No.: 1646007

The illustration shows version HC-M-KV-M20

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1646007>

Metal screw connection up to 5 bar, thread length: 7 mm, cable
diameter: 14 - 21 mm, WAF 34, screw connection: M25

Commercial data

GTIN (EAN)	
sales group	D092
Pack	25 pcs.
Customs tariff	74199990
Catalog page information	Page 521 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
06/01/2006



[http://
www.download.phoenixcontact.com](http://www.download.phoenixcontact.com)
Please note that the data given
here has been taken from the
online catalog. For comprehensive
information and data, please refer
to the user documentation. The
General Terms and Conditions of
Use apply to Internet downloads.

Technical data

General data

Cable gland material	Nickel-plated brass
Seal material	Neoprene
Cable seal material	Neoprene
Material, O-ring	NBR
Wrench size, union nut	34 mm

Wrench size, support	34 mm
Thread type connection side 1	M25
Length of the connecting thread	7.00 mm
External cable diameter	14 mm ... 21 mm
Conductor sealing range	14.00 mm ... 21.00 mm
Tightening torque, union nut	10.00 Nm
Degree of protection	IP68, to 5 bar
Ambient temperature (operation)	-20 °C ... 100 °C

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;