



	10	9	8	7	6	5	4	3	2	106024			
	CONNECTOR P/N	øD (μm)	ød (μm)	HOUSING COLOR	BOOT COLOR	CABLE TYPE							
F	106024-2500	125.50 +0.50 0	1.0	BLUE	WHITE	SINGLE MODE							
	106024-2512				RED								
	106024-3550	127.00 +3.00 0	3.0	BEIGE	WHITE	MULTIMODE							
106024-3500	BLUE												
106024-3530													
106024-4500	125.00 +0.50 0	1.0	BLUE	WHITE	SINGLE MODE								
106024-5500	126.00 +1.00 0			RED									
106024-5540													
106024-5580				BLUE									
106024-5590	125.25 +0.50 0			WHITE									
D	106024-6500	0.5											
	106090-2700					125.50 +0.50 0							
	106090-4500					125.00 +0.50 0							
	106090-6500					125.25 +0.50 0							
	106090-4510					125.2-125.5							
106090-4520	125.51-125.9												
106099-0500	81.0±0.5	1.4		YELLOW									
106024-2513	125.50 +0.50 0	0.5											
	106024-5530	126.00 +1.00 0	1.0	BEIGE	WHITE								
							(DUST CAP NOT SHOWN)						
							BUFFERED FIBER						
													
													
NOTE:													
1. ALL DIMENSIONS ARE GIVEN IN INCHES/MM, EXCEPT OTHERWISE SPECIFIED.													
*2. P/N 106024-3310 AND 106024-5540 ARE BULK PACKED.													