

10 9 8 7 6 5 4 3 2 1

F



E

D


C

B

A






ONLY REQUESTED ANNULAR RING
ON THE REVERSE SIDE




COMPONENT MOUNT SIDE
PWB THICKNESS 1.60MM
(DEFAULT TOLERANCE ±0.05MM)

- NOTE :
1. MATERIAL :
HOUSING : THERMOPLASTIC 30% GLASS FILLED , BLACK,UL94V-0
TERMINAL : COPPER ALLOY THICKNESS 0.20mm.
SHELL : STAINLESS STEEL THICKNESS 0.30mm.
 2. PLATING :
TERMINAL:
CONTACT AREA : GOLD 0.76 MICROMETER MIN.
SOLDERING AREA : MATTE TIN 3.8 MICROMETER MIN.
UNDERPLATING : NICKEL 1.27 MICROMETER MIN.
SHELL:
OVERALL SOLDERING NICKEL 1.27 MICROMETER MIN.
 3. PRODUCT CHARACTERS SPEC: PER PS-105057-001.
 4. PACKAGE INFORMATION: PER PK-105057-001.
 5. THE PART COMPLIANT TO RoHS DIRECTIVE 2002/95/EC AND ELV 2000/53/EC.



SECTION Z-Z



NEW RELEASE EC NO: SH2009-0472 DRWNR:ZHANG CHKD: APPR:HWANG A	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ◻=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
			mm	INCH	DRAWN BY DAVID HU	DATE 2008/06/05	TITLE VERTICAL USB TYPE LEAD FREE					
			4 PLACES	± ---	± ---	CHECKED BY ROST ZHANG						DATE 2008/06/05
			3 PLACES	± ---	± ---	APPROVED BY HARVEY	DATE 2008/06/05	MOLEX INCORPORATED				
			2 PLACES	± 0.25	± ---	MATERIAL NO. 1050570001						
			1 PLACE	± 0.25	± ---	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						
ANGULAR ± 3 °												
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												

9 8 7 6 5 4 3 2 1