





NOTE:
 64 THR'D P.I.
 MAJOR .1875-.0028
 PITCH .1799-.0024
 MINCR .1708

JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
329	2.5	.400	.500	6.91	30	C-2R
325	3.0	.190	.250	3.14	350	C-2R
8662	6.0	.040	.030	0.38	1,000	C-2R
8552	6.3	.200	.550	6.91	5,000	C-2F
8635	28.0	.040	.340	4.27	2,800	C-2R

			METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		JKL COMPONENTS CORPORATION			
					TITLE T-1 1/4 SPECIAL MIDGET SCREW BASE					
A CHNG. FILAMENT TYPE FOR 325 TO C-2R RELEASE & CANCEL 3515, 8645			9/26/06 10/11/00		L. WENGSTROM QC 9/26/06		SIZE A FSCM NO. 55335		DRAWING NO. SCREW BASE SPECIAL T-1 1/4	
REV. NO. DESCRIPTION/ECO NUMBER			APPVD DATE		- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE NONE		RELEASED DATE 10/11/00 REVISION DATE 9/26/06 REV. NO. A SHEET 1 OF 1	