


# Desk-top enclosure – *propac*PRO


Cases, 4 and 6 U, unshielded




05806003



05806008



05806078



05806061

05806062

4 U

6 U

- Desk-top case with pre-configured components, in accordance with IEC 60297-3-101; prepared for 19" components such as plug-in units and euroboards
- Ventilation slots in base plate
- Prepared for GND/earthing

**Delivery comprises** (kit, items 1 - 6 fitted)

| Item | Qty |     | Description                                                                                                                                                    |
|------|-----|-----|----------------------------------------------------------------------------------------------------------------------------------------------------------------|
|      | 4 U | 6 U |                                                                                                                                                                |
| 1    | 1   | 1   | Frame, Al die-cast, powder-coated, RAL 7016                                                                                                                    |
| 2    | 2   | 4   | Side panel, Al extrusion, powder-coated, RAL 9006                                                                                                              |
| 3    | 1   | 1   | Cover plate, Al, 1 mm, internal surface conductive, visible surface powder-coated, RAL 9006, with GND/earthing tag                                             |
| 4    | 1   | 1   | Base plate, Al, 1 mm, internal surface conductive, visible surface powder-coated, RAL 9006, with GND/earthing tag, base plate with 4 rows of ventilation slots |
| 5    | 2   | 2   | End piece for rear, ABS, RAL 7016, UL 94 V-0; can be used as a foot for use in vertical position                                                               |
| 6    | —   | 2   | Adaptor bracket, Al                                                                                                                                            |
| 7    | 2   | 2   | Cover trim for side panel, Al extrusion, powder-coated, RAL 9006                                                                                               |
| 8    | 4   | 4   | Case foot with anti-slip protection, PC, black, UL 94 V-0                                                                                                      |
| 9    | 1   | 1   | Assembly kit                                                                                                                                                   |

## Order Information

| Usable width |       | Width W1 | Depth D | 4 U       | 6 U       |
|--------------|-------|----------|---------|-----------|-----------|
| W2           | W2    |          |         | Part no.  | Part no.  |
| HP           | mm    | mm       | mm      |           |           |
| 42           | 218.4 | 257      | 266     | 14576-221 | –         |
| 42           | 218.4 | 257      | 326     | 14576-223 | –         |
| 63           | 325.1 | 363.7    | 266     | 14576-241 | –         |
| 63           | 325.1 | 363.7    | 326     | 14576-243 | –         |
| 63           | 325.1 | 363.7    | 386     | 14576-245 | –         |
| 63           | 325.1 | 363.7    | 446     | 14576-247 | –         |
| 84           | 431.8 | 470.3    | 326     | –         | 14576-463 |
| 84           | 431.8 | 470.3    | 386     | 14576-265 | 14576-465 |
| 84           | 431.8 | 470.3    | 446     | 14576-267 | 14576-467 |
| 84           | 431.8 | 470.3    | 506     | 14576-269 | 14576-469 |

## Accessories

**GND/earthing kit** Cu wire 1.5 mm<sup>2</sup>, PVC sleeve, green/yellow, links side panels, base, cover and rear panel , 21102-001  
PU 1 piece

Maximum mounting depth = D - 45  
(Distance: front panel - rear panel)

## Note

- Case, 4 U with side panel for tip-up carrying handle, see page 5.52
- Dimensions side panel, see page 5.53



For further information [www.schroff.biz/oneclick](http://www.schroff.biz/oneclick)  
oneClick search code = Part no.



ServicePLUS see page 5.4