


Dimensions: mm (in.)

**Electrical Specifications:**

- Rating: Switching: 25mA/24VDC
Non-Switching: 100mA/50VDC
- Contact Resistance: 50mΩ Max. (Initial)
- Insulation Resistance: 100MΩ Min.
- Dielectric Strength: 500V AC (50Hz or 60Hz) for 1 min.

Soldering Process:

- Manual Soldering:
Soldering Temp and Continuous Time: Max.350°C and Max. 5 seconds

Note:

- RoHS Compliant

Mechanical Specifications:

- Operating Temperature Range: -20° C to +70° C
- Storage Temperature Range: -40° C to +85° C

Side Actuated DIP Switch
106-LP04-EV

Mountain
Switch

Available from Mouser Electronics

www.mouser.com 1-800-346-6873

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[106-LP04-EV](#)