


19-Pin M23 *multifast*® Cordsets, DC Color Code, Standard Wiring

- Straight Female Connector
- For *eurofast*® Junction Boxes and multi-conductor Applications
- IEC IP 67 Protection
- 150 V, 9 A (18 AWG) & 2 A (22 AWG)



Housing Style	Part Number	Cable	Ports, App.	Features	Pinout
	CKM 19-11-*	PLTC PVC Yellow 3x18, 8x22 AWG 105°C 8.5 mm OD Cable #RF50624-*M†	4-port, 2 Signals per port	<i>flexlife</i> ®	3. GY 4. RD/BU 5. GN 6. BU 7. GY/PK 8. WH/GN 12. GN/YE 14. BN/GN 15. WH 16. YE 19. BN
	CKM 19-11-*/S90	AWM PUR Yellow 3x18, 8x22 AWG 105°C 8.4 mm OD Cable #RF50718-*M†		Cut/Abrasion Immune	
	CKM 19-15-*	AWM PVC Yellow 3x18, 12x22 AWG 105°C 8.4 mm OD Cable #RF50625-*M†	6-port, 2 Signals per port	<i>flexlife</i>	2. RD 3. GY 4. RD/BU 5. GN 6. BU 7. GY/PK 8. WH/GN 9. WH/YE 12. GN/YE 13. YE/BN 14. BN/GN 15. WH 16. YE 17. PK 19. BN
	CKM 19-15-*/S90	AWM PUR Yellow 3x18, 12x22 AWG 105°C 8.4 mm OD Cable #RF50818-*M†		Cut/Abrasion Immune	
	CKM 19-19-*	PLTC PVC Yellow 3x18, 16x22 AWG 105°C 10.4 mm OD Cable #RF50620-*M†	8 port, 2 Signals per port	<i>flexlife</i>	1. VT 2. RD 3. GY 4. RD/BU 5. GN 6. BU 7. GY/PK 8. WH/GN 9. WH/YE 10. WH/GY 11. BK 12. GN/YE 13. YE/BN 14. BN/GN 15. WH 16. YE 17. PK 18. GY/BN 19. BN
	CKM 19-19-*/S90	AWM PUR Yellow 3x18, 16x22 AWG 105°C 10.4 mm OD Cable #RF50682-*M†		Cut/Abrasion Immune	
	CKM 19-19-*/S101	AWM TPE Yellow 3x18, 16x22 AWG 105°C 9.3 mm OD Cable #RF50916-*M†		<i>flexlife-10, High Flex - Over 10 million cycles</i>	



* Length in meters.

Standard cable lengths are 5 and 10 meters. Consult factory for other lengths.

Standard coupling nut material is nickel plated brass.. "CKM.."; "CKMV.." indicates stainless steel coupling nut.

† See Section N for *reelfast*® cable information.