




FCI P/N	Q'NTE 12
(NOTE 1)	(NOTE 1)
57634-YXXX	XXX



NOTES:
1. FCI PART NUMBER CONSISTS OF THE DVG NO, A DASH
A SUFFIX XXXX WHERE Y IS THE UNIT OF LENGTH (Y=IN IS
METERS AND Y=IS FEET) AND WHERE XXX IS THE LENGTH "L".
(EX. 57634-F104 IS 4 FEET IN LENGTH)

mat'l. code	tolerances unless otherwise specified	CUSTOMER COPY	projection	title	product family FIBER OPTICS	code
lit	ech no	dr	date	linear	UNLESS NOTED	
A	V11329	JLK	5/11/01			
				angles		
				dr	J. KIL	5/11/01
				eng	G. WARNER	5/11/01
				chr	G. WARNER	5/11/01
				appr	G. WARNER	5/11/01
sheet	revision	A			scale	3:4
index	sheet	1				

SPECIFICATIONS			
INSERTION LOSS	LC	SC	
RETURN LOSS	0.25dB MAX	0.5dB MAX	
FIBER PROTRUSION	300μ MIN	300μ MIN	
APEX OFFSET	50μ MAX	50μ MAX	
FIBER UNDERCUT	45μ MAX	45μ MAX	
	SEE TELECOM DIA GR-326		