



FEATURES:

- Ideal for providing jumper wires between small components.

MATERIALS:

Conn: 1st End - Micrograbber®

Material: Contact – Beryllium Copper per QQ-C-533, Alloy 165, ¼ HM.

Spring – Stainless Steel, Alloy 302.

Finish: Contact – Gold plated per MIL-G-45204, Type 1, Class 00.

Insulation: Glass filled nylon.

Marking: “POMONA ELECTRONICS” “MICROGRABBER®”

Wire: 20 AWG, stranding 41 x 36 t.c., PVC insulated 2.21 (.087) O.D.

Marking: “POMONA 4613-”

Color: See Ordering Information.

Conn: Same as first end.

RATINGS:

Operating Temperature: +102°C. (+216°F.) Max.

Operating Voltage: 30VAC/60VDC Max.

Current: 3 Amperes

ORDERING INFORMATION: Model 4613-XX-*

Single Patch Cord: XX = Cable Lengths, Standard Lengths: 12” (305), 24” (610), 36” (914) & 48” (1219).

Additional lengths can be quoted upon request.

Ordering Example: 4613-48-2 Indicates 48” in length, color is Red

ORDERING INFORMATION: Model 5525

Kit containing 10 pieces of Model 4613-24, one of each color.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ±.005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA