

## Cable Management Accessories


HellermannTyton manufactures a full line of quality cable ties in a wide variety of materials, colors, styles and sizes. Used to bundle and secure wire and cable, these cable ties are engineered and manufactured for maximum performance and quality.

HellermannTyton offers many options of cable ties. Whether the application demands extra strength, mounting, releasable, identification features or more, HellermannTyton has the cable tie to fit the requirement.



## Standard Cable Ties

Standard cable ties include varying strengths and lengths for each individual application.



U.S. Patent Numbers 3,127,648 – 3,486,201

## Product Selection

| Part Number | Color   | Government Designation | Min. Tensile Unlocking Strength | Max. Bundle Diameter In. (mm) | Approx. Length In. (mm) | Approx. Width In. (mm) | Pkg. Qty. | Installation Tools |
|-------------|---------|------------------------|---------------------------------|-------------------------------|-------------------------|------------------------|-----------|--------------------|
| T18S9C2*    | Natural | MS3367-4               | 18 lbs.                         | 5/8"                          | 3-3/8"                  | .08"                   | 100       | MK7, MK7P          |
| T18S0C2*    | Black   |                        |                                 | (15.9)                        | (85.7)                  | (2.0)                  | 100       |                    |
| T18S9M4*    | Natural | MS3367-4               | 18 lbs.                         | 5/8"                          | 3-3/8"                  | .08"                   | 1000      | MK7, MK7P          |
| T18S0M4*    | Black   |                        |                                 | (15.9)                        | (85.7)                  | (2.0)                  | 1000      | MK3P               |
| T18R9C2*    | Natural | MS3367-4               | 18 lbs.                         | 3/4"                          | 4"                      | .10"                   | 100       | MK7, MK7P,         |
| T18R0C2*    | Black   |                        |                                 | (19.0)                        | (101.6)                 | (2.5)                  | 100       | MK9, MK9P          |
| T18R9M4*    | Natural | MS3367-4               | 18 lbs.                         | 3/4"                          | 4"                      | .10"                   | 1000      | MK7, MK7P,         |
| T18R0M4*    | Black   |                        |                                 | (19.0)                        | (101.6)                 | (2.5)                  | 1000      | MK9, MK9P          |
| T18I9C2***  | Natural | MS3367-4               | 18 lbs.                         | 1-1/4"                        | 5-2/3"                  | .10"                   | 100       | MK7, MK7P          |
| T18I0C2***  | Black   |                        |                                 | (31.8)                        | (143.9)                 | (2.5)                  | 100       | MK9, MK9P          |
| T18I9M4***  | Natural | MS3367-4               | 18 lbs.                         | 1-1/4"                        | 5-2/3"                  | .10"                   | 1000      | MK7, MK7P,         |
| T18I0M4***  | Black   |                        |                                 | (31.8)                        | (143.9)                 | (2.5)                  | 1000      | MK9, MK9P          |
| T18L9C2***  | Natural | MS3367-4               | 18 lbs.                         | 2"                            | 8"                      | .10"                   | 100       | MK7, MK7P,         |
| T18L0C2***  | Black   |                        |                                 | (50.8)                        | (203.2)                 | (2.5)                  | 100       | MK9, MK9P          |
| T18L9M4***  | Natural | MS3367-4               | 18 lbs.                         | 2"                            | 8"                      | .10"                   | 1000      | MK7, MK7P,         |
| T18L0M4***  | Black   |                        |                                 | (50.8)                        | (203.2)                 | (2.5)                  | 1000      | MK9, MK9P          |
| T30R9C2*    | Natural | MS3367-5               | 30 lbs.                         | 1-1/4"                        | 6"                      | .14"                   | 100       | MK7, MK7P,         |
| T30R0C2*    | Black   |                        |                                 | (31.8)                        | (152.4)                 | (3.6)                  | 100       | MK9, MK9P          |
| T30R9M4*    | Natural | MS3367-5               | 30 lbs.                         | 1-1/4"                        | 6"                      | .14"                   | 1000      | MK7, MK7P,         |
| T30R0M4*    | Black   |                        |                                 | (31.8)                        | (152.4)                 | (3.6)                  | 1000      | MK9, MK9P          |
| T30M9C2     | Natural |                        | 30 lbs.                         | 2"                            | 8"                      | .14"                   | 100       | MK7, MK7P,         |
| T30M0C2     | Black   |                        |                                 | (50.8)                        | (203.2)                 | (3.6)                  | 100       | MK9, MK9P          |
| T30M9M4     | Natural |                        | 30 lbs.                         | 2"                            | 8"                      | .14"                   | 1000      | MK7, MK7P,         |
| T30M0M4     | Black   |                        |                                 | (50.8)                        | (203.2)                 | (3.6)                  | 1000      | MK9, MK9P          |
| T30I9C2     | Natural |                        | 30 lbs.                         | 3"                            | 11-3/4"                 | .14"                   | 100       | MK7, MK7P,         |
| T30I0C2     | Black   |                        |                                 | (76.2)                        | (298.5)                 | (3.8)                  | 100       | MK9, MK9P          |
| T30I9M4     | Natural |                        | 30 lbs.                         | 3"                            | 11-3/4"                 | .14"                   | 1000      | MK7, MK7P,         |
| T30I0M4     | Black   |                        |                                 | (76.2)                        | (298.5)                 | (3.8)                  | 1000      | MK9, MK9P          |
| T30L9C2     | Natural |                        | 30 lbs.                         | 4"                            | 14-1/4"                 | .15"                   | 100       | MK7, MK7P,         |
| T30L0C2     | Black   |                        |                                 | (101.6)                       | (362)                   | (3.8)                  | 100       | MK9, MK9P          |
| T30L9M4     | Natural |                        | 30 lbs.                         | 4"                            | 14-1/4"                 | .15"                   | 1000      | MK7, MK7P,         |
| T30L0M4     | Black   |                        |                                 | (101.6)                       | (362)                   | (3.8)                  | 1000      | MK9, MK9P          |
| T40R9C2*    | Natural |                        | 40 lbs.                         | 2"                            | 8-1/2"                  | .15"                   | 100       | MK7, MK7P,         |
| T40R0C2*    | Black   |                        |                                 | (50.8)                        | (215.9)                 | (3.8)                  | 100       | MK9, MK9P          |
| T40R9M4*    | Natural |                        | 40 lbs.                         | 2"                            | 8-1/2"                  | .15"                   | 1000      | MK7, MK7P,         |
| T40R0M4*    | Black   |                        |                                 | (50.8)                        | (215.9)                 | (3.8)                  | 1000      | MK9, MK9P          |
| T40I9C2*    | Natural |                        | 40 lbs.                         | 3"                            | 11-1/2"                 | .15"                   | 100       | MK7, MK7P,         |
| T40I0C2*    | Black   |                        |                                 | (76.2)                        | (292.1)                 | (3.8)                  | 100       | MK9, MK9P          |
| T40I9M4*    | Natural |                        | 40 lbs.                         | 3"                            | 11-1/2"                 | .15"                   | 1000      | MK7, MK7P,         |
| T40I0M4*    | Black   |                        |                                 | (76.2)                        | (292.1)                 | (3.8)                  | 1000      | MK9, MK9P          |



Note: \*AS23190E (formerly Mil-S-23190E) (Type I Class 1). \*\*\*HellermannTyton QPL23190 Listed as exceeding the tensile strength of length and meeting MS3367 (Type I Class 1). Contact HellermannTyton for other colors. Note: The official reference to the military specification is now SAE-AS23190 and SAE-AS3367.