



### INTERVOX

? [Product Overview](#)

### [Advanced Product Search](#)

[Search By Part #:](#)

**GO**

### Quick Pick Search

- ? [Transducers](#)
- ? [AC Buzzers](#)
- ? [Surface mounts](#)
- ? [Piezo Electric](#)
- ? [Piezo Elements](#)
- ? [Electronic Buzzers](#)
- ? [Speakers](#)
- ? [Microphones](#)
- ? [Catalog Request](#)

[SEARCH  
DISTRIBUTOR  
INVENTORY](#)

### INTERCAP


? [Product Overview](#)

? [Catalog Request](#)

[Home](#) · [Company Profile](#) · [Sales](#) · [Tracking Center](#) · [What's New](#) · [Contact Us](#)

[Previous Page](#)

### PIEZO SOUNDER WITH BUILT-IN CIRCUIT



**ROHS COMPLIANT UPON REQUEST**

**PART NUMBER:**  
**BPS6055L12-C**

Search Distributor Inventory For This Part:  If "No parts were found", please contact us at 800-645-9154 or your local distributor.

#### SPECIFICATIONS:

RATED VOLTAGE:	12 VDC
OPERATING VOLTAGE:	6 ~ 12 VDC
MAX CURRENT:	350 mA
SOUND OUTPUT LEVEL:	115dB @ 1M
TERMINAL TYPE:	2 LEADWIRES
RESONANT FREQUENCY:	2500-3000 Hz
OPERATING TEMPERATURE:	-20 TO +70 °C
TONE MODE:	SIREN
FRAME DIAMETER:	60 x 55 mm
FRAME DEPTH:	85.0 mm
MOUNTING DIMENSIONS:	35.0 mm

#### DIMENSIONS: