

[Buy Now](#)


Fans and Blowers

[DC Axial Fans](#)
[DC Blowers](#)
[AC Axial Fans](#)
[AC Weather Resistant](#)
[Custom Fan Trays](#)
[High Power R and F Series](#)
[Motorized Impellers](#)
[Fan Accessories](#)
[Fan Guards and Accessories](#)
[Fan Cords](#)
[Mounting Clips](#)
[Buy Fans](#)
[Find a Fan Distributor](#)
[Find Fan Inventory](#)
[Find Fan Part Data](#)
[Cross Reference](#)
[Part Numbering System](#)
[Fan Engineering](#)
[Fan White Papers](#)
[Catalog Download](#)
[Fan FAQ](#)
[RoHS](#)
[Home](#) > [Fans](#) > [Accessories](#) > [Fan Cords](#)

FAN CORDS


- Comply with UL, and CSA requirements
- Ratings: UL Rated 10 AMP/125 VA CSA Rated 7 AMP/125 VAC
- Constructed from 2 conductor 18 AWG SPT-1 105 C VW-1
- Straight and 90 degree style plugs available
- 2 prong style plugs available in all lengths

Straight Style



Cord Sets	Length	Model No.
Straight Style	24"	432000
	36"	432020
	48"	432002

90 Degrees Style



Cord Sets	Length	Model No.
90 degree	36"	432021

2 Prong Style



Cord Sets	Length	Model No.
2 Prong Style	24"	432050
	36"	432051
	48"	432052