



SHS hanging scales offers a strong and safe solution for weighing suspended objects. Ruggedly constructed to perform dependably in industrial settings, the SHS features polycarbonate indicator housing, chrome-plated steel hook, safety catch and oversized swivel shackle and bolt. The hook and shackle rotate, giving complete flexibility. A remote control allows safe and simple operation of the scale. Readings are shown on a bright-red LED display, making them visible in any lighting conditions, including outdoors. The hold function retains the reading on the display after the weight is removed from the scale, allowing time for the operator to record results.

Bringing strength and safety to the forefront of industrial settings



Features

- Bright LED display for easy viewing in most environments
- Rotating hook allows easy access while loading, then safely locks in place during weighing
- Lightweight design simplifies transport and portability
- Rugged construction stands up to industrial use
- Remote control allows safe, hands-free operation
- External calibration allows for verification and adjustment with weights
- Hold function freezes the displayed weight, allowing time to elapse without losing the result
- Zero-tracking feature ensures display returns to zero reading
- Programmable auto power-off to save energy

Applications

- Weighing

About ADAM:

For more than 45 years, professionals worldwide have relied on Adam Equipment for an extensive selection of dependable and affordable weighing equipment. Adam provides the right balance of speed, performance and value.

Model	SHS 100a	SHS 300a	SHS 600a
Capacity	100lb / 50kg	300lb / 150kg	600lb / 300kg
Readability	0.02lb / 0.01kg	0.05lb / 0.02kg	0.1lb / 0.05kg
Repeatability (S.D.)	0.02lb / 0.00001kg	0.05lb / 0.00002kg	0.1lb / 0.00005kg
Linearity (+/-)	0.04lb / 0.02kg	0.1lb / 0.05kg	0.2lb / 0.1kg
Ultimate Overload Limit	200lb / 75kg	600lb / 225kg	900lb / 450kg
Weighing Units	kg, lb		
Stabilization Time (sec)	2		
Calibration	External calibration		
Display	LED with 0.6" / 15mm -high digits		
Power Supply	AC adapter / 4 x AA batteries / Internal rechargeable battery		
Operating Temperature	0° to 40°C / 32° to 104°F		
Housing	Polycarbonate		
Overall Dim.	5.8"x2.6"x12.6" / 148x65x320mm (wxhxd)		
Net Weight	2.6lb / 1.2kg		
Overload Limit	Adam Equipment Co Ltd, its directors, staff, owners and affiliated companies and organizations cannot be held liable for any resulting damage or injury sustained as a result of the machines being used in excess of their capacities and ultimate overload limits.		

Accessories

Item number	Description
700660290	Calibration certificate

Supplied by