




FEATURES:

- For test versatility, the patch cord features vertical/horizontal stacking on the banana plug and vertical stacking on the pin tip side.
- Patch cord converts a pin tip jack to a banana plug or a banana jack to a pin tip plug.
- Banana and Pin Tip Plugs are molded directly to the wire for long life.

MATERIAL:

Banana Plug: Spring – Beryllium Copper, Nickel Plated

Body: Brass, Nickel Plated

Insulation: Polypropylene, Color matches wire

Wire: 20 AWG, Stranding 41 x 36 Tinned Copper, PVC Insulated, .087" (2.21mm) O.D.

Color per part number. Marking: MODEL 1126-*

Pin Tip Plug: Body – Brass, Gold Plated

Stackup Spring: Beryllium Copper, Gold Plated

Insulation: Polypropylene, Color matches wire

RATINGS:

Voltage: Hand-held Testing: 30VAC/60VDC MAX.

Hands Free Testing in Controlled Voltage environments: 3000 WVDC

Operating Temperature: +55°C (+131°F)

Current: 5 Amperes Max.

ORDERING INFORMATION: Model 1126-X-*

X = Length, Standard Lengths: 4" (10,16cm), 8" (20,32cm), 12" (30,48cm), 18" (45,72cm), 24" (60,96cm), 36" (91,44cm), 48" (121,92), & 60" (152,40cm). Custom lengths can be quoted upon request.

* = Color, -0 Black, -2 Red. Ordering Example: 1126-24-2 Patch cord will be 24" (60,96cm), color red.

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ (.51 mm), .xxx = $\pm .005$ (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[1126-18-0](#) [1126-18-2](#) [1126-24-0](#) [1126-24-2](#) [1126-36-0](#) [1126-36-2](#) [1126-12-2](#) [1126-12-0](#) [1126-60-0](#) [1126-60-2](#)
[1126-48-2](#) [1126-48-0](#) [1126-4-0](#) [1126-4-2](#) [1126-8-0](#) [1126-8-2](#)