




NOTES:

1. CONTACT RETENTION 2 LB MIN
EXCEPT ON POSITIONS NEXT TO CUT, THEN 1 LB MIN.
2. MAX ALLOWABLE BOW: .006 [.15] IN/IN
3. "END WALLS" AFTER CUTTING SHOULD BE $.015 \pm .001$ [.38 $\pm .03$].
4. $\textcircled{C}$ REPRESENTS A CRITICAL DIMENSION.
5. CUT FLASH: .015 [.38] MAX WITH NO FLASH ALLOW IN HOLES.
6. .003 [.08] MAX TERMINAL BURR.
7. NOTE DELETED.



DIMENSIONS ARE IN INCHES

UNLESS OTHERWISE NOTED

TOLERANCES ARE:

ONE PLACE DECIMALS $\pm .1$ [.3] THREE PLACE DECIMALS $\pm .005$ [.13]
 TWO PLACE DECIMALS $\pm .01$ [.3] FOUR PLACE DECIMALS $\pm .0020$ [.051]

ANGLES
 $\pm 2^\circ$

TITLE: CLOSED ENTRY
 SOCKET STRIP
 DOUBLE ROW ASSEMBLY

DWG NO:

CES-1XX-XX-X-D

SHEET 1 OF 1

CES-1XX-XX-X-D

POSITION SPECIFICATIONS

-01 THRU -50

CONTACT LEAD STYLE

-01: "A" = $.128 \pm .004$ [3.25 $\pm .10$]
 (USE C-45-01-X)


-02: "A" = .223 [5.66] (USE C-45-02-X)

ROW SPECIFICATION

-D: DOUBLE
 (USE CES-XX-D)

PLATING SPECIFICATIONS


-T: TIN - SPECIFY -T IN CONTACT SUFFIX -X
 -G: GOLD - SPECIFY -G IN CONTACT SUFFIX -X
 -S: SELECTIVE - SPECIFY -S IN CONTACT SUFFIX -X
 -F: FLASH GOLD - SPECIFY -F IN CONTACT SUFFIX -X
 (AVAILABLE IN -01 LEAD STYLE ONLY)



PT-1-24-01-95

PACKAGING VIEW LEAD STYLE -01

SCALE: .75



PT-1-24-02-53

PACKAGING VIEW LEAD STYLE -02

SCALE: .75

NOTE:
 PINS TO ALL BE FACING
 THE SAME DIRECTION

PACKAGING TABLE (5 POS MIN)

CONTACT LEAD STYLE	PACKAGING TUBE	TUBE PLUG
-01	PT-1-24-01-95	TP-09
-02	PT-1-24-02-53	TP-09

DO NOT SCALE
 FROM THIS PRINT

PROPRIETARY NOTE
 THIS DOCUMENT CONTAINS INFORMATION
 CONFIDENTIAL AND PROPRIETARY TO
 SAMTEC INC. AND SHALL NOT BE
 REPRODUCED OR TRANSMITTED IN
 ANY FORM OR BY ANY MEANS
 WITHOUT THE WRITTEN CONSENT OF SAMTEC INC.

MATERIAL:
 GLASS FILLED POLYESTER
 COLOR: BLACK

TERMINAL:
 PHOS BRONZE

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
 PHONE (812) 944-6733 P.O. BOX 1147
 CODE 55322

MADE BY:

REIDINGER 9-9-92

CES-1XX-XX-X-D

SHEET 1 OF 1