

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

MARCH , 2006.

© COPYRIGHT 2006

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

C

ECR-07-010734

08/05/07

AM

FWK

C1

ECR-10-015172

13AUG10

RK

JK

NOTES:

1. ELECTRICAL DATA:

CONTACT RESISTANCE: 10 mOhm MAX

INSULATION RESISTANCE: 100 MOhm MIN at 500VDC

CURRENT RATING: 5 AMPS

BREAKDOWN VOLTAGE: 500 VAC MIN PER MINUTE

2. ENVIRONMENTAL:

OPERATING TEMPERATURE: -20°C TO +80°C

SEALING REQUIREMENTS: IP67

3. PROD SPEC:

108-3641

4. PACKAGING:

107-3334

5. FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE

6. ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED

PIN ASSIGNMENTS

FRONT VIEW

③

④

①

4

3

1

PIN

BLACK

BLUE

BROWN

WIRE COLOUR

42.0

Ø10.5

M8.0 x 1.0

1

2

3

tyco

'A'±'B'

Ø5.0

4

OBSOLETE	10000	500 mm	M8 STRAIGHT MALE CONNECTOR 10.0m CABLE	1838286-5
OBSOLETE	7000	350 mm	M8 STRAIGHT MALE CONNECTOR 7.0m CABLE	1838286-4
	5000	250 mm	M8 STRAIGHT MALE CONNECTOR 5.0m CABLE	1838286-3
OBSOLETE	3000	150 mm	M8 STRAIGHT MALE CONNECTOR 3.0m CABLE	1838286-2
OBSOLETE	2000	100 mm	M8 STRAIGHT MALE CONNECTOR 2.0m CABLE	1838286-1
	DIM A	TOL 'B'	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

± -

± -

± -

± -

± -

± -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

± -

MATERIAL

-

FINISH

-

DWN

MANJUNATH.T.N

29MAR06

CHK

F.WHEELER-KING

07AUG06

APVD

F.WHEELER-KING

07AUG06

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

Tyco Electronics

Tyco Electronics Corporation

Bideford, UK, EX39 4HE

NAME

M8 STRAIGHT MALE CONNECTOR WITH STRAIN RELIEF 3 POSITION, PVC CABLE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1838286

-

CUSTOMER DRAWING

SCALE

NTS

SHEET

1

OF

1

REV

C1

AMP 1470-19 REV 31MAR2000