

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:


0546781639

Status:

Contact Molex

Description:

1.25mm (.049") Pitch Small MGC (Multi-Ground Connector) PCB Header, Polarizing Key 6.00mm (.236") Right From the Center



Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-54678-007 (PDF)	

General	
Product Family	I/O Connectors
Series	54678
Application	Wire-to-Board
Component Type	Receptacle
Product Name	Small MGC
Type	N/A
Physical	
Boot Color	N/A
Circuits (Loaded)	16
Circuits (maximum)	16
Durability (mating cycles max)	100
Gender	Receptacle
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Number of Rows	2
Orientation	Right Angle
PC Tail Length	3.30mm (.130")
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	1.25mm (.049")
Pitch - Termination Interface	1.25mm (.049")
Plating min - Mating	0.102µm (4µ")
Plating min - Termination	1.016µm (40µ")
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-20°C to +80°C
Termination Interface: Style	Through Hole
Waterproof / Dustproof	No
Electrical	
Current - Maximum per Contact	1.5A
Shielded	No
Voltage - Maximum	100V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-54678-007
Sales Drawing	SD-54678-006

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

54678Series

Mates With

55516-1609

This document was generated on 05/09/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION