

Technical datasheet: FT-20T-4.0A1-465

Specifications:

Resonant Frequency	4.0kHz $\pm$ 0.5kHz
Max Resistance (Zr)	300 Ω
Capacitance	30000nF $\pm$ 30%nF

Dimensions:

Type A: (D: Ø20mm, d: Ø15mm, T: 0.26mm, t: 0.15mm)

