



Fxx*₁)SA-K700
e.g. F15SA-K700

*1) xx No. of contacts 09, 15, 25 or 37

xx	A [mm]	B [mm]	C [mm]
09	30.8	16.4	25
15	39.1	24.7	33.3
25	53	38.5	47.04
37	69.3	54.9	63.5

Protection standard IP 67, 100% checked according to DIN 40050

RoHS compliant

3	xx	Signal contact	ISO / Brass	AuroPur / AWG 20
2	1	Shell	Brass	tin plated
1	1	Insulator	PBT (-25°C - +70°C)	red
No.	St.	Part	Type Description /Material	Surface plating/Colour/Class
			Measurement without Knick	
			SCALE	TITLE
			ISO 2748-m	2:1
			NAME / DATE	
		DRAWN	ISSHREF	
		CHECKED	ADlerzinger	
			22-05-2013	
			72-05-2013	
				
			fctgroup.com	
1				DWG.NO.
REV.	DATE	CH.-NO.	ORIGINAL DIN A3-DRAWING AS A FILE	REV. 1
			REPLACEMENT FOR:	PAGES 1

