

DRAWING MADE IN AMERICAN PRODUCTION


© 1976 BY AMP INC. COPIES NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM. AMP INC. IS THE REGISTERED OWNER OF THIS PATENT AND ALL RIGHTS ARE RESERVED.

REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
0	NPS 76-2749		

ASSEMBLED

VIEW

±.010 REF PLANE
/197



FOR USE WITH
RG-213/U & RG-8/U

TABLE OF CONTENTS

ITEM	QTY	DESCRIPTION	PART NO.
1	1	JACK BODY	225082-3
2	1	CONTACT	51704-2
3	1	FERRULE	1-33/987-5

CRIMP WITH TOOL: 220015-1

SEE I.S. 2028-2

CUT DIELECTRIC
SQUARE

3/8 ± 1/64 TOOL IS 2331



RECOMMENDED STRIP LENGTH

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .004 ANGLES ± .004

MATERIAL

T.E.

AMP INCORPORATED

HARRISBURG, PENNSYLVANIA



NAME

COAX/CON-JACK

TYPE "N" 50 OHM WEATHER-PROOF

SIZE

A

CODE IDENT NO.

00779

NUMBER

225664-2

SCALE

1/16

WT: 1.202 MAX

SHEET

1 OF 1