




AD4020GP SERIES

External Dimensions



Frame:Plastic(UL:94V-0)
Impeller:Plastic(UL:94V-0)
Lead wire:UL1007AWG26


Specifications(Nominal)

*:Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: ◎=Ball ※=Sleeve ●=Hypro bearing

Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (VDC)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow (CMM) (CFM)	Maximum Pressure (InAq) (mmAq)	*Noise Level (dB/A)	Weight (g)
40x40x20	AD0412LB-C73GP(P)	◎	12	0.08	0.96	5000	0.181 6.40	0.150 3.81	19.0	28.0
	AD0412MB-C73GP(P)	◎	12	0.12	1.44	6200	0.226 8.00	0.230 5.84	26.0	
	AD0412HB-C73GP(P)	◎	12	0.14	1.68	7200	0.266 9.40	0.320 8.13	30.0	
	AD0412UB-C73GP(P)	◎	12	0.15	1.80	8200	0.311 11.00	0.400 10.16	33.0	
	AD0412XB-C73GP(P)	◎	12	0.24	2.88	10000	0.368 13.00	0.540 13.72	42.0	

Specifications subject to change without notice.



*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
	✓	✓	✓							

*Safety approvals

UL	UL	SP	CE	CE
✓	✓		✓	✓