


| PART NAME | UTILIBOX (STYLE E) | PART No. |
|--|--------------------|----------|
| <p><u>MATERIAL:</u> ABS THERMOPLASTIC (FLAMMABILITY RATING OF 94-VO AT 0.070" THICKNESS AND CONTINUOUS USE TEMPERATURE OF 70° C)</p> <p><u>FINISH:</u> BODY - OUTSIDE SURFACES ARE TEXTURED FINISH COVER - SURFACES ARE SMOOTH.</p> <p><u>COLOR:</u> BLACK</p> <p><u>COVER REDUCES INSIDE HEIGHT BY 0.085.</u></p> <p><u>NOTE: ALL DIMENSIONS HAVE ± 0.010 TOLERANCE</u> <u>UNLESS OTHERWISE SPECIFIED.</u></p> <p><u>LENGTH AND WIDTH DIMENSIONS ARE</u> <u>TAKEN FROM CLOSED END OF THE BOX.</u> <u>DIMENSIONS INCREASE SLIGHTLY AT</u> <u>OPEN END DUE TO TAPER.</u></p>  <p>Four (4) #4 x 1/2 LG. SELF THREADING SCREWS WITH HI/LOW THREADS ARE SUPPLIED FOR MOUNTING COVER.</p> <p>0.250 DIA. BOSS x 0.065 HIGH (4) PLACES</p> <p>0.109</p> <p>0.281</p> <p>2.159</p> <p>4.030</p> <p>3.468</p> <p>0.037 TYP.</p> <p>0.085</p> <p>1.593</p> <p>0.278</p> <p>0.287</p> <p>0.070 TYP.</p> <p>0.150</p> <p>4.063</p> <p>0.070</p> <p>2.230</p> <p>0.900</p> <p>1.30' REF.</p> <p>2.188</p> <p>0.318</p> <p>3.469</p> <p>0.090 DIA. x 0.500 DEEP (4) HOLES</p> <p>0.180 DIA. BOSS (4) PLACES</p> <p>0.318</p> <p>1.200</p> <p>1.594</p> <p>3.603</p> <p>0.318</p> <p>RECESSED AREA 0.010 DEEP INSIDE TOP</p> <p>BODY</p> <p>COVER</p> | | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bud Industries:](#)

[CU-794](#)