

HOME THEATRE AUDIO CABLES & CONNECTORS

LIGHT - LINK AUDIO CABLES

Digital audio fiber optic with universal connectors

ALL NEW!
Toslink "Flipper" Cable.

It's three cables in one!

Either end of the Toslink-flipper can be a 3.5mm optical connector or a standard Toslink optical connector. Simply flip the tip and you can have:

- > Toslink to Toslink cable
- > Toslink to 3.5mm cable
- > 3.5mm to 3.5mm cable




Toslink™ to mini plug



mini plug to Toslink™

This is the cable for the active audio enthusiast; the guy that changes connections and equipment often.



Part no.	Length
45-6203	3 ft (1M)
45-6206	6 ft (2M)
45-6215	15 ft (4.5M)

PREMIUM LIGHT-LINK AUDIO CABLE:

Digital Audio Fiber Optic with Toslink connector. LKG Premium series has 6mm diameter cable, gold plated connectors with rubber grip on handle, and Toslink connectors at each end.

- Endurance
- Transmission Increase
- Expandability

Fiber Optic Advantages:

- Versatility
- Noise immunity



No. 45-2203 - 3 ft. (1M)

No. 45-2206 - 6 ft. (2M)

No. 45-2215 - 15 ft. (4.5M)

DESIGNER PLATE STYLE STEREO VOLUME CONTROL

LKG in-wall volume attenuator will benefit surround sound, home theater and multi-room installations. No matter how complex the system is. All controls work with 4 or 8 ohm speakers. Frequency response for all units is 35Hz-20 KHz at rated power. Fits standard electrical box.

- Number of steps, 12.10 steps of attenuation at 3dB each, and at 6dB for the last two steps. Total attenuation at 30dB and off.
- ABS plastic knob
- Accepts up to 12 AWG wire.

No. 75-1055 - White

10 Watts RMS

30 Watt average

55 Watts Peak

No. 75-1150 - White


No. 75-5150 - Ivory

No. 75-4150 - Light Almond

25 Watts RMS

75 Watt average

150 Watts Peak




HIGH POWER SPEAKER TERMINALS

Recessed Banana Plug/Binding Posts

Dual banana jack style, will accept dual banana plug, up to 10 or 12 gauge wire or tip jacks. Intended for high audio power: 150 watts and above. One red and one black post, angled upward for easy access.

No. 1996



Dual Banana Plug/Binding Posts

Dual banana jack style, will accept dual banana plug, up to 10 or 12 gauge wire or tip jacks. Intended for high audio power: 100 watts and above. Popular round style is easy to mount. One red and one black post, angled upward for easy access.

No. 1997




TERMINAL STRIPS With push - in connection

Mounting centers: 1-3/4"

Size: 2-1/8" x 15" x 16"

No. 1978 - 2 Position


No. 1979 - 4 Position



No. 1979

PUSH TYPE SPEAKER TERMINALS

Color coded four pairs, (8 position) alternating red and black, for quick connection of speakers using bare wire up to and including 16 gauge PCB Mount.



No. 1990