



Side cutting pliers, 2101G

Side cutting plier with progressive edges designed to cut hard material such as piano wire close to the joint and to cut softer material as copper wire and plastic insulated wire at the tip.

ISO: 5749 DIN: 5749

Finish: Black oxidised, anti-corrosion treated.


Material: Chrome-Vanadium. With Ergo handles in two-material combination. Thermoplastic surface on tough polypropylene which gives a superior grip.


Shape: An "open" joint, in which the distance from the joint centre to the cutting edges is reduced, results in greater leverage and increased cutting capacity. Progressive cutting edge which cuts hard material near the joint and soft materials at the tip.

Round shaped jaws give improved accessibility in confined spaces. Equipped with a return spring featuring an on/off function.

Cutting capacity: Piano wire.

IP = Industrial Pack



	 731415+		A mm	B mm	C mm	D mm	E mm	F mm	G mm	
2101G-125	0106462	5	125	14	17.5	8	1.0	1.2	14	1.6 105
2101G-140	0106479	5	140	16	19.5	9	1.5	1.3	16	1.8 126
2101G-160	0106486	5	160	18	21.5	10	2.0	1.5	18	2.0 162
2101G-180	0106493	5	180	20	23.5	11	2.5	1.5	20	2.25 245
2101G-200	0106509	5	200	22	25.5	11	2.5	1.5	22	2.5 304
2101G-125IP	0106516	5	125	14	17.5	8	1.0	1.2	14	1.6 105
2101G-140IP	0106288	5	140	16	19.5	9	1.5	1.3	16	1.8 126
2101G-160IP	0106295	5	160	18	21.5	10	2.0	1.5	18	2.0 162
2101G-180IP	0106523	5	180	20	23.5	11	2.5	1.5	20	2.25 245
2101G-200IP	0106530	5	200	22	25.5	11	2.5	1.5	22	2.5 304