



Dimensions: mm (In.)

**Mechanical Specifications:**

- Switching Positions: 16 positions
- Operating Force: 350 gf. cm max.
- Mechanical Life: 20,000 detent operations min.
- Operating Temperature: -10°C to +70° C

Electrical Specifications:

- Rating: Switching 50mA/24VDC;
Non-switching 100mA/50VDC
- Contact Resistance: 100mΩ max.
- Insulation Resistance: 1,000MΩ @100VDC
- Dielectric Strength: 250VAC for 1 minute
- Electrical life: 10,000 steps min.

Soldering Process:

- Temperature: 250°C ± 5°C for 5 seconds

Materials:

- Housing/Knob: Thermoplastic (PBT)
- O-Ring: Silicone Rubber
- Terminals: Phosphor Bronze, Gold Plated over Nickel

Rotary DIP Switch
106-RS40014

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[106-RS40014](#)