


CAC Customer Layout Rev: D



THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANY OTHERS AND NO PART OF IT MAY BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA 17105-3608.


THIS DRAWING IS A CONTROLLED DOCUMENT.
PAGE NO

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Part #	L (meters)	L (feet)	LC-Duplex Secure, Red		ST	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-1906002-1	0.950 - 1.050	3.11 - 3.44	0.5	-	0.5	-
0-1906002-2	1.950 - 2.050	6.39 - 6.72	0.5	-	0.5	-
0-1906002-3	2.950 - 3.050	9.67 - 10.00	0.5	-	0.5	-
0-1906002-4	3.920 - 4.080	12.86 - 13.38	0.51	-	0.51	-
0-1906002-5	4.920 - 5.080	16.14 - 16.66	0.51	-	0.51	-
0-1906002-6	5.920 - 6.080	19.42 - 19.94	0.51	-	0.51	-
0-1906002-7	6.920 - 7.080	22.70 - 23.22	0.51	-	0.51	-
0-1906002-8	7.920 - 8.080	25.98 - 26.50	0.51	-	0.51	-
0-1906002-9	8.850 - 9.150	29.03 - 30.01	0.51	-	0.51	-
1-1906002-0	9.850 - 10.150	32.31 - 33.30	0.52	-	0.52	-
1-1906002-1	10.850 - 11.150	35.59 - 36.58	0.52	-	0.52	-
1-1906002-2	11.850 - 12.150	38.87 - 39.86	0.52	-	0.52	-
1-1906002-3	12.850 - 13.150	42.15 - 43.14	0.52	-	0.52	-
1-1906002-4	13.850 - 14.150	45.43 - 46.42	0.52	-	0.52	-
1-1906002-5	14.850 - 15.150	48.72 - 49.70	0.52	-	0.52	-
1-1906002-6	15.840 - 16.160	51.96 - 53.01	0.52	-	0.52	-
1-1906002-7	16.830 - 17.170	55.21 - 56.33	0.53	-	0.53	-
1-1906002-8	17.820 - 18.180	58.46 - 59.64	0.53	-	0.53	-
1-1906002-9	18.810 - 19.190	61.71 - 62.95	0.53	-	0.53	-
2-1906002-0	19.800 - 20.200	64.96 - 66.27	0.53	-	0.53	-
2-1906002-1	20.790 - 21.210	68.20 - 69.58	0.53	-	0.53	-
2-1906002-2	21.780 - 22.220	71.45 - 72.90	0.53	-	0.53	-
2-1906002-3	22.770 - 23.230	74.70 - 76.21	0.53	-	0.53	-
2-1906002-4	23.760 - 24.240	77.95 - 79.52	0.54	-	0.54	-
2-1906002-5	24.750 - 25.250	81.20 - 82.84	0.54	-	0.54	-
2-1906002-6	25.740 - 26.260	84.44 - 86.15	0.54	-	0.54	-
2-1906002-7	26.730 - 27.270	87.69 - 89.46	0.54	-	0.54	-
2-1906002-8	27.720 - 28.280	90.94 - 92.78	0.54	-	0.54	-
2-1906002-9	28.710 - 29.290	94.19 - 96.09	0.54	-	0.54	-
3-1906002-0	29.700 - 30.300	97.44 - 99.40	0.55	-	0.55	-
3-1906002-1	30.690 - 31.310	100.68 - 102.72	0.55	-	0.55	-
3-1906002-2	31.680 - 32.320	103.93 - 106.03	0.55	-	0.55	-
3-1906002-3	32.670 - 33.330	107.18 - 109.35	0.55	-	0.55	-
3-1906002-4	33.660 - 34.340	110.43 - 112.66	0.55	-	0.55	-
3-1906002-5	34.650 - 35.350	113.68 - 115.97	0.55	-	0.55	-
3-1906002-6	35.640 - 36.360	116.92 - 119.29	0.55	-	0.55	-
3-1906002-7	36.630 - 37.370	120.17 - 122.60	0.56	-	0.56	-
3-1906002-8	37.620 - 38.380	123.42 - 125.91	0.56	-	0.56	-
3-1906002-9	38.610 - 39.390	126.67 - 129.23	0.56	-	0.56	-
4-1906002-0	39.600 - 40.400	129.92 - 132.54	0.56	-	0.56	-
4-1906002-1	40.590 - 41.410	133.16 - 135.85	0.56	-	0.56	-
4-1906002-2	41.580 - 42.420	136.41 - 139.17	0.56	-	0.56	-

Qty	U of M	Description	Item No.
0.0139	sheet	Leg Label - "A"	13
1	piece	LC Duplex clip, black	12
AR	meter	2 fiber, 50/125, 2.0mm, Twinzip, Orange, OFNR (Riser)	11
2	piece	PVC Build-up tubing	10
2	piece	ST Short Boot - 1.6 to 2.0mm, Beige	9
2	piece	Trace Label	8
2	piece	Crimp Eyelet	7
2	piece	ST Connector, Ceramic, Polymer Nut	6
2	piece	LC, SC, FC Straight Boot, Beige	5
2	piece	2.5mm ferrule cover	4
2	piece	Eyelet/Shrink tube assembly - White	3
0.0139	sheet	Leg Label - "B"	2
2	piece	LC Connector Assy, 1.6mm-2.0mm, MM	1



DIMENSIONS:
meters

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
0 P.L.C. ± .
1 P.L.C. ± .
2 P.L.C. ± .
3 P.L.C. ± .
4 P.L.C. ± .

Restricted To:

DIN	Cable Assy Configurator	MATERIAL	-	HEAT TREAT	-
OK	Jeremy Duncan	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD	Jeremy Duncan				
NAME	FO C/A - 2 fiber, 50/125, OFNR (Riser) jacket, LC-Duplex Secure to ST				
SCALE	NTS	SIZE	A2	DRAWING NO	C- 1906002
SHEET	2 of 4	REV	A		

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

	A	Rev Per EC#	RELEASE	2/22/2007	-	JG
P	LTR	REVISION RECORD		DATE	DIN	AP

DIMENSIONS; meters		TOLERANCES UNLESS OTHERWISE SPECIFIED	
	0 PLC	±	-
	1 PLC	±	-
	2 PLC	±	-
	3 PLC	±	-
	PLC	±	-

AMP Tyco Electronics, Inc.
Harrisburg, PA 17105-3608

A

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

8

7

6

5

4

3

2

1

Label 1

Per specification 107-1645-1



Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1



Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

DIMENSIONS:	
meters	

TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 P.L.C.	± .
1 P.L.C.	± .
2 P.L.C.	± .
3 P.L.C.	± .
4 P.L.C.	± .

Restricted To:

DW Cable Assy Configurator		MATERIAL	HEAT TREAT	
CHK	Jeremy Duncan	-	-	
APVD	Jeremy Duncan	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
NAME	FO C/A - 2 fiber, 50/125, OFNR (Riser) jacket, LC-Duplex Secure to ST			
SCALE	SIZE	DRAWING NO	SHEET	REV
NTS	A2	C- 1906002	4 of 4	A

D

C

B

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[3-1906013-7](#)