


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT* PART NO.	BUNDLE DIA.		A	B	C	D	E	F	G	H	J	K	L	M	N	P	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)			
PRA2S-A	.25 (6.4)	1.85 (47.0)	.052 (1.3)	.190 (4.8)	.258 (6.6)	.220 (5.6)	.316 (8.0)	8.5 (216)	.148 (3.8)	.90 (22.9)	1.00 (25.4)	.200 (5.1)	.134 (3.4)	7.3 (185)	.300 (7.6)	.600 (15.2)	50 (222)	STANDARD	.53 (242)

NOTES:

- SEE CURRENT PRICE SHEET FOR PART
NUMBER SUFFIX DESIGNATIONS
FOR PACKAGE SIZE.

TO APPLY MOUNTS:

- REMOVE PROTECTIVE LINER FROM MOUNT.
- PLACE IN DESIRED LOCATION.
- APPLY PRESSURE TO TOP SURFACE OF MOUNT.

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY
PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE.
AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH
THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE
TO WHICH THEY MAY BE APPLIED ARE BEYOND
PANDUIT'S CONTROL.

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS

G00239EV_PB_PRA2S_01

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

COMBINATION ADHESIVE MOUNT/TIE
PRA SERIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)
(.XX) ±0.02 (0.5) ANGLES ±5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY CGSM

MAT'L:

SCALE NONE

DATE

1/22/97

DRAWING NO.

G00239EV

DWG
SIZE
A

1	4/26/04	JAD		UPDATE DRAWING, ADD REF TO SEVERAL DIMENSIONS	G00239EV	1			
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	