



main menue



home
test & measurement
products
skills
download

online catalogue T&M

clamp-type test probes
crocodile clips
test probes
oscilloscope test probes
measuring leads
plugs
▶ 2 mm system
▶ 2 mm safety system
▶ 4 mm system
▶ 4 mm sliding sleeve system
▶ 4 mm safety system
sockets
sets
miscellaneous

company

portrait
corporate association
location maps
fairs and exhibitions
jobs
imprint
terms and conditions

Home ▶ plugs ▶ plugs ▶ MST 3

MST 3

datasheet for MST 3
article number: 973509103



[View Full-Size Image](#)



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:		order number: 973 509-103	
description:		2 mm diameter miniature connector, nickel-plated brass pin with solder connection. Flexible, shatter-proof insulated sleeve. For making up connecting leads with a maximum external diameter of 1.9 mm.	
typ:		MST 3 gelb/yellow	
system:		2mm system	
order number:		973 509-103	
color			
other color versions:			
technical data			
measurement category acc. to IEC 61010:		CAT I	
pin dimensions		2 mm	
type of contact:		pin (unsprung)	
type of termination:		solder	
rated voltage:		30 VAC / 60 VDC	
rated current:		6 A	
Please consider derating curve!			
contact resistance:		6 mOhm	
material			
contact material:		brass	
contact surface material:		nickel	
housing material:		PVC - P	
environmental conditions:			
temperature range:		-25 °C to +60 °C	
drawing			
			