


C882/3 Series - Metallised Plastic D Hoods 45°/Top Entry



- Manufactured in ABS, nickel plated over copper.
- Unique compression insert ensures excellent strain relief and reliable screen termination.


Order Code

Series **C883** **20000**
 C882 - 45° Entry
 C883 - Top Entry

Size
 00000 - 9 way
 10000 - 15 way
 20000 - 25 way
 30000 - 37 way
 40000 - 50 way (Top entry only)


- Thumbscrews are available.
Part Code:- **JLJ-10S** (4-40 UNC)
- Company logo's available.

Top Entry




Ways	Dim A	Dim B	Dim C	Dim D
9	31.3	35.5	16.3	16.3
15	39.1	38.8	16.3	16.3
25	53.1	42.0	18.0	16.3
37	69.3	46.5	23.0	16.3
50	67.2	47.1	23.9	19.1

45° Entry



Ways	Dim A	Dim B	Dim C	Dim D
9	31.3	37.2	16.3	16.3
15	39.1	40.6	16.3	16.3
25	53.1	44.1	18.0	16.3
37	69.3	45.7	22.4	16.3



C88000 Series - Zinc Die Cast D Hoods Top Entry



Order Code

Series **C88000** **204**
 C88000 - Top entry
 C8842 - 90° entry (25 way only)
 C8852 - Flat cable entry (25 way only)

Size
 209 - 9 way, 211 - 15 way
 204 - 25 way, 210 - 37 way
 212 - 50 way, 0000 - 25 way (C8842/C8852 only)



- Exceeds FCC 20780 Class A and B.
- Die cast zinc shell, zinc plated
- Unique compression insert ensures excellent strain relief and reliable screen termination.
- Thumbscrews are available.
Part Code:- **JLJ-10S** (4-40UNC).
- Company logo's available.

Ways	Dim A	Dim B	Dim C	Dim D
9	31.1	37.2	15.7	15.7
15	39.1	40.6	15.7	15.7
25	53.1	39.1	17.5	15.7
37	66.6	45.7	21.9	18.5
50	66.6	45.7	21.9	18.5
90°	53.1	43.6	18.0	16.3
Flat Cable	55.5	45.7	17.5	17.5