

Fiber optic coupling - VS-SCRJ-GOF-KU - 1654358

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



SCRJ coupling insert, duplex, for VS-PP-19-1HE-16-F patch panel and VS-TO...F...terminal outlets and VS-SI-FP-2F front plate, can be used for glass multi-mode, HCS and polymer fiber types



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 970635
Weight per Piece (excluding packing)	9.74 GRM
Custom tariff number	85366990
Country of origin	Switzerland

Technical data

Mechanical characteristics

Number of positions	2
Number of slots	1
Connection profile	SCRJ according to DIN EN 50377-6-1
Fiber type	GOF, HCS, POF
Ferrule diameter	2.50 mm
Number of fibers	2
Insertion/withdrawal cycles	≥ 500
Connection method	Coupling

Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
Degree of protection	IP20

Material data

Fiber optic coupling - VS-SCRJ-GOF-KU - 1654358

Technical data

Material data

Inflammability class according to UL 94	V0
Housing material	PBT
Ferrule material	Zirconia ceramics
Ferrule holder color	White

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260705
eCl@ss 7.0	27440309
eCl@ss 8.0	27440309

ETIM

ETIM 2.0	EC000764
ETIM 3.0	EC001121
ETIM 4.0	EC001121
ETIM 5.0	EC002641

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501