

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FREDERICK, ILLINOIS

FED. MFR. CODE 91929

ACTUATOR - SWITCH

CATALOG LISTING

JS - 3

(M) JS-3
ISSUE 3

REPLACES

RELEASE NO.

JS-3

M

DRAWING
NUMBER

ISSUE

7

CHECK

REVISIONS

A CO 12901

K L B

25 MAY 59

B CO 17304

M S F

4 DEC 63

C CO 47771

C J H

17 MAY 80

D CO 79303

D L T

7 MAR 95

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK


CHECK

CHECK


2-56 NC X .500 REF ROUND HEAD MACHINE SCREW (2)

2-56 NC HEX NUT (2)

LOCKWASHER (2)



CORROSION RESISTANT
STEEL ACTUATOR



DOTTED LINES INDICATE
BASIC SWITCH IN PLACE

FLEXIBLE INSULATOR

NOTE -

- FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS WITH ISMI BASIC SWITCH INSTALLED

OPERATING FORCE ----- 10 OZ MAX
RELEASE FORCE ----- 2 OZ MIN
DIFFERENTIAL TRAVEL ----- .020 MAX
OVERTRAVEL ----- .015 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED
DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) ± .030
TWO PLACE (.00) ± .015
THREE PLACE (.000) ± .005
ANGLES ± 2°

WEIGHT