





REV.	DATE	DESCRIPTION
A	06/05/03	UPDATE DRAWING FORMAT



RECOMMENDED CABLE
STRIPPING DIM'S



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex								
8						DRAWN	G.R.S.						06/05/03			
7						CHECKED										
6						ISSUED			PART DESCRIPTION BNC CRIMP PLUG (FOR 734A CABLE)							
5						SHEET	1 OF 1							PART NO. 112951		
4	FERRULE	COPPER	NICKEL	1	CAD FILE	C:/112/112951.DWG		DWG. NO.	112951.DWG		REV.	A	SIZE			
3	INSULATOR	TEFLON	NATURAL	1												
2	CONTACT PIN	BRASS	GOLD	1												
1	BODY	BRASS	NICKEL	1												
	DESCRIPTION	MATERIAL	FINISH	QTY												