







REV.	DESCRIPTION	DATE
A	RELEASE	2012.11.12

NOTES:
 Insulator Material: PBT, UL 94V-0
 Contact Plating: flash gold
 Contact Material: Brass

 Current Rating : 1A AC,DC
 Contact Resistance: 20MΩ Max.
 Dielectric Withstanding: AC 500V
 Insulator Resistance: 1000MΩ Min.
 Operating Temp.: -40°C~+105°C

NUMBER OF POSITIONS	DIMENSION	
	A	B
06	2.54	8.00
08	3.81	9.27
10	5.08	10.54
12	6.35	11.81
14	7.62	13.08
16	8.89	14.35
20	11.43	16.89
24	13.97	19.43
26	15.24	20.70
30	17.78	23.24
34	20.32	25.78
40	24.13	29.59
44	26.67	32.13
50	30.48	35.94
60	36.83	42.29
64	39.37	44.83
66	40.64	46.10
68	41.91	47.37
70	43.18	48.64
74	45.72	51.18
76	46.99	52.45
80	49.53	54.99



Mating Part Number		
3220-ALL	3210-XX-001-11-XX	3210-XX-001-12-XX
3210-XX-002-12-XX	3210-XX-003-12-XX	

UNLESS TOLERANCE		DRAW BY		CnC Tech,LLC	
GENERAL	ANGLE	DESIGN BY			
X. ± 0.30	X.* ± 3.0°	CHECK BY			
.X ± 0.20	.X* ± 2.0°	APPROVE BY			
.XX ± 0.15	.XX* ± 1.0°			Part NO.	
.XXX ± 0.10	.XXX* ± 0.5°			3230-XX-0102-00	
		SCALE	SHEET	UNIT	
		1:1	1/1	MM	DRW NO: REV: A