



120x120x25_{mm}

67 to 88 CFM




DIMENSIONS



PERFORMANCE

○ : 12V/24V



SPECIFICATIONS

Model	Voltage (VDC)	Bearing ○ Sleeve ● Ball	Current (AMP)	Input (WATTS)	Speed (RPM)	Air Flow (CFM)	Static Pressure (Inch-H ₂ O)	Noise (dBA)	Weight (g)
KDE1212PTS1-6A	12	○	0.45	5.4	3000	88	0.27	44	250
KDE1212PTS2-6A	12	○	0.30	3.6	2700	78	0.21	40	250
KDE1212PTS3-6A	12	○	0.20	2.4	2300	67	0.16	35	250
KDE2412PTS1-6A	24	○	0.25	6.0	3000	88	0.27	44	250
KDE2412PTS2-6A	24	○	0.20	4.8	2700	78	0.21	40	250
KDE2412PTS3-6A	24	○	0.13	3.1	2300	67	0.16	35	250
VOLTAGE AVAILABLE									