



NOTES:



1. ALL DIMENSION IN MM [INCH]
2. GENERAL TOLERANCE: $X.X=\pm 0.4$
 $X.XX=\pm 0.25$
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
350mA, 110V AC/DC
5. OPERATING FORCE: 425 ± 100 CM/STANDARD
6. OPERATING TEMP: -30° to 85°C
7. CIRCUIT DP: 6 POSITIONS, 30° INDEX, NO STOPS.
8. DIELECTRIC STRENGTH: 1000V RMS min.@Seo Level
9. **DESIGNATE MAJOR FEATURE**
10. HARDWARE SUPPLIED ON SWITCH- SEE BELOW
LOCKRING, LOCKWASHER, & HEX NUT



CONTACT CONFIGURATION
Timing: NON-SHORTING



TERMINATION DETAIL
SCALE 2X



E-SWITCH®

TITLE		SCALE		DATE		DR		DWG		REV	
KC2049.501NLS		1.5:1		3/27/03		AR		G510199		A	
DESCRIPTION		DATE		CHKD		SCALE		DATE		REV	
RELEASED FOR PRODUCTION		3/27/03		AR		1.5:1		3/27/03		A	
REV. ECN No.		DESCRIPTION		DATE		CHKD		SCALE		DATE	
A 12969		RELEASED FOR PRODUCTION		3/27/03		AR		1.5:1		3/27/03	
REV. ECN No.		DESCRIPTION		DATE		CHKD		SCALE		DATE	
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED		RELEASED FOR PRODUCTION		3/27/03		AR		1.5:1		3/27/03	