



Chip Multilayer Hybrid Couplers

Hybrid Dividers



Part Number	Frequency Range (MHz)	Insertion Loss (OUT1,OUT2) (dB)	Isolation (min.) (dB)	VSWR (max.)
LDD18713M03A-164	713.0 ±38.0MHz	3.5 ±0.4dB	17.0	1.6
LDD211G6103A-095	1619.0 ±12.0MHz	3.4 ±0.4dB	17.0	1.5
LDD211G6603A-096	1660.0 ±13.5MHz	3.4 ±0.4dB	20.0	1.5
LDD211G7503A-067	1750.0 ±30.0MHz	3.4 ±0.4dB	20.0	1.5
LDD212G1403A-075	2140.0 ±30.0MHz	3.4 ±0.4dB	22.0	1.5
LDD21718M03A-060	718.5 ±38.0MHz	3.4 ±0.4dB	17.0	1.5
LDD21740M03A-077	740.0 ±19.0MHz	3.4 ±0.4dB	20.0	1.5
LDD21967M03A-068	967.0 ±13.0MHz	3.4 ±0.4dB	20.0	1.5

Characteristics Impedance (Nominal): 50ohm Operating Temperature Range: -40°C to +85°C