




REV. 5

DCO 63333

COIL: @ 25°C


RESISTANCE	390 OHMS ±10%
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	14.0 VDC @ 25°C
MUST RELEASE	1.4 VDC @ 25°C

ENVIRONMENT:

VIBRATION	10	CPS TO	2000	CPS @	15	g's
SHOCK	100	g's	6	MS. DURATION		
TEMPERATURE	-65	°C TO	+125	°C		

NOTES: OPERATE & RELEASE 7 MS MAX.
(INCLUDING BOUNCE)

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO
2 AMP 28 VDC RESISTIVE

DR. R.B. 11/13/92

CK. TLG 10-24-00

CII Technologies
advanced control electronic solutions

CUST. OPL
CUST. NO. M39016/40-008 REV.

SR RELAY

SR-7608