

Product Information

3478HUR125P62

EAN 4031582306378

Fixed castor, Fork made of pressed steel, zinc-chromatised, wheel axle with nut, Hybrid-wheel "SYNTECH", wheel centre and tread made of Polyamide, with elastic solid rubber centre, noise reduced, roller bearing, plate fitting

Wheel diameter	125 mm
Width of Tread	36 mm
Size of Plate	103 x 85 mm
Plate hole centres	80/77 x 60 mm
Plate hole	9 mm
Overall height	155 mm
Temperature	- 20 / + 60 °C
Standard	EN 12532
Weight	0.912 Kg / daN
Dynamic Load capacity	200 Kg / daN
Static Load capacity	400 Kg / daN
Hardness of tread	D 75 Shore



Versions:

