

Non-Metallic Braid How-to-Order

100-022 PTFE-Glass Tubular Braided Sleeving





Table I	
Part No.	Nominal I.D.
100-022 A 004	1.25 (03.2)
100-022 A 005	1.56 (04.0)
100-022 A 006	1.88 (04.7)
100-022 A 008	.250 (06.4)
100-022 A 012	.375 (09.5)
100-022 A 016	.500 (12.7)
100-022 A 020	.625 (15.9)
100-022 A 024	.750 (19.1)
100-022 A 032	1.000 (25.4)
100-022 A 040	1.250 (31.8)
100-022 A 048	1.500 (38.1)

102-001 and -002 Polyethylene Expandable Fabric Tubular Braided Sleeving






Table I					
Product Series	Color	Material	Material Dia.	Wall Thickness Nominal	Temperature Range
102-001	White	Polyethylene Terephthalate	.010 (0.25)	.025 (0.6)	-65°F [-54°C] to +250°F [+121°C]
102-002	Black				

Table II				
Dash No.	Ø Nom.	Ø A (before expansion) Min	Ø B (after expansion) Max	Spec Max Weight in Lbs. Per 100 feet [Kg/30.5 M]
-004	.125 (3.2)	.090 (0.25)	.250 (6.4)	.17 (0.08)
-008	.250 (6.4)	.125 (0.25)	.375 (9.5)	.26 (0.12)
-016	.500 (12.7)	.250 (6.4)	.750 (19.1)	.78 (0.35)
-024	.750 (19.1)	.500 (12.7)	1.250 (31.8)	1.20 (0.54)
-040	1.250 (31.8)	.750 (19.1)	1.500 (38.1)	1.60 (0.73)

Consult factory for sizes not shown



Specify length on purchase order. No minimums!
Metric dimensions (mm) are in parentheses.