

LEAPER-56

Pocket Universal Programmer

/ Smart-phone size and ICT level universal programmer

Introduction

The LEAPER-56 is a pocket size universal programmer. It provides with 75MHz bandwidth and $< \pm 2.5\text{nS}$ signal skew just in smart-phone size. The programming efficiency is much better than the other programmers on the market in any time and any condition.

By letting your PC or laptop connect with LEAPER-56, it will perform your outstanding ability of development and debugging. You can easily have professional factory-level productivity.

Features

- Portable mini size. Without socket, only 136mm(L)* 90mm(W)* 20mm(H). You just need to connect with USB cable to use. No additional power supply.
- Provide with DUT 75MHz bandwidth and $< \pm 2.5\text{nS}$ signal skew. In addition to the high processing speed, you can verify whether the ICs processing frequency meets the specifications.
- Via USB HUB, you can connect multiple LEAPER-56s to do gang programming. It makes development and mass production proficient.
- Provide with DUT device pin checking and memory components ID verification. Ensure the best yield rate of processing.

LEAPER-56 is most suitable on the mobile environment.



The best way to perform your professional capacity and working efficiency.

Standard Accessories

Main unit x1
CD (Included driver and user's manual) x1
Y-USB cable x1
Soft case x1



Specification

Device power signal	Log ic signal level:	1.5V~6.0V,10mV
	IOL, IOH current:	10mA
Logic signal frequency:	75MHz (3-5V)	
	60MHz (2.5V)	
	45MHz (1.8V)	
	25MHz (1.5V)	
Signal skew:	<±2.5nS (3-5V)	
	Clock frequency :	0Hz ~ 75MHz
VDD, VIO level:	1.5V~6.5V,10mV	
	IDD, IIO frequency:	400mA
VPP, VHH level:	1.5V~15.5V,20mV	
	IPP, IHH frequency:	150mA
Power consumption	4W	
Pin drivers	48 Pin Universal Pin Driver (Zero Insertion Force)	
DUT socket	DIP 48 ZIF	
Dimension	136(L) x 90(W) x 20(H) mm	(Socket is not included)
Weight	282g	

PC System Requirements

Operating system	Win 7 / Vista / XP (32bits & 64bits)
Processor	Pentium 4 above
Memory	1GB RAM above
Hard disk	500 MB above / buffer: 1GB above
Communication	USB 2.0 high speed
USB powere	Connect the cable with 2 USB port (600mA above)

Supported Devices

NAND FLASH,NOR FLASH,SPI,EPROM,EEPROM,MPU,MCU,CPLD,NV-RAM, etc.

Supported File Formats

Binary/Machine Code, Intel HEX,TEK HEX, Motorola HEX

Remarks

- 1.Must use the USB cable from the standard package, and connect to the USB ports behind your PC. Besides please also connect it with 2 USB ports, or through the USB Hub (5V/1A)
- 2.When you need adapters to process the high-speed components, be sure to use good quality adapters. In order to have the best high-frequency process performance, the socket and DUT must keep good contact.

Distributors : www.rs-components.com

LEAP-56 DEVICE LIST 2013-10-28

www.seeit.fr	TYPE	TOTAL
	EEPROM	7738
	EPROM	789
	FLASH	4341
	MPU / MCU	1794
	NV RAM	9
	ALL	14671

Manufacturer	Parts Number	Type	ADAPTER
ABOV	MC40P5001D(SOP20-300mil)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC40P5004A-1K(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC40P5004A-2K(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC40P5004A-4K(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC40P5004B-1K(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC40P5004B-2K(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC40P5004B-4K(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC40P5101D(SOP20-300mil)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC40P5104A-1K(SOP16)	MPU / MCU	LP-SOP-16PIN(150mil)
ABOV	MC40P5104A-2K(SOP16)	MPU / MCU	LP-SOP-16PIN(150mil)
ABOV	MC40P5104A-4K(SOP16)	MPU / MCU	LP-SOP-16PIN(150mil)
ABOV	MC40P5104B-1K(SOP16)	MPU / MCU	LP-SOP-16PIN(150mil)
ABOV	MC40P5104B-2K(SOP16)	MPU / MCU	LP-SOP-16PIN(150mil)
ABOV	MC40P5104B-4K(SOP16)	MPU / MCU	LP-SOP-16PIN(150mil)
ABOV	MC40P5204A-1K(SOP24)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC40P5204A-2K(SOP24)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC40P5204B-1K(SOP24)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC40P5204B-2K(SOP24)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC40P5404A-1K(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC40P5404A-2K(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC40P5404A-4K(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC40P5404B-1K(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC40P5404B-2K(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC40P5404B-4K(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC41P6104-1K(SOP16)	MPU / MCU	LP-SOP-16PIN(150mil)
ABOV	MC41P6104-2K(SOP16)	MPU / MCU	LP-SOP-16PIN(150mil)
ABOV	MC41P6104-4K(SOP16)	MPU / MCU	LP-SOP-16PIN(150mil)
ABOV	MC81F4104(DIP8)	MPU / MCU	NONE
ABOV	MC81F4104(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
ABOV	MC81F4104(SSOP10)	MPU / MCU	LP-SSOP-16PIN
ABOV	MC81F4204(DIP16)	MPU / MCU	NONE
ABOV	MC81F4204(DIP20)	MPU / MCU	NONE
ABOV	MC81F4204(SOP16)	MPU / MCU	LP-SOP-16PIN(150mil)
ABOV	MC81F4204(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC81F4204(TSSOP16)	MPU / MCU	LP-TSSOP-20PIN
ABOV	MC81F4204(TSSOP20)	MPU / MCU	LP-TSSOP-20PIN
ABOV	MC81F4215(DIP20)	MPU / MCU	NONE
ABOV	MC81F4215(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC81F4216(DIP20)	MPU / MCU	NONE
ABOV	MC81F4216(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC81F4315(DIP28)	MPU / MCU	NONE
ABOV	MC81F4315(DIP32)	MPU / MCU	NONE
ABOV	MC81F4315(QFP32)	MPU / MCU	LP48-TQFP-32PIN
ABOV	MC81F4315(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC81F4315(SSOP24)	MPU / MCU	LP-SSOP-28PIN
ABOV	MC81F4315(SSOP28)	MPU / MCU	LP-SSOP-28PIN
ABOV	MC81F4316(DIP28)	MPU / MCU	NONE
ABOV	MC81F4316(DIP32)	MPU / MCU	NONE
ABOV	MC81F4316(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)

Manufacturer	Parts Number	Type	ADAPTER
ABOV	MC81F4316(SSOP24)	MPU / MCU	LP-SSOP-28PIN
ABOV	MC81F4332(DIP28)	MPU / MCU	NONE
ABOV	MC81F4332(DIP32)	MPU / MCU	NONE
ABOV	MC81F4332(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ABOV	MC81F4416(DIP42)	MPU / MCU	NONE
ABOV	MC81F4416(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ABOV	MC81F4432(DIP42)	MPU / MCU	NONE
ABOV	MC81F4432(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ACE	ACE24C02(DIP8)	EEPROM	NONE
ACE	ACE24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ACE	ACE24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE24C04(DIP8)	EEPROM	NONE
ACE	ACE24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ACE	ACE24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE24C04A(DIP8)	EEPROM	NONE
ACE	ACE24C04A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ACE	ACE24C04A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE24C08(DIP8)	EEPROM	NONE
ACE	ACE24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ACE	ACE24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE24C08A(DIP8)	EEPROM	NONE
ACE	ACE24C08A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ACE	ACE24C08A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE24C128(DIP8)	EEPROM	NONE
ACE	ACE24C128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ACE	ACE24C128(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE24C16(DIP8)	EEPROM	NONE
ACE	ACE24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ACE	ACE24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE24C256(DIP8)	EEPROM	NONE
ACE	ACE24C256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ACE	ACE24C256(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE24C256A(DIP8)	EEPROM	NONE
ACE	ACE24C256A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ACE	ACE24C256A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE24C32(DIP8)	EEPROM	NONE
ACE	ACE24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ACE	ACE24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE24C512(DIP8)	EEPROM	NONE
ACE	ACE24C512(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ACE	ACE24C512(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE24C512A(DIP8)	EEPROM	NONE
ACE	ACE24C512A(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ACE	ACE24C512A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE24C64(DIP8)	EEPROM	NONE
ACE	ACE24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ACE	ACE24C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE24LC02(DIP8)	EEPROM	NONE
ACE	ACE24LC02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ACE	ACE24LC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE24LC02A(DIP8)	EEPROM	NONE
ACE	ACE24LC02A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ACE	ACE24LC02A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE24LC04(DIP8)	EEPROM	NONE
ACE	ACE24LC04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ACE	ACE24LC04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE24LC08(DIP8)	EEPROM	NONE
ACE	ACE24LC08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
ACE	ACE24LC08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE24LC08A(DIP8)	EEPROM	NONE
ACE	ACE24LC08A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ACE	ACE24LC08A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE24LC16(DIP8)	EEPROM	NONE
ACE	ACE24LC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ACE	ACE24LC16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE24LC32(DIP8)	EEPROM	NONE
ACE	ACE24LC32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ACE	ACE24LC32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE25C160GFM(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ACE	ACE25C400GFM(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ACE	ACE25C400TM(TSSOP8)	FLASH	LP-TSSOP-20PIN or LP-TSSOP-8PIN
ACE	ACE25C800GFM(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ACE	ACE93C46-X16(DIP8)	EEPROM	NONE
ACE	ACE93C46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ACE	ACE93C46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE93C46-X8(DIP8)	EEPROM	NONE
ACE	ACE93C46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ACE	ACE93C46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE93C56-X16(DIP8)	EEPROM	NONE
ACE	ACE93C56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ACE	ACE93C56-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ACE	ACE93C56-X8(DIP8)	EEPROM	NONE
ACE	ACE93C56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ACE	ACE93C56-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Actrans	AC25LV010(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Actrans	AC25LV512(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Actrans	AC39LV010(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
Actrans	AC39LV010(VSOP32)	FLASH	LP48-VSOP-32S
Actrans	AC39LV020(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
Actrans	AC39LV020(VSOP32)	FLASH	LP48-VSOP-32S
Actrans	AC39LV040(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
Actrans	AC39LV040(VSOP32)	FLASH	LP48-VSOP-32S
Actrans	AC39LV088(TSOP48)	FLASH	LP-TSOP-48S
Actrans	AC39LV512(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
Actrans	AC39LV512(VSOP32)	FLASH	LP48-VSOP-32S
AIT	A24C02(DIP8)	EEPROM	NONE
AIT	A24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AIT	A24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
AIT	A24C04(DIP8)	EEPROM	NONE
AIT	A24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AIT	A24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
AIT	A24C08(DIP8)	EEPROM	NONE
AIT	A24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AIT	A24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
AIT	A24C128(DIP8)	EEPROM	NONE
AIT	A24C128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AIT	A24C128(TSSOP8)	EEPROM	LP-TSSOP-8PIN
AIT	A24C16(DIP8)	EEPROM	NONE
AIT	A24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AIT	A24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
AIT	A24C256(DIP8)	EEPROM	NONE
AIT	A24C256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AIT	A24C256(TSSOP8)	EEPROM	LP-TSSOP-8PIN
AIT	A24C32(DIP8)	EEPROM	NONE
AIT	A24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AIT	A24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
AIT	A24C64(DIP8)	EEPROM	NONE
AIT	A24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AIT	A24C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
AKM	AK93C10AF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AKM	AK93C41A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
AKM	AK93C45A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AKM	AK93C45A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
AKM	AK93C45AF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AKM	AK93C45AF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
AKM	AK93C45ANF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AKM	AK93C45ANF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
AKM	AK93C45AV(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AKM	AK93C45AV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
AKM	AK93C46(DIP8)	EEPROM	NONE
AKM	AK93C46(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AKM	AK93C51A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
AKM	AK93C55AF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AKM	AK93C55ANF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AKM	AK93C55ANF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
AKM	AK93C55AV(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AKM	AK93C55AV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
AKM	AK93C56(DIP8)	EEPROM	NONE
AKM	AK93C61A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
AKM	AK93C65AF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AKM	AK93C65ANF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AKM	AK93C65ANF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
AKM	AK93C65AV(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AKM	AK93C65AV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
AKM	AK93C75AF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AKM	AK93C75ANF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AKM	AK93C75ANF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
AKM	AK93C75AV(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
AKM	AK93C75AV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
AKM	AK93C95AF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ALTERA	EPCS1(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ALTERA	EPCS1(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ALTERA	EPCS128(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ALTERA	EPCS128(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ALTERA	EPCS16(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ALTERA	EPCS16(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ALTERA	EPCS4(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ALTERA	EPCS4(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ALTERA	EPCS64(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ALTERA	EPCS64(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMD	AM27128A(DIP28)	EPROM	NONE
AMD	AM2732B(DIP24)	EPROM	NONE
AMD	AM27512(DIP28)	EPROM	NONE
AMD	AM2764A(DIP28)	EPROM	NONE
AMD	AM27C010(DIP32)	EPROM	NONE
AMD	AM27C010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
AMD	AM27C020(DIP32)	EPROM	NONE
AMD	AM27C020(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
AMD	AM27C040(DIP32)	EPROM	NONE
AMD	AM27C040(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
AMD	AM27C100(DIP40)	EPROM	NONE
AMD	AM27C1024(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
AMD	AM27C128(DIP28)	EPROM	NONE
AMD	AM27C2048(DIP40)	EPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
AMD	AM27C2048(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
AMD	AM27C256(DIP28)	EPROM	NONE
AMD	AM27C256(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
AMD	AM27C400(DIP40)	EPROM	NONE
AMD	AM27C4096(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
AMD	AM27C512(DIP28)	EPROM	NONE
AMD	AM27C64(DIP28)	EPROM	NONE
AMD	AM27H010(DIP32)	EPROM	NONE
AMD	AM27H256(DIP28)	EPROM	NONE
AMD	AM27HB010(DIP32)	EPROM	NONE
AMD	AM27X010(DIP32)	EPROM	NONE
AMD	AM27X020(DIP32)	EPROM	NONE
AMD	AM27X040(DIP32)	EPROM	NONE
AMD	AM27X256(DIP28)	EPROM	NONE
AMD	AM27X512(DIP28)	EPROM	NONE
AMD	AM2817A(DIP28)	EEPROM	NONE
AMD	AM2864AE(DIP28)	EEPROM	NONE
AMD	AM2864B(DIP28)	EEPROM	NONE
AMD	AM2864BE(DIP28)	EEPROM	NONE
AMD	AM29DL161DB(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29DL161DT(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29DL162DB(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29DL162DT(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29DL163DB(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29DL163DT(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29DL164DB(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29DL164DT(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29DL400BB(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29DL400BT(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29DL800BB(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29DL800BT(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29F010(DIP32)	FLASH	NONE
AMD	AM29F010(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
AMD	AM29F010(TSOP32)	FLASH	LP48-TSOP-32S
AMD	AM29F010A(DIP32)	FLASH	NONE
AMD	AM29F010A(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
AMD	AM29F010A(TSOP32)	FLASH	LP48-TSOP-32S
AMD	AM29F010B(DIP32)	FLASH	NONE
AMD	AM29F010B(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
AMD	AM29F010B(TSOP32)	FLASH	LP48-TSOP-32S
AMD	AM29F040(DIP32)	FLASH	NONE
AMD	AM29F040(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
AMD	AM29F040(TSOP32)	FLASH	LP48-TSOP-32S
AMD	AM29F040B(DIP32)	FLASH	NONE
AMD	AM29F040B(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
AMD	AM29F040B(TSOP32)	FLASH	LP48-TSOP-32S
AMD	AM29F200AB(SO44)	FLASH	LP48-PSOP-44PIN
AMD	AM29F200AB(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29F200AT(SO44)	FLASH	LP48-PSOP-44PIN
AMD	AM29F200AT(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29F200B(SO44)	FLASH	LP48-PSOP-44PIN
AMD	AM29F200B(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29F200BB(SO44)	FLASH	LP48-PSOP-44PIN
AMD	AM29F200BB(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29F200BT(SO44)	FLASH	LP48-PSOP-44PIN
AMD	AM29F200BT(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29F200CB(SO44)	FLASH	LP48-PSOP-44PIN
AMD	AM29F200CB(TSOP48)	FLASH	LP-TSOP-48S

Manufacturer	Parts Number	Type	ADAPTER
AMD	AM29F200CT(SO44)	FLASH	LP48-PSOP-44PIN
AMD	AM29F200CT(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29F200T(SO44)	FLASH	LP48-PSOP-44PIN
AMD	AM29F200T(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29F400AB(SO44)	FLASH	LP48-PSOP-44PIN
AMD	AM29F400AB(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29F400AT(SO44)	FLASH	LP48-PSOP-44PIN
AMD	AM29F400AT(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29F400B(SO44)	FLASH	LP48-PSOP-44PIN
AMD	AM29F400B(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29F400BB(SO44)	FLASH	LP48-PSOP-44PIN
AMD	AM29F400BB(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29F400BT(SO44)	FLASH	LP48-PSOP-44PIN
AMD	AM29F400BT(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29F400T(SO44)	FLASH	LP48-PSOP-44PIN
AMD	AM29F400T(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29F800B(SO44)	FLASH	LP48-PSOP-44PIN
AMD	AM29F800B(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29F800BB(SO44)	FLASH	LP48-PSOP-44PIN
AMD	AM29F800BB(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29F800BT(SO44)	FLASH	LP48-PSOP-44PIN
AMD	AM29F800BT(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29F800T(SO44)	FLASH	LP48-PSOP-44PIN
AMD	AM29F800T(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29LV040B(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
AMD	AM29LV040B(TSOP32)	FLASH	LP48-TSOP-32S
AMD	AM29LV128MH-E(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
AMD	AM29LV128ML-E(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
AMD	AM29LV160BB(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29LV160BT(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29LV160DB(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29LV160DT(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29LV200BB(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29LV200BT(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29LV256MH-E(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
AMD	AM29LV256ML-E(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
AMD	AM29LV320DB(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29LV320DT(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29LV320MH-E(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
AMD	AM29LV320ML-E(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
AMD	AM29LV400BB(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29LV400BT(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29LV640MH-E(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
AMD	AM29LV640ML-E(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
AMD	AM29LV800BB(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29LV800BT(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29LV800DB(TSOP48)	FLASH	LP-TSOP-48S
AMD	AM29LV800DT(TSOP48)	FLASH	LP-TSOP-48S
AMIC	A25L010(DIP8)	FLASH	NONE
AMIC	A25L010-O(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25L010A(DIP8)	FLASH	NONE
AMIC	A25L010A-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25L010A-O(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25L010PTO(DIP8)	FLASH	NONE
AMIC	A25L010PTO-O(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25L010PUO(DIP8)	FLASH	NONE
AMIC	A25L010PUO-O(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25L016-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)

Manufacturer	Parts Number	Type	ADAPTER
AMIC	A25L016-N(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
AMIC	A25L016-O(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25L016T-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25L016U-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25L020(PDIP8)	FLASH	NONE
AMIC	A25L020-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25L020-O(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25L020C(PDIP8)	FLASH	NONE
AMIC	A25L020C-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25L020C-O(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25L020PTO(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25L032(PDIP8)	FLASH	NONE
AMIC	A25L032-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25L032-N(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
AMIC	A25L040(PDIP8)	FLASH	NONE
AMIC	A25L040-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25L040-O(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25L040A-O(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25L05PTO(PDIP8)	FLASH	NONE
AMIC	A25L05PTO-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25L05PTO-O(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25L05PTO-Q(QFN8)	FLASH	LP48-WSON8-5x6
AMIC	A25L05PUO(PDIP8)	FLASH	NONE
AMIC	A25L05PUO-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25L05PUO-O(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25L05PUO-Q(QFN8)	FLASH	LP48-WSON8-5x6
AMIC	A25L080(PDIP8)	FLASH	NONE
AMIC	A25L080-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25L080-O(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25L080B-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25L16PTM(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25L16PTN(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
AMIC	A25L16PTQ(QFN8)	FLASH	LP48-WSON8-5x6
AMIC	A25L16PUM(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25L16PUN(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
AMIC	A25L16PUQ(QFN8)	FLASH	LP48-WSON8-5x6
AMIC	A25L20PUO(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25L40PTO(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25L40PUO(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25L512(PDIP8)	FLASH	NONE
AMIC	A25L512-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25L512-O(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25L512-V(TSSOP8)	FLASH	LP-TSSOP-8PIN
AMIC	A25L512A(PDIP8)	FLASH	NONE
AMIC	A25L512A-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25L512A-O(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25L80PMF(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25L80PMW(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25L80PNF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
AMIC	A25LQ016(PDIP8)	FLASH	NONE
AMIC	A25LQ016-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25LQ016-N(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
AMIC	A25LQ016-O(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25LQ032(PDIP8)	FLASH	NONE
AMIC	A25LQ032-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25LQ032-N(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
AMIC	A25LQ032-O(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25LQ032A(PDIP8)	FLASH	NONE

Manufacturer	Parts Number	Type	ADAPTER
AMIC	A25LQ032A-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25LQ032A-N(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
AMIC	A25LQ032A-O(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25LQ32A(DIP8)	FLASH	NONE
AMIC	A25LQ32A-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25LQ32A-Q4(WSON8)	FLASH	LP48-WSON8-5x6
AMIC	A25LQ32B(DIP8)	FLASH	NONE
AMIC	A25LQ32B-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25LQ32B-Q4(WSON8)	FLASH	LP48-WSON8-5x6
AMIC	A25LQ64-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25LS080(PDIP8)	FLASH	NONE
AMIC	A25LS080-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25LS080-O(SOP8)	FLASH	LP-SOP-16PIN(150mil)
AMIC	A25QE32(DIP8)	FLASH	NONE
AMIC	A25QE32-M(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
AMIC	A25QE32-Q4(WSON8)	FLASH	LP48-WSON8-5x6
AMIC	A27020(DIP32)	EPROM	NONE
AMIC	A27020(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
AMIC	A276308(DIP28)	EPROM	NONE
AMIC	A276308(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
AMIC	A276308A(DIP28)	EPROM	NONE
AMIC	A276308A(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
AMIC	A277308(DIP32)	EPROM	NONE
AMIC	A277308(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
AMIC	A278308(DIP32)	EPROM	NONE
AMIC	A278308(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
AMIC	A278308A(DIP32)	EPROM	NONE
AMIC	A278308A(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
AMIC	A279308(DIP32)	EPROM	NONE
AMIC	A279308(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
AMIC	A290011T(DIP32)	FLASH	NONE
AMIC	A290011TL(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
AMIC	A290011TV(TSOP32)	FLASH	LP48-TSOP-32S
AMIC	A290011U(DIP32)	FLASH	NONE
AMIC	A290011UL(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
AMIC	A290011UV(TSOP32)	FLASH	LP48-TSOP-32S
AMIC	A29001T(DIP32)	FLASH	NONE
AMIC	A29001TL(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
AMIC	A29001TV(TSOP32)	FLASH	LP48-TSOP-32S
AMIC	A29001U(DIP32)	FLASH	NONE
AMIC	A29001UL(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
AMIC	A29001UV(TSOP32)	FLASH	LP48-TSOP-32S
AMIC	A29010(DIP32)	FLASH	NONE
AMIC	A29010(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
AMIC	A29040(DIP32)	FLASH	NONE
AMIC	A29040(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
AMIC	A29040A(DIP32)	FLASH	NONE
AMIC	A29040A(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
AMIC	A29040B(DIP32)	FLASH	NONE
AMIC	A29040B(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
AMIC	A29512(DIP32)	FLASH	NONE
AMIC	A29512L(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
AMIC	A29512V(TSOP32)	FLASH	LP48-TSOP-32S
AMIC	A29800TM(PSOP44)	FLASH	LP48-PSOP-44PIN
AMIC	A29800TV(TSOP48)	FLASH	LP-TSOP-48S
AMIC	A29800UM(PSOP44)	FLASH	LP48-PSOP-44PIN
AMIC	A29800UV(TSOP48)	FLASH	LP-TSOP-48S
AMIC	A29L004TL(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S

Manufacturer	Parts Number	Type	ADAPTER
AMIC	A29L004TV(TSOP32)	FLASH	LP48-TSOP-32S
AMIC	A29L004TW(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
AMIC	A29L004TX(VSOP32)	FLASH	LP48-VSOP-32S
AMIC	A29L004UL(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
AMIC	A29L004UV(TSOP32)	FLASH	LP48-TSOP-32S
AMIC	A29L004UW(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
AMIC	A29L004UX(VSOP32)	FLASH	LP48-VSOP-32S
AMIC	A29L008ATV(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
AMIC	A29L008AUV(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
AMIC	A29L008TV(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
AMIC	A29L008UV(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
AMIC	A29L040(DIP32)	FLASH	NONE
AMIC	A29L040L(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
AMIC	A29L040V(TSOP32)	FLASH	LP48-TSOP-32S
AMIC	A29L040X(VSOP32)	FLASH	LP48-VSOP-32S
AMIC	A29L160ATV(TSOP48)	FLASH	LP-TSOP-48S
AMIC	A29L160AUV(TSOP48)	FLASH	LP-TSOP-48S
AMIC	A29L320ATV(TSOP48)	FLASH	LP-TSOP-48S
AMIC	A29L320AUV(TSOP48)	FLASH	LP-TSOP-48S
AMIC	A29L400TM(PSOP44)	FLASH	LP48-PSOP-44PIN
AMIC	A29L400TV(TSOP48)	FLASH	LP-TSOP-48S
AMIC	A29L400UM(PSOP44)	FLASH	LP48-PSOP-44PIN
AMIC	A29L400UV(TSOP48)	FLASH	LP-TSOP-48S
AMIC	A29L800ATV(TSOP48)	FLASH	LP-TSOP-48S
AMIC	A29L800AUV(TSOP48)	FLASH	LP-TSOP-48S
AMIC	A29L800TV(TSOP48)	FLASH	LP-TSOP-48S
AMIC	A29L800UV(TSOP48)	FLASH	LP-TSOP-48S
AMIC	AT275308(DIP28)	EPROM	NONE
AMIC	AT275308(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Anachip	AM24LC02(DIP8)	EEPROM	NONE
Anachip	AM24LC02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Anachip	AM24LC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Anachip	AM24LC04(DIP8)	EEPROM	NONE
Anachip	AM24LC04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Anachip	AM24LC04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Anachip	AM24LC08(DIP8)	EEPROM	NONE
Anachip	AM24LC08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Anachip	AM24LC16(DIP8)	EEPROM	NONE
Anachip	AM24LC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Anachip	AM93LC46(DIP8)	EEPROM	NONE
Anachip	AM93LC46(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Anachip	AM93LC46G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Anachip	AM93LC56-X16(DIP8)	EEPROM	NONE
Anachip	AM93LC56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Anachip	AM93LC56-X8(DIP8)	EEPROM	NONE
Anachip	AM93LC56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Anachip	AM93LC56G-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Anachip	AM93LC56G-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Anachip	AM93LC66-X16(DIP8)	EEPROM	NONE
Anachip	AM93LC66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Anachip	AM93LC66-X8(DIP8)	EEPROM	NONE
Anachip	AM93LC66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Anachip	AM93LC66G-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Anachip	AM93LC66G-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Anachip	AM93LC86-X16(DIP8)	EEPROM	NONE
Anachip	AM93LC86-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Anachip	AM93LC86-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Anachip	AM93LC86-X8(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
Anachip	AM93LC86-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Anachip	AM93LC86-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
APLUS	AF24BC01(DIP8)	EEPROM	NONE
APLUS	AF24BC01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
APLUS	AF24BC01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
APLUS	AF24BC02(DIP8)	EEPROM	NONE
APLUS	AF24BC02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
APLUS	AF24BC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
APLUS	AF24BC04(DIP8)	EEPROM	NONE
APLUS	AF24BC04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
APLUS	AF24BC04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
APLUS	AF24BC08(DIP8)	EEPROM	NONE
APLUS	AF24BC08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
APLUS	AF24BC08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
APLUS	AF24BC128(DIP8)	EEPROM	NONE
APLUS	AF24BC128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
APLUS	AF24BC128(TSSOP8)	EEPROM	LP-TSSOP-8PIN
APLUS	AF24BC16(DIP8)	EEPROM	NONE
APLUS	AF24BC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
APLUS	AF24BC16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
APLUS	AF24BC256(DIP8)	EEPROM	NONE
APLUS	AF24BC256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
APLUS	AF24BC256(TSSOP8)	EEPROM	LP-TSSOP-8PIN
APLUS	AF24BC32(DIP8)	EEPROM	NONE
APLUS	AF24BC32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
APLUS	AF24BC32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
APLUS	AF24BC64(DIP8)	EEPROM	NONE
APLUS	AF24BC64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
APLUS	AF24BC64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
APLUS	AF93BC46-X16(DIP8)	EEPROM	NONE
APLUS	AF93BC46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
APLUS	AF93BC46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
APLUS	AF93BC46-X8(DIP8)	EEPROM	NONE
APLUS	AF93BC46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
APLUS	AF93BC46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
APLUS	AF93BC56-X16(DIP8)	EEPROM	NONE
APLUS	AF93BC56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
APLUS	AF93BC56-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
APLUS	AF93BC56-X8(DIP8)	EEPROM	NONE
APLUS	AF93BC56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
APLUS	AF93BC56-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
APLUS	AF93BC66-X16(DIP8)	EEPROM	NONE
APLUS	AF93BC66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
APLUS	AF93BC66-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
APLUS	AF93BC66-X8(DIP8)	EEPROM	NONE
APLUS	AF93BC66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
APLUS	AF93BC66-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
APLUS	AF93BC86-X16(DIP8)	EEPROM	NONE
APLUS	AF93BC86-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
APLUS	AF93BC86-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
APLUS	AF93BC86-X8(DIP8)	EEPROM	NONE
APLUS	AF93BC86-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
APLUS	AF93BC86-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Artship	24AA128(DIP8)	EEPROM	NONE
Artship	24AA128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Artship	24AA64(DIP8)	EEPROM	NONE
Artship	24AA64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Artship	24AA64(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
Artschip	24LC02B(DIP8)	EEPROM	NONE
Artschip	24LC02B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Artschip	24LC02B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Artschip	24LC04B(DIP8)	EEPROM	NONE
Artschip	24LC04B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Artschip	24LC04B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Artschip	24LC08B(DIP8)	EEPROM	NONE
Artschip	24LC08B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Artschip	24LC08B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Artschip	24LC128(DIP8)	EEPROM	NONE
Artschip	24LC128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Artschip	24LC16B(DIP8)	EEPROM	NONE
Artschip	24LC16B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Artschip	24LC16B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Artschip	24LC32B(DIP8)	EEPROM	NONE
Artschip	24LC32B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Artschip	24LC32B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Artschip	24LC64(DIP8)	EEPROM	NONE
Artschip	24LC64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Artschip	24LC64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Artschip	24LC64B(DIP8)	EEPROM	NONE
Artschip	24LC64B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Artschip	24LC64B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Asic Microelect	AX24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Asic Microelect	AX24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Asic Microelect	AX24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Asic Microelect	AX24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATC	AM24C02(DIP8)	EEPROM	NONE
ATC	AM24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATC	AM24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATC	AM24C04(DIP8)	EEPROM	NONE
ATC	AM24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATC	AM24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATC	AM24C08(DIP8)	EEPROM	NONE
ATC	AM24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATC	AM24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATC	AM24LC02(DIP8)	EEPROM	NONE
ATC	AM24LC02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATC	AM24LC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATC	AM24LC02W(DIP8)	EEPROM	NONE
ATC	AM24LC02W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATC	AM24LC04(DIP8)	EEPROM	NONE
ATC	AM24LC04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATC	AM24LC04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATC	AM24LC08(DIP8)	EEPROM	NONE
ATC	AM24LC08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATC	AM24LC16(DIP8)	EEPROM	NONE
ATC	AM24LC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATC	ATC93C46(DIP8)	EEPROM	NONE
ATC	ATC93C46(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATC	ATC93C56-X16(DIP8)	EEPROM	NONE
ATC	ATC93C56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATC	ATC93C56-X8(DIP8)	EEPROM	NONE
ATC	ATC93C56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATC	ATC93C66-X16(DIP8)	EEPROM	NONE
ATC	ATC93C66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATC	ATC93C66-X8(DIP8)	EEPROM	NONE
ATC	ATC93C66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
ATC	ATC93LC46(DIP8)	EEPROM	NONE
ATC	ATC93LC46(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATC	ATC93LC56-X16(DIP8)	EEPROM	NONE
ATC	ATC93LC56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATC	ATC93LC56-X8(DIP8)	EEPROM	NONE
ATC	ATC93LC56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATC	ATC93LC56G-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATC	ATC93LC56G-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATC	ATC93LC66-X16(DIP8)	EEPROM	NONE
ATC	ATC93LC66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATC	ATC93LC66-X8(DIP8)	EEPROM	NONE
ATC	ATC93LC66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATC	ATC93LC66G-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATC	ATC93LC66G-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C01(DIP8)	EEPROM	NONE
ATMEL	AT24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C01-1.8(DIP8)	EEPROM	NONE
ATMEL	AT24C01-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C01-1.8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C01-2.5(DIP8)	EEPROM	NONE
ATMEL	AT24C01-2.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C01-2.5(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C01-2.7(DIP8)	EEPROM	NONE
ATMEL	AT24C01-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C01-2.7(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C01A(DIP8)	EEPROM	NONE
ATMEL	AT24C01A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C01A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C01A-1.8(DIP8)	EEPROM	NONE
ATMEL	AT24C01A-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C01A-1.8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C01A-2.5(DIP8)	EEPROM	NONE
ATMEL	AT24C01A-2.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C01A-2.5(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C01A-2.7(DIP8)	EEPROM	NONE
ATMEL	AT24C01A-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C01A-2.7(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C01B(DIP8)	EEPROM	NONE
ATMEL	AT24C01B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C01B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C02(DIP8)	EEPROM	NONE
ATMEL	AT24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C02-2.7(DIP8)	EEPROM	NONE
ATMEL	AT24C02-2.7(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C02-5.0(DIP8)	EEPROM	NONE
ATMEL	AT24C02-5.0(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C02A(DIP8)	EEPROM	NONE
ATMEL	AT24C02A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C02A-1.8(DIP8)	EEPROM	NONE
ATMEL	AT24C02A-1.8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C02A-2.5(DIP8)	EEPROM	NONE
ATMEL	AT24C02A-2.5(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C02A-2.7(DIP8)	EEPROM	NONE
ATMEL	AT24C02A-2.7(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C02AN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C02AN-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C02AN-2.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
ATMEL	AT24C02AN-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C02B(DIP8)	EEPROM	NONE
ATMEL	AT24C02B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C02B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C02C(DIP8)	EEPROM	NONE
ATMEL	AT24C02C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C02C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C02N(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C02N-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C02N-5.0(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C04(DIP8)	EEPROM	NONE
ATMEL	AT24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C04-2.7(DIP8)	EEPROM	NONE
ATMEL	AT24C04-2.7(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C04-5.0(DIP8)	EEPROM	NONE
ATMEL	AT24C04-5.0(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C04A(DIP8)	EEPROM	NONE
ATMEL	AT24C04A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C04A-1.8(DIP8)	EEPROM	NONE
ATMEL	AT24C04A-1.8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C04A-2.5(DIP8)	EEPROM	NONE
ATMEL	AT24C04A-2.5(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C04A-2.7(DIP8)	EEPROM	NONE
ATMEL	AT24C04A-2.7(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C04AN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C04AN-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C04AN-2.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C04AN-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C04B(DIP8)	EEPROM	NONE
ATMEL	AT24C04B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C04B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C04N(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C04N-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C04N-5.0(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C08(DIP8)	EEPROM	NONE
ATMEL	AT24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C08-2.7(DIP8)	EEPROM	NONE
ATMEL	AT24C08-2.7(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C08-5.0(DIP8)	EEPROM	NONE
ATMEL	AT24C08-5.0(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C08A(DIP8)	EEPROM	NONE
ATMEL	AT24C08A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C08A-1.8(DIP8)	EEPROM	NONE
ATMEL	AT24C08A-1.8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C08A-2.5(DIP8)	EEPROM	NONE
ATMEL	AT24C08A-2.5(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C08A-2.7(DIP8)	EEPROM	NONE
ATMEL	AT24C08A-2.7(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C08AN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C08AN-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C08AN-2.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C08AN-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C08B(DIP8)	EEPROM	NONE
ATMEL	AT24C08B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C08B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C08N(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C08N-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C08N-5.0(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
ATMEL	AT24C1024(DIP8)	EEPROM	NONE
ATMEL	AT24C1024(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C1024(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C1024B(DIP8)	EEPROM	NONE
ATMEL	AT24C1024B(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C1024B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C1024W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C11(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C11-1.8(PDIP8)	EEPROM	NONE
ATMEL	AT24C11-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C11-1.8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C11-2.7(PDIP8)	EEPROM	NONE
ATMEL	AT24C11-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C11-2.7(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C128(DIP8)	EEPROM	NONE
ATMEL	AT24C128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C128(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C128-1.8(DIP8)	EEPROM	NONE
ATMEL	AT24C128-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C128-1.8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C128B(DIP8)	EEPROM	NONE
ATMEL	AT24C128B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C128BN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C128C(DIP8)	EEPROM	NONE
ATMEL	AT24C128C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C128CN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C128N(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C128N-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C128W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C128W-1.8(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C16-2.7(DIP8)	EEPROM	NONE
ATMEL	AT24C16-2.7(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C16-5.0(DIP8)	EEPROM	NONE
ATMEL	AT24C16-5.0(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C164(DIP8)	EEPROM	NONE
ATMEL	AT24C164(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C16A(DIP8)	EEPROM	NONE
ATMEL	AT24C16A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C16AN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C16B(DIP8)	EEPROM	NONE
ATMEL	AT24C16B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C16B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C16BN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C16C(DIP8)	EEPROM	NONE
ATMEL	AT24C16C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C16C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C16N(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C16N-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C16N-5.0(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C21-2.5(DIP8)	EEPROM	NONE
ATMEL	AT24C21-2.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C21-2.5(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C256(DIP8)	EEPROM	NONE
ATMEL	AT24C256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C256(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C256-1.8(DIP8)	EEPROM	NONE
ATMEL	AT24C256-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
ATMEL	AT24C256B(DIP8)	EEPROM	NONE
ATMEL	AT24C256B(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C256B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C256C(DIP8)	EEPROM	NONE
ATMEL	AT24C256C(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C256C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C256N(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C256N-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C256W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C256W-1.8(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C32(DIP8)	EEPROM	NONE
ATMEL	AT24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C32-2.7(DIP8)	EEPROM	NONE
ATMEL	AT24C32-2.7(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C32A(DIP8)	EEPROM	NONE
ATMEL	AT24C32A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C32A-1.8(DIP8)	EEPROM	NONE
ATMEL	AT24C32A-1.8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C32A-2.7(DIP8)	EEPROM	NONE
ATMEL	AT24C32A-2.7(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C32AN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C32AN-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C32AN-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C32AW(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C32AW-1.8(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C32AW-2.7(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C32B(DIP8)	EEPROM	NONE
ATMEL	AT24C32B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C32B-1.8(DIP8)	EEPROM	NONE
ATMEL	AT24C32B-1.8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C32B-2.7(DIP8)	EEPROM	NONE
ATMEL	AT24C32B-2.7(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C32BN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C32BN-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C32BN-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C32C(DIP8)	EEPROM	NONE
ATMEL	AT24C32C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C32C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C32D(DIP8)	EEPROM	NONE
ATMEL	AT24C32D(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C32D(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C32N(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C32N-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C32W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C32W-2.7(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C512(DIP8)	EEPROM	NONE
ATMEL	AT24C512(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C512-1.8(DIP8)	EEPROM	NONE
ATMEL	AT24C512-1.8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C512B(DIP8)	EEPROM	NONE
ATMEL	AT24C512B(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C512B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C512C(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C512C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C512C-D(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C512C-D(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C512C-M(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C512C-M(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
ATMEL	AT24C512N(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C512N-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C512W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C512W-1.8(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C64(DIP8)	EEPROM	NONE
ATMEL	AT24C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C64-2.7(DIP8)	EEPROM	NONE
ATMEL	AT24C64-2.7(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C64A(DIP8)	EEPROM	NONE
ATMEL	AT24C64A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C64A-1.8(DIP8)	EEPROM	NONE
ATMEL	AT24C64A-1.8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C64A-2.7(DIP8)	EEPROM	NONE
ATMEL	AT24C64A-2.7(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C64AN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C64AN-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C64AN-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C64AW(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C64AW-1.8(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C64AW-2.7(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C64B(DIP8)	EEPROM	NONE
ATMEL	AT24C64B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C64B-1.8(DIP8)	EEPROM	NONE
ATMEL	AT24C64B-1.8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C64B-2.7(DIP8)	EEPROM	NONE
ATMEL	AT24C64B-2.7(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C64BN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C64BN-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C64BN-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C64C(DIP8)	EEPROM	NONE
ATMEL	AT24C64C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C64C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C64D(DIP8)	EEPROM	NONE
ATMEL	AT24C64D(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C64D(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24C64N(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C64N-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24C64W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24C64W-2.7(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24CS128(DIP8)	EEPROM	NONE
ATMEL	AT24CS128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24CS128-1.8(DIP8)	EEPROM	NONE
ATMEL	AT24CS128-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24CS128N(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24CS128N-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24CS128W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24CS128W-1.8(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24CS256(DIP8)	EEPROM	NONE
ATMEL	AT24CS256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24CS256-1.8(DIP8)	EEPROM	NONE
ATMEL	AT24CS256N(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24CS256W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24CS256W-1.8(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ATMEL	AT24HC02B(DIP8)	EEPROM	NONE
ATMEL	AT24HC02B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24HC02B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24HC04B(DIP8)	EEPROM	NONE
ATMEL	AT24HC04B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
ATMEL	AT24HC04B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24L02(DIP8)	EEPROM	NONE
ATMEL	AT24L02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24L08(DIP8)	EEPROM	NONE
ATMEL	AT24L16(DIP8)	EEPROM	NONE
ATMEL	AT24L16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24L32(DIP8)	EEPROM	NONE
ATMEL	AT24L32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24L64(DIP8)	EEPROM	NONE
ATMEL	AT24LC01(DIP8)	EEPROM	NONE
ATMEL	AT24LC01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24LC01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24LC01B(DIP8)	EEPROM	NONE
ATMEL	AT24LC01B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24LC01B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24LC02(DIP8)	EEPROM	NONE
ATMEL	AT24LC02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24LC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24LC02B(DIP8)	EEPROM	NONE
ATMEL	AT24LC02B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24LC02B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24LC04(DIP8)	EEPROM	NONE
ATMEL	AT24LC04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24LC04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24LC08(DIP8)	EEPROM	NONE
ATMEL	AT24LC08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24LC08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24LC08B(DIP8)	EEPROM	NONE
ATMEL	AT24LC08B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24LC08B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24LC16(DIP8)	EEPROM	NONE
ATMEL	AT24LC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24LC16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24LC16B(DIP8)	EEPROM	NONE
ATMEL	AT24LC16B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24LC16B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24LC256(DIP8)	EEPROM	NONE
ATMEL	AT24LC256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24LC256(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24LC32(DIP8)	EEPROM	NONE
ATMEL	AT24LC32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24LC32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24LC64(DIP8)	EEPROM	NONE
ATMEL	AT24LC64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24LC64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT24RF08B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT24RF08C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT25020A(PDIP8)	EEPROM	NONE
ATMEL	AT25020A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT25020A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT25040A(PDIP8)	EEPROM	NONE
ATMEL	AT25040A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT25040A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT25080(DIP8)	EEPROM	NONE
ATMEL	AT25080(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT25080B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT25080B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT25128(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
ATMEL	AT25128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT25128A(DIP8)	EEPROM	NONE
ATMEL	AT25128A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT25128B(DIP8)	EEPROM	NONE
ATMEL	AT25128B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT25160(DIP8)	EEPROM	NONE
ATMEL	AT25160(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT25256(DIP8)	EEPROM	NONE
ATMEL	AT25256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT25256(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT25256A(DIP8)	EEPROM	NONE
ATMEL	AT25256A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT25256A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT25256B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT25256B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT25256B(UDFN8)	EEPROM	LP48-MLP8-2x3
ATMEL	AT25320(DIP8)	EEPROM	NONE
ATMEL	AT25320(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT25512(DIP8)	EEPROM	NONE
ATMEL	AT25512(SAP8)	EEPROM	LP48-WSON8-5x6
ATMEL	AT25512(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT25512(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT25640(DIP8)	EEPROM	NONE
ATMEL	AT25640(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT25DF021-M(UDFN8)	FLASH	LP48-WSON8-5x6
ATMEL	AT25DF021-SS(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ATMEL	AT25DF041A-M(SOP8)	FLASH	LP48-WSON8-5x6
ATMEL	AT25DF041A-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ATMEL	AT25DF041A-SS(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ATMEL	AT25DF081(SOP8-150)	FLASH	LP-SOP-16PIN(150mil)
ATMEL	AT25DF081(SOP8-207)	FLASH	LP-SOP-8PIN-B(207mil)
ATMEL	AT25DF081(WSON 5x6)	FLASH	LP48-WSON8-5x6
ATMEL	AT25DF081(WSON 6x8)	FLASH	LP48-WSON8-6x8
ATMEL	AT25DF161-M(UDFN8)	FLASH	LP48-WSON8-5x6
ATMEL	AT25DF161-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ATMEL	AT25DF161-SS(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ATMEL	AT25DF321(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ATMEL	AT25DF321(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ATMEL	AT25DF641-MW1(VDFN8)	FLASH	LP48-WSON8-6x8
ATMEL	AT25DF641-S3(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ATMEL	AT25F1024(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ATMEL	AT25F1024A(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ATMEL	AT25F1024N(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ATMEL	AT25F2048(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ATMEL	AT25F4096(SAP8)	FLASH	LP48-WSON8-5x6
ATMEL	AT25F4096(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ATMEL	AT25F512(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ATMEL	AT25F512A(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ATMEL	AT25F512B(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ATMEL	AT25FS010(SAP8)	FLASH	LP48-WSON8-5x6
ATMEL	AT25FS010(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ATMEL	AT25FS040(SAP8)	FLASH	LP48-WSON8-5x6
ATMEL	AT25FS040(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ATMEL	AT27BV010(DIP32)	EPROM	NONE
ATMEL	AT27BV010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27BV010(SOP32)	EPROM	LP48-SOP-32PIN
ATMEL	AT27BV010(TSOP32)	EPROM	LP48-TSOP-32S
ATMEL	AT27BV020(DIP32)	EPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
ATMEL	AT27BV020(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27BV020(SOP32)	EPROM	LP48-SOP-32PIN
ATMEL	AT27BV020(TSOP32)	EPROM	LP48-TSOP-32S
ATMEL	AT27BV040(DIP32)	EPROM	NONE
ATMEL	AT27BV040(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27BV040(SOP32)	EPROM	LP48-SOP-32PIN
ATMEL	AT27BV040(TSOP32)	EPROM	LP48-TSOP-32S
ATMEL	AT27BV080(DIP32)	EPROM	NONE
ATMEL	AT27BV080(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27BV080(SOP32)	EPROM	LP48-SOP-32PIN
ATMEL	AT27BV080(TSOP32)	EPROM	LP48-TSOP-32S
ATMEL	AT27BV100(DIP40)	EPROM	NONE
ATMEL	AT27BV100(SOP40)	EPROM	LP48-SOP-40PIN
ATMEL	AT27BV100(TSOP48)	EPROM	LP-TSOP-48S
ATMEL	AT27BV1024(DIP40)	EPROM	NONE
ATMEL	AT27BV1024(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT27BV1024(TSOP40)	EPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
ATMEL	AT27BV200(DIP40)	EPROM	NONE
ATMEL	AT27BV200(SOP40)	EPROM	LP48-SOP-40PIN
ATMEL	AT27BV200(TSOIP)	EPROM	LP-TSOP-48S
ATMEL	AT27BV2048(DIP40)	EPROM	NONE
ATMEL	AT27BV2048(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT27BV2048(TSOP40)	EPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
ATMEL	AT27BV256(DIP28)	EPROM	NONE
ATMEL	AT27BV256(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27BV256(TSOP28)	EPROM	LP48-TSOP-28PIN
ATMEL	AT27BV400(DIP40)	EPROM	NONE
ATMEL	AT27BV400(SOP40)	EPROM	LP48-SOP-40PIN
ATMEL	AT27BV400(TSOP48)	EPROM	LP-TSOP-48S
ATMEL	AT27BV4096(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT27BV4096(TSOP40)	EPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
ATMEL	AT27BV512(DIP28)	EPROM	NONE
ATMEL	AT27BV512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27BV512(TSOP28)	EPROM	LP48-TSOP-28PIN
ATMEL	AT27BV516(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT27BV516(TSOP40)	EPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
ATMEL	AT27BV800(DIP42)	EPROM	NONE
ATMEL	AT27BV800(SOP42)	EPROM	LP48-PSOP-44PIN
ATMEL	AT27BV800(TSOP48)	EPROM	LP-TSOP-48S
ATMEL	AT27C010(DIP32)	EPROM	NONE
ATMEL	AT27C010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27C010(SOP32)	EPROM	LP48-SOP-32PIN
ATMEL	AT27C010(TSOP32)	EPROM	LP48-TSOP-32S
ATMEL	AT27C010-L(DIP32)	EPROM	NONE
ATMEL	AT27C010-L(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27C010-L(TSOP32)	EPROM	LP48-TSOP-32S
ATMEL	AT27C020(DIP32)	EPROM	NONE
ATMEL	AT27C020(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27C020(SOP32)	EPROM	LP48-SOP-32PIN
ATMEL	AT27C020(TSOP32)	EPROM	LP48-TSOP-32S
ATMEL	AT27C040(DIP32)	EPROM	NONE
ATMEL	AT27C040(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27C040(SOP32)	EPROM	LP48-SOP-32PIN
ATMEL	AT27C040(TSOP32)	EPROM	LP48-TSOP-32S
ATMEL	AT27C080(DIP32)	EPROM	NONE
ATMEL	AT27C080(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27C080(SOP32)	EPROM	LP48-SOP-32PIN
ATMEL	AT27C080(TSOP32)	EPROM	LP48-TSOP-32S

Manufacturer	Parts Number	Type	ADAPTER
ATMEL	AT27C100(DIP40)	EPROM	NONE
ATMEL	AT27C100(SOP40)	EPROM	LP48-SOP-40PIN
ATMEL	AT27C100(TSOP48)	EPROM	LP-TSOP-48S
ATMEL	AT27C1024(DIP40)	EPROM	NONE
ATMEL	AT27C1024(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT27C1024(TSOP40)	EPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
ATMEL	AT27C1024L(DIP40)	EPROM	NONE
ATMEL	AT27C1024L(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT27C200(DIP40)	EPROM	NONE
ATMEL	AT27C200(SOP40)	EPROM	LP48-SOP-40PIN
ATMEL	AT27C200(TSOP48)	EPROM	LP-TSOP-48S
ATMEL	AT27C2048(DIP40)	EPROM	NONE
ATMEL	AT27C2048(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT27C2048(TSOP40)	EPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
ATMEL	AT27C2048L(DIP40)	EPROM	NONE
ATMEL	AT27C2048L(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT27C256(DIP28)	EPROM	NONE
ATMEL	AT27C256(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27C256(TSOP28)	EPROM	LP48-TSOP-28PIN
ATMEL	AT27C256R(DIP28)	EPROM	NONE
ATMEL	AT27C256R(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27C256R(TSOP28)	EPROM	LP48-TSOP-28PIN
ATMEL	AT27C400(DIP40)	EPROM	NONE
ATMEL	AT27C400(SOP40)	EPROM	LP48-SOP-40PIN
ATMEL	AT27C400(TSOP48)	EPROM	LP-TSOP-48S
ATMEL	AT27C4096(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT27C4096(TSOP40)	EPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
ATMEL	AT27C512(DIP28)	EPROM	NONE
ATMEL	AT27C512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27C512(TSOP28)	EPROM	LP48-TSOP-28PIN
ATMEL	AT27C512R(DIP28)	EPROM	NONE
ATMEL	AT27C512R(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27C512R(TSOP28)	EPROM	LP48-TSOP-28PIN
ATMEL	AT27C516(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT27C516(TSOP40)	EPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
ATMEL	AT27C64(DIP28)	EPROM	NONE
ATMEL	AT27C800(DIP42)	EPROM	NONE
ATMEL	AT27C800(SOP42)	EPROM	LP48-PSOP-44PIN
ATMEL	AT27C800(TSOP48)	EPROM	LP-TSOP-48S
ATMEL	AT27CLV256R(TSOP28)	EPROM	LP48-TSOP-28PIN
ATMEL	AT27HC1024(DIP40)	EPROM	NONE
ATMEL	AT27HC1024(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT27HC256R(DIP28)	EPROM	NONE
ATMEL	AT27HC64(DIP28)	EPROM	NONE
ATMEL	AT27HC642(DIP24)	EPROM	NONE
ATMEL	AT27LV010(DIP32)	EPROM	NONE
ATMEL	AT27LV010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27LV010(SOP32)	EPROM	LP48-SOP-32PIN
ATMEL	AT27LV010(TSOP32)	EPROM	LP48-TSOP-32S
ATMEL	AT27LV010A(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27LV010A(TSOP32)	EPROM	LP48-TSOP-32S
ATMEL	AT27LV010L(DIP32)	EPROM	NONE
ATMEL	AT27LV010L(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27LV010L(SOP32)	EPROM	LP48-SOP-32PIN
ATMEL	AT27LV010L(TSOP32)	EPROM	LP48-TSOP-32S
ATMEL	AT27LV020(DIP32)	EPROM	NONE
ATMEL	AT27LV020(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27LV020(SOP32)	EPROM	LP48-SOP-32PIN

Manufacturer	Parts Number	Type	ADAPTER
ATMEL	AT27LV020(TSOP32)	EPROM	LP48-TSOP-32S
ATMEL	AT27LV020A(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27LV020A(TSOP32)	EPROM	LP48-TSOP-32S
ATMEL	AT27LV040(DIP32)	EPROM	NONE
ATMEL	AT27LV040(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27LV040(SOP32)	EPROM	LP48-SOP-32PIN
ATMEL	AT27LV040(TSOP32)	EPROM	LP48-TSOP-32S
ATMEL	AT27LV040A(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27LV040A(TSOP32)	EPROM	LP48-TSOP-32S
ATMEL	AT27LV080(DIP32)	EPROM	NONE
ATMEL	AT27LV080(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27LV080(SOP32)	EPROM	LP48-SOP-32PIN
ATMEL	AT27LV080(TSOP32)	EPROM	LP48-TSOP-32S
ATMEL	AT27LV080A(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27LV080A(TSOP32)	EPROM	LP48-TSOP-32S
ATMEL	AT27LV100(DIP40)	EPROM	NONE
ATMEL	AT27LV100(SOP40)	EPROM	LP48-SOP-40PIN
ATMEL	AT27LV100(TSOP48)	EPROM	LP-TSOP-48S
ATMEL	AT27LV1024(DIP40)	EPROM	NONE
ATMEL	AT27LV1024(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT27LV1024(TSOP40)	EPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
ATMEL	AT27LV200(DIP40)	EPROM	NONE
ATMEL	AT27LV200(SOP40)	EPROM	LP48-SOP-40PIN
ATMEL	AT27LV200(TSOP48)	EPROM	LP-TSOP-48S
ATMEL	AT27LV2048(DIP40)	EPROM	NONE
ATMEL	AT27LV2048(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT27LV2048(TSOP40)	EPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
ATMEL	AT27LV256(DIP28)	EPROM	NONE
ATMEL	AT27LV256(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27LV256(TSOP28)	EPROM	LP48-TSOP-28PIN
ATMEL	AT27LV256A(DIP28)	EPROM	NONE
ATMEL	AT27LV256A(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27LV256A(TSOP28)	EPROM	LP48-TSOP-28PIN
ATMEL	AT27LV256R(DIP28)	EPROM	NONE
ATMEL	AT27LV256R(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27LV400(DIP40)	EPROM	NONE
ATMEL	AT27LV400(SOP40)	EPROM	LP48-SOP-40PIN
ATMEL	AT27LV400(TSOP48)	EPROM	LP-TSOP-48S
ATMEL	AT27LV4096(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT27LV4096(TSOP40)	EPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
ATMEL	AT27LV512(DIP28)	EPROM	NONE
ATMEL	AT27LV512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27LV512(TSOP28)	EPROM	LP48-TSOP-28PIN
ATMEL	AT27LV512A(DIP28)	EPROM	NONE
ATMEL	AT27LV512A(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27LV512A(TSOP28)	EPROM	LP48-TSOP-28PIN
ATMEL	AT27LV512R(DIP28)	EPROM	NONE
ATMEL	AT27LV512R(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ATMEL	AT27LV512R(TSOP28)	EPROM	LP48-TSOP-28PIN
ATMEL	AT27LV516(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT27LV516(TSOP40)	EPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
ATMEL	AT27LV800(DIP42)	EPROM	NONE
ATMEL	AT27LV800(SOP42)	EPROM	LP48-PSOP-44PIN
ATMEL	AT27LV800(TSOP48)	EPROM	LP-TSOP-48S
ATMEL	AT28BV16(DIP24)	EEPROM	NONE
ATMEL	AT28BV16(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28BV16(SOIC24)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28BV16(TSOP28)	EEPROM	LP-TSOP-28PIN

Manufacturer	Parts Number	Type	ADAPTER
ATMEL	AT28BV256(DIP28)	EEPROM	NONE
ATMEL	AT28BV256(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28BV256(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28BV256(TSOP28)	EEPROM	LP-TSOP-28PIN
ATMEL	AT28BV64(DIP28)	EEPROM	NONE
ATMEL	AT28BV64(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28BV64(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28BV64(TSOP28)	EEPROM	LP-TSOP-28PIN
ATMEL	AT28BV64B(DIP28)	EEPROM	NONE
ATMEL	AT28BV64B(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28BV64B(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28BV64B(TSOP28)	EEPROM	LP-TSOP-28PIN
ATMEL	AT28C010(DIP32)	EEPROM	NONE
ATMEL	AT28C010(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28C010(TSOP32)	EEPROM	LP48-TSOP-32S
ATMEL	AT28C010E(DIP32)	EEPROM	NONE
ATMEL	AT28C010E(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28C010E(TSOP32)	EEPROM	LP48-TSOP-32S
ATMEL	AT28C020(DIP32)	EEPROM	NONE
ATMEL	AT28C04(DIP24)	EEPROM	NONE
ATMEL	AT28C04(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28C040(DIP32)	EEPROM	NONE
ATMEL	AT28C16(DIP24)	EEPROM	NONE
ATMEL	AT28C16(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28C16(SOIC24)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28C16-T(TSOP28)	EEPROM	LP-TSOP-28PIN
ATMEL	AT28C16E(DIP24)	EEPROM	NONE
ATMEL	AT28C16E(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28C16E(SOIC24)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28C17(DIP28)	EEPROM	NONE
ATMEL	AT28C17(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28C17(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28C17E(DIP28)	EEPROM	NONE
ATMEL	AT28C17E(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28C17E(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28C256(DIP28)	EEPROM	NONE
ATMEL	AT28C256(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28C256(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28C256(TSOP28)	EEPROM	LP-TSOP-28PIN
ATMEL	AT28C256E(DIP28)	EEPROM	NONE
ATMEL	AT28C256E(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28C256E(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28C256E(TSOP28)	EEPROM	LP-TSOP-28PIN
ATMEL	AT28C256F(DIP28)	EEPROM	NONE
ATMEL	AT28C256F(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28C256F(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28C256F(TSOP28)	EEPROM	LP-TSOP-28PIN
ATMEL	AT28C64(DIP28)	EEPROM	NONE
ATMEL	AT28C64(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28C64(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28C64(TSOP28)	EEPROM	LP-TSOP-28PIN
ATMEL	AT28C64B(DIP28)	EEPROM	NONE
ATMEL	AT28C64B(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28C64B(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28C64B(TSOP28)	EEPROM	LP-TSOP-28PIN
ATMEL	AT28C64E(DIP28)	EEPROM	NONE
ATMEL	AT28C64E(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28C64E(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)

Manufacturer	Parts Number	Type	ADAPTER
ATMEL	AT28C64E(TSOP28)	EEPROM	LP-TSOP-28PIN
ATMEL	AT28C64X(DIP28)	EEPROM	NONE
ATMEL	AT28C64X(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28C64X(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28C64X(TSOP28)	EEPROM	LP-TSOP-28PIN
ATMEL	AT28HC256(DIP28)	EEPROM	NONE
ATMEL	AT28HC256(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28HC256(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28HC256(TSOP28)	EEPROM	LP-TSOP-28PIN
ATMEL	AT28HC256E(DIP28)	EEPROM	NONE
ATMEL	AT28HC256E(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28HC256E(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28HC256E(TSOP28)	EEPROM	LP-TSOP-28PIN
ATMEL	AT28HC256F(DIP28)	EEPROM	NONE
ATMEL	AT28HC256F(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28HC256F(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28HC256F(TSOP28)	EEPROM	LP-TSOP-28PIN
ATMEL	AT28HC256N(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28HC64(DIP28)	EEPROM	NONE
ATMEL	AT28HC64(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28HC64(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28HC64(TSOP28)	EEPROM	LP-TSOP-28PIN
ATMEL	AT28HC64B(DIP28)	EEPROM	NONE
ATMEL	AT28HC64B(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28HC64B(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28HC64B(TSOP28)	EEPROM	LP-TSOP-28PIN
ATMEL	AT28LV010(DIP32)	EEPROM	NONE
ATMEL	AT28LV010(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28LV010(TSOP32)	EEPROM	LP48-TSOP-32S
ATMEL	AT28LV256(DIP28)	EEPROM	NONE
ATMEL	AT28LV256(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28LV256(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28LV256(TSOP28)	EEPROM	LP-TSOP-28PIN
ATMEL	AT28LV64(DIP28)	EEPROM	NONE
ATMEL	AT28LV64(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28LV64(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28LV64(TSOP28)	EEPROM	LP-TSOP-28PIN
ATMEL	AT28LV64B(DIP28)	EEPROM	NONE
ATMEL	AT28LV64B(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28LV64B(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ATMEL	AT28LV64B(TSOP28)	EEPROM	LP-TSOP-28PIN
ATMEL	AT28MC010(DIP32)	EEPROM	NONE
ATMEL	AT28MC020(DIP32)	EEPROM	NONE
ATMEL	AT28MC040(DIP32)	EEPROM	NONE
ATMEL	AT28PC64(DIP28)	EEPROM	NONE
ATMEL	AT28PC64(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT28PC64(TSOP28)	EEPROM	LP-TSOP-28PIN
ATMEL	AT29BV010A(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT29BV010A(TSOP32)	FLASH	LP48-TSOP-32S
ATMEL	AT29BV020(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT29BV020(TSOP32)	FLASH	LP48-TSOP-32S
ATMEL	AT29BV040A(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT29BV040A(TSOP32)	FLASH	LP48-TSOP-32S
ATMEL	AT29C010(DIP32)	FLASH	NONE
ATMEL	AT29C010(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT29C010(TSOP32)	FLASH	LP48-TSOP-32S
ATMEL	AT29C010A(DIP32)	FLASH	NONE
ATMEL	AT29C010A(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S

Manufacturer	Parts Number	Type	ADAPTER
ATMEL	AT29C010A(TSOP32)	FLASH	LP48-TSOP-32S
ATMEL	AT29C020(DIP32)	FLASH	NONE
ATMEL	AT29C020(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT29C020(TSOP32)	FLASH	LP48-TSOP-32S
ATMEL	AT29C040(DIP32)	FLASH	NONE
ATMEL	AT29C040(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT29C040(TSOP32)	FLASH	LP48-TSOP-32S
ATMEL	AT29C040A(DIP32)	FLASH	NONE
ATMEL	AT29C040A(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT29C040A(TSOP32)	FLASH	LP48-TSOP-32S
ATMEL	AT29C256(DIP28)	FLASH	NONE
ATMEL	AT29C256(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT29C256(TSOP28)	FLASH	LP-TSOP-28PIN
ATMEL	AT29C512(DIP32)	FLASH	NONE
ATMEL	AT29C512(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT29C512(TSOP32)	FLASH	LP48-TSOP-32S
ATMEL	AT29LV010A(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT29LV010A(TSOP32)	FLASH	LP48-TSOP-32S
ATMEL	AT29LV020(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT29LV020(TSOP32)	FLASH	LP48-TSOP-32S
ATMEL	AT29LV040A(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT29LV040A(TSOP32)	FLASH	LP48-TSOP-32S
ATMEL	AT29LV256(DIP28)	FLASH	NONE
ATMEL	AT29LV256(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT29LV256(TSOP28)	FLASH	LP-TSOP-28PIN
ATMEL	AT29LV512(DIP32)	FLASH	NONE
ATMEL	AT29LV512(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
ATMEL	AT29LV512(TSOP32)	FLASH	LP48-TSOP-32S
ATMEL	AT34C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT34C02B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT34C02C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT45BCM021D(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ATMEL	AT45BCM021D-256B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ATMEL	AT45DB011D(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ATMEL	AT45DB011D(UDFN8)	FLASH	LP48-WSON8-5x6
ATMEL	AT45DB011D-256B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ATMEL	AT45DB011D-256B(UDFN8)	FLASH	LP48-WSON8-5x6
ATMEL	AT45DB021D(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ATMEL	AT45DB021D(UDFN8)	FLASH	LP48-WSON8-5x6
ATMEL	AT45DB021D-256B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ATMEL	AT45DB021D-256B(UDFN8)	FLASH	LP48-WSON8-5x6
ATMEL	AT45DB041D(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ATMEL	AT45DB041D(UDFN8)	FLASH	LP48-WSON8-5x6
ATMEL	AT45DB041D-256B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ATMEL	AT45DB041D-256B(UDFN8)	FLASH	LP48-WSON8-5x6
ATMEL	AT45DB081D(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ATMEL	AT45DB081D(VDFN8)	FLASH	LP48-WSON8-5x6
ATMEL	AT45DB081D-256B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ATMEL	AT45DB081D-256B(VDFN8)	FLASH	LP48-WSON8-5x6
ATMEL	AT45DB161D(MLF8)	FLASH	LP48-WSON8-5x6
ATMEL	AT45DB161D(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ATMEL	AT45DB161D-512B(MLF8)	FLASH	LP48-WSON8-5x6
ATMEL	AT45DB161D-512B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ATMEL	AT45DB321D(MLF8)	FLASH	LP48-WSON8-5x6
ATMEL	AT45DB321D(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ATMEL	AT45DB321D-512B(MLF8)	FLASH	LP48-WSON8-5x6
ATMEL	AT45DB321D-512B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ATMEL	AT45DB321D-V2(MLF8)	FLASH	LP48-WSON8-5x6

Manufacturer	Parts Number	Type	ADAPTER
ATMEL	AT45DB321D-V2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ATMEL	AT45DB321D-V2-512B(MLF8)	FLASH	LP48-WSON8-5x6
ATMEL	AT45DB321D-V2-512B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ATMEL	AT49BV160D(TSOP48)	FLASH	LP-TSOP-48S
ATMEL	AT49BV160DT(TSOP48)	FLASH	LP-TSOP-48S
ATMEL	AT49BV322A(TSOP48)	FLASH	LP-TSOP-48S
ATMEL	AT49BV322AT(TSOP48)	FLASH	LP-TSOP-48S
ATMEL	AT49BV322D(TSOP48)	FLASH	LP-TSOP-48S
ATMEL	AT49BV322DT(TSOP48)	FLASH	LP-TSOP-48S
ATMEL	AT49BV4096(TSOP48)	FLASH	LP-TSOP-48S
ATMEL	AT49BV802A(TSOP48)	FLASH	LP-TSOP-48S
ATMEL	AT49BV802AT(TSOP48)	FLASH	LP-TSOP-48S
ATMEL	AT49F1025(PLCC44)	FLASH	LP48-PLCC-44PIN
ATMEL	AT88SC0104C(DIP8)	EEPROM	NONE
ATMEL	AT88SC0104C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT88SC0104CA(DIP8)	EEPROM	NONE
ATMEL	AT88SC0104CA(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT88SC0104CA(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT88SC0204C(DIP8)	EEPROM	NONE
ATMEL	AT88SC0204C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT88SC0204CA(DIP8)	EEPROM	NONE
ATMEL	AT88SC0204CA(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT88SC0204CA(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT88SC0404C(DIP8)	EEPROM	NONE
ATMEL	AT88SC0404C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT88SC0404CA(DIP8)	EEPROM	NONE
ATMEL	AT88SC0404CA(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT88SC0404CA(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT88SC0808C(DIP8)	EEPROM	NONE
ATMEL	AT88SC0808C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT88SC0808CA(DIP8)	EEPROM	NONE
ATMEL	AT88SC0808CA(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT88SC0808CA(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT88SC12816C(DIP8)	EEPROM	NONE
ATMEL	AT88SC12816C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT88SC1616C(DIP8)	EEPROM	NONE
ATMEL	AT88SC1616C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT88SC25616C(DIP8)	EEPROM	NONE
ATMEL	AT88SC25616C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT88SC3216C(DIP8)	EEPROM	NONE
ATMEL	AT88SC3216C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT88SC6416C(DIP8)	EEPROM	NONE
ATMEL	AT88SC6416C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT89C1051(DIP20)	MPU / MCU	NONE
ATMEL	AT89C1051(SOP20)	MPU / MCU	LP-SOP-20PIN(300mil) or LP-SOP-28PIN-B(300mil)
ATMEL	AT89C1051U(DIP20)	MPU / MCU	NONE
ATMEL	AT89C1051U(SOP20)	MPU / MCU	LP-SOP-20PIN(300mil) or LP-SOP-28PIN-B(300mil)
ATMEL	AT89C2051(DIP20)	MPU / MCU	NONE
ATMEL	AT89C2051(SOP20)	MPU / MCU	LP-SOP-20PIN(300mil) or LP-SOP-28PIN-B(300mil)
ATMEL	AT89C2051x2(DIP20)	MPU / MCU	NONE
ATMEL	AT89C2051x2(SOP20)	MPU / MCU	LP-SOP-20PIN(300mil) or LP-SOP-28PIN-B(300mil)
ATMEL	AT89C4051(DIP20)	MPU / MCU	NONE
ATMEL	AT89C4051(SOP20)	MPU / MCU	LP-SOP-20PIN(300mil) or LP-SOP-28PIN-B(300mil)
ATMEL	AT89C51(DIP40)	MPU / MCU	NONE
ATMEL	AT89C51(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT89C51(QFP44)	MPU / MCU	LP48-VQFP-44S
ATMEL	AT89C51ED2(DIP40)	MPU / MCU	NONE
ATMEL	AT89C51ED2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S

Manufacturer	Parts Number	Type	ADAPTER
ATMEL	AT89C51ED2(VQFP44)	MPU / MCU	LP48-VQFP-44S
ATMEL	AT89C51ID2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT89C51ID2(VQFP44)	MPU / MCU	LP48-VQFP-44S
ATMEL	AT89C51RC(DIP40)	MPU / MCU	NONE
ATMEL	AT89C51RC(PLCC44)	MPU / MCU	LP-48-PLCC-44PIN or LP-48-PLCC-44S
ATMEL	AT89C51RC(TQFP44)	MPU / MCU	LP48-VQFP-44S
ATMEL	AT89C51RD2(DIP40)	MPU / MCU	NONE
ATMEL	AT89C51RD2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT89C51RD2(VQFP44)	MPU / MCU	LP48-VQFP-44S
ATMEL	AT89C52(DIP40)	MPU / MCU	NONE
ATMEL	AT89C52(PLCC44)	MPU / MCU	LP-48-PLCC-44PIN or LP-48-PLCC-44S
ATMEL	AT89C52(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	AT89C52(TQFP44)	MPU / MCU	LP48-VQFP-44S
ATMEL	AT89C55(DIP40)	MPU / MCU	NONE
ATMEL	AT89C55(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT89C55(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	AT89C55(TQFP44)	MPU / MCU	LP48-VQFP-44S
ATMEL	AT89C55WD(DIP40)	MPU / MCU	NONE
ATMEL	AT89C55WD(PLCC44)	MPU / MCU	LP-48-PLCC-44PIN or LP-48-PLCC-44S
ATMEL	AT89C55WD(TQFP44)	MPU / MCU	LP48-VQFP-44S
ATMEL	AT89LS51(DIP40)	MPU / MCU	NONE
ATMEL	AT89LS51(PLCC44)	MPU / MCU	LP-48-PLCC-44PIN or LP-48-PLCC-44S
ATMEL	AT89LS51(TQFP44)	MPU / MCU	LP48-VQFP-44S
ATMEL	AT89LS52(DIP40)	MPU / MCU	NONE
ATMEL	AT89LS52(PLCC44)	MPU / MCU	LP-48-PLCC-44PIN or LP-48-PLCC-44S
ATMEL	AT89LS52(TQFP44)	MPU / MCU	LP48-VQFP-44S
ATMEL	AT89LS53(DIP40)	MPU / MCU	NONE
ATMEL	AT89LS53(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT89LS53(TQFP44)	MPU / MCU	LP48-VQFP-44S
ATMEL	AT89LV51(DIP40)	MPU / MCU	NONE
ATMEL	AT89LV51(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT89LV51(TQFP44)	MPU / MCU	LP48-VQFP-44S
ATMEL	AT89LV52(DIP40)	MPU / MCU	NONE
ATMEL	AT89LV52(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT89LV52(TQFP44)	MPU / MCU	LP48-VQFP-44S
ATMEL	AT89S51(DIP40)	MPU / MCU	NONE
ATMEL	AT89S51(PDIP42)	MPU / MCU	NONE
ATMEL	AT89S51(PLCC44)	MPU / MCU	LP-48-PLCC-44PIN or LP-48-PLCC-44S
ATMEL	AT89S51(TQFP44)	MPU / MCU	LP48-VQFP-44S
ATMEL	AT89S52(DIP40)	MPU / MCU	NONE
ATMEL	AT89S52(PDIP42)	MPU / MCU	NONE
ATMEL	AT89S52(PLCC44)	MPU / MCU	LP-48-PLCC-44PIN or LP-48-PLCC-44S
ATMEL	AT89S52(TQFP44)	MPU / MCU	LP48-VQFP-44S
ATMEL	AT89S53(DIP40)	MPU / MCU	NONE
ATMEL	AT89S53(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	AT89S53(TQFP44)	MPU / MCU	LP48-VQFP-44S
ATMEL	AT90PWM1(SOP24)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ATMEL	AT90PWM2(SOP24)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ATMEL	AT90PWM216(SOP24)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ATMEL	AT90PWM2B(SOP24)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ATMEL	AT93C46-X16(DIP8)	EEPROM	NONE
ATMEL	AT93C46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ATMEL	AT93C46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT93C46-X8(DIP8)	EEPROM	NONE
ATMEL	AT93C46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ATMEL	AT93C46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT93C46A(DIP8)	EEPROM	NONE
ATMEL	AT93C46A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
ATMEL	AT93C46A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT93C46B(DIP8)	EEPROM	NONE
ATMEL	AT93C46B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT93C46C(DIP8)	EEPROM	NONE
ATMEL	AT93C46C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT93C46D-X16(DIP8)	EEPROM	NONE
ATMEL	AT93C46D-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT93C46D-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT93C46D-X8(DIP8)	EEPROM	NONE
ATMEL	AT93C46D-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT93C46D-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT93C46E(DIP8)	EEPROM	NONE
ATMEL	AT93C46E(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT93C46E(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT93C46R-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT93C46R-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT93C56-X16(DIP8)	EEPROM	NONE
ATMEL	AT93C56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ATMEL	AT93C56-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT93C56-X8(DIP8)	EEPROM	NONE
ATMEL	AT93C56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ATMEL	AT93C56-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT93C56A-X16(DIP8)	EEPROM	NONE
ATMEL	AT93C56A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT93C56A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT93C56A-X8(DIP8)	EEPROM	NONE
ATMEL	AT93C56A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT93C56A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT93C56AW-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ATMEL	AT93C56AW-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ATMEL	AT93C57-X16(DIP8)	EEPROM	NONE
ATMEL	AT93C57-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ATMEL	AT93C57-X8(DIP8)	EEPROM	NONE
ATMEL	AT93C57-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ATMEL	AT93C66-X16(DIP8)	EEPROM	NONE
ATMEL	AT93C66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ATMEL	AT93C66-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT93C66-X8(DIP8)	EEPROM	NONE
ATMEL	AT93C66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ATMEL	AT93C66-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT93C66A-X16(DIP8)	EEPROM	NONE
ATMEL	AT93C66A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT93C66A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT93C66A-X8(DIP8)	EEPROM	NONE
ATMEL	AT93C66A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT93C66A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT93C66AW-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ATMEL	AT93C66AW-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ATMEL	AT93C86-X16(DIP8)	EEPROM	NONE
ATMEL	AT93C86-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT93C86-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT93C86-X8(DIP8)	EEPROM	NONE
ATMEL	AT93C86-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT93C86-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT93C86A-X16(DIP8)	EEPROM	NONE
ATMEL	AT93C86A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT93C86A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	AT93C86A-X8(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
ATMEL	AT93C86A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ATMEL	AT93C86A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ATMEL	ATmega1284(DIP40)	MPU / MCU	NONE
ATMEL	ATmega1284(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega1284P(DIP40)	MPU / MCU	NONE
ATMEL	ATmega1284P(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega16(DIP40)	MPU / MCU	NONE
ATMEL	ATmega16(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega161(DIP40)	MPU / MCU	NONE
ATMEL	ATmega161(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	ATmega161(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega161L(DIP40)	MPU / MCU	NONE
ATMEL	ATmega161L(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
ATMEL	ATmega161L(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega162(DIP40)	MPU / MCU	NONE
ATMEL	ATmega162(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega162L(DIP40)	MPU / MCU	NONE
ATMEL	ATmega162L(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega162V(DIP40)	MPU / MCU	NONE
ATMEL	ATmega162V(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega163(DIP40)	MPU / MCU	NONE
ATMEL	ATmega163(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega163L(DIP40)	MPU / MCU	NONE
ATMEL	ATmega163L(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega164(DIP40)	MPU / MCU	NONE
ATMEL	ATmega164(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega164A(DIP40)	MPU / MCU	NONE
ATMEL	ATmega164A(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega164P(DIP40)	MPU / MCU	NONE
ATMEL	ATmega164P(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega164PA(DIP40)	MPU / MCU	NONE
ATMEL	ATmega164PA(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega164PV(DIP40)	MPU / MCU	NONE
ATMEL	ATmega164PV(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega164V(DIP40)	MPU / MCU	NONE
ATMEL	ATmega164V(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega168PA(DIP28)	MPU / MCU	NONE
ATMEL	ATmega168PA(MLF32)	MPU / MCU	LP-QFN-32PIN
ATMEL	ATmega168PA(TQFP32)	MPU / MCU	LP-TQFP32
ATMEL	ATmega16A(DIP40)	MPU / MCU	NONE
ATMEL	ATmega16A(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega16L(DIP40)	MPU / MCU	NONE
ATMEL	ATmega16L(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega32(DIP40)	MPU / MCU	NONE
ATMEL	ATmega32(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega323(DIP40)	MPU / MCU	NONE
ATMEL	ATmega323(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega323L(DIP40)	MPU / MCU	NONE
ATMEL	ATmega323L(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega324(DIP40)	MPU / MCU	NONE
ATMEL	ATmega324(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega324A(DIP40)	MPU / MCU	NONE
ATMEL	ATmega324A(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega324P(DIP40)	MPU / MCU	NONE
ATMEL	ATmega324P(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega324PA(DIP40)	MPU / MCU	NONE
ATMEL	ATmega324PA(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega324PV(DIP40)	MPU / MCU	NONE

Manufacturer	Parts Number	Type	ADAPTER
ATMEL	ATmega324PV(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega324V(DIP40)	MPU / MCU	NONE
ATMEL	ATmega324V(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega328P(DIP28)	MPU / MCU	NONE
ATMEL	ATmega328P(MLF32)	MPU / MCU	LP-QFN-32PIN
ATMEL	ATmega328P(TQFP32)	MPU / MCU	LP-TQFP32
ATMEL	ATmega32A(DIP40)	MPU / MCU	NONE
ATMEL	ATmega32A(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega32L(DIP40)	MPU / MCU	NONE
ATMEL	ATmega32L(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega48PA(DIP28)	MPU / MCU	NONE
ATMEL	ATmega48PA(MLF32)	MPU / MCU	LP-QFN-32PIN
ATMEL	ATmega48PA(TQFP32)	MPU / MCU	LP-TQFP32
ATMEL	ATmega644(DIP40)	MPU / MCU	NONE
ATMEL	ATmega644(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega644A(DIP40)	MPU / MCU	NONE
ATMEL	ATmega644A(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega644P(DIP40)	MPU / MCU	NONE
ATMEL	ATmega644P(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega644PA(DIP40)	MPU / MCU	NONE
ATMEL	ATmega644PA(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega644PV(DIP40)	MPU / MCU	NONE
ATMEL	ATmega644PV(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega644V(DIP40)	MPU / MCU	NONE
ATMEL	ATmega644V(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
ATMEL	ATmega8(DIP28)	MPU / MCU	NONE
ATMEL	ATmega8(MLF32)	MPU / MCU	LP-QFN-32PIN
ATMEL	ATmega8(TQFP32)	MPU / MCU	LP-TQFP32
ATMEL	ATmega88PA(DIP28)	MPU / MCU	NONE
ATMEL	ATmega88PA(MLF32)	MPU / MCU	LP-QFN-32PIN
ATMEL	ATmega88PA(TQFP32)	MPU / MCU	LP-TQFP32
ATMEL	ATmega8A(DIP28)	MPU / MCU	NONE
ATMEL	ATmega8A(MLF32)	MPU / MCU	LP-QFN-32PIN
ATMEL	ATmega8A(TQFP32)	MPU / MCU	LP-TQFP32
ATMEL	ATmega8L(DIP28)	MPU / MCU	NONE
ATMEL	ATmega8L(MLF32)	MPU / MCU	LP-QFN-32PIN
ATMEL	ATmega8L(TQFP32)	MPU / MCU	LP-TQFP32
ATMEL	ATtiny11(DIP8)	MPU / MCU	NONE
ATMEL	ATtiny11(SOP8)	MPU / MCU	LP-SOP-8PIN-B(207mil)
ATMEL	ATtiny11L(DIP8)	MPU / MCU	NONE
ATMEL	ATtiny11L(SOP8)	MPU / MCU	LP-SOP-8PIN-B(207mil)
ATMEL	ATtiny12(DIP8)	MPU / MCU	NONE
ATMEL	ATtiny12(SOP8)	MPU / MCU	LP-SOP-8PIN-B(207mil)
ATMEL	ATtiny12L(DIP8)	MPU / MCU	NONE
ATMEL	ATtiny12L(SOP8)	MPU / MCU	LP-SOP-8PIN-B(207mil)
ATMEL	ATtiny12V(DIP8)	MPU / MCU	NONE
ATMEL	ATtiny12V(SOP8)	MPU / MCU	LP-SOP-8PIN-B(207mil)
ATMEL	ATtiny13(DIP8)	MPU / MCU	NONE
ATMEL	ATtiny13(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
ATMEL	ATtiny13A(DIP8)	MPU / MCU	NONE
ATMEL	ATtiny13A(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
ATMEL	ATtiny13V(DIP8)	MPU / MCU	NONE
ATMEL	ATtiny13V(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
ATMEL	ATtiny15L(DIP8)	MPU / MCU	NONE
ATMEL	ATtiny15L(SOP8)	MPU / MCU	LP-SOP-8PIN-B(207mil)
ATMEL	ATtiny1634(MLF20)	MPU / MCU	LP-QFN-20PIN-4x4
ATMEL	ATtiny1634(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ATMEL	ATtiny2313(DIP20)	MPU / MCU	NONE

Manufacturer	Parts Number	Type	ADAPTER
ATMEL	ATtiny2313(MLF20)	MPU / MCU	LP-QFN-20PIN-4x4
ATMEL	ATtiny2313(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ATMEL	ATtiny24A(DIP14)	MPU / MCU	NONE
ATMEL	ATtiny24A(QFN20)	MPU / MCU	LP-QFN-20PIN-4x4
ATMEL	ATtiny24A(SOP14)	MPU / MCU	LP-SOP-16PIN(150mil)
ATMEL	ATtiny25(DIP8)	MPU / MCU	NONE
ATMEL	ATtiny25(SOP8-150)	MPU / MCU	LP-SOP-16PIN(150mil)
ATMEL	ATtiny25(SOP8-207)	MPU / MCU	LP-SOP-8PIN-B(207mil)
ATMEL	ATtiny25V(DIP8)	MPU / MCU	NONE
ATMEL	ATtiny25V(SOP8-150)	MPU / MCU	LP-SOP-16PIN(150mil)
ATMEL	ATtiny25V(SOP8-207)	MPU / MCU	LP-SOP-8PIN-B(207mil)
ATMEL	ATtiny44A(DIP14)	MPU / MCU	NONE
ATMEL	ATtiny44A(QFN20)	MPU / MCU	LP-QFN-20PIN-4x4
ATMEL	ATtiny44A(SOP14)	MPU / MCU	LP-SOP-16PIN(150mil)
ATMEL	ATtiny45(DIP8)	MPU / MCU	NONE
ATMEL	ATtiny45(SOP8-150)	MPU / MCU	LP-SOP-16PIN(150mil)
ATMEL	ATtiny45(SOP8-207)	MPU / MCU	LP-SOP-8PIN-B(207mil)
ATMEL	ATtiny45V(DIP8)	MPU / MCU	NONE
ATMEL	ATtiny45V(SOP8-150)	MPU / MCU	LP-SOP-16PIN(150mil)
ATMEL	ATtiny45V(SOP8-207)	MPU / MCU	LP-SOP-8PIN-B(207mil)
ATMEL	ATTINY461A(DIP20)	MPU / MCU	NONE
ATMEL	ATTINY461A(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
ATMEL	ATTINY461A(TSSOP20)	MPU / MCU	LP-TSSOP-20PIN
ATMEL	ATtiny828(MLF32)	MPU / MCU	LP-TQFP32
ATMEL	ATtiny828(TQFP32)	MPU / MCU	LP-TQFP32
ATMEL	ATtiny84A(DIP14)	MPU / MCU	NONE
ATMEL	ATtiny84A(QFN20)	MPU / MCU	LP-QFN-20PIN-4x4
ATMEL	ATtiny84A(SOP14)	MPU / MCU	LP-SOP-16PIN(150mil)
ATMEL	ATtiny85(DIP8)	MPU / MCU	NONE
ATMEL	ATtiny85(SOP8-150)	MPU / MCU	LP-SOP-16PIN(150mil)
ATMEL	ATtiny85(SOP8-207)	MPU / MCU	LP-SOP-8PIN-B(207mil)
ATMEL	ATtiny85V(DIP8)	MPU / MCU	NONE
ATMEL	ATtiny85V(SOP8-150)	MPU / MCU	LP-SOP-16PIN(150mil)
ATMEL	ATtiny85V(SOP8-207)	MPU / MCU	LP-SOP-8PIN-B(207mil)
ATO	ATO25Q16-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ATO	ATO25Q16-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ATO	ATO25Q16-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ATO	ATO25Q16-V(VDFN8)	FLASH	LP48-WSON8-5x6
Belling	BL24C02(DIP8)	EEPROM	NONE
Belling	BL24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Belling	BL24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Belling	BL24C04(DIP8)	EEPROM	NONE
Belling	BL24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Belling	BL24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Belling	BL24C08(DIP8)	EEPROM	NONE
Belling	BL24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Belling	BL24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Belling	BL24C128(DIP8)	EEPROM	NONE
Belling	BL24C128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Belling	BL24C128(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Belling	BL24C16(DIP8)	EEPROM	NONE
Belling	BL24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Belling	BL24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Belling	BL24C256(DIP8)	EEPROM	NONE
Belling	BL24C256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Belling	BL24C256(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Belling	BL24C32(DIP8)	EEPROM	NONE
Belling	BL24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
Belling	BL24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Belling	BL24C64(DIP8)	EEPROM	NONE
Belling	BL24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Belling	BL24C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Belling	BL93C46-X16(DIP8)	EEPROM	NONE
Belling	BL93C46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Belling	BL93C46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Belling	BL93C46-X8(DIP8)	EEPROM	NONE
Belling	BL93C46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Belling	BL93C46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Belling	BL93C56-X16(DIP8)	EEPROM	NONE
Belling	BL93C56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Belling	BL93C56-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Belling	BL93C56-X8(DIP8)	EEPROM	NONE
Belling	BL93C56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Belling	BL93C56-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Belling	BL93C66-X16(DIP8)	EEPROM	NONE
Belling	BL93C66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Belling	BL93C66-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Belling	BL93C66-X8(DIP8)	EEPROM	NONE
Belling	BL93C66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Belling	BL93C66-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
BENCHMARQ	bq4010(DIP28)	NV RAM	NONE
BENCHMARQ	bq4822YMA(DIP28)	NV RAM	NONE
BJX	BJX24LC02(DIP8)	EEPROM	NONE
BJX	BJX24LC02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
BJX	BJX24LC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
BJX	BJX24LC04(DIP8)	EEPROM	NONE
BJX	BJX24LC04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
BJX	BJX24LC04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
BJX	BJX24LC08(DIP8)	EEPROM	NONE
BJX	BJX24LC08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
BJX	BJX24LC08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
BJX	BJX24LC16(DIP8)	EEPROM	NONE
BJX	BJX24LC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
BJX	BJX24LC16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Bookly Micro	24C02(DIP8)	EEPROM	NONE
Bookly Micro	24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Bookly Micro	24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Bookly Micro	24C04(DIP8)	EEPROM	NONE
Bookly Micro	24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Bookly Micro	24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Bookly Micro	24C08(DIP8)	EEPROM	NONE
Bookly Micro	24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Bookly Micro	24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Bookly Micro	24C16(DIP8)	EEPROM	NONE
Bookly Micro	24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Bookly Micro	24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Bookly Micro	24C32(DIP8)	EEPROM	NONE
Bookly Micro	24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Bookly Micro	24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Bookly Micro	24C64(DIP8)	EEPROM	NONE
Bookly Micro	24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Bookly Micro	24C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT1021(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT1022(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT1023(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT1024(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
CATALYST	CAT1024(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT1024(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT1025(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT1026(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT1027(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24AA01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24AA02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24AA04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24AA08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24AA16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24AC128(DIP8)	EEPROM	NONE
CATALYST	CAT24AC128(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CATALYST	CAT24C00(DIP8)	EEPROM	NONE
CATALYST	CAT24C00(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24C00(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24C01(DIP8)	EEPROM	NONE
CATALYST	CAT24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24C01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24C01B(DIP8)	EEPROM	NONE
CATALYST	CAT24C01B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24C01B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24C02(DIP8)	EEPROM	NONE
CATALYST	CAT24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24C021(DIP8)	EEPROM	NONE
CATALYST	CAT24C022(DIP8)	EEPROM	NONE
CATALYST	CAT24C023(DIP8)	EEPROM	NONE
CATALYST	CAT24C02A(DIP8)	EEPROM	NONE
CATALYST	CAT24C02A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24C02AI(DIP8)	EEPROM	NONE
CATALYST	CAT24C02AI(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24C03(DIP8)	EEPROM	NONE
CATALYST	CAT24C03(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24C03(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24C04(DIP8)	EEPROM	NONE
CATALYST	CAT24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24C041(DIP8)	EEPROM	NONE
CATALYST	CAT24C042(DIP8)	EEPROM	NONE
CATALYST	CAT24C043(DIP8)	EEPROM	NONE
CATALYST	CAT24C05(DIP8)	EEPROM	NONE
CATALYST	CAT24C05(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24C05(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24C08(DIP8)	EEPROM	NONE
CATALYST	CAT24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24C081(DIP8)	EEPROM	NONE
CATALYST	CAT24C082(DIP8)	EEPROM	NONE
CATALYST	CAT24C083(DIP8)	EEPROM	NONE
CATALYST	CAT24C128(DIP8)	EEPROM	NONE
CATALYST	CAT24C128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24C128(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24C16(DIP8)	EEPROM	NONE
CATALYST	CAT24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24C161(DIP8)	EEPROM	NONE
CATALYST	CAT24C162(DIP8)	EEPROM	NONE
CATALYST	CAT24C163(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
CATALYST	CAT24C164(DIP8)	EEPROM	NONE
CATALYST	CAT24C164(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24C164(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24C16I(DIP8)	EEPROM	NONE
CATALYST	CAT24C16Z(DIP8)	EEPROM	NONE
CATALYST	CAT24C208W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24C256(DIP8)	EEPROM	NONE
CATALYST	CAT24C256(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CATALYST	CAT24C256(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24C32(DIP8)	EEPROM	NONE
CATALYST	CAT24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24C32I(DIP8)	EEPROM	NONE
CATALYST	CAT24C32I(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24C32I(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24C322(DIP8)	EEPROM	NONE
CATALYST	CAT24C322(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24C322(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24C323(DIP8)	EEPROM	NONE
CATALYST	CAT24C323(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24C323(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24C32Z(DIP8)	EEPROM	NONE
CATALYST	CAT24C64(DIP8)	EEPROM	NONE
CATALYST	CAT24C64(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CATALYST	CAT24C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24C64I(DIP8)	EEPROM	NONE
CATALYST	CAT24C64I(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CATALYST	CAT24C64I(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24C642(DIP8)	EEPROM	NONE
CATALYST	CAT24C642(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CATALYST	CAT24C642(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24C643(DIP8)	EEPROM	NONE
CATALYST	CAT24C643(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CATALYST	CAT24C643(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24FC01(DIP8)	EEPROM	NONE
CATALYST	CAT24FC01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24FC01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24FC02(DIP8)	EEPROM	NONE
CATALYST	CAT24FC02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24FC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24FC16(DIP8)	EEPROM	NONE
CATALYST	CAT24FC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24FC16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24FC17(DIP8)	EEPROM	NONE
CATALYST	CAT24FC17(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24FC17(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24FC256(DIP8)	EEPROM	NONE
CATALYST	CAT24FC256(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CATALYST	CAT24FC32(DIP8)	EEPROM	NONE
CATALYST	CAT24FC32(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CATALYST	CAT24FC32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24FC32A(DIP8)	EEPROM	NONE
CATALYST	CAT24FC32A(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CATALYST	CAT24FC32A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24FC512(DIP8)	EEPROM	NONE
CATALYST	CAT24FC512W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CATALYST	CAT24FC512X(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CATALYST	CAT24FC64(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
CATALYST	CAT24FC64(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CATALYST	CAT24FC64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24FC65(DIP8)	EEPROM	NONE
CATALYST	CAT24FC65(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CATALYST	CAT24FC65(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24FC66(DIP8)	EEPROM	NONE
CATALYST	CAT24FC66(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CATALYST	CAT24FC66(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24LC02(DIP8)	EEPROM	NONE
CATALYST	CAT24LC02A(DIP8)	EEPROM	NONE
CATALYST	CAT24LC02AZ(DIP8)	EEPROM	NONE
CATALYST	CAT24LC02I(DIP8)	EEPROM	NONE
CATALYST	CAT24LC02Z(DIP8)	EEPROM	NONE
CATALYST	CAT24LC04(DIP8)	EEPROM	NONE
CATALYST	CAT24LC04I(DIP8)	EEPROM	NONE
CATALYST	CAT24LC04Z(DIP8)	EEPROM	NONE
CATALYST	CAT24LC08(DIP8)	EEPROM	NONE
CATALYST	CAT24LC08I(DIP8)	EEPROM	NONE
CATALYST	CAT24LC08Z(DIP8)	EEPROM	NONE
CATALYST	CAT24LC16(DIP8)	EEPROM	NONE
CATALYST	CAT24LC16I(DIP8)	EEPROM	NONE
CATALYST	CAT24LC16Z(DIP8)	EEPROM	NONE
CATALYST	CAT24WC01(DIP8)	EEPROM	NONE
CATALYST	CAT24WC01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24WC01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24WC02(DIP8)	EEPROM	NONE
CATALYST	CAT24WC02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24WC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24WC03(DIP8)	EEPROM	NONE
CATALYST	CAT24WC03(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24WC03(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24WC04(DIP8)	EEPROM	NONE
CATALYST	CAT24WC04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24WC04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24WC05(DIP8)	EEPROM	NONE
CATALYST	CAT24WC05(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24WC05(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24WC08(DIP8)	EEPROM	NONE
CATALYST	CAT24WC08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24WC08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24WC09(DIP8)	EEPROM	NONE
CATALYST	CAT24WC09(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24WC09(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24WC128(DIP8)	EEPROM	NONE
CATALYST	CAT24WC128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24WC129(DIP8)	EEPROM	NONE
CATALYST	CAT24WC129(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24WC16(DIP8)	EEPROM	NONE
CATALYST	CAT24WC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24WC16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24WC164(DIP8)	EEPROM	NONE
CATALYST	CAT24WC164(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24WC164(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24WC17(DIP8)	EEPROM	NONE
CATALYST	CAT24WC17(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24WC17(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT24WC256(DIP8)	EEPROM	NONE
CATALYST	CAT24WC256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
CATALYST	CAT24WC257(DIP8)	EEPROM	NONE
CATALYST	CAT24WC257J(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24WC32(DIP8)	EEPROM	NONE
CATALYST	CAT24WC32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24WC33(DIP8)	EEPROM	NONE
CATALYST	CAT24WC33J(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24WC64(DIP8)	EEPROM	NONE
CATALYST	CAT24WC64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24WC65(DIP8)	EEPROM	NONE
CATALYST	CAT24WC65J(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT24WC66(DIP8)	EEPROM	NONE
CATALYST	CAT24WC66W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CATALYST	CAT24WC66X(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT27010(DIP32)	EPROM	NONE
CATALYST	CAT27128A(DIP28)	EPROM	NONE
CATALYST	CAT27256(DIP28)	EPROM	NONE
CATALYST	CAT27512(DIP28)	EPROM	NONE
CATALYST	CAT27C210(DIP40)	EPROM	NONE
CATALYST	CAT27C210(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
CATALYST	CAT27C64A(DIP28)	EPROM	NONE
CATALYST	CAT27HC256(DIP28)	EPROM	NONE
CATALYST	CAT28C16A(DIP24)	EEPROM	NONE
CATALYST	CAT28C16A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CATALYST	CAT28C16A(SOIC24)	EEPROM	LP-SOP-28PIN-B(300mil)
CATALYST	CAT28C17A(DIP28)	EEPROM	NONE
CATALYST	CAT28C17A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CATALYST	CAT28C17A(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
CATALYST	CAT28C256(DIP28)	EEPROM	NONE
CATALYST	CAT28C256(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CATALYST	CAT28C256(TSOP28)	EEPROM	LP-TSOP-28PIN
CATALYST	CAT28C257(DIP28)	EEPROM	NONE
CATALYST	CAT28C257(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CATALYST	CAT28C257(TSOP28)	EEPROM	LP-TSOP-28PIN
CATALYST	CAT28C512(DIP32)	EEPROM	NONE
CATALYST	CAT28C512(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CATALYST	CAT28C512(TSOP32)	EEPROM	LP48-TSOP-32S
CATALYST	CAT28C512(TSOP40)	EEPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
CATALYST	CAT28C513(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CATALYST	CAT28C64A(DIP28)	EEPROM	NONE
CATALYST	CAT28C64A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CATALYST	CAT28C64A(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
CATALYST	CAT28C64B(DIP28)	EEPROM	NONE
CATALYST	CAT28C64B(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CATALYST	CAT28C64B(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
CATALYST	CAT28C64B(TSOP28)	EEPROM	LP-TSOP-28PIN
CATALYST	CAT28C65A(DIP28)	EEPROM	NONE
CATALYST	CAT28C65A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CATALYST	CAT28C65A(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
CATALYST	CAT28C65B(DIP28)	EEPROM	NONE
CATALYST	CAT28C65B(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CATALYST	CAT28C65B(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
CATALYST	CAT28C65B(TSOP28)	EEPROM	LP-TSOP-28PIN
CATALYST	CAT28LV256(DIP28)	EEPROM	NONE
CATALYST	CAT28LV256(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CATALYST	CAT28LV256(TSOP28)	EEPROM	LP-TSOP-28PIN
CATALYST	CAT28LV64(DIP28)	EEPROM	NONE
CATALYST	CAT28LV64(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CATALYST	CAT28LV64(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)

Manufacturer	Parts Number	Type	ADAPTER
CATALYST	CAT28LV64(TSOP28)	EEPROM	LP-TSOP-28PIN
CATALYST	CAT28LV65(DIP28)	EEPROM	NONE
CATALYST	CAT28LV65(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CATALYST	CAT28LV65(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
CATALYST	CAT28LV65(TSOP28)	EEPROM	LP-TSOP-28PIN
CATALYST	CAT34C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT34RC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT34WC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT93C46-X16(DIP8)	EEPROM	NONE
CATALYST	CAT93C46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CATALYST	CAT93C46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT93C46-X8(DIP8)	EEPROM	NONE
CATALYST	CAT93C46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CATALYST	CAT93C46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT93C46A(DIP8)	EEPROM	NONE
CATALYST	CAT93C46A(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CATALYST	CAT93C46AH(DIP8)	EEPROM	NONE
CATALYST	CAT93C46AJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT93C46B(DIP8)	EEPROM	NONE
CATALYST	CAT93C46H-X16(DIP8)	EEPROM	NONE
CATALYST	CAT93C46H-X8(DIP8)	EEPROM	NONE
CATALYST	CAT93C46R-X16(DIP8)	EEPROM	NONE
CATALYST	CAT93C46R-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CATALYST	CAT93C46R-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT93C46R-X8(DIP8)	EEPROM	NONE
CATALYST	CAT93C46R-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CATALYST	CAT93C46R-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT93C46RW-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT93C46RW-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT93C46W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT93C46W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT93C56-X16(DIP8)	EEPROM	NONE
CATALYST	CAT93C56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CATALYST	CAT93C56-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT93C56-X8(DIP8)	EEPROM	NONE
CATALYST	CAT93C56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CATALYST	CAT93C56-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT93C56A(DIP8)	EEPROM	NONE
CATALYST	CAT93C56A(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CATALYST	CAT93C56AJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT93C56W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT93C56W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT93C57-X16(DIP8)	EEPROM	NONE
CATALYST	CAT93C57-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CATALYST	CAT93C57-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT93C57-X8(DIP8)	EEPROM	NONE
CATALYST	CAT93C57-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CATALYST	CAT93C57-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT93C57W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT93C57W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT93C66-X16(DIP8)	EEPROM	NONE
CATALYST	CAT93C66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CATALYST	CAT93C66-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT93C66-X8(DIP8)	EEPROM	NONE
CATALYST	CAT93C66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CATALYST	CAT93C66-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT93C66A(DIP8)	EEPROM	NONE
CATALYST	CAT93C66A(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)

Manufacturer	Parts Number	Type	ADAPTER
CATALYST	CAT93C66W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT93C66W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT93C76-X16(DIP8)	EEPROM	NONE
CATALYST	CAT93C76-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT93C76-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT93C76-X8(DIP8)	EEPROM	NONE
CATALYST	CAT93C76-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT93C76-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT93C86-X16(DIP8)	EEPROM	NONE
CATALYST	CAT93C86-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CATALYST	CAT93C86-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT93C86-X8(DIP8)	EEPROM	NONE
CATALYST	CAT93C86-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CATALYST	CAT93C86-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT93C86A(DIP8)	EEPROM	NONE
CATALYST	CAT93C86A(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CATALYST	CAT93C86W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT93C86W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT93HC46-X16(DIP8)	EEPROM	NONE
CATALYST	CAT93HC46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT93HC46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT93HC46-X8(DIP8)	EEPROM	NONE
CATALYST	CAT93HC46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT93HC46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CATALYST	CAT93HC46J-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT93HC46J-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT93HC46W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CATALYST	CAT93HC46W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CBC Microelectr	MC24LC02(DIP8)	EEPROM	NONE
CBC Microelectr	MC24LC02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CBC Microelectr	MC24LC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CBC Microelectr	MC24LC04(DIP8)	EEPROM	NONE
CBC Microelectr	MC24LC04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CBC Microelectr	MC24LC04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CBC Microelectr	MC24LC08(DIP8)	EEPROM	NONE
CBC Microelectr	MC24LC08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CBC Microelectr	MC24LC08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CBC Microelectr	MC24LC16(DIP8)	EEPROM	NONE
CBC Microelectr	MC24LC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CBC Microelectr	MC24LC16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Ceramate Technical	24LC02(DIP8)	EEPROM	NONE
Ceramate Technical	24LC02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ceramate Technical	24LC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Ceramate Technical	24LC08(DIP8)	EEPROM	NONE
Ceramate Technical	24LC08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ceramate Technical	24LC08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Ceramate Technical	24LC16(DIP8)	EEPROM	NONE
Ceramate Technical	24LC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ceramate Technical	24LC16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Ceramate Technical	24LLC02(DIP8)	EEPROM	NONE
Ceramate Technical	24LLC02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ceramate Technical	24LLC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Ceramate Technical	24LLC08(DIP8)	EEPROM	NONE
Ceramate Technical	24LLC08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ceramate Technical	24LLC08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Ceramate Technical	24LLC16(DIP8)	EEPROM	NONE
Ceramate Technical	24LLC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ceramate Technical	24LLC16(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
Ceramate Technical	93LC46(DIP8)	EEPROM	NONE
Ceramate Technical	93LC46(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ceramate Technical	93LC46G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
cFeon	EN25B10-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25B10-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25B10T-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25B10T-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25B16-H(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25B16-Q(PDIP8)	FLASH	NONE
cFeon	EN25B16-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25B16T-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25B16T-Q(PDIP8)	FLASH	NONE
cFeon	EN25B16T-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25B20-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25B20-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25B20T-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25B20T-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25B32-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25B32T-Q(PDIP8)	FLASH	NONE
cFeon	EN25B32T-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25B40-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25B40-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25B40-Q(PDIP8)	FLASH	NONE
cFeon	EN25B40-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25B40T-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25B40T-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25B40T-Q(PDIP8)	FLASH	NONE
cFeon	EN25B40T-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25B64-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
cFeon	EN25B80-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25B80-Q(PDIP8)	FLASH	NONE
cFeon	EN25B80-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25B80T-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25B80T-Q(PDIP8)	FLASH	NONE
cFeon	EN25B80T-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25D16-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25D16-Q(PDIP8)	FLASH	NONE
cFeon	EN25D16-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25D80-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25D80-Q(PDIP8)	FLASH	NONE
cFeon	EN25D80-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25F10-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25F10-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25F16-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25F16-Q(PDIP8)	FLASH	NONE
cFeon	EN25F16-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25F20-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25F20-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25F32-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25F32-Q(PDIP8)	FLASH	NONE
cFeon	EN25F32-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25F40-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25F40-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25F40-Q(PDIP8)	FLASH	NONE
cFeon	EN25F40-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25F64-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
cFeon	EN25F64-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25F64-Q(PDIP8)	FLASH	NONE

Manufacturer	Parts Number	Type	ADAPTER
cFeon	EN25F64-W(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25F64-Y(VDFN8)	FLASH	LP48-WSON8-6x8
cFeon	EN25F80-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25F80-Q(PDIP8)	FLASH	NONE
cFeon	EN25F80-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25LF05-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25LF05-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25LF05-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25LF10-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25LF10-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25LF20-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25LF20-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25LF40-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25LF40-Q(PDIP8)	FLASH	NONE
cFeon	EN25LF40-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25M32-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25M32-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25P10-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25P10-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25P16-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
cFeon	EN25P16-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25P16-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25P20-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25P20-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25P32-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
cFeon	EN25P32-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25P32-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25P40-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25P40-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25P40-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25P64-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
cFeon	EN25P80-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25P80-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25Q128-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
cFeon	EN25Q128-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
cFeon	EN25Q128-W(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25Q128-Y(VDFN8)	FLASH	LP48-WSON8-6x8
cFeon	EN25Q16-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25Q16-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25Q16-Q(PDIP8)	FLASH	NONE
cFeon	EN25Q16-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25Q32-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25Q32-Q(PDIP8)	FLASH	NONE
cFeon	EN25Q32-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25Q32A-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25Q32A-Q(PDIP8)	FLASH	NONE
cFeon	EN25Q32A-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25Q32B-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
cFeon	EN25Q32B-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
cFeon	EN25Q32B-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25Q32B-Q(PDIP8)	FLASH	NONE
cFeon	EN25Q32B-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25Q40-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25Q40-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25Q40-Q(PDIP8)	FLASH	NONE
cFeon	EN25Q40-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25Q64-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
cFeon	EN25Q64-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)

Manufacturer	Parts Number	Type	ADAPTER
cFeon	EN25Q64-Q(PDIP8)	FLASH	NONE
cFeon	EN25Q64-W(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25Q64-Y(VDFN8)	FLASH	LP48-WSON8-6x8
cFeon	EN25Q80-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25Q80-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25Q80-Q(PDIP8)	FLASH	NONE
cFeon	EN25Q80-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25QA128-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
cFeon	EN25QA128-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
cFeon	EN25QA128-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25QA128-Q(PDIP8)	FLASH	NONE
cFeon	EN25QA16-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
cFeon	EN25QA16-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25QA32-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
cFeon	EN25QA32-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25QA32-Q(PDIP8)	FLASH	NONE
cFeon	EN25QA64-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
cFeon	EN25QA64-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25QA64-Q(PDIP8)	FLASH	NONE
cFeon	EN25QF256-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
cFeon	EN25QF256-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
cFeon	EN25QF256-Y(VDFN8)	FLASH	LP48-WSON8-6x8
cFeon	EN25QH128-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
cFeon	EN25QH128-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
cFeon	EN25QH128-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25QH128-Q(PDIP8)	FLASH	NONE
cFeon	EN25QH16-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
cFeon	EN25QH16-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
cFeon	EN25QH16-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25QH16-Q(PDIP8)	FLASH	NONE
cFeon	EN25QH16-W(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25QH256-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
cFeon	EN25QH256-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
cFeon	EN25QH256-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25QH256-Q(PDIP8)	FLASH	NONE
cFeon	EN25QH256-W(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25QH32-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
cFeon	EN25QH32-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
cFeon	EN25QH32-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25QH32-Q(PDIP8)	FLASH	NONE
cFeon	EN25QH32-W(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25QH64-BB(TFBGA24)	FLASH	LP-SOP-28PIN-B(300mil)
cFeon	EN25QH64-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
cFeon	EN25QH64-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25QH64-Q(PDIP8)	FLASH	NONE
cFeon	EN25QH64-W(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25S10-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25S10-X(VDFN8)	FLASH	LP48-MLP8-2x3
cFeon	EN25S16-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
cFeon	EN25S16-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25S16-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25S16T-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
cFeon	EN25S16T-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25S16T-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25S20-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25S20-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25S20-X(VDFN8)	FLASH	LP48-MLP8-2x3
cFeon	EN25S32-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B

Manufacturer	Parts Number	Type	ADAPTER
cFeon	EN25S32-R(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25S32-W(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25S40-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25S40-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25S40-X(VDFN8)	FLASH	LP48-MLP8-2x3
cFeon	EN25S80-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25S80-V(VDFN8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25S80A-R(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25S80A-W(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25SA10-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25SA10-X(VDFN8)	FLASH	LP48-MLP8-2x3
cFeon	EN25SF80(SOP8-150)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25T16-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25T16-Q(PDIP8)	FLASH	NONE
cFeon	EN25T16-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25T40-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
cFeon	EN25T40-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25T40-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN25T80-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
cFeon	EN25T80-V(VDFN8)	FLASH	LP48-WSON8-5x6
cFeon	EN29F001B(DIP32)	FLASH	NONE
cFeon	EN29F001B(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
cFeon	EN29F001B(TSOP32)	FLASH	LP48-TSOP-32S
cFeon	EN29F001NB(DIP32)	FLASH	NONE
cFeon	EN29F001NB(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
cFeon	EN29F001NB(TSOP32)	FLASH	LP48-TSOP-32S
cFeon	EN29F001NT(DIP32)	FLASH	NONE
cFeon	EN29F001NT(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
cFeon	EN29F001NT(TSOP32)	FLASH	LP48-TSOP-32S
cFeon	EN29F001T(DIP32)	FLASH	NONE
cFeon	EN29F001T(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
cFeon	EN29F001T(TSOP32)	FLASH	LP48-TSOP-32S
cFeon	EN29F002AB(DIP32)	FLASH	NONE
cFeon	EN29F002AB(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
cFeon	EN29F002AB(TSOP32)	FLASH	LP48-TSOP-32S
cFeon	EN29F002ANB(DIP32)	FLASH	NONE
cFeon	EN29F002ANB(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
cFeon	EN29F002ANB(TSOP32)	FLASH	LP48-TSOP-32S
cFeon	EN29F002ANT(DIP32)	FLASH	NONE
cFeon	EN29F002ANT(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
cFeon	EN29F002ANT(TSOP32)	FLASH	LP48-TSOP-32S
cFeon	EN29F002AT(DIP32)	FLASH	NONE
cFeon	EN29F002AT(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
cFeon	EN29F002AT(TSOP32)	FLASH	LP48-TSOP-32S
cFeon	EN29F002B(DIP32)	FLASH	NONE
cFeon	EN29F002B(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
cFeon	EN29F002B(TSOP32)	FLASH	LP48-TSOP-32S
cFeon	EN29F002T(DIP32)	FLASH	NONE
cFeon	EN29F002T(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
cFeon	EN29F002T(TSOP32)	FLASH	LP48-TSOP-32S
cFeon	EN29F040(DIP32)	FLASH	NONE
cFeon	EN29F040(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
cFeon	EN29F040(TSOP32)	FLASH	LP48-TSOP-32S
cFeon	EN29F040A(DIP32)	FLASH	NONE
cFeon	EN29F040A(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
cFeon	EN29F040A(TSOP32)	FLASH	LP48-TSOP-32S
cFeon	EN29F800B(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29F800T(TSOP48)	FLASH	LP-TSOP-48S

Manufacturer	Parts Number	Type	ADAPTER
cFeon	EN29GA064H(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
cFeon	EN29GA064L(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
cFeon	EN29GA128H(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
cFeon	EN29GA128L(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
cFeon	EN29GA256H(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
cFeon	EN29GA256L(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
cFeon	EN29GL064AB(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
cFeon	EN29GL064AB(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29GL064AT(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
cFeon	EN29GL064AT(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29GL064B(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29GL064B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
cFeon	EN29GL064H(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29GL064H(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
cFeon	EN29GL064H-BA(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
cFeon	EN29GL064L(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29GL064L(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
cFeon	EN29GL064L-BA(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
cFeon	EN29GL064T(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29GL064T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
cFeon	EN29GL128H(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
cFeon	EN29GL128L(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
cFeon	EN29LV040(DIP32)	FLASH	NONE
cFeon	EN29LV040(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
cFeon	EN29LV040(TSOP32 8X14)	FLASH	LP48-VSOP-32S
cFeon	EN29LV040(TSOP32 8X20)	FLASH	LP48-TSOP-32S
cFeon	EN29LV040A(DIP32)	FLASH	NONE
cFeon	EN29LV040A(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
cFeon	EN29LV040A(TSOP32 8X14)	FLASH	LP48-VSOP-32S
cFeon	EN29LV040A(TSOP32 8X20)	FLASH	LP48-TSOP-32S
cFeon	EN29LV040J(DIP32)	FLASH	NONE
cFeon	EN29LV040J(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
cFeon	EN29LV040J(TSOP32)	FLASH	LP48-VSOP-32S
cFeon	EN29LV160AB(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV160AT(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV160B(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV160BB(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV160BT(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV160CB(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
cFeon	EN29LV160CB(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV160CT(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
cFeon	EN29LV160CT(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV160JB(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV160JT(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV160T(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV320AB(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV320AT(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV320BB(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
cFeon	EN29LV320BB(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV320BT(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
cFeon	EN29LV320BT(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV320CB(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
cFeon	EN29LV320CB(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV320CT(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
cFeon	EN29LV320CT(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV400AB(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV400AT(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV400B(TSOP48)	FLASH	LP-TSOP-48S

Manufacturer	Parts Number	Type	ADAPTER
cFeon	EN29LV400T(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV640B(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV640H(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV640L(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV640T(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV641H(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV641L(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV800AB(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV800AT(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV800B(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV800BB(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV800BT(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV800CB(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
cFeon	EN29LV800CB(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV800CT(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
cFeon	EN29LV800CT(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29LV800T(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29PL032(TSOP48)	FLASH	LP-TSOP-48S
cFeon	EN29PL064(TSOP48)	FLASH	LP-TSOP-48S
Chipswinner	CW24C02(DIP8)	EEPROM	NONE
Chipswinner	CW24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Chipswinner	CW24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Chipswinner	CW24C02B(DIP8)	EEPROM	NONE
Chipswinner	CW24C02B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Chipswinner	CW24C02B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Chipswinner	CW24C02C(DIP8)	EEPROM	NONE
Chipswinner	CW24C02C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Chipswinner	CW24C02C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Chipswinner	CW24C04(DIP8)	EEPROM	NONE
Chipswinner	CW24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Chipswinner	CW24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Chipswinner	CW24C04A(DIP8)	EEPROM	NONE
Chipswinner	CW24C04A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Chipswinner	CW24C04A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Chipswinner	CW24C08(DIP8)	EEPROM	NONE
Chipswinner	CW24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Chipswinner	CW24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Chipswinner	CW24C08B(DIP8)	EEPROM	NONE
Chipswinner	CW24C08B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Chipswinner	CW24C08B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Chipswinner	CW24C16(DIP8)	EEPROM	NONE
Chipswinner	CW24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Chipswinner	CW24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Chipswinner	CW24C16A(DIP8)	EEPROM	NONE
Chipswinner	CW24C16A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Chipswinner	CW24C16A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Chipswinner	CW24C32(DIP8)	EEPROM	NONE
Chipswinner	CW24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Chipswinner	CW24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Chipswinner	CW24C64(DIP8)	EEPROM	NONE
Chipswinner	CW24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Chipswinner	CW24C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Chrontel	CH9904(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CKD	CKD24A02(DIP8)	EEPROM	NONE
CKD	CKD24A02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Coreriver	CR24C01(DIP8)	EEPROM	NONE
Coreriver	CR24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Coreriver	CR24C01(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
Coreriver	CR24C02(DIP8)	EEPROM	NONE
Coreriver	CR24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Coreriver	CR24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Coreriver	CR24C04(DIP8)	EEPROM	NONE
Coreriver	CR24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Coreriver	CR24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Coreriver	CR24C08(DIP8)	EEPROM	NONE
Coreriver	CR24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Coreriver	CR24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Coreriver	CR24C128(DIP8)	EEPROM	NONE
Coreriver	CR24C128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Coreriver	CR24C128(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Coreriver	CR24C16(DIP8)	EEPROM	NONE
Coreriver	CR24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Coreriver	CR24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Coreriver	CR24C256(DIP8)	EEPROM	NONE
Coreriver	CR24C256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Coreriver	CR24C32(DIP8)	EEPROM	NONE
Coreriver	CR24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Coreriver	CR24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Coreriver	CR24C64(DIP8)	EEPROM	NONE
Coreriver	CR24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Coreriver	CR24C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Coreriver	CR93C46-X16(DIP8)	EEPROM	NONE
Coreriver	CR93C46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Coreriver	CR93C46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Coreriver	CR93C46-X8(DIP8)	EEPROM	NONE
Coreriver	CR93C46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Coreriver	CR93C46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Coreriver	CR93C46W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Coreriver	CR93C46W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT1021(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT1022(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT1023(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT1024(DIP8)	EEPROM	NONE
CSI	CAT1024(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT1024(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT1025(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT1026(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT1027(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24AA01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24AA02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24AA04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24AA08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24AA16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24AC128(DIP8)	EEPROM	NONE
CSI	CAT24AC128(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CSI	CAT24C00(DIP8)	EEPROM	NONE
CSI	CAT24C00(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24C00(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24C01(DIP8)	EEPROM	NONE
CSI	CAT24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24C01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24C01B(DIP8)	EEPROM	NONE
CSI	CAT24C01B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24C01B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24C02(DIP8)	EEPROM	NONE
CSI	CAT24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
CSI	CAT24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24C021(DIP8)	EEPROM	NONE
CSI	CAT24C022(DIP8)	EEPROM	NONE
CSI	CAT24C023(DIP8)	EEPROM	NONE
CSI	CAT24C02A(DIP8)	EEPROM	NONE
CSI	CAT24C02A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24C02AI(DIP8)	EEPROM	NONE
CSI	CAT24C02AI(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24C03(DIP8)	EEPROM	NONE
CSI	CAT24C03(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24C03(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24C04(DIP8)	EEPROM	NONE
CSI	CAT24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24C041(DIP8)	EEPROM	NONE
CSI	CAT24C042(DIP8)	EEPROM	NONE
CSI	CAT24C043(DIP8)	EEPROM	NONE
CSI	CAT24C05(DIP8)	EEPROM	NONE
CSI	CAT24C05(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24C05(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24C08(DIP8)	EEPROM	NONE
CSI	CAT24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24C081(DIP8)	EEPROM	NONE
CSI	CAT24C082(DIP8)	EEPROM	NONE
CSI	CAT24C083(DIP8)	EEPROM	NONE
CSI	CAT24C128(DIP8)	EEPROM	NONE
CSI	CAT24C128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24C128(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24C16(DIP8)	EEPROM	NONE
CSI	CAT24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24C161(DIP8)	EEPROM	NONE
CSI	CAT24C162(DIP8)	EEPROM	NONE
CSI	CAT24C163(DIP8)	EEPROM	NONE
CSI	CAT24C164(DIP8)	EEPROM	NONE
CSI	CAT24C164(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24C164(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24C16I(DIP8)	EEPROM	NONE
CSI	CAT24C16Z(DIP8)	EEPROM	NONE
CSI	CAT24C208W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24C256(DIP8)	EEPROM	NONE
CSI	CAT24C256(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CSI	CAT24C256(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24C32(DIP8)	EEPROM	NONE
CSI	CAT24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24C321(DIP8)	EEPROM	NONE
CSI	CAT24C321(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24C321(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24C322(DIP8)	EEPROM	NONE
CSI	CAT24C322(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24C322(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24C323(DIP8)	EEPROM	NONE
CSI	CAT24C323(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24C323(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24C32Z(DIP8)	EEPROM	NONE
CSI	CAT24C64(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
CSI	CAT24C64(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CSI	CAT24C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24C641(DIP8)	EEPROM	NONE
CSI	CAT24C641(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CSI	CAT24C641(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24C642(DIP8)	EEPROM	NONE
CSI	CAT24C642(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CSI	CAT24C642(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24C643(DIP8)	EEPROM	NONE
CSI	CAT24C643(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CSI	CAT24C643(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24FC01(DIP8)	EEPROM	NONE
CSI	CAT24FC01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24FC01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24FC02(DIP8)	EEPROM	NONE
CSI	CAT24FC02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24FC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24FC16(DIP8)	EEPROM	NONE
CSI	CAT24FC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24FC16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24FC17(DIP8)	EEPROM	NONE
CSI	CAT24FC17(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24FC17(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24FC256(DIP8)	EEPROM	NONE
CSI	CAT24FC256(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CSI	CAT24FC32(DIP8)	EEPROM	NONE
CSI	CAT24FC32(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CSI	CAT24FC32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24FC32A(DIP8)	EEPROM	NONE
CSI	CAT24FC32A(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CSI	CAT24FC32A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24FC512(DIP8)	EEPROM	NONE
CSI	CAT24FC512W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CSI	CAT24FC512X(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CSI	CAT24FC64(DIP8)	EEPROM	NONE
CSI	CAT24FC64(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CSI	CAT24FC64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24FC65(DIP8)	EEPROM	NONE
CSI	CAT24FC65(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CSI	CAT24FC65(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24FC66(DIP8)	EEPROM	NONE
CSI	CAT24FC66(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CSI	CAT24FC66(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24LC02(DIP8)	EEPROM	NONE
CSI	CAT24LC02A(DIP8)	EEPROM	NONE
CSI	CAT24LC02AZ(DIP8)	EEPROM	NONE
CSI	CAT24LC02I(DIP8)	EEPROM	NONE
CSI	CAT24LC02Z(DIP8)	EEPROM	NONE
CSI	CAT24LC04(DIP8)	EEPROM	NONE
CSI	CAT24LC04I(DIP8)	EEPROM	NONE
CSI	CAT24LC04Z(DIP8)	EEPROM	NONE
CSI	CAT24LC08(DIP8)	EEPROM	NONE
CSI	CAT24LC08I(DIP8)	EEPROM	NONE
CSI	CAT24LC08Z(DIP8)	EEPROM	NONE
CSI	CAT24LC16(DIP8)	EEPROM	NONE
CSI	CAT24LC16I(DIP8)	EEPROM	NONE
CSI	CAT24LC16Z(DIP8)	EEPROM	NONE
CSI	CAT24WC01(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
CSI	CAT24WC01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24WC01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24WC02(DIP8)	EEPROM	NONE
CSI	CAT24WC02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24WC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24WC03(DIP8)	EEPROM	NONE
CSI	CAT24WC03(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24WC03(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24WC04(DIP8)	EEPROM	NONE
CSI	CAT24WC04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24WC04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24WC05(DIP8)	EEPROM	NONE
CSI	CAT24WC05(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24WC05(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24WC08(DIP8)	EEPROM	NONE
CSI	CAT24WC08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24WC08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24WC09(DIP8)	EEPROM	NONE
CSI	CAT24WC09(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24WC09(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24WC128(DIP8)	EEPROM	NONE
CSI	CAT24WC128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24WC129(DIP8)	EEPROM	NONE
CSI	CAT24WC129(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24WC16(DIP8)	EEPROM	NONE
CSI	CAT24WC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24WC16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24WC164(DIP8)	EEPROM	NONE
CSI	CAT24WC164(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24WC164(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24WC17(DIP8)	EEPROM	NONE
CSI	CAT24WC17(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24WC17(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT24WC256(DIP8)	EEPROM	NONE
CSI	CAT24WC256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24WC257(DIP8)	EEPROM	NONE
CSI	CAT24WC257J(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24WC32(DIP8)	EEPROM	NONE
CSI	CAT24WC32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24WC33(DIP8)	EEPROM	NONE
CSI	CAT24WC33J(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24WC64(DIP8)	EEPROM	NONE
CSI	CAT24WC64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24WC65(DIP8)	EEPROM	NONE
CSI	CAT24WC65J(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT24WC66(DIP8)	EEPROM	NONE
CSI	CAT24WC66W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
CSI	CAT24WC66X(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT28C16A(DIP24)	EEPROM	NONE
CSI	CAT28C16A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CSI	CAT28C16A(SOIC24)	EEPROM	LP-SOP-28PIN-B(300mil)
CSI	CAT28C17A(DIP28)	EEPROM	NONE
CSI	CAT28C17A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CSI	CAT28C17A(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
CSI	CAT28C256(DIP28)	EEPROM	NONE
CSI	CAT28C256(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CSI	CAT28C256(TSOP28)	EEPROM	LP-TSOP-28PIN
CSI	CAT28C257(DIP28)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
CSI	CAT28C257(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CSI	CAT28C257(TSOP28)	EEPROM	LP-TSOP-28PIN
CSI	CAT28C512(DIP32)	EEPROM	NONE
CSI	CAT28C512(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CSI	CAT28C512(TSOP32)	EEPROM	LP48-TSOP-32S
CSI	CAT28C512(TSOP40)	EEPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
CSI	CAT28C513(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CSI	CAT28C64A(DIP28)	EEPROM	NONE
CSI	CAT28C64A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CSI	CAT28C64A(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
CSI	CAT28C64B(DIP28)	EEPROM	NONE
CSI	CAT28C64B(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CSI	CAT28C64B(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
CSI	CAT28C64B(TSOP28)	EEPROM	LP-TSOP-28PIN
CSI	CAT28C65A(DIP28)	EEPROM	NONE
CSI	CAT28C65A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CSI	CAT28C65A(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
CSI	CAT28C65B(DIP28)	EEPROM	NONE
CSI	CAT28C65B(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CSI	CAT28C65B(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
CSI	CAT28C65B(TSOP28)	EEPROM	LP-TSOP-28PIN
CSI	CAT28LV256(DIP28)	EEPROM	NONE
CSI	CAT28LV256(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CSI	CAT28LV256(TSOP28)	EEPROM	LP-TSOP-28PIN
CSI	CAT28LV64(DIP28)	EEPROM	NONE
CSI	CAT28LV64(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CSI	CAT28LV64(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
CSI	CAT28LV64(TSOP28)	EEPROM	LP-TSOP-28PIN
CSI	CAT28LV65(DIP28)	EEPROM	NONE
CSI	CAT28LV65(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
CSI	CAT28LV65(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
CSI	CAT28LV65(TSOP28)	EEPROM	LP-TSOP-28PIN
CSI	CAT34C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT34RC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT34WC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT93C46(DIP8)	EEPROM	NONE
CSI	CAT93C46(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CSI	CAT93C46(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT93C46-X16(DIP8)	EEPROM	NONE
CSI	CAT93C46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CSI	CAT93C46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT93C46-X8(DIP8)	EEPROM	NONE
CSI	CAT93C46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CSI	CAT93C46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT93C46A(DIP8)	EEPROM	NONE
CSI	CAT93C46A(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CSI	CAT93C46AH(DIP8)	EEPROM	NONE
CSI	CAT93C46AJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT93C46B(DIP8)	EEPROM	NONE
CSI	CAT93C46H-X16(DIP8)	EEPROM	NONE
CSI	CAT93C46H-X8(DIP8)	EEPROM	NONE
CSI	CAT93C46R-X16(DIP8)	EEPROM	NONE
CSI	CAT93C46R-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CSI	CAT93C46R-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT93C46R-X8(DIP8)	EEPROM	NONE
CSI	CAT93C46R-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CSI	CAT93C46R-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT93C46RW-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
CSI	CAT93C46RW-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT93C46W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT93C46W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT93C46W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT93C56(DIP8)	EEPROM	NONE
CSI	CAT93C56(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CSI	CAT93C56(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT93C56-X16(DIP8)	EEPROM	NONE
CSI	CAT93C56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CSI	CAT93C56-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT93C56-X8(DIP8)	EEPROM	NONE
CSI	CAT93C56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CSI	CAT93C56-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT93C56A(DIP8)	EEPROM	NONE
CSI	CAT93C56A(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CSI	CAT93C56AJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT93C56W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT93C56W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT93C56W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT93C57-X16(DIP8)	EEPROM	NONE
CSI	CAT93C57-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CSI	CAT93C57-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT93C57-X8(DIP8)	EEPROM	NONE
CSI	CAT93C57-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CSI	CAT93C57-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT93C66-X16(DIP8)	EEPROM	NONE
CSI	CAT93C66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CSI	CAT93C66-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT93C66-X8(DIP8)	EEPROM	NONE
CSI	CAT93C66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CSI	CAT93C66-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT93C66A(DIP8)	EEPROM	NONE
CSI	CAT93C66A(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CSI	CAT93C66W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT93C66W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT93C76-X16(DIP8)	EEPROM	NONE
CSI	CAT93C76-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT93C76-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT93C76-X8(DIP8)	EEPROM	NONE
CSI	CAT93C76-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT93C76-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT93C86-X16(DIP8)	EEPROM	NONE
CSI	CAT93C86-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CSI	CAT93C86-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT93C86-X8(DIP8)	EEPROM	NONE
CSI	CAT93C86-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CSI	CAT93C86-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT93C86A(DIP8)	EEPROM	NONE
CSI	CAT93C86A(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
CSI	CAT93C86W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT93C86W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT93HC46-X16(DIP8)	EEPROM	NONE
CSI	CAT93HC46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT93HC46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT93HC46-X8(DIP8)	EEPROM	NONE
CSI	CAT93HC46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
CSI	CAT93HC46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CSI	CAT93HC46J-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT93HC46J-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT93HC46W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CSI	CAT93HC46W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CYPRESS	CG6457AM(SSOP20)	MPU / MCU	LP-SSOP-28PIN
CYPRESS	CG6462AM(SOIC8)	MPU / MCU	LP-SOP-16PIN(150mil)
CYPRESS	CY24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CYPRESS	CY24C01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CYPRESS	CY24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CYPRESS	CY24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CYPRESS	CY24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CYPRESS	CY24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CYPRESS	CY24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CYPRESS	CY24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CYPRESS	CY24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
CYPRESS	CY24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
CYPRESS	CY27C010(DIP32)	EPROM	NONE
CYPRESS	CY27C010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
CYPRESS	CY27C010(TSOP32)	EPROM	LP48-TSOP-32S
CYPRESS	CY27C256(DIP28)	EPROM	NONE
CYPRESS	CY27C256(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
CYPRESS	CY27C256(TSOP28)	EPROM	LP-TSOP-28PIN
CYPRESS	CY27C256(TSOP32)	EPROM	LP48-TSOP-32S
CYPRESS	CY27C512(DIP28)	EPROM	NONE
CYPRESS	CY27C512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
CYPRESS	CY27C512(TSOP28)	EPROM	LP48-TSOP-28PIN
CYPRESS	CY27H010(DIP32)	EPROM	NONE
CYPRESS	CY27H010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
CYPRESS	CY27H010(TSOP32)	EPROM	LP48-TSOP-32S
CYPRESS	CY27H512(DIP28)	EPROM	NONE
CYPRESS	CY27H512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
CYPRESS	CY27H512(TSOP28)	EPROM	LP48-TSOP-28PIN
CYPRESS	CY7C291A(DIP24)	EPROM	NONE
CYPRESS	CY7C291A(PLCC28)	EPROM	LP48-PLCC-28PIN
CYPRESS	CY7C60113(SSOP28)	MPU / MCU	LP-SSOP-28PIN
CYPRESS	CY7C60123(DIP40)	MPU / MCU	NONE
CYPRESS	CY7C60323(MLF32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY7C60323(SSOP28)	MPU / MCU	LP-SSOP-28PIN
CYPRESS	CY7C60333(MLF32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY7C60445(QFN32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY7C60455(QFN48)	MPU / MCU	LP-QFN-48S-7x7
CYPRESS	CY7C63310(DIP16)	MPU / MCU	NONE
CYPRESS	CY7C63310(SOP16)	MPU / MCU	LP-SOP-16PIN(150mil)
CYPRESS	CY7C63413(PDIP40)	MPU / MCU	NONE
CYPRESS	CY7C63413(PDIP48)	MPU / MCU	NONE
CYPRESS	CY7C63723(DIP18)	MPU / MCU	NONE
CYPRESS	CY7C63723(SOP18)	MPU / MCU	LP48-SOP-20PIN
CYPRESS	CY7C63743(DIP24)	MPU / MCU	NONE
CYPRESS	CY7C63743(SOP24)	MPU / MCU	LP-SOP-28PIN-B(300mil)
CYPRESS	CY7C63801(DIP16)	MPU / MCU	NONE
CYPRESS	CY7C63801(SOP16)	MPU / MCU	LP-SOP-16PIN(150mil)
CYPRESS	CY7C63803(SOP16)	MPU / MCU	LP-SOP-16PIN(150mil)
CYPRESS	CY7C63813(DIP18)	MPU / MCU	NONE
CYPRESS	CY7C63813(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
CYPRESS	CY7C63823(SOP24)	MPU / MCU	LP-SOP-28PIN-B(300mil)
CYPRESS	CY7C63833(QFN32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY7C63903(SSOP28)	MPU / MCU	LP-SSOP-28PIN

Manufacturer	Parts Number	Type	ADAPTER
CYPRESS	CY7C63913(DIP40)	MPU / MCU	NONE
CYPRESS	CY7C64215(SSOP28)	MPU / MCU	LP-SSOP-28PIN
CYPRESS	CY7C64355(QFN48)	MPU / MCU	LP-QFN-48S-7x7
CYPRESS	CY7C64356(QFN48)	MPU / MCU	LP-QFN-48S-7x7
CYPRESS	CY8C20224(QFN16)	MPU / MCU	LP-QFN-16PIN-3x3
CYPRESS	CY8C20234(QFN16)	MPU / MCU	LP-QFN-16PIN-3x3
CYPRESS	CY8C20324(QFN24)	MPU / MCU	LP-QFN-24PIN-4x4
CYPRESS	CY8C20334(QFN24)	MPU / MCU	LP-QFN-24PIN-4x4
CYPRESS	CY8C20424(QFN32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8C20434(MLF32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8C20436(QFN32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8C20436A(QFN32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8C20446(QFN32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8C20446A(QFN32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8C20466(QFN32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8C20466A(QFN32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8C20636(QFN48)	MPU / MCU	LP-QFN-48S-7x7
CYPRESS	CY8C20636A(QFN48)	MPU / MCU	LP-QFN-48S-7x7
CYPRESS	CY8C20646(QFN48)	MPU / MCU	LP-QFN-48S-7x7
CYPRESS	CY8C20646A(QFN48)	MPU / MCU	LP-QFN-48S-7x7
CYPRESS	CY8C20666(QFN48)	MPU / MCU	LP-QFN-48S-7x7
CYPRESS	CY8C20666A(QFN48)	MPU / MCU	LP-QFN-48S-7x7
CYPRESS	CY8C21123(DIP8)	MPU / MCU	NONE
CYPRESS	CY8C21123(SOIC8)	MPU / MCU	LP-SOP-16PIN(150mil)
CYPRESS	CY8C21234(SOP16)	MPU / MCU	LP-SOP-16PIN(150mil)
CYPRESS	CY8C21323(QFN24)	MPU / MCU	LP-QFN-24PIN-4x4
CYPRESS	CY8C21323(SSOP20)	MPU / MCU	LP-SSOP-28PIN
CYPRESS	CY8C21334(SSOP20)	MPU / MCU	LP-SSOP-28PIN
CYPRESS	CY8C21345(SOIC28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
CYPRESS	CY8C21434(MLF32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8C21534(SSOP28)	MPU / MCU	LP-SSOP-28PIN
CYPRESS	CY8C21634(MLF32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8C22113(DIP8)	MPU / MCU	NONE
CYPRESS	CY8C22113(SOIC8)	MPU / MCU	LP-SOP-16PIN(150mil)
CYPRESS	CY8C22213(DIP20)	MPU / MCU	NONE
CYPRESS	CY8C22213(MLF32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8C22213(SSOP20)	MPU / MCU	LP-SSOP-28PIN
CYPRESS	CY8C22345(SOIC28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
CYPRESS	CY8C22545(TQFP44)	MPU / MCU	LP48-VQFP-44S
CYPRESS	CY8C24123(DIP8)	MPU / MCU	NONE
CYPRESS	CY8C24123(SOIC8)	MPU / MCU	LP-SOP-16PIN(150mil)
CYPRESS	CY8C24123A(DIP8)	MPU / MCU	NONE
CYPRESS	CY8C24123A(SOIC8)	MPU / MCU	LP-SOP-16PIN(150mil)
CYPRESS	CY8C24223(DIP20)	MPU / MCU	NONE
CYPRESS	CY8C24223A(DIP20)	MPU / MCU	NONE
CYPRESS	CY8C24223A(SSOP20)	MPU / MCU	LP-SSOP-28PIN
CYPRESS	CY8C24423(DIP28)	MPU / MCU	NONE
CYPRESS	CY8C24423(MLF32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8C24423(SSOP28)	MPU / MCU	LP-SSOP-28PIN
CYPRESS	CY8C24423A(DIP28)	MPU / MCU	NONE
CYPRESS	CY8C24423A(MLF32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8C24423A(SSOP28)	MPU / MCU	LP-SSOP-28PIN
CYPRESS	CY8C27143(DIP8)	MPU / MCU	NONE
CYPRESS	CY8C27243(DIP20)	MPU / MCU	NONE
CYPRESS	CY8C27243(SOIC20)	MPU / MCU	NONE
CYPRESS	CY8C27243(SSOP20)	MPU / MCU	LP-SSOP-28PIN
CYPRESS	CY8C27443(DIP28)	MPU / MCU	NONE
CYPRESS	CY8C27443(SOIC28)	MPU / MCU	LP-SOP-28PIN-B(300mil)

Manufacturer	Parts Number	Type	ADAPTER
CYPRESS	CY8C27443(SSOP28)	MPU / MCU	LP-SSOP-28PIN
CYPRESS	CY8C27543(TQFP44)	MPU / MCU	LP48-VQFP-44S
CYPRESS	CY8C27643(MLF48)	MPU / MCU	LP-QFN-48S-7x7
CYPRESS	CY8C29466(DIP28)	MPU / MCU	NONE
CYPRESS	CY8C29466(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
CYPRESS	CY8C29466(SSOP28)	MPU / MCU	LP-SSOP-28PIN
CYPRESS	CY8C29566(TQFP44)	MPU / MCU	LP48-VQFP-44S
CYPRESS	CY8C29666(MLF48)	MPU / MCU	LP-QFN-48S-7x7
CYPRESS	CY8C41000(MLF32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8C41123(DIP8)	MPU / MCU	NONE
CYPRESS	CY8C41123(SOIC8)	MPU / MCU	LP-SOP-16PIN(150mil)
CYPRESS	CY8C42000(MLF32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8C42123(DIP8)	MPU / MCU	NONE
CYPRESS	CY8C42123(SOIC8)	MPU / MCU	LP-SOP-16PIN(150mil)
CYPRESS	CY8C42423(MLF32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8CLED08(QFN48)	MPU / MCU	LP-QFN-48S-7x7
CYPRESS	CY8CLED16(MLF48)	MPU / MCU	LP-QFN-48S-7x7
CYPRESS	CY8CLED16(SSOP28)	MPU / MCU	LP-SSOP-28PIN
CYPRESS	CY8CTMA300E-48LQXI(QFN48)	MPU / MCU	LP-QFN-48S-6x6
CYPRESS	CY8CTMA300E-48LTXI(QFN48)	MPU / MCU	LP-QFN-48S-6x6
CYPRESS	CY8CTMA301E-48LQXI(QFN48)	MPU / MCU	LP-QFN-48S-6x6
CYPRESS	CY8CTMA301E-48LTXI(QFN48)	MPU / MCU	LP-QFN-48S-6x6
CYPRESS	CY8CTMA340-48LQI-01(QFN48)	MPU / MCU	LP-QFN-48S-6x6
CYPRESS	CY8CTMA340-48LQI-03(QFN48)	MPU / MCU	LP-QFN-48S-6x6
CYPRESS	CY8CTMA340-48LQI-09(QFN48)	MPU / MCU	LP-QFN-48S-6x6
CYPRESS	CY8CTMA340-48LQI-11(QFN48)	MPU / MCU	LP-QFN-48S-6x6
CYPRESS	CY8CTMA340-LTI-01(QFN48)	MPU / MCU	LP-QFN-48S-6x6
CYPRESS	CY8CTMA340-LTI-03(QFN48)	MPU / MCU	LP-QFN-48S-6x6
CYPRESS	CY8CTMA340-LTI-09(QFN48)	MPU / MCU	LP-QFN-48S-6x6
CYPRESS	CY8CTMA340-LTI-11(QFN48)	MPU / MCU	LP-QFN-48S-6x6
CYPRESS	CY8CTMA350-LTI-XX(QFN48)	MPU / MCU	LP-QFN-48S-6x6
CYPRESS	CY8CTMA375-LQI-00(QFN48)	MPU / MCU	LP-QFN-48S-6x6
CYPRESS	CY8CTMA375-LQI-02(QFN48)	MPU / MCU	LP-QFN-48S-6x6
CYPRESS	CY8CTMG110(QFN32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8CTMG200(QFN32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8CTMG200(QFN48)	MPU / MCU	LP-QFN-48S-7x7
CYPRESS	CY8CTMG200A(QFN32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8CTMG200A(QFN48)	MPU / MCU	LP-QFN-48S-7x7
CYPRESS	CY8CTMG201(QFN32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8CTMG201(QFN48)	MPU / MCU	LP-QFN-48S-7x7
CYPRESS	CY8CTMG201A(QFN32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8CTMG201A(QFN48)	MPU / MCU	LP-QFN-48S-7x7
CYPRESS	CY8CTST110(QFN32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8CTST200(QFN32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8CTST200(QFN48)	MPU / MCU	LP-QFN-48S-7x7
CYPRESS	CY8CTST200A(QFN32)	MPU / MCU	LP-QFN-32PIN
CYPRESS	CY8CTST200A(QFN48)	MPU / MCU	LP-QFN-48S-7x7
CYPRESS	CY8CTST341-48LQI-01(QFN48)	MPU / MCU	LP-QFN-48S-6x6
CYPRESS	CYRF69103(QFN40)	MPU / MCU	LP-QFN-40PIN-6x6
CYPRESS	CYRF69213(QFN40)	MPU / MCU	LP-QFN-40PIN-6x6
DALLAS	DS1287(DIP24)	NV RAM	NONE
DALLAS	DS12887(DIP24)	NV RAM	NONE
DALLAS	DS5000-32(DIP40)	NV RAM	NONE
DALLAS	DS5000-8(DIP40)	NV RAM	NONE
E-CMOS	EC24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
E-CMOS	EC24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
E-CMOS	EC24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
E-CMOS	EC24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
E-CMOS	EC24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
E-CMOS	EC24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
E-CMOS	EC24C128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
E-CMOS	EC24C128(TSSOP8)	EEPROM	LP-TSSOP-8PIN
E-CMOS	EC24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
E-CMOS	EC24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
E-CMOS	EC24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
E-CMOS	EC24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
E-CMOS	EC24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
E-CMOS	EC24C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
E-CMOS	EC93C46A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
E-CMOS	EC93C46A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
E-CMOS	EC93C46B-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
E-CMOS	EC93C46B-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ELAN	EM25LV010(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ELAN	EM25LV512(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EMTC	EM27SL512AU(DIP28)	EPROM	NONE
EMTC	EM27SL512AU(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
EMTC	EM27SL512AU(TSOP28)	EPROM	LP48-TSOP-28PIN
EON	EN25B10-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25B10-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25B10T-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25B10T-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25B16-H(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25B16-Q(PDIP8)	FLASH	NONE
EON	EN25B16-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25B16T-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25B16T-Q(PDIP8)	FLASH	NONE
EON	EN25B16T-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25B20-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25B20-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25B20T-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25B20T-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25B32-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25B32T-Q(PDIP8)	FLASH	NONE
EON	EN25B32T-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25B40-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25B40-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25B40-Q(PDIP8)	FLASH	NONE
EON	EN25B40-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25B40T-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25B40T-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25B40T-Q(PDIP8)	FLASH	NONE
EON	EN25B40T-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25B64-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
EON	EN25B80-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25B80-Q(PDIP8)	FLASH	NONE
EON	EN25B80-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25B80T-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25B80T-Q(PDIP8)	FLASH	NONE
EON	EN25B80T-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25D16-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25D16-Q(PDIP8)	FLASH	NONE
EON	EN25D16-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25D80-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25D80-Q(PDIP8)	FLASH	NONE
EON	EN25D80-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25F10-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
EON	EN25F10-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25F16-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25F16-Q(PDIP8)	FLASH	NONE
EON	EN25F16-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25F20-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25F20-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25F32-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25F32-Q(PDIP8)	FLASH	NONE
EON	EN25F32-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25F40-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25F40-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25F40-Q(PDIP8)	FLASH	NONE
EON	EN25F40-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25F64-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
EON	EN25F64-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25F64-Q(PDIP8)	FLASH	NONE
EON	EN25F64-W(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25F64-Y(VDFN8)	FLASH	LP48-WSON8-6x8
EON	EN25F80-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25F80-Q(PDIP8)	FLASH	NONE
EON	EN25F80-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25LF05-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25LF05-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25LF05-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25LF10-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25LF10-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25LF20-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25LF20-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25LF40-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25LF40-Q(PDIP8)	FLASH	NONE
EON	EN25LF40-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25M32-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25M32-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25P10-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25P10-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25P16-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
EON	EN25P16-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25P16-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25P20-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25P20-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25P32-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
EON	EN25P32-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25P32-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25P40-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25P40-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25P40-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25P64-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
EON	EN25P80-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25P80-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25Q128-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
EON	EN25Q128-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
EON	EN25Q128-W(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25Q128-Y(VDFN8)	FLASH	LP48-WSON8-6x8
EON	EN25Q16-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25Q16-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25Q16-Q(PDIP8)	FLASH	NONE
EON	EN25Q16-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25Q32-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)

Manufacturer	Parts Number	Type	ADAPTER
EON	EN25Q32-Q(PDIP8)	FLASH	NONE
EON	EN25Q32-V(VDFN8)	FLASH	LP48-WSO8-5x6
EON	EN25Q32A-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25Q32A-Q(PDIP8)	FLASH	NONE
EON	EN25Q32A-V(VDFN8)	FLASH	LP48-WSO8-5x6
EON	EN25Q32B-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
EON	EN25Q32B-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
EON	EN25Q32B-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25Q32B-Q(PDIP8)	FLASH	NONE
EON	EN25Q32B-V(VDFN8)	FLASH	LP48-WSO8-5x6
EON	EN25Q40-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25Q40-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25Q40-Q(PDIP8)	FLASH	NONE
EON	EN25Q40-V(VDFN8)	FLASH	LP48-WSO8-5x6
EON	EN25Q64-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
EON	EN25Q64-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25Q64-Q(PDIP8)	FLASH	NONE
EON	EN25Q64-W(VDFN8)	FLASH	LP48-WSO8-5x6
EON	EN25Q64-Y(VDFN8)	FLASH	LP48-WSO8-6x8
EON	EN25Q80-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25Q80-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25Q80-Q(PDIP8)	FLASH	NONE
EON	EN25Q80-V(VDFN8)	FLASH	LP48-WSO8-5x6
EON	EN25QA128-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
EON	EN25QA128-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
EON	EN25QA128-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25QA128-Q(PDIP8)	FLASH	NONE
EON	EN25QA16-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
EON	EN25QA16-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25QA256-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
EON	EN25QA256-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
EON	EN25QA256-Y(VDFN8)	FLASH	LP48-WSO8-6x8
EON	EN25QA32-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
EON	EN25QA32-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25QA32-Q(PDIP8)	FLASH	NONE
EON	EN25QA64-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
EON	EN25QA64-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25QA64-Q(PDIP8)	FLASH	NONE
EON	EN25QF256-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
EON	EN25QF256-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
EON	EN25QF256-Y(VDFN8)	FLASH	LP48-WSO8-6x8
EON	EN25QH128-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
EON	EN25QH128-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
EON	EN25QH128-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25QH128-Q(PDIP8)	FLASH	NONE
EON	EN25QH128A-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
EON	EN25QH128A-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
EON	EN25QH128A-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25QH128A-Q(PDIP8)	FLASH	NONE
EON	EN25QH128A-W(WSO8)	FLASH	LP48-WSO8-5x6
EON	EN25QH128A-Y(WSO8)	FLASH	LP48-WSO8-6x8
EON	EN25QH16-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
EON	EN25QH16-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
EON	EN25QH16-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25QH16-Q(PDIP8)	FLASH	NONE
EON	EN25QH16-W(VDFN8)	FLASH	LP48-WSO8-5x6
EON	EN25QH256-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
EON	EN25QH256-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)

Manufacturer	Parts Number	Type	ADAPTER
EON	EN25QH256-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25QH256-Q(PDIP8)	FLASH	NONE
EON	EN25QH256-W(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25QH32-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
EON	EN25QH32-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
EON	EN25QH32-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25QH32-Q(PDIP8)	FLASH	NONE
EON	EN25QH32-W(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25QH64-BB(TFBGA24)	FLASH	LP-SOP-28PIN-B(300mil)
EON	EN25QH64-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
EON	EN25QH64-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25QH64-Q(PDIP8)	FLASH	NONE
EON	EN25QH64-W(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25S10-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25S10-X(VDFN8)	FLASH	LP48-MLP8-2x3
EON	EN25S16-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
EON	EN25S16-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25S16-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25S16T-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
EON	EN25S16T-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25S16T-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25S20-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25S20-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25S20-X(VDFN8)	FLASH	LP48-MLP8-2x3
EON	EN25S32-BB(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
EON	EN25S32-R(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25S32-W(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25S40-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25S40-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25S40-X(VDFN8)	FLASH	LP48-MLP8-2x3
EON	EN25S80-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25S80-V(VDFN8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25S80A-R(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25S80A-W(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25SA10-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25SA10-X(VDFN8)	FLASH	LP48-MLP8-2x3
EON	EN25SF80(SOP8-150)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25T16-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25T16-Q(PDIP8)	FLASH	NONE
EON	EN25T16-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25T40-G(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EON	EN25T40-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25T40-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN25T80-H(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EON	EN25T80-V(VDFN8)	FLASH	LP48-WSON8-5x6
EON	EN29F001B(DIP32)	FLASH	NONE
EON	EN29F001B(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
EON	EN29F001B(TSOP32)	FLASH	LP48-TSOP-32S
EON	EN29F001NB(DIP32)	FLASH	NONE
EON	EN29F001NB(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
EON	EN29F001NB(TSOP32)	FLASH	LP48-TSOP-32S
EON	EN29F001NT(DIP32)	FLASH	NONE
EON	EN29F001NT(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
EON	EN29F001NT(TSOP32)	FLASH	LP48-TSOP-32S
EON	EN29F001T(DIP32)	FLASH	NONE
EON	EN29F001T(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
EON	EN29F001T(TSOP32)	FLASH	LP48-TSOP-32S
EON	EN29F002AB(DIP32)	FLASH	NONE

Manufacturer	Parts Number	Type	ADAPTER
EON	EN29F002AB(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
EON	EN29F002AB(TSOP32)	FLASH	LP48-TSOP-32S
EON	EN29F002ANB(DIP32)	FLASH	NONE
EON	EN29F002ANB(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
EON	EN29F002ANB(TSOP32)	FLASH	LP48-TSOP-32S
EON	EN29F002ANT(DIP32)	FLASH	NONE
EON	EN29F002ANT(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
EON	EN29F002ANT(TSOP32)	FLASH	LP48-TSOP-32S
EON	EN29F002AT(DIP32)	FLASH	NONE
EON	EN29F002AT(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
EON	EN29F002AT(TSOP32)	FLASH	LP48-TSOP-32S
EON	EN29F002B(DIP32)	FLASH	NONE
EON	EN29F002B(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
EON	EN29F002B(TSOP32)	FLASH	LP48-TSOP-32S
EON	EN29F002T(DIP32)	FLASH	NONE
EON	EN29F002T(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
EON	EN29F002T(TSOP32)	FLASH	LP48-TSOP-32S
EON	EN29F040(DIP32)	FLASH	NONE
EON	EN29F040(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
EON	EN29F040(TSOP32)	FLASH	LP48-TSOP-32S
EON	EN29F040A(DIP32)	FLASH	NONE
EON	EN29F040A(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
EON	EN29F040A(TSOP32)	FLASH	LP48-TSOP-32S
EON	EN29F800B(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29F800T(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29GA064H(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
EON	EN29GA064L(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
EON	EN29GA128H(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
EON	EN29GA128L(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
EON	EN29GA256H(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
EON	EN29GA256L(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
EON	EN29GL064AB(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
EON	EN29GL064AB(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29GL064AT(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
EON	EN29GL064AT(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29GL064B(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29GL064B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
EON	EN29GL064H(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29GL064H(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
EON	EN29GL064H-BA(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
EON	EN29GL064L(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29GL064L(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
EON	EN29GL064L-BA(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
EON	EN29GL064T(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29GL064T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
EON	EN29GL128H(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
EON	EN29GL128L(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
EON	EN29GL256H(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
EON	EN29GL256L(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
EON	EN29LV040(DIP32)	FLASH	NONE
EON	EN29LV040(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
EON	EN29LV040(TSOP32 8X14)	FLASH	LP48-VSOP-32S
EON	EN29LV040(TSOP32 8X20)	FLASH	LP48-TSOP-32S
EON	EN29LV040A(DIP32)	FLASH	NONE
EON	EN29LV040A(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
EON	EN29LV040A(TSOP32 8X14)	FLASH	LP48-VSOP-32S
EON	EN29LV040A(TSOP32 8X20)	FLASH	LP48-TSOP-32S
EON	EN29LV040J(DIP32)	FLASH	NONE

Manufacturer	Parts Number	Type	ADAPTER
EON	EN29LV040J(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
EON	EN29LV040J(TSOP32)	FLASH	LP48-VSOP-32S
EON	EN29LV160AB(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV160AT(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV160B(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV160BB(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV160BT(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV160CB(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
EON	EN29LV160CB(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV160CT(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
EON	EN29LV160CT(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV160JB(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV160JT(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV160T(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV320AB(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV320AT(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV320BB(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
EON	EN29LV320BB(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV320BT(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
EON	EN29LV320BT(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV320CB(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
EON	EN29LV320CB(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV320CT(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
EON	EN29LV320CT(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV400AB(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV400AT(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV400B(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV400T(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV640B(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV640H(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV640L(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV640T(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV641H(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV641L(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV800AB(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV800AT(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV800B(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV800BB(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV800BT(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV800CB(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
EON	EN29LV800CB(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV800CT(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
EON	EN29LV800CT(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29LV800T(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29PL032(TSOP48)	FLASH	LP-TSOP-48S
EON	EN29PL064(TSOP48)	FLASH	LP-TSOP-48S
Eorex	EM24LC02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Eorex	EM93LC46-X16(DIP8)	EEPROM	NONE
Eorex	EM93LC46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Eorex	EM93LC46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Eorex	EM93LC46-X8(DIP8)	EEPROM	NONE
Eorex	EM93LC46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Eorex	EM93LC46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Eorex	EM93LC46J-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Eorex	EM93LC46J-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Eorex	EM93LC46W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Eorex	EM93LC46W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Eorex	EM93LC56-X16(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
Eorex	EM93LC56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Eorex	EM93LC56-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Eorex	EM93LC56-X8(DIP8)	EEPROM	NONE
Eorex	EM93LC56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Eorex	EM93LC56-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Eorex	EM93LC56J-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Eorex	EM93LC56J-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Eorex	EM93LC56W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Eorex	EM93LC56W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Eorex	EM93LC57-X16(DIP8)	EEPROM	NONE
Eorex	EM93LC57-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Eorex	EM93LC57-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Eorex	EM93LC57-X8(DIP8)	EEPROM	NONE
Eorex	EM93LC57-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Eorex	EM93LC57-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Eorex	EM93LC57J-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Eorex	EM93LC57J-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Eorex	EM93LC57W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Eorex	EM93LC57W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Eorex	EM93LC66-X16(DIP8)	EEPROM	NONE
Eorex	EM93LC66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Eorex	EM93LC66-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Eorex	EM93LC66-X8(DIP8)	EEPROM	NONE
Eorex	EM93LC66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Eorex	EM93LC66-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Eorex	EM93LC66J-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Eorex	EM93LC66J-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Eorex	EM93LC66W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Eorex	EM93LC66W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Eorex	EM93LC86-X16(DIP8)	EEPROM	NONE
Eorex	EM93LC86-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Eorex	EM93LC86-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Eorex	EM93LC86-X8(DIP8)	EEPROM	NONE
Eorex	EM93LC86-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Eorex	EM93LC86-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Eorex	EM93LC86J-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Eorex	EM93LC86J-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Eorex	EM93LC86W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Eorex	EM93LC86W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ESMT	F25D04QA(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ESMT	F25D04QA(WSON8)	FLASH	LP48-WSON8-5x6
ESMT	F25D08QA(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ESMT	F25D08QA(WSON8)	FLASH	LP48-WSON8-5x6
ESMT	F25D64QA(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ESMT	F25D64QA(WSON8)	FLASH	LP48-WSON8-5x6
ESMT	F25L004(DIP8)	FLASH	NONE
ESMT	F25L004(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ESMT	F25L008(DIP8)	FLASH	NONE
ESMT	F25L008(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ESMT	F25L016A(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ESMT	F25L01PA-2D(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ESMT	F25L01PA-2D(TSSOP8)	FLASH	LP-TSSOP-8PIN
ESMT	F25L02PA(SOP8-150mil)	FLASH	LP-SOP-16PIN(150mil)
ESMT	F25L02PA(SOP8-207mil)	FLASH	LP-SOP-8PIN-B(207mil)
ESMT	F25L02PA(WSON8)	FLASH	LP48-WSON8-5x6
ESMT	F25L08PA(PDIP8)	FLASH	NONE
ESMT	F25L08PA(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ESMT	F25L08QA(SOP8-150mil)	FLASH	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
ESMT	F25L08QA(SOP8-207mil)	FLASH	LP-SOP-8PIN-B(207mil)
ESMT	F25L16PA(PDIP8)	FLASH	NONE
ESMT	F25L16PA(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ESMT	F25L32PA(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ESMT	F25L32PA(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ESMT	F25L32QA(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ESMT	F25L32QA(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ESMT	F25L32QA-2S(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ESMT	F25L32QA-2S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ESMT	F25L64PA(PDIP8)	FLASH	NONE
ESMT	F25L64PA(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ESMT	F25L64PA(SOP8-150mil)	FLASH	LP-SOP-16PIN(150mil)
ESMT	F25L64PA(SOP8-207mil)	FLASH	LP-SOP-8PIN-B(207mil)
ESMT	F25L64QA(BGA24)	FLASH	LP-BGA-24PIN-4x6B
ESMT	F25L64QA(PDIP8)	FLASH	NONE
ESMT	F25L64QA(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ESMT	F25L64QA(SOP8-150mil)	FLASH	LP-SOP-16PIN(150mil)
ESMT	F25L64QA(SOP8-207mil)	FLASH	LP-SOP-8PIN-B(207mil)
ESMT	F29L064BGA(TSOP48)	FLASH	LP-TSOP-48S
ESMT	F29L064UGA(TSOP48)	FLASH	LP-TSOP-48S
ESMT	F49L160BA(TSOP48)	FLASH	LP-TSOP-48S
ESMT	F49L160UA(TSOP48)	FLASH	LP-TSOP-48S
ESMT	F49L320BA(TSOP48)	FLASH	LP-TSOP-48S
ESMT	F49L320UA(TSOP48)	FLASH	LP-TSOP-48S
ESMT	F49L400BA(TSOP48)	FLASH	LP-TSOP-48S
ESMT	F49L400UA(TSOP48)	FLASH	LP-TSOP-48S
ESMT	F49L800BA(TSOP48)	FLASH	LP-TSOP-48S
ESMT	F49L800UA(TSOP48)	FLASH	LP-TSOP-48S
Estek	24C02(DIP8)	EEPROM	NONE
Estek	24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Estek	24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Estek	24C04(DIP8)	EEPROM	NONE
Estek	24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Estek	24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Estek	24C08(DIP8)	EEPROM	NONE
Estek	24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Estek	24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Estek	24C16(DIP8)	EEPROM	NONE
Estek	24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Estek	24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Estek	24C32(DIP8)	EEPROM	NONE
Estek	24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Estek	24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Estek	24C64(DIP8)	EEPROM	NONE
Estek	24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Estek	24C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
EXCELSEMI	ES25M16-1(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EXCELSEMI	ES25M16-2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EXCELSEMI	ES25M16-3(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
EXCELSEMI	ES25M16-4(PDIP8)	FLASH	NONE
EXCELSEMI	ES25M16-5(WSON8)	FLASH	LP48-WSON8-5x6
EXCELSEMI	ES25M40-1(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EXCELSEMI	ES25M40-2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
EXCELSEMI	ES25M40-3(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
EXCELSEMI	ES25M40-4(PDIP8)	FLASH	NONE
EXCELSEMI	ES25M40-5(WSON8)	FLASH	LP48-WSON8-5x6
EXCELSEMI	ES25M80-1(SOP8)	FLASH	LP-SOP-16PIN(150mil)
EXCELSEMI	ES25M80-2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)

Manufacturer	Parts Number	Type	ADAPTER
EXCELSEMI	ES25M80-3(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
EXCELSEMI	ES25M80-4(PDIP8)	FLASH	NONE
EXCELSEMI	ES25M80-5(WSON8)	FLASH	LP48-WSON8-5x6
EXCELSEMI	ES29LV160DB(TSOP48)	FLASH	LP-TSOP-48S
EXCELSEMI	ES29LV160DT(TSOP48)	FLASH	LP-TSOP-48S
EXCELSEMI	ES29LV160EB(TSOP48)	FLASH	LP-TSOP-48S
EXCELSEMI	ES29LV160ET(TSOP48)	FLASH	LP-TSOP-48S
EXCELSEMI	ES29LV160FB(TSOP48)	FLASH	LP-TSOP-48S
EXCELSEMI	ES29LV160FT(TSOP48)	FLASH	LP-TSOP-48S
EXCELSEMI	ES29LV320DB(TSOP48)	FLASH	LP-TSOP-48S
EXCELSEMI	ES29LV320DT(TSOP48)	FLASH	LP-TSOP-48S
EXCELSEMI	ES29LV320EB(TSOP48)	FLASH	LP-TSOP-48S
EXCELSEMI	ES29LV320ET(TSOP48)	FLASH	LP-TSOP-48S
EXCELSEMI	ES29LV320FB(TSOP48)	FLASH	LP-TSOP-48S
EXCELSEMI	ES29LV320FT(TSOP48)	FLASH	LP-TSOP-48S
EXCELSEMI	ES29LV400DB(TSOP48)	FLASH	LP-TSOP-48S
EXCELSEMI	ES29LV400DT(TSOP48)	FLASH	LP-TSOP-48S
EXCELSEMI	ES29LV400EB(TSOP48)	FLASH	LP-TSOP-48S
EXCELSEMI	ES29LV400ET(TSOP48)	FLASH	LP-TSOP-48S
EXCELSEMI	ES29LV800DB(TSOP48)	FLASH	LP-TSOP-48S
EXCELSEMI	ES29LV800DT(TSOP48)	FLASH	LP-TSOP-48S
EXCELSEMI	ES29LV800EB(TSOP48)	FLASH	LP-TSOP-48S
EXCELSEMI	ES29LV800ET(TSOP48)	FLASH	LP-TSOP-48S
EXEL	XL24C01A(DIP8)	EEPROM	NONE
EXEL	XL24C01A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL24C02(DIP8)	EEPROM	NONE
EXEL	XL24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL24C04(DIP8)	EEPROM	NONE
EXEL	XL24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL24C08(DIP8)	EEPROM	NONE
EXEL	XL24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL24C16(DIP8)	EEPROM	NONE
EXEL	XL24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL24C163(DIP8)	EEPROM	NONE
EXEL	XL24C163(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL24C164(DIP8)	EEPROM	NONE
EXEL	XL24C164(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL2804A(DIP24)	EEPROM	NONE
EXEL	XL2816A(DIP24)	EEPROM	NONE
EXEL	XL2816A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XL2816A(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
EXEL	XL2817A(DIP28)	EEPROM	NONE
EXEL	XL2864A(DIP28)	EEPROM	NONE
EXEL	XL2864A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XL2864A(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
EXEL	XL2865A(DIP28)	EEPROM	NONE
EXEL	XL2865A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XL28C16A(DIP24)	EEPROM	NONE
EXEL	XL28C16A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XL28C16A(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
EXEL	XL28C256(DIP28)	EEPROM	NONE
EXEL	XL28C256(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XL28C64(DIP28)	EEPROM	NONE
EXEL	XL28C64(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XL28C64(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
EXEL	XL28C64B(DIP28)	EEPROM	NONE
EXEL	XL28C64B(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XL28C64B(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)

Manufacturer	Parts Number	Type	ADAPTER
EXEL	XL28C65A(DIP28)	EEPROM	NONE
EXEL	XL28C65A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XL28C65A(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
EXEL	XL93C06(DIP8)	EEPROM	NONE
EXEL	XL93C46(DIP8)	EEPROM	NONE
EXEL	XL93C46J(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93C56(DIP8)	EEPROM	NONE
EXEL	XL93C56J(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93C56JR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93C66(DIP8)	EEPROM	NONE
EXEL	XL93C66JR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93CS46(DIP8)	EEPROM	NONE
EXEL	XL93LC06A(DIP8)	EEPROM	NONE
EXEL	XL93LC06A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC46(DIP8)	EEPROM	NONE
EXEL	XL93LC46A(DIP8)	EEPROM	NONE
EXEL	XL93LC46ARY(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC46AY(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC46B(DIP8)	EEPROM	NONE
EXEL	XL93LC46B-X16(DIP8)	EEPROM	NONE
EXEL	XL93LC46B-X8(DIP8)	EEPROM	NONE
EXEL	XL93LC46BRY(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC46BRY-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC46BRY-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC46BY(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC46BY-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC46BY-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC46RY(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC46Y(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC56(DIP8)	EEPROM	NONE
EXEL	XL93LC56A(DIP8)	EEPROM	NONE
EXEL	XL93LC56ARY(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC56AY(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC56B(DIP8)	EEPROM	NONE
EXEL	XL93LC56B-X16(DIP8)	EEPROM	NONE
EXEL	XL93LC56B-X8(DIP8)	EEPROM	NONE
EXEL	XL93LC56BRY(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC56BRY-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC56BRY-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC56BY(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC56BY-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC56BY-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC56RY(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC56Y(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC66(DIP8)	EEPROM	NONE
EXEL	XL93LC66A(DIP8)	EEPROM	NONE
EXEL	XL93LC66ARY(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC66AY(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC66B(DIP8)	EEPROM	NONE
EXEL	XL93LC66B-X16(DIP8)	EEPROM	NONE
EXEL	XL93LC66B-X8(DIP8)	EEPROM	NONE
EXEL	XL93LC66BRY(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC66BRY-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC66BRY-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC66BY(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC66BY-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC66BY-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LC66RY(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
EXEL	XL93LC66Y(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LL46(DIP8)	EEPROM	NONE
EXEL	XL93LL46(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LL46F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LL56(DIP8)	EEPROM	NONE
EXEL	XL93LL56(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LL56F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LL66(DIP8)	EEPROM	NONE
EXEL	XL93LL66(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XL93LL66F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XLE2816A(DIP24)	EEPROM	NONE
EXEL	XLE2816A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XLE2816A(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
EXEL	XLE2864A(DIP28)	EEPROM	NONE
EXEL	XLE2864A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XLE2864A(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
EXEL	XLE2865A(DIP28)	EEPROM	NONE
EXEL	XLE2865A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XLE28C16A(DIP24)	EEPROM	NONE
EXEL	XLE28C16A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XLE28C16A(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
EXEL	XLE28C256(DIP28)	EEPROM	NONE
EXEL	XLE28C256(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XLE28C64(DIP28)	EEPROM	NONE
EXEL	XLE28C64(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XLE28C64(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
EXEL	XLE28C64B(DIP28)	EEPROM	NONE
EXEL	XLE28C64B(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XLE28C64B(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
EXEL	XLE28C65A(DIP28)	EEPROM	NONE
EXEL	XLE28C65A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XLE28C65A(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
EXEL	XLE93C46(DIP8)	EEPROM	NONE
EXEL	XLE93C56(DIP8)	EEPROM	NONE
EXEL	XLE93C66(DIP8)	EEPROM	NONE
EXEL	XLE93CS46(DIP8)	EEPROM	NONE
EXEL	XLM2817A(DIP28)	EEPROM	NONE
EXEL	XLM28C65A(DIP28)	EEPROM	NONE
EXEL	XLM28C65A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XLM28C65A(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
EXEL	XLS2816A(DIP24)	EEPROM	NONE
EXEL	XLS2816A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XLS2816A(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
EXEL	XLS2864A(DIP28)	EEPROM	NONE
EXEL	XLS2864A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XLS2864A(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
EXEL	XLS2865A(DIP28)	EEPROM	NONE
EXEL	XLS2865A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XLS28C04A(DIP24)	EEPROM	NONE
EXEL	XLS28C16A(DIP24)	EEPROM	NONE
EXEL	XLS28C16A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XLS28C16A(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
EXEL	XLS28C256(DIP28)	EEPROM	NONE
EXEL	XLS28C256(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XLS28C64(DIP28)	EEPROM	NONE
EXEL	XLS28C64(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XLS28C64(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
EXEL	XLS28C64B(DIP28)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
EXEL	XLS28C64B(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XLS28C64B(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
EXEL	XLS28C65A(DIP28)	EEPROM	NONE
EXEL	XLS28C65A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
EXEL	XLS28C65A(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
EXEL	XLS93C46(DIP8)	EEPROM	NONE
EXEL	XLS93C46RY(SOP8)	EEPROM	NONE
EXEL	XLS93C46Y(SOP8)	EEPROM	NONE
EXEL	XLS93C56(DIP8)	EEPROM	NONE
EXEL	XLS93C56RY(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XLS93C56Y(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XLS93C66(DIP8)	EEPROM	NONE
EXEL	XLS93C66RY(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XLS93C66Y(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
EXEL	XLS93CS46(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C02U(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C02U(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C02U(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C02UF(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C02UF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C02UF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C02UFL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C02UFL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C02UFL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C02UFLZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C02UFLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C02UFLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C02UL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C02UL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C02UL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C02ULZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C02ULZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C02ULZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C03U(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C03U(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C03U(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C03UF(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C03UF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C03UF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C03UFL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C03UFL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C03UFL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C03UFLZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C03UFLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C03UFLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C03UL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C03UL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C03UL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C03ULZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C03ULZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C03ULZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C04U(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C04U(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C04U(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C04UF(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C04UF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C04UF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C04UFL(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
FAIRCHILD	FM24C04UFL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C04UFL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C04UFLZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C04UFLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C04UFLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C04UL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C04UL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C04UL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C04ULZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C04ULZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C04ULZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C05U(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C05U(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C05U(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C05UF(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C05UF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C05UF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C05UFL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C05UFL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C05UFL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C05UFLZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C05UFLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C05UFLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C05UL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C05UL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C05UL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C05ULZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C05ULZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C05ULZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C08U(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C08U(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C08U(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C08UF(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C08UF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C08UF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C08UFL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C08UFL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C08UFL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C08UFLZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C08UFLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C08UFLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C08UL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C08UL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C08UL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C08ULZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C08ULZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C08ULZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C09U(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C09U(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C09U(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C09UF(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C09UF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C09UF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C09UFL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C09UFL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C09UFL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C09UFLZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C09UFLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
FAIRCHILD	FM24C09UFLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C09UL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C09UL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C09UL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C09ULZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C09ULZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C09ULZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C128(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C128(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C128F(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C128F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C128F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C128FL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C128FL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C128FL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C128FLZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C128FLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C128FLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C128L(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C128L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C128L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C128LZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C128LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C128LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C16U(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C16U(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C16U(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C16UF(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C16UF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C16UF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C16UFL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C16UFL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C16UFL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C16UFLZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C16UFLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C16UFLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C16UFT(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C16UFT(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C16UFT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C16UFTL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C16UFTL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C16UFTL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C16UFTLZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C16UFTLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C16UFTLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C16UL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C16UL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C16UL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C16ULZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C16ULZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C16ULZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C16UT(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C16UT(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C16UT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C16UTL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C16UTL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C16UTL(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
FAIRCHILD	FM24C16UTLZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C16UTLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C16UTLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C17U(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C17U(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C17U(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C17UF(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C17UF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C17UF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C17UFL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C17UFL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C17UFL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C17UFLZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C17UFLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C17UFLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C17UFT(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C17UFT(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C17UFT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C17UFTL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C17UFTL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C17UFTL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C17UFTLZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C17UFTLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C17UFTLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C17UL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C17UL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C17UL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C17ULZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C17ULZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C17ULZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C17UT(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C17UT(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C17UT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C17UTL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C17UTL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C17UTL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C17UTLZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C17UTLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C17UTLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C256(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C256F(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C256F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C256FL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C256FL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C256FLZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C256FLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C256L(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C256L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C256LZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C256LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C32U(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C32U(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C32UF(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C32UF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C32UFH(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C32UFH(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C32UFL(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
FAIRCHILD	FM24C32UFL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C32UFLZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C32UFLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C32UH(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C32UH(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C32UL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C32UL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C32ULZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C32ULZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C64(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C64F(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C64F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C64F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C64FL(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C64FL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C64FL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C64FLZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C64FLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C64FLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C64L(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C64L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C64L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM24C64LZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM24C64LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM24C64LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM27C256(DIP28)	EPROM	NONE
FAIRCHILD	FM93C06(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C06(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C06(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C06L(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C06L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C06L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C06LZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C06LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C06LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C46(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C46(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C46(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C46A-X16(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C46A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C46A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C46A-X8(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C46A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C46A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C46AL-X16(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C46AL-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C46AL-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C46AL-X8(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C46AL-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C46AL-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C46ALZ-X16(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C46ALZ-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C46ALZ-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C46ALZ-X8(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C46ALZ-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C46ALZ-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
FAIRCHILD	FM93C46AT-X16(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C46AT-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C46AT-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C46AT-X8(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C46AT-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C46AT-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C46ATL-X16(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C46ATL-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C46ATL-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C46ATL-X8(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C46ATL-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C46ATL-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C46ATLZ-X16(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C46ATLZ-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C46ATLZ-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C46ATLZ-X8(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C46ATLZ-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C46ATLZ-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C46L(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C46L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C46L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C46LZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C46LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C46LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C46T(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C46T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C46T(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C46TL(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C46TL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C46TL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C46TLZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C46TLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C46TLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C56(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C56(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C56(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C56A-X16(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C56A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C56A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C56A-X8(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C56A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C56A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C56AL-X16(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C56AL-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C56AL-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C56AL-X8(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C56AL-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C56AL-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C56ALZ-X16(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C56ALZ-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C56ALZ-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C56ALZ-X8(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C56ALZ-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C56ALZ-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C56AT-X16(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C56AT-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C56AT-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C56AT-X8(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
FAIRCHILD	FM93C56AT-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C56AT-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C56ATL-X16(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C56ATL-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C56ATL-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C56ATL-X8(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C56ATL-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C56ATL-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C56ATLZ-X16(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C56ATLZ-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C56ATLZ-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C56ATLZ-X8(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C56ATLZ-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C56ATLZ-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C56L(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C56L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C56L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C56LZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C56LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C56LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C56T(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C56T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C56T(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C56TL(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C56TL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C56TL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C56TLZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C56TLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C56TLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C66(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C66(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C66(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C66A-X16(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C66A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C66A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C66A-X8(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C66A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C66A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C66AL-X16(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C66AL-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C66AL-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C66AL-X8(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C66AL-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C66AL-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C66ALZ-X16(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C66ALZ-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C66ALZ-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C66ALZ-X8(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C66ALZ-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C66ALZ-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C66L(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C66L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C66L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C66LZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C66LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C66LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93C86A-X16(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C86A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
FAIRCHILD	FM93C86A-X8(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C86A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C86AL-X16(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C86AL-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C86AL-X8(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C86AL-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C86ALZ-X16(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C86ALZ-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93C86ALZ-X8(DIP8)	EEPROM	NONE
FAIRCHILD	FM93C86ALZ-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93CS06(DIP8)	EEPROM	NONE
FAIRCHILD	FM93CS06(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93CS06(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93CS06L(DIP8)	EEPROM	NONE
FAIRCHILD	FM93CS06L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93CS06L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93CS06LZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM93CS06LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93CS06LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93CS46(DIP8)	EEPROM	NONE
FAIRCHILD	FM93CS46(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93CS46(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93CS46L(DIP8)	EEPROM	NONE
FAIRCHILD	FM93CS46L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93CS46L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93CS46LZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM93CS46LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93CS46LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93CS46T(DIP8)	EEPROM	NONE
FAIRCHILD	FM93CS46T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93CS46T(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93CS46TL(DIP8)	EEPROM	NONE
FAIRCHILD	FM93CS46TL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93CS46TL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93CS46TLZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM93CS46TLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93CS46TLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93CS56(DIP8)	EEPROM	NONE
FAIRCHILD	FM93CS56(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93CS56(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93CS56L(DIP8)	EEPROM	NONE
FAIRCHILD	FM93CS56L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93CS56L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93CS56LZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM93CS56LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93CS56LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93CS56T(DIP8)	EEPROM	NONE
FAIRCHILD	FM93CS56T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93CS56T(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93CS66(DIP8)	EEPROM	NONE
FAIRCHILD	FM93CS66(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93CS66(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93CS66L(DIP8)	EEPROM	NONE
FAIRCHILD	FM93CS66L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93CS66L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	FM93CS66LZ(DIP8)	EEPROM	NONE
FAIRCHILD	FM93CS66LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93CS66LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
FAIRCHILD	FM93CS66T(DIP8)	EEPROM	NONE
FAIRCHILD	FM93CS66T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	FM93CS66T(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C00(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C00(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C00F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C00F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C01(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C01F(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C01F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C01F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C02(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C02F(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C02F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C02F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C02FL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C02FL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C02FL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C02FLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C02FLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C02FLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C02L(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C02L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C02L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C02LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C02LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C02LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C02U(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C02U(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C02U(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C02UF(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C02UF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C02UF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C02UFL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C02UFL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C02UFL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C02UFLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C02UFLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C02UFLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C02UL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C02UL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C02UL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C02ULZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C02ULZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C02ULZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C03(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C03(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C03(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C03F(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C03F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C03F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C03FL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C03FL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C03FL(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
FAIRCHILD	NM24C03FLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C03FLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C03FLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C03L(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C03L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C03L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C03LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C03LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C03LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C03U(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C03U(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C03U(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C03UF(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C03UF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C03UF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C03UFL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C03UFL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C03UFL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C03UFLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C03UFLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C03UFLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C03UL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C03UL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C03UL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C03ULZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C03ULZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C03ULZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C04(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C04F(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C04F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C04F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C04FL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C04FL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C04FL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C04FLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C04FLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C04FLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C04L(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C04L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C04L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C04LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C04LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C04LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C04U(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C04U(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C04U(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C04UF(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C04UF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C04UF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C04UFL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C04UFL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C04UFL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C04UFLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C04UFLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C04UFLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C04UL(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
FAIRCHILD	NM24C04UL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C04UL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C04ULZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C04ULZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C04ULZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C05(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C05(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C05(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C05F(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C05F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C05F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C05FL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C05FL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C05FL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C05FLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C05FLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C05FLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C05L(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C05L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C05L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C05LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C05LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C05LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C05U(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C05U(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C05U(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C05UF(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C05UF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C05UF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C05UFL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C05UFL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C05UFL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C05UFLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C05UFLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C05UFLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C05UL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C05UL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C05UL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C05ULZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C05ULZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C05ULZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C08(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C08F(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C08F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C08F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C08FL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C08FL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C08FL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C08FLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C08FLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C08FLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C08L(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C08L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C08L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C08LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C08LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
FAIRCHILD	NM24C08LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C08U(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C08U(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C08U(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C08UF(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C08UF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C08UF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C08UFL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C08UFL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C08UFL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C08UFLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C08UFLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C08UFLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C08UL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C08UL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C08UL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C08ULZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C08ULZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C08ULZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C09(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C09(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C09(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C09F(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C09F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C09F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C09FL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C09FL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C09FL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C09FLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C09FLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C09FLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C09L(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C09L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C09L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C09LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C09LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C09LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C09U(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C09U(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C09U(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C09UF(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C09UF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C09UF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C09UFL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C09UFL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C09UFL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C09UFLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C09UFLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C09UFLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C09UL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C09UL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C09UL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C09ULZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C09ULZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C09ULZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
FAIRCHILD	NM24C16F(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16FL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16FL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16FL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16FLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16FLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16FLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16FT(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16FT(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16FT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16FTL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16FTL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16FTL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16FTLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16FTLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16FTLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16L(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16T(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16T(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16TL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16TL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16TL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16TLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16TLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16TLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16U(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16U(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16U(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16UF(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16UF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16UF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16UFL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16UFL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16UFL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16UFLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16UFLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16UFLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16UFT(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16UFT(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16UFT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16UFTL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16UFTL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16UFTL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16UFTLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16UFTLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16UFTLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16UL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16UL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16UL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16ULZ(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
FAIRCHILD	NM24C16ULZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16ULZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16UT(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16UT(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16UT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16UTL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16UTL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16UTL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C16UTLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C16UTLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C16UTLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C17(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C17F(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C17FL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17FL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17FL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C17FLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17FLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17FLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C17FT(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17FT(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17FT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C17FTL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17FTL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17FTL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C17FTLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17FTLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17FTLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C17L(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C17LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C17T(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17T(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C17TL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17TL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17TL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C17TLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17TLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17TLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C17U(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17U(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17UF(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17UF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17UF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C17UFL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17UFL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17UFL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C17UFLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17UFLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17UFLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
FAIRCHILD	NM24C17UFT(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17UFT(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17UFT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C17UFTL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17UFTL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17UFTL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C17UFTLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17UFTLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17UFTLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C17UL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17UL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17ULZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17ULZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17UT(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17UT(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17UT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C17UTL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17UTL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17UTL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C17UTLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C17UTLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C17UTLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C32(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C32F(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C32F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C32F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C32FL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C32FL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C32FL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C32FLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C32FLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C32FLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C32L(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C32L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C32L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C32LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C32LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C32LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C32U(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C32U(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C32U(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C32UF(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C32UF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C32UF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C32UFL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C32UFL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C32UFL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C32UFLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C32UFLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C32UFLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C32UL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C32UL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C32UL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C32ULZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C32ULZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C32ULZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
FAIRCHILD	NM24C65(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C65(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C65(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C65F(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C65F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C65F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C65FL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C65FL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C65FL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C65FLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C65FLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C65FLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C65L(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C65L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C65L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C65LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C65LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C65LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C65U(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C65U(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C65U(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C65UF(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C65UF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C65UF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C65UFL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C65UFL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C65UFL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C65UFLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C65UFLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C65UFLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C65UL(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C65UL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C65UL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24C65ULZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24C65ULZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24C65ULZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24W02(DIP8)	EEPROM	NONE
FAIRCHILD	NM24W02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24W02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24W02L(DIP8)	EEPROM	NONE
FAIRCHILD	NM24W02L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24W02L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24W02LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24W02LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24W02LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24W04(DIP8)	EEPROM	NONE
FAIRCHILD	NM24W04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24W04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24W04L(DIP8)	EEPROM	NONE
FAIRCHILD	NM24W04L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24W04L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24W04LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24W04LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24W04LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24W08(DIP8)	EEPROM	NONE
FAIRCHILD	NM24W08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24W08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24W08L(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
FAIRCHILD	NM24W08L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24W08L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24W08LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24W08LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24W08LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24W16(DIP8)	EEPROM	NONE
FAIRCHILD	NM24W16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24W16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24W16L(DIP8)	EEPROM	NONE
FAIRCHILD	NM24W16L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24W16L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM24W16LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM24W16LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM24W16LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C06(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C06(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C06(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C06L(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C06L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C06L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C06LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C06LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C06LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C13(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C13(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C13N(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C13N(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C13T(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C13T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C14(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C14(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C14N(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C14N(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C14T(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C14T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C46(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C46(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C46(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C46A(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C46A-X16(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C46A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C46A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C46A-X8(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C46A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C46A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C46AL(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C46AL-X16(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C46AL-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C46AL-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C46AL-X8(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C46AL-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C46AL-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C46ALZ-X16(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C46ALZ-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C46ALZ-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C46ALZ-X8(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C46ALZ-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C46ALZ-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
FAIRCHILD	NM93C46AT-X16(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C46AT-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C46AT-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C46AT-X8(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C46AT-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C46AT-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C46ATL-X16(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C46ATL-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C46ATL-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C46ATL-X8(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C46ATL-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C46ATL-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C46ATLZ-X16(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C46ATLZ-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C46ATLZ-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C46ATLZ-X8(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C46ATLZ-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C46ATLZ-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C46L(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C46L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C46L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C46LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C46LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C46LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C46T(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C46T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C46T(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C46TL(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C46TL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C46TL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C46TLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C46TLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C46TLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C56(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C56(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C56(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C56A-X16(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C56A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C56A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C56A-X8(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C56A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C56A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C56AL-X16(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C56AL-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C56AL-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C56AL-X8(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C56AL-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C56AL-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C56ALZ-X16(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C56ALZ-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C56ALZ-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C56ALZ-X8(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C56ALZ-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C56ALZ-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C56AT-X16(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C56AT-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C56AT-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C56AT-X8(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
FAIRCHILD	NM93C56AT-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C56AT-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C56ATL-X16(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C56ATL-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C56ATL-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C56ATL-X8(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C56ATL-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C56ATL-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C56ATLZ-X16(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C56ATLZ-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C56ATLZ-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C56ATLZ-X8(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C56ATLZ-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C56ATLZ-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C56L(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C56L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C56L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C56LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C56LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C56LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C56T(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C56T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C56T(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C56TL(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C56TL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C56TL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C56TLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C56TLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C56TLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C66(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C66(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C66(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C66A-X16(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C66A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C66A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C66A-X8(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C66A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C66A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C66AL-X16(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C66AL-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C66AL-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C66AL-X8(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C66AL-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C66AL-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C66ALZ-X16(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C66ALZ-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C66ALZ-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C66ALZ-X8(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C66ALZ-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C66ALZ-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C66L(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C66L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C66L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C66LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C66LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C66LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C86A-X16(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C86A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
FAIRCHILD	NM93C86A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C86A-X8(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C86A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C86A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93C86AL(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C86AL-X16(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C86AL-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C86AL-X8(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C86AL-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C86ALZ-X16(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C86ALZ-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93C86ALZ-X8(DIP8)	EEPROM	NONE
FAIRCHILD	NM93C86ALZ-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93CS06(DIP8)	EEPROM	NONE
FAIRCHILD	NM93CS06(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93CS06(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93CS06L(DIP8)	EEPROM	NONE
FAIRCHILD	NM93CS06L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93CS06L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93CS06LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM93CS06LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93CS06LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93CS26(DIP8)	EEPROM	NONE
FAIRCHILD	NM93CS46(DIP8)	EEPROM	NONE
FAIRCHILD	NM93CS46(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93CS46(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93CS46L(DIP8)	EEPROM	NONE
FAIRCHILD	NM93CS46L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93CS46L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93CS46LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM93CS46LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93CS46LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93CS46T(DIP8)	EEPROM	NONE
FAIRCHILD	NM93CS46T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93CS46T(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93CS46TL(DIP8)	EEPROM	NONE
FAIRCHILD	NM93CS46TL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93CS46TL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93CS46TLZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM93CS46TLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93CS46TLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93CS56(DIP8)	EEPROM	NONE
FAIRCHILD	NM93CS56(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93CS56(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93CS56L(DIP8)	EEPROM	NONE
FAIRCHILD	NM93CS56L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93CS56L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93CS56LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM93CS56LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93CS56LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93CS66(DIP8)	EEPROM	NONE
FAIRCHILD	NM93CS66(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93CS66(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93CS66L(DIP8)	EEPROM	NONE
FAIRCHILD	NM93CS66L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
FAIRCHILD	NM93CS66L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93CS66LZ(DIP8)	EEPROM	NONE
FAIRCHILD	NM93CS66LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
FAIRCHILD	NM93CS66LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
FAIRCHILD	NM93S06(DIP8)	EEPROM	NONE
FAIRCHILD	NM93S46(DIP8)	EEPROM	NONE
FAIRCHILD	NM93S56(DIP8)	EEPROM	NONE
FAIRCHILD	NM93S66(DIP8)	EEPROM	NONE
FIDELIX	FM25D08-A1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25D08-A2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25D08-A3(PDIP8)	FLASH	NONE
FIDELIX	FM25D08-A4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25D08-A5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25D08-A6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25D08-B1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25D08-B2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25D08-B3(PDIP8)	FLASH	NONE
FIDELIX	FM25D08-B4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25D08-B5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25D08-B6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25D16-A1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25D16-A2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25D16-A3(PDIP8)	FLASH	NONE
FIDELIX	FM25D16-A4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25D16-A5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25D16-A6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25D16-B1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25D16-B2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25D16-B3(PDIP8)	FLASH	NONE
FIDELIX	FM25D16-B4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25D16-B5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25D16-B6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25D32-A1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25D32-A2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25D32-A3(PDIP8)	FLASH	NONE
FIDELIX	FM25D32-A4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25D32-A5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25D32-A6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25D32-B1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25D32-B2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25D32-B3(PDIP8)	FLASH	NONE
FIDELIX	FM25D32-B4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25D32-B5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25D32-B6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25D64-A1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25D64-A2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25D64-A3(PDIP8)	FLASH	NONE
FIDELIX	FM25D64-A4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25D64-A5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25D64-A6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25D64-B1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25D64-B2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25D64-B3(PDIP8)	FLASH	NONE
FIDELIX	FM25D64-B4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25D64-B5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25D64-B6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25M04A-B1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25M04A-B3(PDIP8)	FLASH	NONE
FIDELIX	FM25M04A-B4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25M04A-B5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25M04A-B7(VSOP8)	FLASH	LP-SOP-8PIN-B(207mil)

Manufacturer	Parts Number	Type	ADAPTER
FIDELIX	FM25M04A-BU(USON8)	FLASH	LP48-MLP8-2x3
FIDELIX	FM25M08A-B1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25M08A-B2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25M08A-B3(PDIP8)	FLASH	NONE
FIDELIX	FM25M08A-B4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25M08A-B5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25M08A-B7(VSOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25M08A-B8(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
FIDELIX	FM25M16A-B1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25M16A-B2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25M16A-B3(PDIP8)	FLASH	NONE
FIDELIX	FM25M16A-B4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25M16A-B5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25M16A-B7(VSOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25M16A-B8(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
FIDELIX	FM25M32A-B1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25M32A-B2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25M32A-B3(PDIP8)	FLASH	NONE
FIDELIX	FM25M32A-B4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25M32A-B7(VSOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25M64A-B1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25M64A-B2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25M64A-B3(PDIP8)	FLASH	NONE
FIDELIX	FM25M64A-B4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25M64A-B7(VSOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25Q08-A1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25Q08-A2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25Q08-A3(PDIP8)	FLASH	NONE
FIDELIX	FM25Q08-A4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25Q08-A5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25Q08-A6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25Q08-B1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25Q08-B2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25Q08-B3(PDIP8)	FLASH	NONE
FIDELIX	FM25Q08-B4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25Q08-B5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25Q08-B6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25Q16-1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25Q16-2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25Q16-3(PDIP8)	FLASH	NONE
FIDELIX	FM25Q16-4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25Q16-5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25Q16-6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25Q16-A1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25Q16-A2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25Q16-A3(PDIP8)	FLASH	NONE
FIDELIX	FM25Q16-A4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25Q16-A5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25Q16-A6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25Q16-B1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25Q16-B2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25Q16-B3(PDIP8)	FLASH	NONE
FIDELIX	FM25Q16-B4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25Q16-B5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25Q16-B6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25Q16B-A1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25Q16B-A2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25Q16B-A3(PDIP8)	FLASH	NONE

Manufacturer	Parts Number	Type	ADAPTER
FIDELIX	FM25Q16B-A4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25Q16B-A5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25Q16B-A7(VSOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25Q16B-A8(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
FIDELIX	FM25Q32-A1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25Q32-A2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25Q32-A3(PDIP8)	FLASH	NONE
FIDELIX	FM25Q32-A4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25Q32-A5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25Q32-A6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25Q32-B1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25Q32-B2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25Q32-B3(PDIP8)	FLASH	NONE
FIDELIX	FM25Q32-B4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25Q32-B5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25Q32-B6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25Q64-A1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25Q64-A2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25Q64-A3(PDIP8)	FLASH	NONE
FIDELIX	FM25Q64-A4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25Q64-A5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25Q64-A6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25Q64-B1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25Q64-B2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25Q64-B3(PDIP8)	FLASH	NONE
FIDELIX	FM25Q64-B4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25Q64-B5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25Q64-B6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25S08-A1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25S08-A2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25S08-A3(PDIP8)	FLASH	NONE
FIDELIX	FM25S08-A4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25S08-A5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25S08-A6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25S08-B1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25S08-B2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25S08-B3(PDIP8)	FLASH	NONE
FIDELIX	FM25S08-B4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25S08-B5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25S08-B6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25S16-A1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25S16-A2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25S16-A3(PDIP8)	FLASH	NONE
FIDELIX	FM25S16-A4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25S16-A5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25S16-A6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25S16-B1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25S16-B2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25S16-B3(PDIP8)	FLASH	NONE
FIDELIX	FM25S16-B4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25S16-B5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25S16-B6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25S32-A1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25S32-A2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25S32-A3(PDIP8)	FLASH	NONE
FIDELIX	FM25S32-A4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25S32-A5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25S32-A6(WSON8)	FLASH	LP48-WSON8-6x8

Manufacturer	Parts Number	Type	ADAPTER
FIDELIX	FM25S32-B1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25S32-B2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25S32-B3(PDIP8)	FLASH	NONE
FIDELIX	FM25S32-B4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25S32-B5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25S32-B6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25S64-A1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25S64-A2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25S64-A3(PDIP8)	FLASH	NONE
FIDELIX	FM25S64-A4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25S64-A5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25S64-A6(WSON8)	FLASH	LP48-WSON8-6x8
FIDELIX	FM25S64-B1(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
FIDELIX	FM25S64-B2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
FIDELIX	FM25S64-B3(PDIP8)	FLASH	NONE
FIDELIX	FM25S64-B4(WSON8)	FLASH	LP48-WSON8-5x6
FIDELIX	FM25S64-B5(SOP8)	FLASH	LP-SOP-16PIN(150mil)
FIDELIX	FM25S64-B6(WSON8)	FLASH	LP48-WSON8-6x8
Fremont	FT93C46AR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT93C46AR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT93C46R-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT93C46R-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T24C02(DIP8)	EEPROM	NONE
First-Rank Techn	T24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T24C02A(DIP8)	EEPROM	NONE
First-Rank Techn	T24C02A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T24C02A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T24C04(DIP8)	EEPROM	NONE
First-Rank Techn	T24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T24C04A(DIP8)	EEPROM	NONE
First-Rank Techn	T24C04A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T24C04A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T24C08(DIP8)	EEPROM	NONE
First-Rank Techn	T24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T24C08A(DIP8)	EEPROM	NONE
First-Rank Techn	T24C08A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T24C08A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T24C128(DIP8)	EEPROM	NONE
First-Rank Techn	T24C128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T24C128(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T24C128A(DIP8)	EEPROM	NONE
First-Rank Techn	T24C128A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T24C128A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T24C16(DIP8)	EEPROM	NONE
First-Rank Techn	T24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T24C16A(DIP8)	EEPROM	NONE
First-Rank Techn	T24C16A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T24C16A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T24C256(DIP8)	EEPROM	NONE
First-Rank Techn	T24C256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T24C256(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T24C256A(DIP8)	EEPROM	NONE
First-Rank Techn	T24C256A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T24C256A(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
First-Rank Techn	T24C32(DIP8)	EEPROM	NONE
First-Rank Techn	T24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T24C32A(DIP8)	EEPROM	NONE
First-Rank Techn	T24C32A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T24C32A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T24C64(DIP8)	EEPROM	NONE
First-Rank Techn	T24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T24C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T24C64A(DIP8)	EEPROM	NONE
First-Rank Techn	T24C64A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T24C64A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T93C46-X16(DIP8)	EEPROM	NONE
First-Rank Techn	T93C46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T93C46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T93C46-X8(DIP8)	EEPROM	NONE
First-Rank Techn	T93C46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T93C46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T93C46A-X16(DIP8)	EEPROM	NONE
First-Rank Techn	T93C46A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T93C46A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T93C46A-X8(DIP8)	EEPROM	NONE
First-Rank Techn	T93C46A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T93C46A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T93C56-X16(DIP8)	EEPROM	NONE
First-Rank Techn	T93C56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T93C56-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T93C56-X8(DIP8)	EEPROM	NONE
First-Rank Techn	T93C56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T93C56-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T93C56A-X16(DIP8)	EEPROM	NONE
First-Rank Techn	T93C56A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T93C56A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T93C56A-X8(DIP8)	EEPROM	NONE
First-Rank Techn	T93C56A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T93C56A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T93C66-X16(DIP8)	EEPROM	NONE
First-Rank Techn	T93C66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T93C66-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T93C66-X8(DIP8)	EEPROM	NONE
First-Rank Techn	T93C66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T93C66-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T93C66A-X16(DIP8)	EEPROM	NONE
First-Rank Techn	T93C66A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T93C66A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
First-Rank Techn	T93C66A-X8(DIP8)	EEPROM	NONE
First-Rank Techn	T93C66A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
First-Rank Techn	T93C66A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Forward	24LC01(DIP8)	EEPROM	NONE
Forward	24LC01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Forward	24LC02(DIP8)	EEPROM	NONE
Forward	24LC02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Forward	24LC04(DIP8)	EEPROM	NONE
Forward	24LC04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Forward	24LC08(DIP8)	EEPROM	NONE
Forward	24LC08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Forward	24LC16(DIP8)	EEPROM	NONE
Forward	24LC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
Forward	24LC32(DIP8)	EEPROM	NONE
Forward	24LC32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Forward	24LC64(DIP8)	EEPROM	NONE
Forward	24LC64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT24C02(DIP8)	EEPROM	NONE
Fremont	FT24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT24C02A(DIP8)	EEPROM	NONE
Fremont	FT24C02A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT24C02A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT24C02A-5(DIP8)	EEPROM	NONE
Fremont	FT24C02A-5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT24C02A-5(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT24C04(DIP8)	EEPROM	NONE
Fremont	FT24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT24C04A(DIP8)	EEPROM	NONE
Fremont	FT24C04A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT24C04A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT24C08(DIP8)	EEPROM	NONE
Fremont	FT24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT24C08A(DIP8)	EEPROM	NONE
Fremont	FT24C08A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT24C08A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT24C128(DIP8)	EEPROM	NONE
Fremont	FT24C128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT24C128(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT24C128A(DIP8)	EEPROM	NONE
Fremont	FT24C128A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT24C128A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT24C16(DIP8)	EEPROM	NONE
Fremont	FT24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT24C16A(DIP8)	EEPROM	NONE
Fremont	FT24C16A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT24C16A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT24C256(DIP8)	EEPROM	NONE
Fremont	FT24C256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT24C256(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT24C256A(DIP8)	EEPROM	NONE
Fremont	FT24C256A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT24C256A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT24C32(DIP8)	EEPROM	NONE
Fremont	FT24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT24C32A(DIP8)	EEPROM	NONE
Fremont	FT24C32A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT24C32A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT24C512(DIP8)	EEPROM	NONE
Fremont	FT24C512(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT24C512(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT24C512A(DIP8)	EEPROM	NONE
Fremont	FT24C512A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT24C512A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT24C64(DIP8)	EEPROM	NONE
Fremont	FT24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT24C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
Fremont	FT24C64A(DIP8)	EEPROM	NONE
Fremont	FT24C64A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT24C64A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT93C46-X16(DIP8)	EEPROM	NONE
Fremont	FT93C46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT93C46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT93C46-X8(DIP8)	EEPROM	NONE
Fremont	FT93C46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT93C46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT93C46A-X16(DIP8)	EEPROM	NONE
Fremont	FT93C46A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT93C46A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT93C46A-X8(DIP8)	EEPROM	NONE
Fremont	FT93C46A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT93C46A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT93C46AR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT93C46AR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT93C46R-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT93C46R-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT93C56-X16(DIP8)	EEPROM	NONE
Fremont	FT93C56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT93C56-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT93C56-X8(DIP8)	EEPROM	NONE
Fremont	FT93C56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT93C56-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT93C56A-X16(DIP8)	EEPROM	NONE
Fremont	FT93C56A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT93C56A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT93C56A-X8(DIP8)	EEPROM	NONE
Fremont	FT93C56A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT93C56A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT93C66-X16(DIP8)	EEPROM	NONE
Fremont	FT93C66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT93C66-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT93C66-X8(DIP8)	EEPROM	NONE
Fremont	FT93C66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT93C66-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT93C66A-X16(DIP8)	EEPROM	NONE
Fremont	FT93C66A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT93C66A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fremont	FT93C66A-X8(DIP8)	EEPROM	NONE
Fremont	FT93C66A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fremont	FT93C66A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM24C02(DIP8)	EEPROM	NONE
Fudan Microelect	FM24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM24C02A(DIP8)	EEPROM	NONE
Fudan Microelect	FM24C02A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM24C02A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM24C02B(DIP8)	EEPROM	NONE
Fudan Microelect	FM24C02B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM24C02B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM24C02C(DIP8)	EEPROM	NONE
Fudan Microelect	FM24C02C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM24C02C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM24C04(DIP8)	EEPROM	NONE
Fudan Microelect	FM24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
Fudan Microelect	FM24C04A(DIP8)	EEPROM	NONE
Fudan Microelect	FM24C04A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM24C04A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM24C04B(DIP8)	EEPROM	NONE
Fudan Microelect	FM24C04B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM24C04B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM24C08(DIP8)	EEPROM	NONE
Fudan Microelect	FM24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM24C08A(DIP8)	EEPROM	NONE
Fudan Microelect	FM24C08A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM24C08A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM24C08B(DIP8)	EEPROM	NONE
Fudan Microelect	FM24C08B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM24C08B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM24C1024A(DIP8)	EEPROM	NONE
Fudan Microelect	FM24C1024A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM24C1024A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM24C128A(DIP8)	EEPROM	NONE
Fudan Microelect	FM24C128A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM24C128A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM24C16(DIP8)	EEPROM	NONE
Fudan Microelect	FM24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM24C16A(DIP8)	EEPROM	NONE
Fudan Microelect	FM24C16A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM24C16A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM24C16B(DIP8)	EEPROM	NONE
Fudan Microelect	FM24C16B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM24C16B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM24C256A(DIP8)	EEPROM	NONE
Fudan Microelect	FM24C256A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM24C256A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM24C32A(DIP8)	EEPROM	NONE
Fudan Microelect	FM24C32A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM24C32A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM24C512A(DIP8)	EEPROM	NONE
Fudan Microelect	FM24C512A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM24C512A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM24C64A(DIP8)	EEPROM	NONE
Fudan Microelect	FM24C64A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM24C64A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM25F005(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Fudan Microelect	FM25F005(TDFN8)	FLASH	LP48-MLP8-2x3
Fudan Microelect	FM25F005(TSSOP8)	FLASH	LP-TSSOP-8PIN
Fudan Microelect	FM25F01(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Fudan Microelect	FM25F01(TDFN8)	FLASH	LP48-MLP8-2x3
Fudan Microelect	FM25F01(TSSOP8)	FLASH	LP-TSSOP-8PIN
Fudan Microelect	FM25F02(SOP8)	FLASH	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Fudan Microelect	FM25F02(TDFN8)	FLASH	LP48-MLP8-2x3
Fudan Microelect	FM25F04(SOP8)	FLASH	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Fudan Microelect	FM25F04(TDFN8)	FLASH	LP48-MLP8-2x3
Fudan Microelect	FM93C46-X16(DIP8)	EEPROM	NONE
Fudan Microelect	FM93C46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM93C46-X16(TDFN8)	EEPROM	LP48-MLP8-2x3
Fudan Microelect	FM93C46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM93C46-X8(DIP8)	EEPROM	NONE
Fudan Microelect	FM93C46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
Fudan Microelect	FM93C46-X8(TDFN8)	EEPROM	LP48-MLP8-2x3
Fudan Microelect	FM93C46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM93C56-X16(DIP8)	EEPROM	NONE
Fudan Microelect	FM93C56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM93C56-X16(TDFN8)	EEPROM	LP48-MLP8-2x3
Fudan Microelect	FM93C56-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM93C56-X8(DIP8)	EEPROM	NONE
Fudan Microelect	FM93C56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM93C56-X8(TDFN8)	EEPROM	LP48-MLP8-2x3
Fudan Microelect	FM93C56-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM93C66-X16(DIP8)	EEPROM	NONE
Fudan Microelect	FM93C66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM93C66-X16(TDFN8)	EEPROM	LP48-MLP8-2x3
Fudan Microelect	FM93C66-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fudan Microelect	FM93C66-X8(DIP8)	EEPROM	NONE
Fudan Microelect	FM93C66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Fudan Microelect	FM93C66-X8(TDFN8)	EEPROM	LP48-MLP8-2x3
Fudan Microelect	FM93C66-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Fujitsu	MBM27128A(DIP28)	EPROM	NONE
Fujitsu	MBM27256(DIP28)	EPROM	NONE
Fujitsu	MBM27C1000(DIP32)	EPROM	NONE
Fujitsu	MBM27C1000(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Fujitsu	MBM27C1000A(DIP32)	EPROM	NONE
Fujitsu	MBM27C1001(DIP32)	EPROM	NONE
Fujitsu	MBM27C1001(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Fujitsu	MBM27C1001A(DIP32)	EPROM	NONE
Fujitsu	MBM27C1024(DIP40)	EPROM	NONE
Fujitsu	MBM27C1024(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
Fujitsu	MBM27C1024A(DIP40)	EPROM	NONE
Fujitsu	MBM27C128(DIP28)	EPROM	NONE
Fujitsu	MBM27C128P(DIP28)	EPROM	NONE
Fujitsu	MBM27C2000(DIP32)	EPROM	NONE
Fujitsu	MBM27C2001(DIP32)	EPROM	NONE
Fujitsu	MBM27C2048(DIP40)	EPROM	NONE
Fujitsu	MBM27C256A(DIP28)	EPROM	NONE
Fujitsu	MBM27C256AP(DIP28)	EPROM	NONE
Fujitsu	MBM27C256H(DIP28)	EPROM	NONE
Fujitsu	MBM27C4000(DIP32)	EPROM	NONE
Fujitsu	MBM27C4001(DIP32)	EPROM	NONE
Fujitsu	MBM27C512(DIP28)	EPROM	NONE
Fujitsu	MBM27C512P(DIP28)	EPROM	NONE
Fujitsu	MBM28C256(DIP28)	EEPROM	NONE
Fujitsu	MBM28C64(DIP28)	EEPROM	NONE
Fujitsu	MBM28C65(DIP28)	EEPROM	NONE
Fujitsu	MBM29F160A(TSOP48)	FLASH	LP-TSOP-48S
Fujitsu	MBM29F400BC(SO44)	FLASH	LP48-PSOP-44PIN
Fujitsu	MBM29F400BC(TSOP48)	FLASH	LP-TSOP-48S
Fujitsu	MBM29F400TC(SO44)	FLASH	LP48-PSOP-44PIN
Fujitsu	MBM29F400TC(TSOP48)	FLASH	LP-TSOP-48S
Fujitsu	MBM29LV160B(TSOP48)	FLASH	LP-TSOP-48S
Fujitsu	MBM29LV160BE(TSOP48)	FLASH	LP-TSOP-48S
Fujitsu	MBM29LV160T(TSOP48)	FLASH	LP-TSOP-48S
Fujitsu	MBM29LV160TE(TSOP48)	FLASH	LP-TSOP-48S
Gatelevel	GM24LC02B(DIP8)	EEPROM	NONE
Gatelevel	GM24LC02B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Gatelevel	GM24LC02B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Gatelevel	GM24LC04B(DIP8)	EEPROM	NONE
Gatelevel	GM24LC04B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
Gatelevel	GM24LC08B(DIP8)	EEPROM	NONE
Gatelevel	GM24LC08B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Gatelevel	GM24LC16B(DIP8)	EEPROM	NONE
Gatelevel	GM24LC16B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Generalplus	GPR25L005E(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Generalplus	GPR25L011E(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Generalplus	GPR25L021B(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Generalplus	GPR25L041B(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Generalplus	GPR25L081B(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Generalplus	GPR25L162B(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Generalplus	GPR25L322B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Generalplus	GPR25L642B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GI	28C16-F(DIP24)	EEPROM	NONE
GI	28C16-F(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
GI	28C17-F(DIP28)	EEPROM	NONE
GI	28C17-F(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
GI	28C64-F(DIP28)	EEPROM	NONE
GI	28C64-F(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
GI	28C64X(DIP28)	EEPROM	NONE
GI	28C64X(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
GI	GI2764(DIP28)	EPROM	NONE
GI	GR27128(DIP28)	EPROM	NONE
Giantec Semicond	GT24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT24C01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT24C128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT24C128(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT24C256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT24C256(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT24C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT25C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT25C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT25C08(UDFN8)	EEPROM	LP48-MLP8-2x3
Giantec Semicond	GT25C128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT25C128(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT25C128A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT25C128A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT25C128A(UDFN8)	EEPROM	LP48-MLP8-2x3
Giantec Semicond	GT25C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT25C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT25C16(UDFN8)	EEPROM	LP48-MLP8-2x3
Giantec Semicond	GT25C256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT25C256(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT25C256(UDFN8)	EEPROM	LP48-MLP8-2x3
Giantec Semicond	GT25C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT25C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT25C32A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT25C32A(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
Giantec Semicond	GT25C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT25C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT25C64(UDFN8)	EEPROM	LP48-MLP8-2x3
Giantec Semicond	GT34C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT93C46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT93C46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT93C46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT93C46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT93C46A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT93C46A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT93C46A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT93C46A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT93C56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT93C56-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT93C56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT93C56-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT93C56A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT93C56A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT93C56A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT93C56A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT93C66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT93C66-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT93C66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT93C66-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT93C66A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT93C66A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT93C66A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT93C66A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT93C76-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT93C76-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT93C76-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT93C76-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT93C86-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT93C86-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Giantec Semicond	GT93C86-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Giantec Semicond	GT93C86-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
GIGADEVICE	GD25B128C-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25B128C-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25B128C-W(WSON8)	FLASH	LP48-WSON8-5x6
GIGADEVICE	GD25B128C-Y(WSON8)	FLASH	LP48-WSON8-6x8
GIGADEVICE	GD25B128C-Z(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
GIGADEVICE	GD25B16B-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
GIGADEVICE	GD25B16B-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25B16B-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25B16B-W(WSON8)	FLASH	LP48-WSON8-5x6
GIGADEVICE	GD25B16B-Z(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
GIGADEVICE	GD25B32B-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
GIGADEVICE	GD25B32B-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25B32B-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25B32B-W(WSON8)	FLASH	LP48-WSON8-5x6
GIGADEVICE	GD25B32B-Z(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
GIGADEVICE	GD25B64B-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
GIGADEVICE	GD25B64B-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25B64B-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25B64B-W(WSON8)	FLASH	LP48-WSON8-5x6
GIGADEVICE	GD25B64B-Z(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
GIGADEVICE	GD25D40-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25D40-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)

Manufacturer	Parts Number	Type	ADAPTER
GIGADEVICE	GD25D80-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25D80-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25E16-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25E16-T(SOP8)	FLASH	LP-SOP-16PIN(150mil)
GIGADEVICE	GD25E32-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25E32-T(SOP8)	FLASH	LP-SOP-16PIN(150mil)
GIGADEVICE	GD25E40-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25E40-T(SOP8)	FLASH	LP-SOP-16PIN(150mil)
GIGADEVICE	GD25E64-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
GIGADEVICE	GD25E64-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25E64-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25E64-W(WSON8)	FLASH	LP48-WSON8-5x6
GIGADEVICE	GD25E64-Z(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
GIGADEVICE	GD25E80-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25E80-T(SOP8)	FLASH	LP-SOP-16PIN(150mil)
GIGADEVICE	GD25F40-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25F40-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25F80-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25F80-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25LQ128-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
GIGADEVICE	GD25LQ128-Y(WSON)	FLASH	LP48-WSON8-6x8
GIGADEVICE	GD25LQ16-V(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25LQ32-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
GIGADEVICE	GD25LQ32-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25LQ32-W(WSON)	FLASH	LP48-WSON8-5x6
GIGADEVICE	GD25LQ32-Y(WSON)	FLASH	LP48-WSON8-6x8
GIGADEVICE	GD25LQ40-V(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25LQ64-V(TSOP8)	FLASH	LP-TSSOP-8PIN
GIGADEVICE	GD25LQ64-W(WSON)	FLASH	LP48-WSON8-5x6
GIGADEVICE	GD25LQ64-Y(WSON)	FLASH	LP48-WSON8-6x8
GIGADEVICE	GD25LQ64B-V(TSOP8)	FLASH	LP-TSSOP-8PIN
GIGADEVICE	GD25LQ64B-W(WSON)	FLASH	LP48-WSON8-5x6
GIGADEVICE	GD25LQ64B-Y(WSON)	FLASH	LP48-WSON8-6x8
GIGADEVICE	GD25LQ80-V(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25Q10-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25Q10-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25Q10-T(SOP8)	FLASH	LP-SOP-16PIN(150mil)
GIGADEVICE	GD25Q128B-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
GIGADEVICE	GD25Q128B-Y(WSON)	FLASH	LP48-WSON8-6x8
GIGADEVICE	GD25Q128C-F(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
GIGADEVICE	GD25Q128C-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25Q128C-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25Q128C-W(WSON8)	FLASH	LP48-WSON8-5x6
GIGADEVICE	GD25Q128C-Y(WSON8)	FLASH	LP48-WSON8-6x8
GIGADEVICE	GD25Q128C-Z(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
GIGADEVICE	GD25Q16-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25Q16-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25Q16-T(SOP8)	FLASH	LP-SOP-16PIN(150mil)
GIGADEVICE	GD25Q16B-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25Q16B-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25Q16B-T(SOP8)	FLASH	LP-SOP-16PIN(150mil)
GIGADEVICE	GD25Q16B-W(WSON8)	FLASH	LP48-WSON8-5x6
GIGADEVICE	GD25Q20-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25Q20-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25Q20-T(SOP8)	FLASH	LP-SOP-16PIN(150mil)
GIGADEVICE	GD25Q20B-O(TSSOP8)	FLASH	LP-TSSOP-8PIN
GIGADEVICE	GD25Q20B-T(SOP8)	FLASH	LP-SOP-16PIN(150mil)
GIGADEVICE	GD25Q20B-U(USON8)	FLASH	LP48-MLP8-2x3

Manufacturer	Parts Number	Type	ADAPTER
GIGADEVICE	GD25Q32-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25Q32-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25Q32-T(SOP8)	FLASH	LP-SOP-16PIN(150mil)
GIGADEVICE	GD25Q32B-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25Q32B-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25Q32B-V(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25Q32B-W(WSON8)	FLASH	LP48-WSON8-5x6
GIGADEVICE	GD25Q32B-Z(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
GIGADEVICE	GD25Q40-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25Q40-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25Q40-T(SOP8)	FLASH	LP-SOP-16PIN(150mil)
GIGADEVICE	GD25Q40B-O(TSSOP8)	FLASH	LP-TSSOP-8PIN
GIGADEVICE	GD25Q40B-T(SOP8)	FLASH	LP-SOP-16PIN(150mil)
GIGADEVICE	GD25Q40B-U(USON8)	FLASH	LP48-MLP8-2x3
GIGADEVICE	GD25Q512-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25Q512-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25Q512-T(SOP8)	FLASH	LP-SOP-16PIN(150mil)
GIGADEVICE	GD25Q64-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25Q64-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25Q64-T(SOP8)	FLASH	LP-SOP-16PIN(150mil)
GIGADEVICE	GD25Q64B-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25Q64B-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25Q64B-W(WSON)	FLASH	LP48-WSON8-5x6
GIGADEVICE	GD25Q64B-Z(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
GIGADEVICE	GD25Q80-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25Q80-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25Q80-T(SOP8)	FLASH	LP-SOP-16PIN(150mil)
GIGADEVICE	GD25Q80B-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25Q80B-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD25Q80B-T(SOP8)	FLASH	LP-SOP-16PIN(150mil)
GIGADEVICE	GD25Q80B-W(WSON8)	FLASH	LP48-WSON8-5x6
GIGADEVICE	GD25T80-P(DIP8)	FLASH	NONE
GIGADEVICE	GD25T80-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
GIGADEVICE	GD29GL064CAB(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
Green Engine	GE24C01(DIP8)	EEPROM	NONE
Green Engine	GE24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Green Engine	GE24C01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Green Engine	GE24C02(DIP8)	EEPROM	NONE
Green Engine	GE24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Green Engine	GE24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Green Engine	GE24C04(DIP8)	EEPROM	NONE
Green Engine	GE24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Green Engine	GE24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Greenliant	GLS29EE010(DIP32)	FLASH	NONE
Greenliant	GLS29EE010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29EE010(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Greenliant	GLS29EE010(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Greenliant	GLS29EE010A(DIP32)	FLASH	NONE
Greenliant	GLS29EE010A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29EE010A(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Greenliant	GLS29EE010A(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Greenliant	GLS29EE020(DIP32)	FLASH	NONE
Greenliant	GLS29EE020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29EE020(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Greenliant	GLS29EE020(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Greenliant	GLS29EE020A(DIP32)	FLASH	NONE
Greenliant	GLS29EE020A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29EE020A(TSOP32 8X14)	FLASH	LP48-VSOP-32S

Manufacturer	Parts Number	Type	ADAPTER
Greenliant	GLS29EE020A(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Greenliant	GLS29EE512(DIP32)	FLASH	NONE
Greenliant	GLS29EE512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29EE512(TSOP32)	FLASH	LP48-TSOP-32S
Greenliant	GLS29EE512A(DIP32)	FLASH	NONE
Greenliant	GLS29EE512A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29EE512A(TSOP32)	FLASH	LP48-TSOP-32S
Greenliant	GLS29LE010(DIP32)	FLASH	NONE
Greenliant	GLS29LE010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29LE010(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Greenliant	GLS29LE010(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Greenliant	GLS29LE010A(DIP32)	FLASH	NONE
Greenliant	GLS29LE010A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29LE010A(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Greenliant	GLS29LE010A(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Greenliant	GLS29LE020(DIP32)	FLASH	NONE
Greenliant	GLS29LE020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29LE020(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Greenliant	GLS29LE020(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Greenliant	GLS29LE020A(DIP32)	FLASH	NONE
Greenliant	GLS29LE020A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29LE020A(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Greenliant	GLS29LE020A(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Greenliant	GLS29LE512(DIP32)	FLASH	NONE
Greenliant	GLS29LE512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29LE512(TSOP32)	FLASH	LP48-TSOP-32S
Greenliant	GLS29LE512A(DIP32)	FLASH	NONE
Greenliant	GLS29LE512A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29LE512A(TSOP32)	FLASH	LP48-TSOP-32S
Greenliant	GLS29SF010(DIP32)	FLASH	NONE
Greenliant	GLS29SF010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29SF010(TSOP32)	FLASH	LP48-VSOP-32S
Greenliant	GLS29SF020(DIP32)	FLASH	NONE
Greenliant	GLS29SF020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29SF020(TSOP32)	FLASH	LP48-VSOP-32S
Greenliant	GLS29SF040(DIP32)	FLASH	NONE
Greenliant	GLS29SF040(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29SF040(TSOP32)	FLASH	LP48-VSOP-32S
Greenliant	GLS29SF512(DIP32)	FLASH	NONE
Greenliant	GLS29SF512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29SF512(TSOP32)	FLASH	LP48-VSOP-32S
Greenliant	GLS29VE010(DIP32)	FLASH	NONE
Greenliant	GLS29VE010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29VE010(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Greenliant	GLS29VE010(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Greenliant	GLS29VE010A(DIP32)	FLASH	NONE
Greenliant	GLS29VE010A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29VE010A(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Greenliant	GLS29VE010A(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Greenliant	GLS29VE020(DIP32)	FLASH	NONE
Greenliant	GLS29VE020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29VE020(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Greenliant	GLS29VE020(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Greenliant	GLS29VE020A(DIP32)	FLASH	NONE
Greenliant	GLS29VE020A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29VE020A(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Greenliant	GLS29VE020A(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Greenliant	GLS29VE512(DIP32)	FLASH	NONE

Manufacturer	Parts Number	Type	ADAPTER
Greenliant	GLS29VE512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29VE512(TSOP32)	FLASH	LP48-TSOP-32S
Greenliant	GLS29VE512A(DIP32)	FLASH	NONE
Greenliant	GLS29VE512A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29VE512A(TSOP32)	FLASH	LP48-TSOP-32S
Greenliant	GLS29VF010(DIP32)	FLASH	NONE
Greenliant	GLS29VF010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29VF010(TSOP32)	FLASH	LP48-VSOP-32S
Greenliant	GLS29VF020(DIP32)	FLASH	NONE
Greenliant	GLS29VF020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29VF020(TSOP32)	FLASH	LP48-VSOP-32S
Greenliant	GLS29VF040(DIP32)	FLASH	NONE
Greenliant	GLS29VF040(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29VF040(TSOP32)	FLASH	LP48-VSOP-32S
Greenliant	GLS29VF512(DIP32)	FLASH	NONE
Greenliant	GLS29VF512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Greenliant	GLS29VF512(TSOP32)	FLASH	LP48-VSOP-32S
GTM	GSC24BC01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
GTM	GSC24BC02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
GTM	GSC24BC04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
GTM	GSC24BC08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
GTM	GSC24BC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
GTM	GSC93BC46A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
GTM	GSC93BC46A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
GTM	GSC93BC46B-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
GTM	GSC93BC46B-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
GTM	GSC93BC56A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
GTM	GSC93BC56A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
GTM	GSC93BC56B-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
GTM	GSC93BC56B-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
GTM	GSC93BC66A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
GTM	GSC93BC66A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
GTM	GSC93BC66B-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
GTM	GSC93BC66B-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HITACHI	HN27128A(DIP28)	EPROM	NONE
HITACHI	HN27128AG(DIP28)	EPROM	NONE
HITACHI	HN27256G(DIP28)	EPROM	NONE
HITACHI	HN27512G(DIP28)	EPROM	NONE
HITACHI	HN27C101A(DIP32)	EPROM	NONE
HITACHI	HN27C101AG(DIP32)	EPROM	NONE
HITACHI	HN27C101G(DIP32)	EPROM	NONE
HITACHI	HN27C1024(DIP40)	EPROM	NONE
HITACHI	HN27C1024(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
HITACHI	HN27C128(DIP28)	EPROM	NONE
HITACHI	HN27C256AG(DIP28)	EPROM	NONE
HITACHI	HN27C256HG(DIP28)	EPROM	NONE
HITACHI	HN27C4096(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
HITACHI	HN27C4096ACC(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
HITACHI	HN27C4096G(DIP40)	EPROM	NONE
HITACHI	HN58C65FP(SOP28)	EEPROM	LP-SOP-28PIN-A(330mil)
HITACHI	HN58C65P(DIP28)	EEPROM	NONE
HITACHI	HN58C66FP(SOP28)	EEPROM	LP-SOP-28PIN-A(330mil)
HITACHI	HN58C66P(DIP28)	EEPROM	NONE
HITACHI	HN58V65AFP(SOP28)	EEPROM	LP-SOP-28PIN-A(330mil)
HITACHI	HN58V65AP(DIP28)	EEPROM	NONE
HITACHI	HN58V66AFP(SOP28)	EEPROM	LP-SOP-28PIN-A(330mil)
HITACHI	HN58V66AP(DIP28)	EEPROM	NONE
HOLTEK	HT24C01(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
HOLTEK	HT24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT24C02(DIP8)	EEPROM	NONE
HOLTEK	HT24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT24C04(DIP8)	EEPROM	NONE
HOLTEK	HT24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT24C08(DIP8)	EEPROM	NONE
HOLTEK	HT24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT24C16(DIP8)	EEPROM	NONE
HOLTEK	HT24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT24LC01(DIP8)	EEPROM	NONE
HOLTEK	HT24LC01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT24LC01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
HOLTEK	HT24LC02(DIP8)	EEPROM	NONE
HOLTEK	HT24LC02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT24LC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
HOLTEK	HT24LC04(DIP8)	EEPROM	NONE
HOLTEK	HT24LC04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT24LC04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
HOLTEK	HT24LC08(DIP8)	EEPROM	NONE
HOLTEK	HT24LC08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT24LC08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
HOLTEK	HT24LC16(DIP8)	EEPROM	NONE
HOLTEK	HT24LC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT24LC32(DIP8)	EEPROM	NONE
HOLTEK	HT24LC32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT24LC32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
HOLTEK	HT24LC64(DIP8)	EEPROM	NONE
HOLTEK	HT24LC64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT24LC64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
HOLTEK	HT27C010(DIP32)	EPROM	NONE
HOLTEK	HT27C010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
HOLTEK	HT27C010(SOP32)	EPROM	LP48-SOP-32PIN
HOLTEK	HT27C020(DIP32)	EPROM	NONE
HOLTEK	HT27C020(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
HOLTEK	HT27C020(SOP32)	EPROM	LP48-SOP-32PIN
HOLTEK	HT27C040(DIP32)	EPROM	NONE
HOLTEK	HT27C040(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
HOLTEK	HT27C040(SOP32)	EPROM	LP48-SOP-32PIN
HOLTEK	HT27C256(DIP28)	EPROM	NONE
HOLTEK	HT27C512(DIP28)	EPROM	NONE
HOLTEK	HT27C512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
HOLTEK	HT27LC010(DIP32)	EPROM	NONE
HOLTEK	HT27LC010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
HOLTEK	HT27LC010(SOP32)	EPROM	LP48-SOP-32PIN
HOLTEK	HT27LC020(DIP32)	EPROM	NONE
HOLTEK	HT27LC020(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
HOLTEK	HT27LC020(SOP32)	EPROM	LP48-SOP-32PIN
HOLTEK	HT27LC040(DIP32)	EPROM	NONE
HOLTEK	HT27LC040(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
HOLTEK	HT27LC040(SOP32)	EPROM	LP48-SOP-32PIN
HOLTEK	HT27LC256(DIP28)	EPROM	NONE
HOLTEK	HT27LC512(DIP28)	EPROM	NONE
HOLTEK	HT27PC010(DIP32)	EPROM	NONE
HOLTEK	HT27PC020(DIP32)	EPROM	NONE
HOLTEK	HT27PC256(DIP28)	EPROM	NONE
HOLTEK	HT27PC256(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
HOLTEK	HT27PC512(DIP28)	EPROM	NONE
HOLTEK	HT27PC512(PLCC28)	EPROM	LP48-PLCC-28PIN

Manufacturer	Parts Number	Type	ADAPTER
HOLTEK	HT45R37(SOP20)	MPU / MCU	LP-SOP-20PIN(300mil) or LP-SOP-28PIN-B(300mil)
HOLTEK	HT93C46(DIP8)	EEPROM	NONE
HOLTEK	HT93C46-A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C46-B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C56-B-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C56-B-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C56-C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C56-C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C56-D-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C56-D-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C56A-X16(DIP8)	EEPROM	NONE
HOLTEK	HT93C56A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C56A-X8(DIP8)	EEPROM	NONE
HOLTEK	HT93C56A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C56B-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C56B-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C56C(DIP8)	EEPROM	NONE
HOLTEK	HT93C56C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C56D(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C66-A-X16(DIP8)	EEPROM	NONE
HOLTEK	HT93C66-A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C66-A-X8(DIP8)	EEPROM	NONE
HOLTEK	HT93C66-A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C66-B-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C66-B-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C66-C(DIP8)	EEPROM	NONE
HOLTEK	HT93C66-C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C66-C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C66-C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C66-D(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C66-D-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C66-D-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C76-X16(DIP8)	EEPROM	NONE
HOLTEK	HT93C76-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C76-X8(DIP8)	EEPROM	NONE
HOLTEK	HT93C76-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C86-X16(DIP8)	EEPROM	NONE
HOLTEK	HT93C86-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93C86-X8(DIP8)	EEPROM	NONE
HOLTEK	HT93C86-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC46(DIP8)	EEPROM	NONE
HOLTEK	HT93LC46(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC46-B-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC46-B-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC46A-X16(DIP8)	EEPROM	NONE
HOLTEK	HT93LC46A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC46A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
HOLTEK	HT93LC46A-X8(DIP8)	EEPROM	NONE
HOLTEK	HT93LC46A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC46A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
HOLTEK	HT93LC46B-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC46B-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC56(DIP8)	EEPROM	NONE
HOLTEK	HT93LC56(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC56-B-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC56-B-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC56-C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC56-C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
HOLTEK	HT93LC56A-X16(DIP8)	EEPROM	NONE
HOLTEK	HT93LC56A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC56A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
HOLTEK	HT93LC56A-X8(DIP8)	EEPROM	NONE
HOLTEK	HT93LC56A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC56A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
HOLTEK	HT93LC56B-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC56B-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC56C(DIP8)	EEPROM	NONE
HOLTEK	HT93LC56C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC56D(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC66(DIP8)	EEPROM	NONE
HOLTEK	HT93LC66(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC66-A-X16(DIP8)	EEPROM	NONE
HOLTEK	HT93LC66-A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC66-A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
HOLTEK	HT93LC66-A-X8(DIP8)	EEPROM	NONE
HOLTEK	HT93LC66-A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC66-A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
HOLTEK	HT93LC66-B-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC66-B-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC66-C(DIP8)	EEPROM	NONE
HOLTEK	HT93LC66-C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC66-C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC66-C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC66-D(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC76-A-X16(DIP8)	EEPROM	NONE
HOLTEK	HT93LC76-A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC76-A-X8(DIP8)	EEPROM	NONE
HOLTEK	HT93LC76-A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC76-X16(DIP8)	EEPROM	NONE
HOLTEK	HT93LC76-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC76-X8(DIP8)	EEPROM	NONE
HOLTEK	HT93LC76-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC86-A-X16(DIP8)	EEPROM	NONE
HOLTEK	HT93LC86-A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC86-A-X8(DIP8)	EEPROM	NONE
HOLTEK	HT93LC86-A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC86-B-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC86-B-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC86-X16(DIP8)	EEPROM	NONE
HOLTEK	HT93LC86-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
HOLTEK	HT93LC86-X8(DIP8)	EEPROM	NONE
HOLTEK	HT93LC86-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hopefind	HM24LC01(DIP8)	EEPROM	NONE
Hopefind	HM24LC01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hopefind	HM24LC01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hopefind	HM24LC02(DIP8)	EEPROM	NONE
Hopefind	HM24LC02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hopefind	HM24LC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hopefind	HM24LC04(DIP8)	EEPROM	NONE
Hopefind	HM24LC04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hopefind	HM24LC04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hopefind	HM24LC08(DIP8)	EEPROM	NONE
Hopefind	HM24LC08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hopefind	HM24LC08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hopefind	HM24LC16(DIP8)	EEPROM	NONE
Hopefind	HM24LC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
Hopefind	HM24LC16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hopefind	HM24LC32(DIP8)	EEPROM	NONE
Hopefind	HM24LC32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hopefind	HM24LC32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hopefind	HM24LC64(DIP8)	EEPROM	NONE
Hopefind	HM24LC64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hopefind	HM24LC64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Hong NEC	K24C02(DIP8)	EEPROM	NONE
Hua Hong NEC	K24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Hong NEC	K24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Hong NEC	K24C02C(DIP8)	EEPROM	NONE
Hua Hong NEC	K24C02C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Hong NEC	K24C02C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Hong NEC	K24C04(DIP8)	EEPROM	NONE
Hua Hong NEC	K24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Hong NEC	K24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Hong NEC	K24C08(DIP8)	EEPROM	NONE
Hua Hong NEC	K24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Hong NEC	K24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Hong NEC	K24C08C(DIP8)	EEPROM	NONE
Hua Hong NEC	K24C08C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Hong NEC	K24C08C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Hong NEC	K24C128(DIP8)	EEPROM	NONE
Hua Hong NEC	K24C128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Hong NEC	K24C128(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Hong NEC	K24C16(DIP8)	EEPROM	NONE
Hua Hong NEC	K24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Hong NEC	K24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Hong NEC	K24C256(DIP8)	EEPROM	NONE
Hua Hong NEC	K24C256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Hong NEC	K24C256(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Hong NEC	K24C32(DIP8)	EEPROM	NONE
Hua Hong NEC	K24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Hong NEC	K24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Hong NEC	K24C64(DIP8)	EEPROM	NONE
Hua Hong NEC	K24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Hong NEC	K24C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Hong NEC	K25F04-P(PDIP8)	FLASH	NONE
Hua Hong NEC	K25F04-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Hua Hong NEC	K25F04-T(TSSOP8)	FLASH	LP-TSSOP-8PIN
Hua Hong NEC	K93C46-X16(DIP8)	EEPROM	NONE
Hua Hong NEC	K93C46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Hong NEC	K93C46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Hong NEC	K93C46-X8(DIP8)	EEPROM	NONE
Hua Hong NEC	K93C46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Hong NEC	K93C46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Hong NEC	K93C56-X16(DIP8)	EEPROM	NONE
Hua Hong NEC	K93C56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Hong NEC	K93C56-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Hong NEC	K93C56-X8(DIP8)	EEPROM	NONE
Hua Hong NEC	K93C56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Hong NEC	K93C56-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Hong NEC	K93C66-X16(DIP8)	EEPROM	NONE
Hua Hong NEC	K93C66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Hong NEC	K93C66-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Hong NEC	K93C66-X8(DIP8)	EEPROM	NONE
Hua Hong NEC	K93C66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Hong NEC	K93C66-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
Hua Jie Tech	K24C02(DIP8)	EEPROM	NONE
Hua Jie Tech	K24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Jie Tech	K24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Jie Tech	K24C02C(DIP8)	EEPROM	NONE
Hua Jie Tech	K24C02C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Jie Tech	K24C02C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Jie Tech	K24C04(DIP8)	EEPROM	NONE
Hua Jie Tech	K24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Jie Tech	K24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Jie Tech	K24C08(DIP8)	EEPROM	NONE
Hua Jie Tech	K24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Jie Tech	K24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Jie Tech	K24C08C(DIP8)	EEPROM	NONE
Hua Jie Tech	K24C08C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Jie Tech	K24C08C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Jie Tech	K24C128(DIP8)	EEPROM	NONE
Hua Jie Tech	K24C128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Jie Tech	K24C128(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Jie Tech	K24C16(DIP8)	EEPROM	NONE
Hua Jie Tech	K24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Jie Tech	K24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Jie Tech	K24C256(DIP8)	EEPROM	NONE
Hua Jie Tech	K24C256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Jie Tech	K24C256(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Jie Tech	K24C32(DIP8)	EEPROM	NONE
Hua Jie Tech	K24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Jie Tech	K24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Jie Tech	K24C64(DIP8)	EEPROM	NONE
Hua Jie Tech	K24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Jie Tech	K24C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Jie Tech	K25F04-P(PDIP8)	FLASH	NONE
Hua Jie Tech	K25F04-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Hua Jie Tech	K25F04-T(TSSOP8)	FLASH	LP-TSSOP-8PIN
Hua Jie Tech	K34C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Jie Tech	K93C46-X16(DIP8)	EEPROM	NONE
Hua Jie Tech	K93C46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Jie Tech	K93C46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Jie Tech	K93C46-X8(DIP8)	EEPROM	NONE
Hua Jie Tech	K93C46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Jie Tech	K93C46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Jie Tech	K93C56-X16(DIP8)	EEPROM	NONE
Hua Jie Tech	K93C56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Jie Tech	K93C56-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Jie Tech	K93C56-X8(DIP8)	EEPROM	NONE
Hua Jie Tech	K93C56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Jie Tech	K93C56-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Jie Tech	K93C66-X16(DIP8)	EEPROM	NONE
Hua Jie Tech	K93C66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Jie Tech	K93C66-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Hua Jie Tech	K93C66-X8(DIP8)	EEPROM	NONE
Hua Jie Tech	K93C66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hua Jie Tech	K93C66-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
HYNIX	HY29DS162B(TSOP48)	FLASH	LP-TSOP-48S
HYNIX	HY29DS162T(TSOP48)	FLASH	LP-TSOP-48S
HYNIX	HY29DS163B(TSOP48)	FLASH	LP-TSOP-48S
HYNIX	HY29DS163TT(TSOP48)	FLASH	LP-TSOP-48S
HYNIX	HY29F400BT(TSOP48)	FLASH	LP-TSOP-48S
HYNIX	HY29F400TT(TSOP48)	FLASH	LP-TSOP-48S

Manufacturer	Parts Number	Type	ADAPTER
HYNIX	HY29F800BT(TSOP48)	FLASH	LP-TSOP-48S
HYNIX	HY29F800TT(TSOP48)	FLASH	LP-TSOP-48S
HYNIX	HY29LV160B(TSOP48)	FLASH	LP-TSOP-48S
HYNIX	HY29LV160T(TSOP48)	FLASH	LP-TSOP-48S
HYNIX	HY93C46(DIP8)	EEPROM	NONE
HYNIX	HY93C46(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Hyundai	HY27C64(DIP28)	EPROM	NONE
Hyundai	HY27C64A(DIP28)	EPROM	NONE
Hyundai	HY29F400BT(TSOP48)	FLASH	LP-TSOP-48S
Hyundai	HY29F400TT(TSOP48)	FLASH	LP-TSOP-48S
Hyundai	HY29F800BT(TSOP48)	FLASH	LP-TSOP-48S
Hyundai	HY29F800TT(TSOP48)	FLASH	LP-TSOP-48S
Hyundai	HY29LV160B(TSOP48)	FLASH	LP-TSOP-48S
Hyundai	HY29LV160T(TSOP48)	FLASH	LP-TSOP-48S
Hyundai	HY93C46(DIP8)	EEPROM	NONE
Hyundai	HY93C46(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24001(DIP8)	EEPROM	NONE
IC Microsystems	X24001(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24001-2.7(DIP8)	EEPROM	NONE
IC Microsystems	X24001-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24001-3(DIP8)	EEPROM	NONE
IC Microsystems	X24001-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24012(DIP8)	EEPROM	NONE
IC Microsystems	X24012(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24012-2.7(DIP8)	EEPROM	NONE
IC Microsystems	X24012-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24012-3(DIP8)	EEPROM	NONE
IC Microsystems	X24012-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X2402(DIP8)	EEPROM	NONE
IC Microsystems	X24022(DIP8)	EEPROM	NONE
IC Microsystems	X24022(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24022(TSSOP8)	EEPROM	LP-TSSOP-8PIN
IC Microsystems	X24022-2.7(DIP8)	EEPROM	NONE
IC Microsystems	X24022-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24022-2.7(TSSOP8)	EEPROM	LP-TSSOP-8PIN
IC Microsystems	X24022-3(DIP8)	EEPROM	NONE
IC Microsystems	X24022-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24022-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
IC Microsystems	X2404(DIP8)	EEPROM	NONE
IC Microsystems	X24042(DIP8)	EEPROM	NONE
IC Microsystems	X24042(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24042-2.7(DIP8)	EEPROM	NONE
IC Microsystems	X24042-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24042-3(DIP8)	EEPROM	NONE
IC Microsystems	X24042-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24164(DIP8)	EEPROM	NONE
IC Microsystems	X24164(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24164-2.7(DIP8)	EEPROM	NONE
IC Microsystems	X24164-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24164-3(DIP8)	EEPROM	NONE
IC Microsystems	X24164-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24165(DIP8)	EEPROM	NONE
IC Microsystems	X24165(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24165-2.7(DIP8)	EEPROM	NONE
IC Microsystems	X24165-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24257-1.8(TSSOP8)	EEPROM	LP-TSSOP-20PIN
IC Microsystems	X24257-A8(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
IC Microsystems	X24257-A8-1.8(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)

Manufacturer	Parts Number	Type	ADAPTER
IC Microsystems	X24257-A8-2.5(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
IC Microsystems	X24257-S8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24257-S8-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24257-S8-2.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24320(DIP8)	EEPROM	NONE
IC Microsystems	X24320(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24320-1.8(DIP8)	EEPROM	NONE
IC Microsystems	X24320-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24320-2.5(DIP8)	EEPROM	NONE
IC Microsystems	X24320-2.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24320-2.5(TSSOP8)	EEPROM	LP-TSSOP-20PIN
IC Microsystems	X24321(DIP8)	EEPROM	NONE
IC Microsystems	X24321(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24321-1.8(DIP8)	EEPROM	NONE
IC Microsystems	X24321-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24321-2.5(DIP8)	EEPROM	NONE
IC Microsystems	X24321-2.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24325(DIP8)	EEPROM	NONE
IC Microsystems	X24325(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24325-2.7(DIP8)	EEPROM	NONE
IC Microsystems	X24325-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24640(DIP8)	EEPROM	NONE
IC Microsystems	X24640(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24640-1.8(DIP8)	EEPROM	NONE
IC Microsystems	X24640-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24640-18(DIP8)	EEPROM	NONE
IC Microsystems	X24640-18(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24640-2.7(DIP8)	EEPROM	NONE
IC Microsystems	X24640-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24641(DIP8)	EEPROM	NONE
IC Microsystems	X24641(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24641-1.8(DIP8)	EEPROM	NONE
IC Microsystems	X24641-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24641-18(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24641-2.5(DIP8)	EEPROM	NONE
IC Microsystems	X24641-2.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24645(DIP8)	EEPROM	NONE
IC Microsystems	X24645(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24645-1.8(DIP8)	EEPROM	NONE
IC Microsystems	X24645-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24645-2.5(DIP8)	EEPROM	NONE
IC Microsystems	X24645-2.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C00(DIP8)	EEPROM	NONE
IC Microsystems	X24C00(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C00-2.7(DIP8)	EEPROM	NONE
IC Microsystems	X24C00-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C00-3(DIP8)	EEPROM	NONE
IC Microsystems	X24C00-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C01(DIP8)	EEPROM	NONE
IC Microsystems	X24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C01-2.7(DIP8)	EEPROM	NONE
IC Microsystems	X24C01-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C01-3(DIP8)	EEPROM	NONE
IC Microsystems	X24C01-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C01-3.5(DIP8)	EEPROM	NONE
IC Microsystems	X24C01-3.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C01A(DIP8)	EEPROM	NONE
IC Microsystems	X24C01A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
IC Microsystems	X24C01A-3(DIP8)	EEPROM	NONE
IC Microsystems	X24C01A-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C01A-3.5(DIP8)	EEPROM	NONE
IC Microsystems	X24C01A-3.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C02(DIP8)	EEPROM	NONE
IC Microsystems	X24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C02-2.7(DIP8)	EEPROM	NONE
IC Microsystems	X24C02-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C02-3(DIP8)	EEPROM	NONE
IC Microsystems	X24C02-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C02-3.5(DIP8)	EEPROM	NONE
IC Microsystems	X24C02-3.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C04(DIP8)	EEPROM	NONE
IC Microsystems	X24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
IC Microsystems	X24C04-1.8(DIP8)	EEPROM	NONE
IC Microsystems	X24C04-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C04-1.8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
IC Microsystems	X24C04-2.7(DIP8)	EEPROM	NONE
IC Microsystems	X24C04-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C04-2.7(TSSOP8)	EEPROM	LP-TSSOP-8PIN
IC Microsystems	X24C04-3(DIP8)	EEPROM	NONE
IC Microsystems	X24C04-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C04-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
IC Microsystems	X24C04-3.5(DIP8)	EEPROM	NONE
IC Microsystems	X24C04-3.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C04-3.5(TSSOP8)	EEPROM	LP-TSSOP-8PIN
IC Microsystems	X24C08(DIP8)	EEPROM	NONE
IC Microsystems	X24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C08-2.7(DIP8)	EEPROM	NONE
IC Microsystems	X24C08-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C08-3(DIP8)	EEPROM	NONE
IC Microsystems	X24C08-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C08-3.5(DIP8)	EEPROM	NONE
IC Microsystems	X24C08-3.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C16(DIP8)	EEPROM	NONE
IC Microsystems	X24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C16-1.8(DIP8)	EEPROM	NONE
IC Microsystems	X24C16-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C16-2.7(DIP8)	EEPROM	NONE
IC Microsystems	X24C16-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C16-3(DIP8)	EEPROM	NONE
IC Microsystems	X24C16-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24C16-3.5(DIP8)	EEPROM	NONE
IC Microsystems	X24C16-3.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24F016(DIP8)	EEPROM	NONE
IC Microsystems	X24F016(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24F016-5(DIP8)	EEPROM	NONE
IC Microsystems	X24F016-5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24F032(DIP8)	EEPROM	NONE
IC Microsystems	X24F032(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24F032-5(DIP8)	EEPROM	NONE
IC Microsystems	X24F032-5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24F064(DIP8)	EEPROM	NONE
IC Microsystems	X24F064(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24F064-5(DIP8)	EEPROM	NONE
IC Microsystems	X24F064-5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IC Microsystems	X24F128(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
IC Microsystems	X24F128-5(DIP8)	EEPROM	NONE
ICE	ICE24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICE	ICE27C010(DIP32)	EPROM	NONE
ICE	ICE27C010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ICE	ICE27C010(TSOP32)	EPROM	LP48-TSOP-32S
ICE	ICE27C512(DIP28)	EPROM	NONE
ICE	ICE27C512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ICE	ICE27C512(TSOP28)	EPROM	LP48-TSOP-28PIN
ICE	ICE27LC512(DIP28)	EPROM	NONE
ICE	ICE27LC512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ICE	ICE27LC512(TSOP28)	EPROM	LP48-TSOP-28PIN
ICSI	IS24C01-3(DIP8)	EEPROM	NONE
ICSI	IS24C01-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C01-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C01-5(DIP8)	EEPROM	NONE
ICSI	IS24C01-5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C01-5(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C01B(DIP8)	EEPROM	NONE
ICSI	IS24C01B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C01B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C01C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C01C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C02-3(DIP8)	EEPROM	NONE
ICSI	IS24C02-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C02-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C02-5(DIP8)	EEPROM	NONE
ICSI	IS24C02-5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C02-5(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C02A-2(DIP8)	EEPROM	NONE
ICSI	IS24C02A-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C02A-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C02A-3(DIP8)	EEPROM	NONE
ICSI	IS24C02A-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C02A-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C02B(DIP8)	EEPROM	NONE
ICSI	IS24C02B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C02B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C02C-2(DIP8)	EEPROM	NONE
ICSI	IS24C02C-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C02C-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C02D-3(DIP8)	EEPROM	NONE
ICSI	IS24C02D-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C02D-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C02E-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C02E-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C04-3(DIP8)	EEPROM	NONE
ICSI	IS24C04-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C04-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C04-5(DIP8)	EEPROM	NONE
ICSI	IS24C04-5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C04-5(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C04A-2(DIP8)	EEPROM	NONE
ICSI	IS24C04A-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C04A-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C04A-3(DIP8)	EEPROM	NONE
ICSI	IS24C04A-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C04A-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C04B-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
ICSI	IS24C04B-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C08-3(DIP8)	EEPROM	NONE
ICSI	IS24C08-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C08-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C08-5(DIP8)	EEPROM	NONE
ICSI	IS24C08-5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C08-5(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C08A-2(DIP8)	EEPROM	NONE
ICSI	IS24C08A-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C08A-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C08A-3(DIP8)	EEPROM	NONE
ICSI	IS24C08A-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C08A-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C08B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C08B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C128-3(DIP8)	EEPROM	NONE
ICSI	IS24C128-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C128A-2G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C128A-2P(DIP8)	EEPROM	NONE
ICSI	IS24C128A-2W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ICSI	IS24C128A-3G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C128A-3P(DIP8)	EEPROM	NONE
ICSI	IS24C128A-3W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ICSI	IS24C128B-2G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C128B-2P(DIP8)	EEPROM	NONE
ICSI	IS24C128B-2W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ICSI	IS24C128B-2Z(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C128B-3G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C128B-3P(DIP8)	EEPROM	NONE
ICSI	IS24C128B-3W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ICSI	IS24C128B-3Z(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C16-3(DIP8)	EEPROM	NONE
ICSI	IS24C16-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C16-5(DIP8)	EEPROM	NONE
ICSI	IS24C16-5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C16A-2(DIP8)	EEPROM	NONE
ICSI	IS24C16A-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C16A-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C16A-3(DIP8)	EEPROM	NONE
ICSI	IS24C16A-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C16A-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C16B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C16B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C256-2(DIP8)	EEPROM	NONE
ICSI	IS24C256-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C256-3(DIP8)	EEPROM	NONE
ICSI	IS24C256-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C256A-2G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C256A-2P(DIP8)	EEPROM	NONE
ICSI	IS24C256A-2W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ICSI	IS24C256A-3G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C256A-3P(DIP8)	EEPROM	NONE
ICSI	IS24C256A-3W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ICSI	IS24C256B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C256B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C32-2(DIP8)	EEPROM	NONE
ICSI	IS24C32-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C32-3(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
ICSI	IS24C32-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C32A-2(DIP8)	EEPROM	NONE
ICSI	IS24C32A-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C32A-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C32B-2(DIP8)	EEPROM	NONE
ICSI	IS24C32B-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C32B-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C32C-2(DIP8)	EEPROM	NONE
ICSI	IS24C32C-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C32C-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C32C-3(DIP8)	EEPROM	NONE
ICSI	IS24C32C-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C32C-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C64-2(DIP8)	EEPROM	NONE
ICSI	IS24C64-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C64-3(DIP8)	EEPROM	NONE
ICSI	IS24C64-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C64A-2(DIP8)	EEPROM	NONE
ICSI	IS24C64A-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C64A-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C64B-2(DIP8)	EEPROM	NONE
ICSI	IS24C64B-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C64B-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24C64C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24C64C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS24L128-2G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24L128-2P(DIP8)	EEPROM	NONE
ICSI	IS24L128-2W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ICSI	IS24L128-3G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS24L128-3P(DIP8)	EEPROM	NONE
ICSI	IS24L128-3W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ICSI	IS24L256-2P(DIP8)	EEPROM	NONE
ICSI	IS24L256-2W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ICSI	IS24L256-3P(DIP8)	EEPROM	NONE
ICSI	IS24L256-3W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ICSI	IS93C46-3(DIP8)	EEPROM	NONE
ICSI	IS93C46-3G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C46-3GR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C46A-X16(DIP8)	EEPROM	NONE
ICSI	IS93C46A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS93C46A-X8(DIP8)	EEPROM	NONE
ICSI	IS93C46A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS93C46AG-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C46AG-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C46AGR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C46AGR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C46B(DIP8)	EEPROM	NONE
ICSI	IS93C46B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS93C46BG(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C46BGR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C46D-2G-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C46D-2G-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C46D-2GR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C46D-2GR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C46D-2P-X16(DIP8)	EEPROM	NONE
ICSI	IS93C46D-2P-X8(DIP8)	EEPROM	NONE
ICSI	IS93C46D-2Z-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS93C46D-2Z-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
ICSI	IS93C46D-3G-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C46D-3G-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C46D-3GR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C46D-3GR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C46D-3P-X16(DIP8)	EEPROM	NONE
ICSI	IS93C46D-3P-X8(DIP8)	EEPROM	NONE
ICSI	IS93C46D-3Z-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS93C46D-3Z-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS93C56-3(DIP8)	EEPROM	NONE
ICSI	IS93C56-3G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C56-3GR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C56A-2-X16(DIP8)	EEPROM	NONE
ICSI	IS93C56A-2-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS93C56A-2-X8(DIP8)	EEPROM	NONE
ICSI	IS93C56A-2-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS93C56A-2G-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C56A-2G-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C56A-2GR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C56A-2GR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C56A-3-X16(DIP8)	EEPROM	NONE
ICSI	IS93C56A-3-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS93C56A-3-X8(DIP8)	EEPROM	NONE
ICSI	IS93C56A-3-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS93C56A-3G-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C56A-3G-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C56A-3GR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C56A-3GR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C66-3(DIP8)	EEPROM	NONE
ICSI	IS93C66-3G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C66-3GR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C66A-2-X16(DIP8)	EEPROM	NONE
ICSI	IS93C66A-2-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS93C66A-2-X8(DIP8)	EEPROM	NONE
ICSI	IS93C66A-2-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS93C66A-2G-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C66A-2G-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C66A-2GR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C66A-2GR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C66A-3-X16(DIP8)	EEPROM	NONE
ICSI	IS93C66A-3-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS93C66A-3-X8(DIP8)	EEPROM	NONE
ICSI	IS93C66A-3-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS93C66A-3G-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C66A-3G-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C66A-3GR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C66A-3GR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C76A-2-X16(DIP8)	EEPROM	NONE
ICSI	IS93C76A-2-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C76A-2-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS93C76A-2-X8(DIP8)	EEPROM	NONE
ICSI	IS93C76A-2-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C76A-2-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS93C76A-3-X16(DIP8)	EEPROM	NONE
ICSI	IS93C76A-3-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C76A-3-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS93C76A-3-X8(DIP8)	EEPROM	NONE
ICSI	IS93C76A-3-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C76A-3-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
ICSI	IS93C86A-2-X16(DIP8)	EEPROM	NONE
ICSI	IS93C86A-2-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C86A-2-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS93C86A-2-X8(DIP8)	EEPROM	NONE
ICSI	IS93C86A-2-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C86A-2-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS93C86A-3-X16(DIP8)	EEPROM	NONE
ICSI	IS93C86A-3-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C86A-3-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICSI	IS93C86A-3-X8(DIP8)	EEPROM	NONE
ICSI	IS93C86A-3-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICSI	IS93C86A-3-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ICT	93C46(DIP8)	EEPROM	NONE
ICT	93C46(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICT	93C46A(DIP8)	EEPROM	NONE
ICT	93C46AK(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICT	93C46AS(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICT	93CX56(DIP8)	EEPROM	NONE
ICT	93CX56(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ICT	93CX66(DIP8)	EEPROM	NONE
ICT	93CX66(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IK Semiconductor	IN24LC02B(DIP8)	EEPROM	NONE
IK Semiconductor	IN24LC02B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IK Semiconductor	IN24LC04(DIP8)	EEPROM	NONE
IK Semiconductor	IN24LC04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IK Semiconductor	IN24LC04B(DIP8)	EEPROM	NONE
IK Semiconductor	IN24LC04B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IK Semiconductor	IN24LC08(DIP8)	EEPROM	NONE
IK Semiconductor	IN24LC08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IK Semiconductor	IN24LC08B(DIP8)	EEPROM	NONE
IK Semiconductor	IN24LC08B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IK Semiconductor	IN24LC16(DIP8)	EEPROM	NONE
IK Semiconductor	IN24LC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
IK Semiconductor	IN24LC16B(DIP8)	EEPROM	NONE
IK Semiconductor	IN24LC16B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLA24C01(DIP8)	EEPROM	NONE
Infineon	SLA24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLA24C01-3(DIP8)	EEPROM	NONE
Infineon	SLA24C01-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLA24C02(DIP8)	EEPROM	NONE
Infineon	SLA24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLA24C02-3(DIP8)	EEPROM	NONE
Infineon	SLA24C02-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLA24C04(DIP8)	EEPROM	NONE
Infineon	SLA24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLA24C04-3(DIP8)	EEPROM	NONE
Infineon	SLA24C04-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLA24C08(DIP8)	EEPROM	NONE
Infineon	SLA24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLA24C08-3(DIP8)	EEPROM	NONE
Infineon	SLA24C08-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLA24C16(DIP8)	EEPROM	NONE
Infineon	SLA24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLA24C16-3(DIP8)	EEPROM	NONE
Infineon	SLA24C16-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLA24C164(DIP8)	EEPROM	NONE
Infineon	SLA24C164(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLA24C164-3(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
Infineon	SLA24C164-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLA24C32(DIP8)	EEPROM	NONE
Infineon	SLA24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLA24C32-3(DIP8)	EEPROM	NONE
Infineon	SLA24C32-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLA24C64(DIP8)	EEPROM	NONE
Infineon	SLA24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLA24C64-3(DIP8)	EEPROM	NONE
Infineon	SLA24C64-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLE24C01(DIP8)	EEPROM	NONE
Infineon	SLE24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLE24C02(DIP8)	EEPROM	NONE
Infineon	SLE24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLE24C04(DIP8)	EEPROM	NONE
Infineon	SLE24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLE24C08(DIP8)	EEPROM	NONE
Infineon	SLE24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLE24C16(DIP8)	EEPROM	NONE
Infineon	SLE24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLE24C164(DIP8)	EEPROM	NONE
Infineon	SLE24C164(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLE24C32(DIP8)	EEPROM	NONE
Infineon	SLE24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Infineon	SLE24C64(DIP8)	EEPROM	NONE
Infineon	SLE24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN24AA02A(DIP8)	EEPROM	NONE
Integral	IN24AA02A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN24AA02B(DIP8)	EEPROM	NONE
Integral	IN24AA02B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN24AA32A(DIP8)	EEPROM	NONE
Integral	IN24AA32A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN24LC02B(DIP8)	EEPROM	NONE
Integral	IN24LC02B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN24LC04(DIP8)	EEPROM	NONE
Integral	IN24LC04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN24LC04B(DIP8)	EEPROM	NONE
Integral	IN24LC04B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN24LC08(DIP8)	EEPROM	NONE
Integral	IN24LC08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN24LC08B(DIP8)	EEPROM	NONE
Integral	IN24LC08B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN24LC16(DIP8)	EEPROM	NONE
Integral	IN24LC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN24LC16B(DIP8)	EEPROM	NONE
Integral	IN24LC16B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN24LC32A(DIP8)	EEPROM	NONE
Integral	IN24LC32A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93AA46A(DIP8)	EEPROM	NONE
Integral	IN93AA46A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93AA46B(DIP8)	EEPROM	NONE
Integral	IN93AA46B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93AA46C-X16(DIP8)	EEPROM	NONE
Integral	IN93AA46C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93AA46C-X8(DIP8)	EEPROM	NONE
Integral	IN93AA46C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93AA56A(DIP8)	EEPROM	NONE
Integral	IN93AA56A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93AA56B(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
Integral	IN93AA56B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93AA56C-X16(DIP8)	EEPROM	NONE
Integral	IN93AA56C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93AA56C-X8(DIP8)	EEPROM	NONE
Integral	IN93AA56C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93AA66A(DIP8)	EEPROM	NONE
Integral	IN93AA66A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93AA66B(DIP8)	EEPROM	NONE
Integral	IN93AA66B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93AA66C-X16(DIP8)	EEPROM	NONE
Integral	IN93AA66C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93AA66C-X8(DIP8)	EEPROM	NONE
Integral	IN93AA66C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93AA86A(DIP8)	EEPROM	NONE
Integral	IN93AA86A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93AA86B(DIP8)	EEPROM	NONE
Integral	IN93AA86B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93AA86C-X16(DIP8)	EEPROM	NONE
Integral	IN93AA86C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93AA86C-X8(DIP8)	EEPROM	NONE
Integral	IN93AA86C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93LC46A(DIP8)	EEPROM	NONE
Integral	IN93LC46A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93LC46B(DIP8)	EEPROM	NONE
Integral	IN93LC46B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93LC46C-X16(DIP8)	EEPROM	NONE
Integral	IN93LC46C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93LC46C-X8(DIP8)	EEPROM	NONE
Integral	IN93LC46C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93LC56A(DIP8)	EEPROM	NONE
Integral	IN93LC56A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93LC56B(DIP8)	EEPROM	NONE
Integral	IN93LC56B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93LC56C-X16(DIP8)	EEPROM	NONE
Integral	IN93LC56C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93LC56C-X8(DIP8)	EEPROM	NONE
Integral	IN93LC56C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93LC66A(DIP8)	EEPROM	NONE
Integral	IN93LC66A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93LC66B(DIP8)	EEPROM	NONE
Integral	IN93LC66B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93LC66C-X16(DIP8)	EEPROM	NONE
Integral	IN93LC66C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93LC66C-X8(DIP8)	EEPROM	NONE
Integral	IN93LC66C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93LC86A(DIP8)	EEPROM	NONE
Integral	IN93LC86A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93LC86B(DIP8)	EEPROM	NONE
Integral	IN93LC86B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93LC86C-X16(DIP8)	EEPROM	NONE
Integral	IN93LC86C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Integral	IN93LC86C-X8(DIP8)	EEPROM	NONE
Integral	IN93LC86C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
intel	27010(DIP32)	EPROM	NONE
intel	27010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
intel	27128A(DIP28)	EPROM	NONE
intel	27256(DIP28)	EPROM	NONE
intel	27512(DIP28)	EPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
intel	27512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
intel	27C010(DIP32)	EPROM	NONE
intel	27C010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
intel	27C020(DIP32)	EPROM	NONE
intel	27C020(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
intel	27C040(DIP32)	EPROM	NONE
intel	27C040(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
intel	27C100(DIP40)	EPROM	NONE
intel	27C256(DIP28)	EPROM	NONE
intel	27C400(DIP40)	EPROM	NONE
intel	27C400(SOP40)	EPROM	LP48-SOP-40PIN
intel	27C400(TSOP48)	EPROM	LP-TSOP-48S
intel	27C512(DIP28)	EPROM	NONE
intel	27C512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
intel	2817A(DIP28)	EEPROM	NONE
intel	D27128B(DIP28)	EPROM	NONE
intel	D2732B(DIP24)	EPROM	NONE
intel	D2764A(DIP28)	EPROM	NONE
intel	D27C256(DIP28)	EPROM	NONE
intel	D27C64(DIP28)	EPROM	NONE
intel	E28F004B5B(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
intel	E28F004B5T(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
intel	E28F016SC(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
intel	E28F128J3A(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	E28F200B5B(TSOP48)	FLASH	LP-TSOP-48S
intel	E28F200B5T(TSOP48)	FLASH	LP-TSOP-48S
intel	E28F256J3A(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	E28F320J3A(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	E28F400B5B(TSOP48)	FLASH	LP-TSOP-48S
intel	E28F400B5T(TSOP48)	FLASH	LP-TSOP-48S
intel	E28F640J3A(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	E28F800B5B(TSOP48)	FLASH	LP-TSOP-48S
intel	E28F800B5T(TSOP48)	FLASH	LP-TSOP-48S
intel	JR28F032M29EWB(TSOP48)	FLASH	LP-TSOP-48S
intel	JR28F032M29EWH(TSOP48)	FLASH	LP-TSOP-48S
intel	JR28F032M29EWL(TSOP48)	FLASH	LP-TSOP-48S
intel	JR28F032M29EWT(TSOP48)	FLASH	LP-TSOP-48S
intel	JR28F064M29EWB(TSOP48)	FLASH	LP-TSOP-48S
intel	JR28F064M29EWH(TSOP48)	FLASH	LP-TSOP-48S
intel	JR28F064M29EWL(TSOP48)	FLASH	LP-TSOP-48S
intel	JR28F064M29EWT(TSOP48)	FLASH	LP-TSOP-48S
intel	JS28F00AM29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
intel	JS28F00AM29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
intel	JS28F00BM29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
intel	JS28F00BM29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
intel	JS28F032M29EWB(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
intel	JS28F032M29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
intel	JS28F032M29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
intel	JS28F032M29EWT(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
intel	JS28F064M29EWB(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
intel	JS28F064M29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
intel	JS28F064M29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
intel	JS28F064M29EWT(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
intel	JS28F128J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	JS28F128J3D(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	JS28F128J3F(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	JS28F128M29EWB(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
intel	JS28F128M29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)

Manufacturer	Parts Number	Type	ADAPTER
intel	JS28F128M29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
intel	JS28F128M29EWT(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
intel	JS28F128P30B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	JS28F128P30BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	JS28F128P30T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	JS28F128P30TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	JS28F256J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	JS28F256J3F(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	JS28F256M29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
intel	JS28F256M29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
intel	JS28F256P30B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	JS28F256P30BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	JS28F256P30T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	JS28F256P30TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	JS28F256P33BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	JS28F256P33TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	JS28F320J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	JS28F320J3D(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	JS28F320J3F(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	JS28F512M29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
intel	JS28F512M29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
intel	JS28F640J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	JS28F640J3D(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	JS28F640J3F(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	JS28F640P30B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	JS28F640P30BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	JS28F640P30T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	JS28F640P30TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	JS28F640P33B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	JS28F640P33T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	N28F001BX-B(DIP32)	EEPROM	NONE
intel	N28F001BX-B(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
intel	N28F001BX-B(TSOP32)	EEPROM	LP48-TSOP-32S
intel	N28F001BX-T(DIP32)	EEPROM	NONE
intel	N28F001BX-T(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
intel	N28F001BX-T(TSOP32)	EEPROM	LP48-TSOP-32S
intel	P27128A(DIP28)	EPROM	NONE
intel	P2764A(DIP28)	EPROM	NONE
intel	PC28F00AM29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
intel	PC28F00AM29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
intel	PC28F00BM29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
intel	PC28F00BM29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
intel	PC28F128J3C(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
intel	PC28F128J3D(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
intel	PC28F128J3F(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
intel	PC28F128M29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
intel	PC28F128M29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
intel	PC28F128P30B(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
intel	PC28F128P30BF(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
intel	PC28F128P30T(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
intel	PC28F128P30TF(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
intel	PC28F256J3C(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
intel	PC28F256J3D(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
intel	PC28F256J3F(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
intel	PC28F256M29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
intel	PC28F256M29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
intel	PC28F256P30B(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
intel	PC28F256P30BF(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)

[illegible]

Manufacturer	Parts Number	Type	ADAPTER
intel	RC28F640P30T(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
intel	RC28F640P30TF(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
intel	TE28F004B3B(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
intel	TE28F004B3T(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
intel	TE28F008B3B(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
intel	TE28F008B3T(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
intel	TE28F016B3B(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
intel	TE28F016B3T(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
intel	TE28F128J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	TE28F128J3D(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	TE28F128P30B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	TE28F128P30BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	TE28F128P30T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	TE28F128P30TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	TE28F160B3B(TSOP48)	FLASH	LP-TSOP-48S
intel	TE28F160B3T(TSOP48)	FLASH	LP-TSOP-48S
intel	TE28F256J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	TE28F256J3F(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	TE28F256P30B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	TE28F256P30BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	TE28F256P30T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	TE28F256P30TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	TE28F256P33BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	TE28F256P33TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	TE28F320B3B(TSOP48)	FLASH	LP-TSOP-48S
intel	TE28F320B3T(TSOP48)	FLASH	LP-TSOP-48S
intel	TE28F320J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	TE28F320J3D(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	TE28F400B3B(TSOP48)	FLASH	LP-TSOP-48S
intel	TE28F400B3T(TSOP48)	FLASH	LP-TSOP-48S
intel	TE28F640B3B(TSOP48)	FLASH	LP-TSOP-48S
intel	TE28F640B3T(TSOP48)	FLASH	LP-TSOP-48S
intel	TE28F640J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	TE28F640J3D(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
intel	TE28F640P30B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	TE28F640P30BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	TE28F640P30T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	TE28F640P30TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	TE28F640P33B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	TE28F640P33T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
intel	TE28F800B3B(TSOP48)	FLASH	LP-TSOP-48S
intel	TE28F800B3T(TSOP48)	FLASH	LP-TSOP-48S
Intersil	X28C010(DIP32)	EEPROM	NONE
Intersil	X28C010(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Intersil	X28C010(TSOP40)	EEPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
Intersil	X28C512(DIP32)	EEPROM	NONE
Intersil	X28C512(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Intersil	X28C512(TSOP40)	EEPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
Intersil	X28C513(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Intersil	X28HC256(DIP28)	EEPROM	NONE
Intersil	X28HC256(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Intersil	X28HC256(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
Intersil	X28HC256(TSOP32)	EEPROM	LP48-TSOP-32S
Intersil	X28HC64(DIP28)	EEPROM	NONE
Intersil	X28HC64(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Intersil	X28HC64(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
Intersil	X28HC64(TSOP32)	EEPROM	LP48-TSOP-32S
ISSI	IS24C01(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
ISSI	IS24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C01-3(DIP8)	EEPROM	NONE
ISSI	IS24C01-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C01-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C01-5(DIP8)	EEPROM	NONE
ISSI	IS24C01-5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C01-5(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C01B(DIP8)	EEPROM	NONE
ISSI	IS24C01B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C01B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C01C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C01C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C02(DIP8)	EEPROM	NONE
ISSI	IS24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C02-3(DIP8)	EEPROM	NONE
ISSI	IS24C02-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C02-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C02-5(DIP8)	EEPROM	NONE
ISSI	IS24C02-5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C02-5(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C02A(DIP8)	EEPROM	NONE
ISSI	IS24C02A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C02A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C02A-2(DIP8)	EEPROM	NONE
ISSI	IS24C02A-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C02A-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C02A-3(DIP8)	EEPROM	NONE
ISSI	IS24C02A-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C02A-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C02B(DIP8)	EEPROM	NONE
ISSI	IS24C02B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C02B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C02C(DIP8)	EEPROM	NONE
ISSI	IS24C02C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C02C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C02C-2(DIP8)	EEPROM	NONE
ISSI	IS24C02C-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C02C-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C02D(DIP8)	EEPROM	NONE
ISSI	IS24C02D(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C02D(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C02D-3(DIP8)	EEPROM	NONE
ISSI	IS24C02D-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C02D-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C02E(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C02E(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C02E-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C02E-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C04(DIP8)	EEPROM	NONE
ISSI	IS24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C04-3(DIP8)	EEPROM	NONE
ISSI	IS24C04-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C04-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C04-5(DIP8)	EEPROM	NONE
ISSI	IS24C04-5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
ISSI	IS24C04-5(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C04A(DIP8)	EEPROM	NONE
ISSI	IS24C04A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C04A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C04A-2(DIP8)	EEPROM	NONE
ISSI	IS24C04A-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C04A-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C04A-3(DIP8)	EEPROM	NONE
ISSI	IS24C04A-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C04A-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C04B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C04B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C04B-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C04B-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C08(DIP8)	EEPROM	NONE
ISSI	IS24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C08-3(DIP8)	EEPROM	NONE
ISSI	IS24C08-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C08-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C08-5(DIP8)	EEPROM	NONE
ISSI	IS24C08-5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C08-5(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C08A(DIP8)	EEPROM	NONE
ISSI	IS24C08A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C08A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C08A-2(DIP8)	EEPROM	NONE
ISSI	IS24C08A-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C08A-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C08A-3(DIP8)	EEPROM	NONE
ISSI	IS24C08A-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C08A-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C08B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C08B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C128(DIP8)	EEPROM	NONE
ISSI	IS24C128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C128-3(DIP8)	EEPROM	NONE
ISSI	IS24C128-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C128A(DIP8)	EEPROM	NONE
ISSI	IS24C128A(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ISSI	IS24C128A-2G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C128A-2P(DIP8)	EEPROM	NONE
ISSI	IS24C128A-2W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ISSI	IS24C128A-3G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C128A-3P(DIP8)	EEPROM	NONE
ISSI	IS24C128A-3W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ISSI	IS24C128B-2(DIP8)	EEPROM	NONE
ISSI	IS24C128B-2(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ISSI	IS24C128B-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C128B-2G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C128B-2P(DIP8)	EEPROM	NONE
ISSI	IS24C128B-2W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ISSI	IS24C128B-2Z(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C128B-3(DIP8)	EEPROM	NONE
ISSI	IS24C128B-3(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ISSI	IS24C128B-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C128B-3G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C128B-3P(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
ISSI	IS24C128B-3W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ISSI	IS24C128B-3Z(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C16-3(DIP8)	EEPROM	NONE
ISSI	IS24C16-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C16-5(DIP8)	EEPROM	NONE
ISSI	IS24C16-5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C16A(DIP8)	EEPROM	NONE
ISSI	IS24C16A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C16A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C16A-2(DIP8)	EEPROM	NONE
ISSI	IS24C16A-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C16A-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C16A-3(DIP8)	EEPROM	NONE
ISSI	IS24C16A-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C16A-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C16B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C16B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C256(DIP8)	EEPROM	NONE
ISSI	IS24C256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C256-2(DIP8)	EEPROM	NONE
ISSI	IS24C256-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C256-3(DIP8)	EEPROM	NONE
ISSI	IS24C256-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C256A(DIP8)	EEPROM	NONE
ISSI	IS24C256A(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ISSI	IS24C256A-2G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C256A-2P(DIP8)	EEPROM	NONE
ISSI	IS24C256A-2W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ISSI	IS24C256A-3G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C256A-3P(DIP8)	EEPROM	NONE
ISSI	IS24C256A-3W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ISSI	IS24C256B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C256B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C32(DIP8)	EEPROM	NONE
ISSI	IS24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C32-2(DIP8)	EEPROM	NONE
ISSI	IS24C32-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C32-3(DIP8)	EEPROM	NONE
ISSI	IS24C32-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C32A(DIP8)	EEPROM	NONE
ISSI	IS24C32A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C32A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C32A-2(DIP8)	EEPROM	NONE
ISSI	IS24C32A-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C32A-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C32B(DIP8)	EEPROM	NONE
ISSI	IS24C32B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C32B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C32B-2(DIP8)	EEPROM	NONE
ISSI	IS24C32B-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C32B-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C32C(DIP8)	EEPROM	NONE
ISSI	IS24C32C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C32C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C32C-2(DIP8)	EEPROM	NONE
ISSI	IS24C32C-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C32C-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C32C-3(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
ISSI	IS24C32C-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C32C-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C64(DIP8)	EEPROM	NONE
ISSI	IS24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C64-2(DIP8)	EEPROM	NONE
ISSI	IS24C64-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C64-3(DIP8)	EEPROM	NONE
ISSI	IS24C64-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C64A(DIP8)	EEPROM	NONE
ISSI	IS24C64A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C64A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C64A-2(DIP8)	EEPROM	NONE
ISSI	IS24C64A-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C64A-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C64B(DIP8)	EEPROM	NONE
ISSI	IS24C64B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C64B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C64B-2(DIP8)	EEPROM	NONE
ISSI	IS24C64B-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C64B-2(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24C64C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24C64C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS24L128(DIP8)	EEPROM	NONE
ISSI	IS24L128(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ISSI	IS24L128-2G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24L128-2P(DIP8)	EEPROM	NONE
ISSI	IS24L128-2W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ISSI	IS24L128-3G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24L128-3P(DIP8)	EEPROM	NONE
ISSI	IS24L128-3W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ISSI	IS24L256(DIP8)	EEPROM	NONE
ISSI	IS24L256(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ISSI	IS24L256-2G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24L256-2P(DIP8)	EEPROM	NONE
ISSI	IS24L256-2W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ISSI	IS24L256-3G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS24L256-3P(DIP8)	EEPROM	NONE
ISSI	IS24L256-3W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ISSI	IS25LD010-JD(TSSOP8)	FLASH	LP-TSSOP-8PIN
ISSI	IS25LD010-JN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25LD010-JP(WSON8)	FLASH	LP48-WSON8-5x6
ISSI	IS25LD010-JU(USON8)	FLASH	LP48-MLP8-2x3
ISSI	IS25LD010-JV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25LD020-JD(TSSOP8)	FLASH	LP-TSSOP-8PIN
ISSI	IS25LD020-JN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25LD020-JP(WSON8)	FLASH	LP48-WSON8-5x6
ISSI	IS25LD020-JU(USON8)	FLASH	LP48-MLP8-2x3
ISSI	IS25LD020-JV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25LD025C-JD(TSSOP8)	FLASH	LP-TSSOP-8PIN
ISSI	IS25LD025C-JN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25LD040-JA(PDIP8)	FLASH	NONE
ISSI	IS25LD040-JB(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ISSI	IS25LD040-JN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25LD040-JP(WSON8)	FLASH	LP48-WSON8-5x6
ISSI	IS25LD040-JV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25LD512-JD(TSSOP8)	FLASH	LP-TSSOP-8PIN
ISSI	IS25LD512-JN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25LD512-JP(WSON8)	FLASH	LP48-WSON8-5x6

Manufacturer	Parts Number	Type	ADAPTER
ISSI	IS25LD512-JU(USON8)	FLASH	LP48-MLP8-2x3
ISSI	IS25LD512-JV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25LQ016-JA(PDIP8)	FLASH	NONE
ISSI	IS25LQ016-JB(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ISSI	IS25LQ016-JF(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25LQ016-JP(WSON8)	FLASH	LP48-WSON8-5x6
ISSI	IS25LQ032-JD(TSSOP8)	FLASH	LP-TSSOP-8PIN
ISSI	IS25LQ032-JN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25LQ032-JP(WSON8)	FLASH	LP48-WSON8-5x6
ISSI	IS25LQ032-JV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25LQ032C-JD(TSSOP8)	FLASH	LP-TSSOP-8PIN
ISSI	IS25LQ032C-JN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25LQ032C-JP(WSON8)	FLASH	LP48-WSON8-5x6
ISSI	IS25LQ032C-JV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25LQ040-JA(PDIP8)	FLASH	NONE
ISSI	IS25LQ040-JB(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ISSI	IS25LQ040-JN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25LQ040-JP(WSON8)	FLASH	LP48-WSON8-5x6
ISSI	IS25LQ040-JV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25LQ064-JB(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ISSI	IS25LQ064-JF(VSOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ISSI	IS25LQ064-JM(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ISSI	IS25LQ064-JN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25LQ064-JP(WSON8)	FLASH	LP48-WSON8-5x6
ISSI	IS25LQ080-JA(PDIP8)	FLASH	NONE
ISSI	IS25LQ080-JB(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ISSI	IS25LQ080-JP(WSON8)	FLASH	LP48-WSON8-5x6
ISSI	IS25LQ080-JV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25LQ128-JB(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ISSI	IS25LQ128-JM(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ISSI	IS25LQ128-JN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25LQ128-JP(WSON8)	FLASH	LP48-WSON8-5x6
ISSI	IS25WD020-JA(PDIP8)	FLASH	NONE
ISSI	IS25WD020-JB(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ISSI	IS25WD020-JN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25WD020-JP(WSON8)	FLASH	LP48-WSON8-5x6
ISSI	IS25WD020-JV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25WD040-JA(PDIP8)	FLASH	NONE
ISSI	IS25WD040-JB(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ISSI	IS25WD040-JN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25WD040-JP(WSON8)	FLASH	LP48-WSON8-5x6
ISSI	IS25WD040-JV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25WQ080-JA(PDIP8)	FLASH	NONE
ISSI	IS25WQ080-JB(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ISSI	IS25WQ080-JM(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ISSI	IS25WQ080-JN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS25WQ080-JP(WSON8)	FLASH	LP48-WSON8-5x6
ISSI	IS25WQ080-JV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
ISSI	IS27C256(DIP28)	EPROM	NONE
ISSI	IS27C512(DIP28)	EPROM	NONE
ISSI	IS27C512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ISSI	IS27HC010(DIP32)	EPROM	NONE
ISSI	IS27HC010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ISSI	IS27HC020(DIP32)	EPROM	NONE
ISSI	IS27HC020(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ISSI	IS27HC256(DIP28)	EPROM	NONE
ISSI	IS27HC512(DIP28)	EPROM	NONE
ISSI	IS27HC512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S

Manufacturer	Parts Number	Type	ADAPTER
ISSI	IS34C02(DFN8)	EEPROM	LP48-MLP8-2x3
ISSI	IS34C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS34C02B(DFN8)	EEPROM	LP48-MLP8-2x3
ISSI	IS34C02B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS39LV010(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
ISSI	IS39LV010(VSOP32)	FLASH	LP48-VSOP-32S
ISSI	IS39LV040(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
ISSI	IS39LV040(VSOP32)	FLASH	LP48-VSOP-32S
ISSI	IS39LV512(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
ISSI	IS39LV512(VSOP32)	FLASH	LP48-VSOP-32S
ISSI	IS49FL004T(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
ISSI	IS49FL004T(VSOP32)	FLASH	LP48-VSOP-32S
ISSI	IS93C46-3(DIP8)	EEPROM	NONE
ISSI	IS93C46-3G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C46-3GR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C46A-X16(DIP8)	EEPROM	NONE
ISSI	IS93C46A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C46A-X8(DIP8)	EEPROM	NONE
ISSI	IS93C46A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C46AG-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C46AG-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C46AGR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C46AGR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C46B(DIP8)	EEPROM	NONE
ISSI	IS93C46B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C46BG(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C46BGR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C46D-2G-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C46D-2G-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C46D-2GR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C46D-2GR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C46D-2P-X16(DIP8)	EEPROM	NONE
ISSI	IS93C46D-2P-X8(DIP8)	EEPROM	NONE
ISSI	IS93C46D-2Z-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C46D-2Z-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C46D-3G-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C46D-3G-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C46D-3GR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C46D-3GR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C46D-3P-X16(DIP8)	EEPROM	NONE
ISSI	IS93C46D-3P-X8(DIP8)	EEPROM	NONE
ISSI	IS93C46D-3Z-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C46D-3Z-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C46D-X16(DIP8)	EEPROM	NONE
ISSI	IS93C46D-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C46D-X8(DIP8)	EEPROM	NONE
ISSI	IS93C46D-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C46DG-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C46DG-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C46DGR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C46DGR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C56-3(DIP8)	EEPROM	NONE
ISSI	IS93C56-3G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C56-3GR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C56A-2-X16(DIP8)	EEPROM	NONE
ISSI	IS93C56A-2-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C56A-2-X8(DIP8)	EEPROM	NONE
ISSI	IS93C56A-2-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
ISSI	IS93C56A-2G-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C56A-2G-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C56A-2GR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C56A-2GR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C56A-3-X16(DIP8)	EEPROM	NONE
ISSI	IS93C56A-3-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C56A-3-X8(DIP8)	EEPROM	NONE
ISSI	IS93C56A-3-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C56A-3G-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C56A-3G-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C56A-3GR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C56A-3GR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C56A-X16(DIP8)	EEPROM	NONE
ISSI	IS93C56A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C56A-X8(DIP8)	EEPROM	NONE
ISSI	IS93C56A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C56AG-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C56AG-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C56AGR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C56AGR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C66(DIP8)	EEPROM	NONE
ISSI	IS93C66-3(DIP8)	EEPROM	NONE
ISSI	IS93C66-3G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C66-3GR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C66A-2-X16(DIP8)	EEPROM	NONE
ISSI	IS93C66A-2-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C66A-2-X8(DIP8)	EEPROM	NONE
ISSI	IS93C66A-2-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C66A-2G-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C66A-2G-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C66A-2GR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C66A-2GR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C66A-3-X16(DIP8)	EEPROM	NONE
ISSI	IS93C66A-3-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C66A-3-X8(DIP8)	EEPROM	NONE
ISSI	IS93C66A-3-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C66A-3G-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C66A-3G-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C66A-3GR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C66A-3GR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C66A-X16(DIP8)	EEPROM	NONE
ISSI	IS93C66A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C66A-X8(DIP8)	EEPROM	NONE
ISSI	IS93C66A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C66AG-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C66AG-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C66AGR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C66AGR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C76A-2-X16(DIP8)	EEPROM	NONE
ISSI	IS93C76A-2-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C76A-2-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C76A-2-X8(DIP8)	EEPROM	NONE
ISSI	IS93C76A-2-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C76A-2-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C76A-3-X16(DIP8)	EEPROM	NONE
ISSI	IS93C76A-3-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C76A-3-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C76A-3-X8(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
ISSI	IS93C76A-3-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C76A-3-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C76A-X16(DIP8)	EEPROM	NONE
ISSI	IS93C76A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C76A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C76A-X8(DIP8)	EEPROM	NONE
ISSI	IS93C76A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C76A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C86A-2-X16(DIP8)	EEPROM	NONE
ISSI	IS93C86A-2-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C86A-2-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C86A-2-X8(DIP8)	EEPROM	NONE
ISSI	IS93C86A-2-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C86A-2-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C86A-3-X16(DIP8)	EEPROM	NONE
ISSI	IS93C86A-3-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C86A-3-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C86A-3-X8(DIP8)	EEPROM	NONE
ISSI	IS93C86A-3-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C86A-3-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C86A-X16(DIP8)	EEPROM	NONE
ISSI	IS93C86A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C86A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ISSI	IS93C86A-X8(DIP8)	EEPROM	NONE
ISSI	IS93C86A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ISSI	IS93C86A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
K-line	K24C02(DIP8)	EEPROM	NONE
K-line	K24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
K-line	K24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
K-line	K24C02C(DIP8)	EEPROM	NONE
K-line	K24C02C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
K-line	K24C02C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
K-line	K24C04(DIP8)	EEPROM	NONE
K-line	K24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
K-line	K24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
K-line	K24C08(DIP8)	EEPROM	NONE
K-line	K24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
K-line	K24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
K-line	K24C08C(DIP8)	EEPROM	NONE
K-line	K24C08C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
K-line	K24C08C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
K-line	K24C128(DIP8)	EEPROM	NONE
K-line	K24C128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
K-line	K24C128(TSSOP8)	EEPROM	LP-TSSOP-8PIN
K-line	K24C16(DIP8)	EEPROM	NONE
K-line	K24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
K-line	K24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
K-line	K24C256(DIP8)	EEPROM	NONE
K-line	K24C256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
K-line	K24C256(TSSOP8)	EEPROM	LP-TSSOP-8PIN
K-line	K24C32(DIP8)	EEPROM	NONE
K-line	K24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
K-line	K24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
K-line	K24C64(DIP8)	EEPROM	NONE
K-line	K24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
K-line	K24C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
K-line	K25F04-P(PDIP8)	FLASH	NONE
K-line	K25F04-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
K-line	K25F04-T(TSSOP8)	FLASH	LP-TSSOP-8PIN
K-line	K93C46-X16(DIP8)	EEPROM	NONE
K-line	K93C46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
K-line	K93C46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
K-line	K93C46-X8(DIP8)	EEPROM	NONE
K-line	K93C46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
K-line	K93C46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
K-line	K93C56-X16(DIP8)	EEPROM	NONE
K-line	K93C56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
K-line	K93C56-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
K-line	K93C56-X8(DIP8)	EEPROM	NONE
K-line	K93C56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
K-line	K93C56-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
K-line	K93C66-X16(DIP8)	EEPROM	NONE
K-line	K93C66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
K-line	K93C66-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
K-line	K93C66-X8(DIP8)	EEPROM	NONE
K-line	K93C66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
K-line	K93C66-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Kodenshi	KK24LC02B(DIP8)	EEPROM	NONE
Kodenshi	KK24LC02B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Kodenshi	KK24LC04(DIP8)	EEPROM	NONE
Kodenshi	KK24LC04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Kodenshi	KK24LC04B(DIP8)	EEPROM	NONE
Kodenshi	KK24LC04B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Kodenshi	KK24LC08(DIP8)	EEPROM	NONE
Kodenshi	KK24LC08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Kodenshi	KK24LC08B(DIP8)	EEPROM	NONE
Kodenshi	KK24LC08B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Kodenshi	KK24LC16(DIP8)	EEPROM	NONE
Kodenshi	KK24LC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Kodenshi	KK24LC16B(DIP8)	EEPROM	NONE
Kodenshi	KK24LC16B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
LinkSmart	L24C02(DIP8)	EEPROM	NONE
LinkSmart	L24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
LinkSmart	L24C04(DIP8)	EEPROM	NONE
LinkSmart	L24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
LinkSmart	L24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
LinkSmart	L24M04(DIP8)	EEPROM	NONE
LinkSmart	L24M04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
LinkSmart	L24M08(DIP8)	EEPROM	NONE
LinkSmart	L24M08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
LinkSmart	L24W02(DIP8)	EEPROM	NONE
LinkSmart	L24W02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
LinkSmart	L24W04(DIP8)	EEPROM	NONE
LinkSmart	L24W04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
LinkSmart	L24W08(DIP8)	EEPROM	NONE
LinkSmart	L24W08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
LinkSmart	L24W16(DIP8)	EEPROM	NONE
LinkSmart	L24W16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
LinkSmart	L24W32(DIP8)	EEPROM	NONE
LinkSmart	L24W32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
LinkSmart	L24W64(DIP8)	EEPROM	NONE
LinkSmart	L24W64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Litao	LT24C01(DIP8)	EEPROM	NONE
Litao	LT24C02(DIP8)	EEPROM	NONE
Litao	LT24C04(DIP8)	EEPROM	NONE
Litao	LT24C08(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
Litao	LT24C16(DIP8)	EEPROM	NONE
Lyontek	LY24C02(DIP8)	EEPROM	NONE
Lyontek	LY24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Lyontek	LY24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Lyontek	LY24C04(DIP8)	EEPROM	NONE
Lyontek	LY24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Lyontek	LY24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Lyontek	LY24C08(DIP8)	EEPROM	NONE
Lyontek	LY24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Lyontek	LY24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Lyontek	LY24C16(DIP8)	EEPROM	NONE
Lyontek	LY24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Lyontek	LY24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
MATSHUSHITA	MN27C64(DIP28)	EPROM	NONE
MATSHUSHITA	MN27HC64(DIP28)	EPROM	NONE
Maxcom	MAX24A02(DIP8)	EEPROM	NONE
Maxcom	MAX24A02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Maxcom	MAX24A08(DIP8)	EEPROM	NONE
Maxcom	MAX24A08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Maxcom	MAX24A08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Maxcom	MAX24A16(DIP8)	EEPROM	NONE
Maxcom	MAX24A16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Maxcom	MAX24A16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Maxcom	MAX93LC46(DIP8)	EEPROM	NONE
Maxcom	MAX93LC46(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Maxcom	MAX93LC46G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Maxwell	28C256T(DIP28)	EEPROM	NONE
Megawin	MG84FL54B(LQFP48)	MPU / MCU	LP-LQFP-48PIN
Megawin	MG84FL54RB(LQFP48)	MPU / MCU	LP-LQFP-48PIN
Megawin	MG86FE104(DIP16)	MPU / MCU	NONE
Megawin	MG86FE104(DIP20)	MPU / MCU	NONE
Megawin	MG86FE104(SOP16)	MPU / MCU	LP-SOP-16PIN(150mil)
Megawin	MG86FE104(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Megawin	MG86FL104(DIP16)	MPU / MCU	NONE
Megawin	MG86FL104(DIP20)	MPU / MCU	NONE
Megawin	MG86FL104(SOP16)	MPU / MCU	LP-SOP-16PIN(150mil)
Megawin	MG86FL104(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Megawin	MG87FE51(DIP40)	MPU / MCU	NONE
Megawin	MG87FE51(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Megawin	MG87FE51(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Megawin	MG87FE52(DIP40)	MPU / MCU	NONE
Megawin	MG87FE52(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Megawin	MG87FE52(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Megawin	MG87FL51(DIP40)	MPU / MCU	NONE
Megawin	MG87FL51(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Megawin	MG87FL51(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Megawin	MG87FL52(DIP40)	MPU / MCU	NONE
Megawin	MG87FL52(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Megawin	MG87FL52(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Megawin	MM25SB010(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Megawin	MM25SB512(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Megawin	MPC82E52AE(DIP20)	MPU / MCU	NONE
Megawin	MPC82E52AS(SOP20)	MPU / MCU	LP-SOP-20PIN(300mil) or LP-SOP-28PIN-B(300mil)
Megawin	MPC82E52AT(TSSOP20)	MPU / MCU	LP-TSSOP-20PIN
Megawin	MPC82E54AE(DIP20)	MPU / MCU	NONE
Megawin	MPC82E54AE2(DIP28)	MPU / MCU	NONE
Megawin	MPC82E54AP(PLCC32)	MPU / MCU	LP-PLCC-1M32 or LP-PLCC-1M32S
Megawin	MPC82E54AS(SOP20)	MPU / MCU	LP-SOP-20PIN(300mil) or LP-SOP-28PIN-B(300mil)

Manufacturer	Parts Number	Type	ADAPTER
Megawin	MPC82E54AS2(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Megawin	MPC82E54AS3(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Megawin	MPC82E54AT(TSSOP20)	MPU / MCU	LP-TSSOP-20PIN
Megawin	MPC82L52AE(DIP20)	MPU / MCU	NONE
Megawin	MPC82L52AS(SOP20)	MPU / MCU	LP-SOP-20PIN(300mil) or LP-SOP-28PIN-B(300mil)
Megawin	MPC82L52AT(TSSOP20)	MPU / MCU	LP-TSSOP-20PIN
Megawin	MPC82L54AE(DIP20)	MPU / MCU	NONE
Megawin	MPC82L54AE2(DIP28)	MPU / MCU	NONE
Megawin	MPC82L54AP(PLCC32)	MPU / MCU	LP-PLCC-1M32 or LP-PLCC-1M32S
Megawin	MPC82L54AS(SOP20)	MPU / MCU	LP-SOP-20PIN(300mil) or LP-SOP-28PIN-B(300mil)
Megawin	MPC82L54AS2(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Megawin	MPC82L54AS3(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Megawin	MPC82L54AT(TSSOP20)	MPU / MCU	LP-TSSOP-20PIN
Megawin	MPC89E51(DIP40)	MPU / MCU	NONE
Megawin	MPC89E51(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Megawin	MPC89E51(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Megawin	MPC89E515(DIP40)	MPU / MCU	NONE
Megawin	MPC89E515(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Megawin	MPC89E515(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Megawin	MPC89E52(DIP40)	MPU / MCU	NONE
Megawin	MPC89E52(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Megawin	MPC89E52(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Megawin	MPC89E53(DIP40)	MPU / MCU	NONE
Megawin	MPC89E53(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Megawin	MPC89E53(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Megawin	MPC89E54(DIP40)	MPU / MCU	NONE
Megawin	MPC89E54(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Megawin	MPC89E54(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Megawin	MPC89E58(DIP40)	MPU / MCU	NONE
Megawin	MPC89E58(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Megawin	MPC89E58(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Megawin	MPC89L51(DIP40)	MPU / MCU	NONE
Megawin	MPC89L51(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Megawin	MPC89L51(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Megawin	MPC89L515(DIP40)	MPU / MCU	NONE
Megawin	MPC89L515(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Megawin	MPC89L515(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Megawin	MPC89L52(DIP40)	MPU / MCU	NONE
Megawin	MPC89L52(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Megawin	MPC89L52(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Megawin	MPC89L53(DIP40)	MPU / MCU	NONE
Megawin	MPC89L53(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Megawin	MPC89L53(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Megawin	MPC89L54(DIP40)	MPU / MCU	NONE
Megawin	MPC89L54(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Megawin	MPC89L54(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Megawin	MPC89L58(DIP40)	MPU / MCU	NONE
Megawin	MPC89L58(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Megawin	MPC89L58(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Microchip	24AA00(DIP8)	EEPROM	NONE
Microchip	24AA00(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24AA00(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA01(DIP8)	EEPROM	NONE
Microchip	24AA01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24AA01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA014(DIP8)	EEPROM	NONE
Microchip	24AA014(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24AA014(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
Microchip	24AA014H(DIP8)	EEPROM	NONE
Microchip	24AA014H(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24AA014H(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA01H(DIP8)	EEPROM	NONE
Microchip	24AA01H(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24AA01H(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA02(DIP8)	EEPROM	NONE
Microchip	24AA02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24AA02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA024(DIP8)	EEPROM	NONE
Microchip	24AA024(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24AA024(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA024H(DIP8)	EEPROM	NONE
Microchip	24AA024H(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24AA024H(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA025(DIP8)	EEPROM	NONE
Microchip	24AA025(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24AA025(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA025E48(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24AA02E48(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24AA02H(DIP8)	EEPROM	NONE
Microchip	24AA02H(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24AA02H(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA04(DIP8)	EEPROM	NONE
Microchip	24AA04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24AA04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA04H(DIP8)	EEPROM	NONE
Microchip	24AA04H(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24AA04H(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA08(DIP8)	EEPROM	NONE
Microchip	24AA08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24AA08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA08H(DIP8)	EEPROM	NONE
Microchip	24AA08H(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24AA08H(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA1025(DIP8)	EEPROM	NONE
Microchip	24AA1025(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24AA128(DIP8)	EEPROM	NONE
Microchip	24AA128(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24AA128(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA16(DIP8)	EEPROM	NONE
Microchip	24AA16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24AA16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA164(DIP8)	EEPROM	NONE
Microchip	24AA164(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24AA16H(DIP8)	EEPROM	NONE
Microchip	24AA16H(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24AA16H(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA256(DIP8)	EEPROM	NONE
Microchip	24AA256(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24AA256(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA32(DIP8)	EEPROM	NONE
Microchip	24AA32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24AA32A(DIP8)	EEPROM	NONE
Microchip	24AA32A(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24AA32A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA32AF(DIP8)	EEPROM	NONE
Microchip	24AA32AF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
Microchip	24AA32AF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA32AX(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA512(DIP8)	EEPROM	NONE
Microchip	24AA512(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24AA512(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA515(DIP8)	EEPROM	NONE
Microchip	24AA515(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24AA515(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA64(DIP8)	EEPROM	NONE
Microchip	24AA64(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24AA64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA64F(DIP8)	EEPROM	NONE
Microchip	24AA64F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24AA64F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24AA64X(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24C00(DIP8)	EEPROM	NONE
Microchip	24C00(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24C00(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24C01A(DIP8)	EEPROM	NONE
Microchip	24C01A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24C01A(SOP8-200)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24C01B(DIP8)	EEPROM	NONE
Microchip	24C01B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24C01C(DIP8)	EEPROM	NONE
Microchip	24C01C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24C01C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24C02A(DIP8)	EEPROM	NONE
Microchip	24C02A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24C02A(SOP8-200)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24C02B(DIP8)	EEPROM	NONE
Microchip	24C02B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24C02C(DIP8)	EEPROM	NONE
Microchip	24C02C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24C02C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24C04A(DIP8)	EEPROM	NONE
Microchip	24C04A(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24C04B(DIP8)	EEPROM	NONE
Microchip	24C08A(DIP8)	EEPROM	NONE
Microchip	24C08B(DIP8)	EEPROM	NONE
Microchip	24C08B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24C128(DIP8)	EEPROM	NONE
Microchip	24C16A(DIP8)	EEPROM	NONE
Microchip	24C16B(DIP8)	EEPROM	NONE
Microchip	24C16B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24C256(DIP8)	EEPROM	NONE
Microchip	24C32(DIP8)	EEPROM	NONE
Microchip	24C32(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24C32A(DIP8)	EEPROM	NONE
Microchip	24C32A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24C64(DIP8)	EEPROM	NONE
Microchip	24FC1025(DIP8)	EEPROM	NONE
Microchip	24FC1025(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24FC128(DIP8)	EEPROM	NONE
Microchip	24FC128(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24FC128(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24FC16(DIP8)	EEPROM	NONE
Microchip	24FC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24FC256(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
Microchip	24FC256(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24FC256(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24FC32(DIP8)	EEPROM	NONE
Microchip	24FC32(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24FC512(DIP8)	EEPROM	NONE
Microchip	24FC512(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24FC512(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24FC515(DIP8)	EEPROM	NONE
Microchip	24FC515(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24FC515(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24FC64(DIP8)	EEPROM	NONE
Microchip	24FC64(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24FC64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC00(DIP8)	EEPROM	NONE
Microchip	24LC00(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC00(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC01(DIP8)	EEPROM	NONE
Microchip	24LC014(DIP8)	EEPROM	NONE
Microchip	24LC014(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC014(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC014H(DIP8)	EEPROM	NONE
Microchip	24LC014H(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC014H(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC01B(DIP8)	EEPROM	NONE
Microchip	24LC01B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC01B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC01BH(DIP8)	EEPROM	NONE
Microchip	24LC01BH(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC01BH(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC02(DIP8)	EEPROM	NONE
Microchip	24LC024(DIP8)	EEPROM	NONE
Microchip	24LC024(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC024(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC024H(DIP8)	EEPROM	NONE
Microchip	24LC024H(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC024H(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC025(DIP8)	EEPROM	NONE
Microchip	24LC025(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC025(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC02B(DIP8)	EEPROM	NONE
Microchip	24LC02B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC02B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC02BH(DIP8)	EEPROM	NONE
Microchip	24LC02BH(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC02BH(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC04(DIP8)	EEPROM	NONE
Microchip	24LC04B(DIP8)	EEPROM	NONE
Microchip	24LC04B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC04B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC04BH(DIP8)	EEPROM	NONE
Microchip	24LC04BH(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC04BH(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC08(DIP8)	EEPROM	NONE
Microchip	24LC08B(DIP8)	EEPROM	NONE
Microchip	24LC08B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC08B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC08BH(DIP8)	EEPROM	NONE
Microchip	24LC08BH(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
Microchip	24LC08BH(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC1025(DIP8)	EEPROM	NONE
Microchip	24LC1025(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24LC128(DIP8)	EEPROM	NONE
Microchip	24LC128(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24LC128(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC16(DIP8)	EEPROM	NONE
Microchip	24LC164(DIP8)	EEPROM	NONE
Microchip	24LC164(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC16B(DIP8)	EEPROM	NONE
Microchip	24LC16B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC16B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC16BH(DIP8)	EEPROM	NONE
Microchip	24LC16BH(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC16BH(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC174(DIP8)	EEPROM	NONE
Microchip	24LC174(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC21(PDIP8)	EEPROM	NONE
Microchip	24LC21(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC21A(PDIP8)	EEPROM	NONE
Microchip	24LC21A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC22(PDIP8)	EEPROM	NONE
Microchip	24LC22(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC22A(PDIP8)	EEPROM	NONE
Microchip	24LC22A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC256(DIP8)	EEPROM	NONE
Microchip	24LC256(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24LC256(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC32(DIP8)	EEPROM	NONE
Microchip	24LC32(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24LC32A(DIP8)	EEPROM	NONE
Microchip	24LC32A(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24LC32A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC32AF(DIP8)	EEPROM	NONE
Microchip	24LC32AF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC32AF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC32AX(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC512(DIP8)	EEPROM	NONE
Microchip	24LC512(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24LC512(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC515(DIP8)	EEPROM	NONE
Microchip	24LC515(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24LC515(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC64(DIP8)	EEPROM	NONE
Microchip	24LC64(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24LC64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC64F(DIP8)	EEPROM	NONE
Microchip	24LC64F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LC64F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC64X(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24LC65(DIP8)	EEPROM	NONE
Microchip	24LC65(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	24LCS21A(PDIP8)	EEPROM	NONE
Microchip	24LCS21A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24LCS22A(PDIP8)	EEPROM	NONE
Microchip	24LCS22A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24VL014(DIP8)	EEPROM	NONE
Microchip	24VL014(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
Microchip	24VL014(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24VL014H(DIP8)	EEPROM	NONE
Microchip	24VL014H(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24VL014H(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24VL024(DIP8)	EEPROM	NONE
Microchip	24VL024(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24VL024(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24VL024H(DIP8)	EEPROM	NONE
Microchip	24VL024H(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24VL024H(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	24VL025(DIP8)	EEPROM	NONE
Microchip	24VL025(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	24VL025(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25AA010A-MC(DFN8)	EEPROM	LP48-MLP8-2x3
Microchip	25AA010A-P(DIP8)	EEPROM	NONE
Microchip	25AA010A-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25AA010A-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25AA020A-MC(DFN8)	EEPROM	LP48-MLP8-2x3
Microchip	25AA020A-P(DIP8)	EEPROM	NONE
Microchip	25AA020A-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25AA020A-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25AA040-P(DIP8)	EEPROM	NONE
Microchip	25AA040-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25AA040-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25AA040A-MC(DFN8)	EEPROM	LP48-MLP8-2x3
Microchip	25AA040A-P(DIP8)	EEPROM	NONE
Microchip	25AA040A-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25AA040A-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25AA080-P(DIP8)	EEPROM	NONE
Microchip	25AA080-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25AA080-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25AA080A-P(DIP8)	EEPROM	NONE
Microchip	25AA080A-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25AA080A-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25AA080B-P(DIP8)	EEPROM	NONE
Microchip	25AA080B-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25AA080B-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25AA080C-P(DIP8)	EEPROM	NONE
Microchip	25AA080C-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25AA080C-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25AA080D-P(DIP8)	EEPROM	NONE
Microchip	25AA080D-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25AA080D-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25AA1024-MF(DFN8)	EEPROM	LP48-WSO8-5x6
Microchip	25AA1024-P(DIP8)	EEPROM	NONE
Microchip	25AA1024-SM(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	25AA128-MF(MLF8)	EEPROM	LP48-WSO8-5x6
Microchip	25AA128-P(DIP8)	EEPROM	NONE
Microchip	25AA128-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25AA128-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25AA160-P(DIP8)	EEPROM	NONE
Microchip	25AA160-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25AA160-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25AA160A-P(DIP8)	EEPROM	NONE
Microchip	25AA160A-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25AA160A-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25AA160B-P(DIP8)	EEPROM	NONE
Microchip	25AA160B-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
Microchip	25AA160B-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25AA160C-MN(TDFN8)	EEPROM	LP48-MLP8-2x3
Microchip	25AA160C-P(DIP8)	EEPROM	NONE
Microchip	25AA160C-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25AA160C-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25AA160D-MN(TDFN8)	EEPROM	LP48-MLP8-2x3
Microchip	25AA160D-P(DIP8)	EEPROM	NONE
Microchip	25AA160D-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25AA160D-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25AA256-MF(MLF8)	EEPROM	LP48-WSON8-5x6
Microchip	25AA256-P(DIP8)	EEPROM	NONE
Microchip	25AA256-SM(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	25AA256-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25AA256-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25AA320-P(DIP8)	EEPROM	NONE
Microchip	25AA320-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25AA320-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25AA512-MF(MLF8)	EEPROM	LP48-WSON8-5x6
Microchip	25AA512-P(DIP8)	EEPROM	NONE
Microchip	25AA512-SM(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	25AA512-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25AA640-P(DIP8)	EEPROM	NONE
Microchip	25AA640-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25AA640-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25AA640A-MF(DFN8)	EEPROM	LP48-MLP8-2x3
Microchip	25AA640A-P(DIP8)	EEPROM	NONE
Microchip	25AA640A-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25AA640A-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25C040-P(DIP8)	EEPROM	NONE
Microchip	25C040-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25C040-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25C080-P(DIP8)	EEPROM	NONE
Microchip	25C080-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25C080-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25C160-P(DIP8)	EEPROM	NONE
Microchip	25C160-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25C160-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25C320-P(DIP8)	EEPROM	NONE
Microchip	25C320-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25C320-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25C640-P(DIP8)	EEPROM	NONE
Microchip	25C640-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25C640-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25LC010A-MC(DFN8)	EEPROM	LP48-MLP8-2x3
Microchip	25LC010A-P(DIP8)	EEPROM	NONE
Microchip	25LC010A-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25LC010A-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25LC020A-MC(DFN8)	EEPROM	LP48-MLP8-2x3
Microchip	25LC020A-P(DIP8)	EEPROM	NONE
Microchip	25LC020A-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25LC020A-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25LC040-P(DIP8)	EEPROM	NONE
Microchip	25LC040-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25LC040-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25LC040A-MC(DFN8)	EEPROM	LP48-MLP8-2x3
Microchip	25LC040A-P(DIP8)	EEPROM	NONE
Microchip	25LC040A-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25LC040A-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
Microchip	25LC080-P(DIP8)	EEPROM	NONE
Microchip	25LC080-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25LC080-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25LC080A-P(DIP8)	EEPROM	NONE
Microchip	25LC080A-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25LC080A-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25LC080B-P(DIP8)	EEPROM	NONE
Microchip	25LC080B-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25LC080B-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25LC080C-P(DIP8)	EEPROM	NONE
Microchip	25LC080C-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25LC080C-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25LC080D-P(DIP8)	EEPROM	NONE
Microchip	25LC080D-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25LC080D-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25LC1024-MF(DFN8)	EEPROM	LP48-WSON8-5x6
Microchip	25LC1024-P(DIP8)	EEPROM	NONE
Microchip	25LC1024-SM(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	25LC128-MF(MLF8)	EEPROM	LP48-WSON8-5x6
Microchip	25LC128-P(DIP8)	EEPROM	NONE
Microchip	25LC128-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25LC128-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25LC160-P(DIP8)	EEPROM	NONE
Microchip	25LC160-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25LC160-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25LC256-MF(MLF8)	EEPROM	LP48-WSON8-5x6
Microchip	25LC256-P(DIP8)	EEPROM	NONE
Microchip	25LC256-SM(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	25LC256-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25LC256-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25LC320-P(DIP8)	EEPROM	NONE
Microchip	25LC320-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25LC320-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25LC512-MF(MLF8)	EEPROM	LP48-WSON8-5x6
Microchip	25LC512-P(DIP8)	EEPROM	NONE
Microchip	25LC512-SM(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Microchip	25LC512-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25LC640-P(DIP8)	EEPROM	NONE
Microchip	25LC640-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25LC640-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	25LC640A-MF(DFN8)	EEPROM	LP48-WSON8-5x6
Microchip	25LC640A-P(DIP8)	EEPROM	NONE
Microchip	25LC640A-SN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	25LC640A-ST(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	2764(DIP28)	EPROM	NONE
Microchip	27C128(DIP28)	EPROM	NONE
Microchip	27C256(DIP28)	EPROM	NONE
Microchip	27C512A(DIP28)	EPROM	NONE
Microchip	27C64(DIP28)	EPROM	NONE
Microchip	27C64(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip	27HC256(DIP28)	EPROM	NONE
Microchip	27HC64(DIP28)	EPROM	NONE
Microchip	27LV256(DIP28)	EPROM	NONE
Microchip	27LV64(DIP28)	EPROM	NONE
Microchip	28C04(DIP24)	EEPROM	NONE
Microchip	28C04A(DIP24)	EEPROM	NONE
Microchip	28C04A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Microchip	28C04AF(DIP24)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
Microchip	28C04AF(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Microchip	28C16A(DIP24)	EEPROM	NONE
Microchip	28C16A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Microchip	28C16AF(DIP24)	EEPROM	NONE
Microchip	28C16AF(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Microchip	28C17A(DIP28)	EEPROM	NONE
Microchip	28C17A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Microchip	28C17AF(DIP28)	EEPROM	NONE
Microchip	28C17AF(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Microchip	28C64A(DIP28)	EEPROM	NONE
Microchip	28C64A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Microchip	28C64AF(DIP28)	EEPROM	NONE
Microchip	28C64AF(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Microchip	28C64AX(DIP28)	EEPROM	NONE
Microchip	28C64AX(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Microchip	34AA02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	34LC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	34VL02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA46-X16(DIP8)	EEPROM	NONE
Microchip	93AA46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93AA46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA46-X8(DIP8)	EEPROM	NONE
Microchip	93AA46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93AA46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA46A(DIP8)	EEPROM	NONE
Microchip	93AA46A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA46A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA46AX(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA46B(DIP8)	EEPROM	NONE
Microchip	93AA46B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA46B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA46BX(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA46C-X16(DIP8)	EEPROM	NONE
Microchip	93AA46C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA46C-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA46C-X8(DIP8)	EEPROM	NONE
Microchip	93AA46C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA46C-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA46CX-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA46CX-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA46X-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA46X-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA56-X16(DIP8)	EEPROM	NONE
Microchip	93AA56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93AA56-X16(TSSOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93AA56-X8(DIP8)	EEPROM	NONE
Microchip	93AA56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93AA56-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA56A(DIP8)	EEPROM	NONE
Microchip	93AA56A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA56A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA56AX(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA56B(DIP8)	EEPROM	NONE
Microchip	93AA56B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA56B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA56BX(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA56C-X16(DIP8)	EEPROM	NONE
Microchip	93AA56C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
Microchip	93AA56C-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA56C-X8(DIP8)	EEPROM	NONE
Microchip	93AA56C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA56C-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA56CX-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA56CX-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA56X-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA56X-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA66-X16(DIP8)	EEPROM	NONE
Microchip	93AA66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93AA66-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA66-X8(DIP8)	EEPROM	NONE
Microchip	93AA66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93AA66-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA66A(DIP8)	EEPROM	NONE
Microchip	93AA66A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA66A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA66AX(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA66B(DIP8)	EEPROM	NONE
Microchip	93AA66B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA66B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA66BX(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA66C-X16(DIP8)	EEPROM	NONE
Microchip	93AA66C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA66C-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA66C-X8(DIP8)	EEPROM	NONE
Microchip	93AA66C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA66C-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA66CX-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA66CX-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA66X-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA66X-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA76-X16(DIP8)	EEPROM	NONE
Microchip	93AA76-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA76-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA76-X8(DIP8)	EEPROM	NONE
Microchip	93AA76-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA76-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA76A(DIP8)	EEPROM	NONE
Microchip	93AA76A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA76A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA76B(DIP8)	EEPROM	NONE
Microchip	93AA76B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA76B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA76C-X16(DIP8)	EEPROM	NONE
Microchip	93AA76C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA76C-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA76C-X8(DIP8)	EEPROM	NONE
Microchip	93AA76C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA76C-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA76X-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA76X-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA86-X16(DIP8)	EEPROM	NONE
Microchip	93AA86-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA86-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA86-X8(DIP8)	EEPROM	NONE
Microchip	93AA86-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA86-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
Microchip	93AA86A(DIP8)	EEPROM	NONE
Microchip	93AA86A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA86A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA86B(DIP8)	EEPROM	NONE
Microchip	93AA86B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA86B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA86C-X16(DIP8)	EEPROM	NONE
Microchip	93AA86C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA86C-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA86C-X8(DIP8)	EEPROM	NONE
Microchip	93AA86C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA86C-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93AA86X-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93AA86X-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C06(DIP8)	EEPROM	NONE
Microchip	93C06(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93C46-X16(DIP8)	EEPROM	NONE
Microchip	93C46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93C46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C46-X8(DIP8)	EEPROM	NONE
Microchip	93C46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93C46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C46A(DIP8)	EEPROM	NONE
Microchip	93C46A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C46A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C46A-X16(DIP8)	EEPROM	NONE
Microchip	93C46A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C46A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C46A-X8(DIP8)	EEPROM	NONE
Microchip	93C46A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C46A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C46AX(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C46AX-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C46AX-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C46B(DIP8)	EEPROM	NONE
Microchip	93C46B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C46B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C46BX(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C46C-X16(DIP8)	EEPROM	NONE
Microchip	93C46C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C46C-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C46C-X8(DIP8)	EEPROM	NONE
Microchip	93C46C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C46C-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C46CX-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C46CX-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C46X-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C46X-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C56-X16(DIP8)	EEPROM	NONE
Microchip	93C56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93C56-X16(TSSOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93C56-X8(DIP8)	EEPROM	NONE
Microchip	93C56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93C56-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C56A(DIP8)	EEPROM	NONE
Microchip	93C56A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C56A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C56A-X16(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
Microchip	93C56A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C56A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C56A-X8(DIP8)	EEPROM	NONE
Microchip	93C56A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C56A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C56AX(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C56AX-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C56AX-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C56B(DIP8)	EEPROM	NONE
Microchip	93C56B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C56B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C56BX(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C56C-X16(DIP8)	EEPROM	NONE
Microchip	93C56C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C56C-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C56C-X8(DIP8)	EEPROM	NONE
Microchip	93C56C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C56C-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C56CX-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C56CX-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C56X-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C56X-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C66-X16(DIP8)	EEPROM	NONE
Microchip	93C66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93C66-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C66-X8(DIP8)	EEPROM	NONE
Microchip	93C66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93C66-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C66A(DIP8)	EEPROM	NONE
Microchip	93C66A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C66A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C66A-X16(DIP8)	EEPROM	NONE
Microchip	93C66A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C66A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C66A-X8(DIP8)	EEPROM	NONE
Microchip	93C66A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C66A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C66AX(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C66B(DIP8)	EEPROM	NONE
Microchip	93C66B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C66B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C66BX(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C66C-X16(DIP8)	EEPROM	NONE
Microchip	93C66C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C66C-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C66C-X8(DIP8)	EEPROM	NONE
Microchip	93C66C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C66C-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C66CX-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C66CX-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C66X-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C66X-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C76-X16(DIP8)	EEPROM	NONE
Microchip	93C76-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C76-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C76-X8(DIP8)	EEPROM	NONE
Microchip	93C76-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C76-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
Microchip	93C76A(DIP8)	EEPROM	NONE
Microchip	93C76A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C76A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C76A-X16(DIP8)	EEPROM	NONE
Microchip	93C76A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C76A-X8(DIP8)	EEPROM	NONE
Microchip	93C76A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C76B(DIP8)	EEPROM	NONE
Microchip	93C76B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C76B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C76C-X16(DIP8)	EEPROM	NONE
Microchip	93C76C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C76C-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C76C-X8(DIP8)	EEPROM	NONE
Microchip	93C76C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C76C-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C86(DIP8)	EEPROM	NONE
Microchip	93C86(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C86-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C86-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C86A(DIP8)	EEPROM	NONE
Microchip	93C86A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C86A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C86A-X16(DIP8)	EEPROM	NONE
Microchip	93C86A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C86A-X8(DIP8)	EEPROM	NONE
Microchip	93C86A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C86B(DIP8)	EEPROM	NONE
Microchip	93C86B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C86B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C86C-X16(DIP8)	EEPROM	NONE
Microchip	93C86C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C86C-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93C86C-X8(DIP8)	EEPROM	NONE
Microchip	93C86C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93C86C-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC46-X16(DIP8)	EEPROM	NONE
Microchip	93LC46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93LC46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC46-X8(DIP8)	EEPROM	NONE
Microchip	93LC46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93LC46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC46A(DIP8)	EEPROM	NONE
Microchip	93LC46A(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93LC46A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC46A-X16(DIP8)	EEPROM	NONE
Microchip	93LC46A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93LC46A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC46A-X8(DIP8)	EEPROM	NONE
Microchip	93LC46A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93LC46A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC46AX(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC46AX-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC46AX-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC46B(DIP8)	EEPROM	NONE
Microchip	93LC46B(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93LC46B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC46BX(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
Microchip	93LC46C-X16(DIP8)	EEPROM	NONE
Microchip	93LC46C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC46C-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC46C-X8(DIP8)	EEPROM	NONE
Microchip	93LC46C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC46C-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC46CX-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC46CX-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC46X-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC46X-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC56-X16(DIP8)	EEPROM	NONE
Microchip	93LC56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93LC56-X16(TSSOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93LC56-X8(DIP8)	EEPROM	NONE
Microchip	93LC56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93LC56-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC56A(DIP8)	EEPROM	NONE
Microchip	93LC56A(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93LC56A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC56A-X16(DIP8)	EEPROM	NONE
Microchip	93LC56A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93LC56A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC56A-X8(DIP8)	EEPROM	NONE
Microchip	93LC56A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93LC56A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC56AX(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC56AX-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC56AX-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC56B(DIP8)	EEPROM	NONE
Microchip	93LC56B(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93LC56B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC56BX(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC56C-X16(DIP8)	EEPROM	NONE
Microchip	93LC56C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC56C-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC56C-X8(DIP8)	EEPROM	NONE
Microchip	93LC56C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC56C-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC56CX-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC56CX-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC56X-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC56X-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC66-X16(DIP8)	EEPROM	NONE
Microchip	93LC66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93LC66-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC66-X8(DIP8)	EEPROM	NONE
Microchip	93LC66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93LC66-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC66A(DIP8)	EEPROM	NONE
Microchip	93LC66A(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93LC66A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC66A-X16(DIP8)	EEPROM	NONE
Microchip	93LC66A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93LC66A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC66A-X8(DIP8)	EEPROM	NONE
Microchip	93LC66A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93LC66A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC66AX(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
Microchip	93LC66AX-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC66AX-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC66B(DIP8)	EEPROM	NONE
Microchip	93LC66B(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93LC66B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC66BX(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC66C-X16(DIP8)	EEPROM	NONE
Microchip	93LC66C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC66C-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC66C-X8(DIP8)	EEPROM	NONE
Microchip	93LC66C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC66C-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC66CX-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC66CX-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC66X-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC66X-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC76-X16(DIP8)	EEPROM	NONE
Microchip	93LC76-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC76-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC76-X8(DIP8)	EEPROM	NONE
Microchip	93LC76-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC76-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC76A(DIP8)	EEPROM	NONE
Microchip	93LC76A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC76A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC76A-X16(DIP8)	EEPROM	NONE
Microchip	93LC76A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC76A-X8(DIP8)	EEPROM	NONE
Microchip	93LC76A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC76AX-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC76AX-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC76B(DIP8)	EEPROM	NONE
Microchip	93LC76B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC76B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC76C-X16(DIP8)	EEPROM	NONE
Microchip	93LC76C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC76C-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC76C-X8(DIP8)	EEPROM	NONE
Microchip	93LC76C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC76C-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC76X-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC76X-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC86-X16(DIP8)	EEPROM	NONE
Microchip	93LC86-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC86-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC86-X8(DIP8)	EEPROM	NONE
Microchip	93LC86-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC86-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC86A(DIP8)	EEPROM	NONE
Microchip	93LC86A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC86A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC86A-X16(DIP8)	EEPROM	NONE
Microchip	93LC86A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC86A-X8(DIP8)	EEPROM	NONE
Microchip	93LC86A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC86AX-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC86AX-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC86B(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
Microchip	93LC86B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC86B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC86C-X16(DIP8)	EEPROM	NONE
Microchip	93LC86C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC86C-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC86C-X8(DIP8)	EEPROM	NONE
Microchip	93LC86C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC86C-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Microchip	93LC86X-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LC86X-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Microchip	93LCS56(DIP8)	EEPROM	NONE
Microchip	93LCS56(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	93LCS66(DIP8)	EEPROM	NONE
Microchip	93LCS66(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
Microchip	dsPIC33FJ06GS101(SOP18)	MPU / MCU	LP-SOP-20PIN(300mil) or LP-SOP-28PIN-B(300mil)
Microchip	dsPIC33FJ06GS102(DIP28)	MPU / MCU	NONE
Microchip	dsPIC33FJ06GS102(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	dsPIC33FJ06GS202(DIP28)	MPU / MCU	NONE
Microchip	dsPIC33FJ06GS202(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	dsPIC33FJ16GS402(DIP28)	MPU / MCU	NONE
Microchip	dsPIC33FJ16GS402(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	dsPIC33FJ16GS404(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	dsPIC33FJ16GS502(DIP28)	MPU / MCU	NONE
Microchip	dsPIC33FJ16GS502(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	dsPIC33FJ16GS504(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC10F200(PDIP8)	MPU / MCU	NONE
Microchip	PIC10F200(SOT23)	MPU / MCU	SU2000-SEEPROM-SOT23/M
Microchip	PIC10F202(PDIP8)	MPU / MCU	NONE
Microchip	PIC10F204(PDIP8)	MPU / MCU	NONE
Microchip	PIC10F206(PDIP8)	MPU / MCU	NONE
Microchip	PIC10F220(PDIP8)	MPU / MCU	NONE
Microchip	PIC10F220(SOT23)	MPU / MCU	SU2000-SEEPROM-SOT23/M
Microchip	PIC10F222(PDIP8)	MPU / MCU	NONE
Microchip	PIC10F222(SOT23)	MPU / MCU	SU2000-SEEPROM-SOT23/M
Microchip	PIC12C508(PDIP8)	MPU / MCU	NONE
Microchip	PIC12C508-SM(SOP8)	MPU / MCU	LP-SOP-8PIN-B(207mil)
Microchip	PIC12C508A(DIP8)	MPU / MCU	NONE
Microchip	PIC12C508A-SM(SOP8)	MPU / MCU	LP-SOP-8PIN-B(207mil)
Microchip	PIC12C508A-SN(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC12C671(DIP8)	MPU / MCU	NONE
Microchip	PIC12C671(SOP8)	MPU / MCU	LP-SOP-8PIN-B(207mil)
Microchip	PIC12F1822(PDIP8)	MPU / MCU	NONE
Microchip	PIC12F1822(SOIC8)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC12F508(DIP8)	MPU / MCU	NONE
Microchip	PIC12F508(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC12F509(DIP8)	MPU / MCU	NONE
Microchip	PIC12F509(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC12F510(DIP8)	MPU / MCU	NONE
Microchip	PIC12F510(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC12F519(DIP)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC12F519(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC12F617(DIP8)	MPU / MCU	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Microchip	PIC12F617(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC12F629(DIP8)	MPU / MCU	NONE
Microchip	PIC12F629(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC12F675(DIP8)	MPU / MCU	NONE
Microchip	PIC12F675(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC12F683(DFN8)	MPU / MCU	LP48-WSON8-5x6

Manufacturer	Parts Number	Type	ADAPTER
Microchip	PIC12F683(PDIP8)	MPU / MCU	NONE
Microchip	PIC12F683(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC12LF1822(PDIP8)	MPU / MCU	NONE
Microchip	PIC12LF1822(SOIC8)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC16C54(DIP18)	MPU / MCU	NONE
Microchip	PIC16C54(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16C54(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16C54-HS(DIP18)	MPU / MCU	NONE
Microchip	PIC16C54-HS(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16C54-HS(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16C54-LP(DIP18)	MPU / MCU	NONE
Microchip	PIC16C54-LP(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16C54-LP(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16C54-RC(DIP18)	MPU / MCU	NONE
Microchip	PIC16C54-RC(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16C54-RC(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16C54-XT(DIP18)	MPU / MCU	NONE
Microchip	PIC16C54-XT(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16C54-XT(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16C54B(DIP18)	MPU / MCU	NONE
Microchip	PIC16C54B(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16C54B(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16C54C(DIP18)	MPU / MCU	NONE
Microchip	PIC16C54C(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16C54C(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16C55(PDIP28)	MPU / MCU	NONE
Microchip	PIC16C55(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16C55(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16C55-HS(PDIP28)	MPU / MCU	NONE
Microchip	PIC16C55-HS(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16C55-HS(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16C55-LP(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16C55-LP(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16C55-RC(PDIP28)	MPU / MCU	NONE
Microchip	PIC16C55-RC(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16C55-RC(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16C55-XT(PDIP28)	MPU / MCU	NONE
Microchip	PIC16C55-XT(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16C55-XT(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16C712(PDIP18)	MPU / MCU	NONE
Microchip	PIC16C712(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16C712(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16C716(PDIP18)	MPU / MCU	NONE
Microchip	PIC16C716(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16C716(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F1503(PDIP14)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC16F1503(SOIC14)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC16F1503(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
Microchip	PIC16F1508(DIP20)	MPU / MCU	NONE
Microchip	PIC16F1508(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F1508(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F1509(DIP20)	MPU / MCU	NONE
Microchip	PIC16F1509(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F1509(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F1823(PDIP14)	MPU / MCU	NONE
Microchip	PIC16F1823(QFN16)	MPU / MCU	LP-QFN-16PIN-4x4
Microchip	PIC16F1823(SOIC14)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC16F1823(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN

Manufacturer	Parts Number	Type	ADAPTER
Microchip	PIC16F1824(PDIP14)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC16F1824(SOIC14)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC16F1824(TSSOP14)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC16F1825(PDIP14)	MPU / MCU	NONE
Microchip	PIC16F1825(SOIC14)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC16F1825(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
Microchip	PIC16F1826(PDIP18)	MPU / MCU	NONE
Microchip	PIC16F1827(PDIP18)	MPU / MCU	NONE
Microchip	PIC16F1828(PDIP20)	MPU / MCU	NONE
Microchip	PIC16F1828(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F1828(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F1828(TSSOP20)	MPU / MCU	LP-TSSOP-20PIN
Microchip	PIC16F1829(PDIP20)	MPU / MCU	NONE
Microchip	PIC16F1933(PDIP28)	MPU / MCU	NONE
Microchip	PIC16F1933(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F1933(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F1934(DIP40)	MPU / MCU	NONE
Microchip	PIC16F1934(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC16F1936(PDIP28)	MPU / MCU	NONE
Microchip	PIC16F1936(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F1936(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F1937(DIP40)	MPU / MCU	NONE
Microchip	PIC16F1937(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC16F1938(PDIP28)	MPU / MCU	NONE
Microchip	PIC16F1938(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F1938(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F1939(DIP40)	MPU / MCU	NONE
Microchip	PIC16F1939(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC16F505(DIP14)	MPU / MCU	NONE
Microchip	PIC16F505(SOP14)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC16F505(TSSOP14)	MPU / MCU	LP48-TSSOP-20PIN
Microchip	PIC16F506(DIP14)	MPU / MCU	NONE
Microchip	PIC16F506(SOP14)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC16F506(TSSOP14)	MPU / MCU	LP48-TSSOP-20PIN
Microchip	PIC16F54(DIP18)	MPU / MCU	NONE
Microchip	PIC16F54(SOP18)	MPU / MCU	LP-SOP-28PIN-A(330mil)
Microchip	PIC16F54(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F57(DIP28)	MPU / MCU	NONE
Microchip	PIC16F57(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F57(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F59(PDIP40)	MPU / MCU	NONE
Microchip	PIC16F59(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC16F627(PDIP18)	MPU / MCU	NONE
Microchip	PIC16F627(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F627(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F627A(PDIP18)	MPU / MCU	NONE
Microchip	PIC16F627A(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F628(PDIP18)	MPU / MCU	NONE
Microchip	PIC16F628(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F628(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F628A(PDIP18)	MPU / MCU	NONE
Microchip	PIC16F628A(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F630(DIP14)	MPU / MCU	NONE
Microchip	PIC16F630(SOP14)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC16F630(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
Microchip	PIC16F631(DIP20)	MPU / MCU	LP-SOP-8PIN-B(207mil)
Microchip	PIC16F631(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F631(SSOP20)	MPU / MCU	LP-SSOP-28PIN

Manufacturer	Parts Number	Type	ADAPTER
Microchip	PIC16F636(PDIP14)	MPU / MCU	NONE
Microchip	PIC16F636(SOP14)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC16F636(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
Microchip	PIC16F639(DIP20)	MPU / MCU	LP-SOP-8PIN-B(207mil)
Microchip	PIC16F639(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F648A(PDIP18)	MPU / MCU	NONE
Microchip	PIC16F648A(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F676(DIP14)	MPU / MCU	NONE
Microchip	PIC16F676(SOP14)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC16F676(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
Microchip	PIC16F677(DIP20)	MPU / MCU	LP-SOP-8PIN-B(207mil)
Microchip	PIC16F677(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F677(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F684(PDIP14)	MPU / MCU	NONE
Microchip	PIC16F684(SOP14)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC16F684(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
Microchip	PIC16F685(PDIP20)	MPU / MCU	NONE
Microchip	PIC16F685(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F685(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F687(DIP20)	MPU / MCU	LP-SOP-8PIN-B(207mil)
Microchip	PIC16F687(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F687(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F688(PDIP14)	MPU / MCU	NONE
Microchip	PIC16F688(SOP14)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC16F688(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
Microchip	PIC16F689(PDIP20)	MPU / MCU	NONE
Microchip	PIC16F689(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F689(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F690(PDIP20)	MPU / MCU	NONE
Microchip	PIC16F690(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F690(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F716(PDIP18)	MPU / MCU	NONE
Microchip	PIC16F716(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F716(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F72(PDIP28)	MPU / MCU	NONE
Microchip	PIC16F72(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F72(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F722(DIP28)	MPU / MCU	NONE
Microchip	PIC16F722(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F722(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F722A(DIP28)	MPU / MCU	NONE
Microchip	PIC16F722A(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F722A(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F723(DIP28)	MPU / MCU	NONE
Microchip	PIC16F723(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F723(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F723A(DIP28)	MPU / MCU	NONE
Microchip	PIC16F723A(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F723A(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F724(DIP28)	MPU / MCU	NONE
Microchip	PIC16F724(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F724(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F73(PDIP28)	MPU / MCU	NONE
Microchip	PIC16F73(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F73(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F737(PDIP28)	MPU / MCU	LP48-WSON8-5x6
Microchip	PIC16F737(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F737(SSOP28)	MPU / MCU	LP-SSOP-28PIN

Manufacturer	Parts Number	Type	ADAPTER
Microchip	PIC16F74(PDIP40)	MPU / MCU	NONE
Microchip	PIC16F74(PLCC44)	MPU / MCU	LP48-PLCC-44PIN & LP48-PLCC-44S
Microchip	PIC16F74(QFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC16F747(PDIP40)	MPU / MCU	LP48-WSON8-5x6
Microchip	PIC16F747(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC16F76(DIP28)	MPU / MCU	NONE
Microchip	PIC16F76(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F76(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F767(PDIP28)	MPU / MCU	LP-USON8-4x4
Microchip	PIC16F767(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F767(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F77(PDIP40)	MPU / MCU	NONE
Microchip	PIC16F77(PLCC44)	MPU / MCU	LP48-PLCC-44PIN & LP48-PLCC-44S
Microchip	PIC16F77(QFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC16F777(PDIP40)	MPU / MCU	LP48-WSON8-5x6
Microchip	PIC16F777(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC16F818(PDIP18)	MPU / MCU	NONE
Microchip	PIC16F818(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F818(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F819(PDIP18)	MPU / MCU	NONE
Microchip	PIC16F819(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F819(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F83(PDIP18)	MPU / MCU	NONE
Microchip	PIC16F83(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F84(PDIP18)	MPU / MCU	NONE
Microchip	PIC16F84(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F84A(PDIP18)	MPU / MCU	NONE
Microchip	PIC16F84A(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F87(PDIP18)	MPU / MCU	NONE
Microchip	PIC16F87(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F87(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F870(PDIP28)	MPU / MCU	LP48-WSON8-5x6
Microchip	PIC16F870(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F871(PDIP40)	MPU / MCU	NONE
Microchip	PIC16F872(PDIP28)	MPU / MCU	LP-TSOP-48S
Microchip	PIC16F872(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F872(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F873(PDIP28)	MPU / MCU	LP48-SOP-32PIN
Microchip	PIC16F873(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F873A(PDIP28)	MPU / MCU	None
Microchip	PIC16F873A(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F873A(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F874(PDIP40)	MPU / MCU	NONE
Microchip	PIC16F874A(PDIP40)	MPU / MCU	NONE
Microchip	PIC16F874A(PLCC44)	MPU / MCU	LP48-PLCC-44PIN & LP48-PLCC-44S
Microchip	PIC16F874A(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC16F876(PDIP28)	MPU / MCU	None
Microchip	PIC16F876(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F876A(PDIP28)	MPU / MCU	LP48-TSOP-40PIN or LP48-TSOP-40S
Microchip	PIC16F876A(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F876A(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F877(PDIP40)	MPU / MCU	NONE
Microchip	PIC16F877A(PDIP40)	MPU / MCU	NONE
Microchip	PIC16F877A(PLCC44)	MPU / MCU	LP48-PLCC-44PIN & LP48-PLCC-44S
Microchip	PIC16F877A(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC16F88(PDIP18)	MPU / MCU	NONE
Microchip	PIC16F88(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F88(SSOP20)	MPU / MCU	LP-SSOP-28PIN

Manufacturer	Parts Number	Type	ADAPTER
Microchip	PIC16F882(PDIP28)	MPU / MCU	NONE
Microchip	PIC16F882(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F882(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F883(PDIP28)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Microchip	PIC16F883(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F883(SSOP28)	MPU / MCU	LP-PST-SSOPP28
Microchip	PIC16F884(PDIP40)	MPU / MCU	NONE
Microchip	PIC16F884(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC16F886(PDIP28)	MPU / MCU	NONE
Microchip	PIC16F886(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F886(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F887(PDIP40)	MPU / MCU	NONE
Microchip	PIC16F887(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC16F913(PDIP28)	MPU / MCU	NONE
Microchip	PIC16F913(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F913(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F914(PDIP40)	MPU / MCU	LP48-TSOP-32S
Microchip	PIC16F914(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC16F916(PDIP28)	MPU / MCU	NONE
Microchip	PIC16F916(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16F916(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16F917(PDIP40)	MPU / MCU	LP48-PSOP-44PIN
Microchip	PIC16F917(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC16LC54C(DIP18)	MPU / MCU	NONE
Microchip	PIC16LC54C(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LC54C(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF1508(DIP20)	MPU / MCU	NONE
Microchip	PIC16LF1508(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF1508(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF1509(DIP20)	MPU / MCU	NONE
Microchip	PIC16LF1509(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF1509(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF1823(PDIP14)	MPU / MCU	NONE
Microchip	PIC16LF1823(SOIC14)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC16LF1823(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
Microchip	PIC16LF1824(PDIP14)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC16LF1824(SOIC14)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC16LF1824(TSSOP14)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC16LF1825(PDIP14)	MPU / MCU	NONE
Microchip	PIC16LF1825(SOIC14)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC16LF1825(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
Microchip	PIC16LF1826(PDIP18)	MPU / MCU	NONE
Microchip	PIC16LF1827(PDIP18)	MPU / MCU	NONE
Microchip	PIC16LF1828(DIP20)	MPU / MCU	NONE
Microchip	PIC16LF1828(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF1828(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF1828(TSSOP20)	MPU / MCU	LP-TSSOP-20PIN
Microchip	PIC16LF1829(PDIP)	MPU / MCU	NONE
Microchip	PIC16LF1933(PDIP28)	MPU / MCU	LP48-TSOP-32S
Microchip	PIC16LF1933(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF1933(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF1934(DIP40)	MPU / MCU	LP48-TSOP-28PIN
Microchip	PIC16LF1934(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC16LF1936(PDIP28)	MPU / MCU	LP-PLCC-1M32 or LP-PLCC-1M32S
Microchip	PIC16LF1936(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF1937(DIP40)	MPU / MCU	None
Microchip	PIC16LF1937(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC16LF1938(PDIP28)	MPU / MCU	LP48-TSOP-32S

Manufacturer	Parts Number	Type	ADAPTER
Microchip	PIC16LF1938(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF1938(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF1939(DIP40)	MPU / MCU	LP48-TSOP-32S
Microchip	PIC16LF1939(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC16LF627(PDIP18)	MPU / MCU	NONE
Microchip	PIC16LF627(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF627(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF627A(PDIP18)	MPU / MCU	NONE
Microchip	PIC16LF627A(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF628(PDIP18)	MPU / MCU	NONE
Microchip	PIC16LF628(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF628(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF628A(PDIP18)	MPU / MCU	NONE
Microchip	PIC16LF628A(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF648A(PDIP18)	MPU / MCU	NONE
Microchip	PIC16LF648A(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF722(DIP28)	MPU / MCU	NONE
Microchip	PIC16LF722(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF722(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF722A(DIP28)	MPU / MCU	NONE
Microchip	PIC16LF722A(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF722A(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF723(DIP28)	MPU / MCU	NONE
Microchip	PIC16LF723(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF723(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF723A(DIP28)	MPU / MCU	NONE
Microchip	PIC16LF723A(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF723A(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF73(PDIP28)	MPU / MCU	NONE
Microchip	PIC16LF73(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF73(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF74(PDIP40)	MPU / MCU	NONE
Microchip	PIC16LF74(PLCC44)	MPU / MCU	LP48-PLCC-44PIN & LP48-PLCC-44S
Microchip	PIC16LF74(QFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC16LF76(DIP28)	MPU / MCU	NONE
Microchip	PIC16LF76(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF76(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF77(PDIP40)	MPU / MCU	NONE
Microchip	PIC16LF77(PLCC44)	MPU / MCU	LP48-PLCC-44PIN & LP48-PLCC-44S
Microchip	PIC16LF77(QFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC16LF818(PDIP18)	MPU / MCU	LP-TSOP-48S
Microchip	PIC16LF818(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF818(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF819(PDIP18)	MPU / MCU	LP48-PSOP-44PIN
Microchip	PIC16LF819(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF819(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF83(PDIP18)	MPU / MCU	NONE
Microchip	PIC16LF83(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF84(PDIP18)	MPU / MCU	NONE
Microchip	PIC16LF84(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF84A(PDIP18)	MPU / MCU	NONE
Microchip	PIC16LF84A(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF87(PDIP18)	MPU / MCU	NONE
Microchip	PIC16LF87(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF87(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF870(PDIP28)	MPU / MCU	LP48-PSOP-44PIN
Microchip	PIC16LF870(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF871(PDIP40)	MPU / MCU	NONE

Manufacturer	Parts Number	Type	ADAPTER
Microchip	PIC16LF872(PDIP28)	MPU / MCU	LP-TSOP-48S
Microchip	PIC16LF872(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF872(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF873(PDIP28)	MPU / MCU	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
Microchip	PIC16LF873(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF873A(PDIP28)	MPU / MCU	LP-BGA64-SOCKET-10x13 + LP-BGA64-A (For 29xxx)
Microchip	PIC16LF873A(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF873A(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF874(PDIP40)	MPU / MCU	NONE
Microchip	PIC16LF874A(PDIP40)	MPU / MCU	NONE
Microchip	PIC16LF874A(PLCC44)	MPU / MCU	LP48-PLCC-44PIN & LP48-PLCC-44S
Microchip	PIC16LF874A(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC16LF876(PDIP28)	MPU / MCU	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
Microchip	PIC16LF876(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF876A(PDIP28)	MPU / MCU	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
Microchip	PIC16LF876A(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF876A(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC16LF877(PDIP40)	MPU / MCU	NONE
Microchip	PIC16LF877A(PDIP40)	MPU / MCU	NONE
Microchip	PIC16LF877A(PLCC44)	MPU / MCU	LP48-PLCC-44PIN & LP48-PLCC-44S
Microchip	PIC16LF877A(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC16LF88(PDIP18)	MPU / MCU	NONE
Microchip	PIC16LF88(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC16LF88(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC17C42(PDIP40)	MPU / MCU	NONE
Microchip	PIC17C42A(PDIP40)	MPU / MCU	NONE
Microchip	PIC17C43(PDIP40)	MPU / MCU	NONE
Microchip	PIC17C44(PDIP40)	MPU / MCU	NONE
Microchip	PIC17CR42(PDIP40)	MPU / MCU	NONE
Microchip	PIC17CR43(PDIP40)	MPU / MCU	NONE
Microchip	PIC18F1220(DIP18)	MPU / MCU	NONE
Microchip	PIC18F1220(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC18F1220(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC18F1320(DIP18)	MPU / MCU	NONE
Microchip	PIC18F1320(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC18F1320(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC18F2220(DIP28)	MPU / MCU	NONE
Microchip	PIC18F2220(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC18F2320(DIP28)	MPU / MCU	NONE
Microchip	PIC18F2320(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC18F242(DIP28)	MPU / MCU	LP48-PSOP-44PIN
Microchip	PIC18F242(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC18F248(DIP28)	MPU / MCU	LP48-PSOP-44PIN
Microchip	PIC18F248(SOP28)	MPU / MCU	LP-TSOP-48S
Microchip	PIC18F24J10(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC18F24J10(SPDIP28)	MPU / MCU	LP-TSOP-48S
Microchip	PIC18F24J10(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC18F24K20(PDIP28)	MPU / MCU	LP-TSOP-48S
Microchip	PIC18F24K20(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC18F24K20(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC18F252(DIP28)	MPU / MCU	LP-TSOP-48S
Microchip	PIC18F252(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC18F2550(PDIP28)	MPU / MCU	NONE
Microchip	PIC18F2550(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC18F258(DIP28)	MPU / MCU	LP-TSOP-48S
Microchip	PIC18F258(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC18F25K20(PDIP28)	MPU / MCU	LP48-PSOP-44PIN
Microchip	PIC18F25K20(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)

Manufacturer	Parts Number	Type	ADAPTER
Microchip	PIC18F25K20(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC18F26K20(PDIP28)	MPU / MCU	LP-TSOP-48S
Microchip	PIC18F26K20(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC18F26K20(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC18F4220(PDIP40)	MPU / MCU	NONE
Microchip	PIC18F4220(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18F4320(PDIP40)	MPU / MCU	NONE
Microchip	PIC18F4320(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18F442(PDIP40)	MPU / MCU	LP-TFBGA-48PIN-6x8
Microchip	PIC18F442(PLCC44)	MPU / MCU	LP48-PLCC-44PIN OR LP48-PLCC-44S
Microchip	PIC18F442(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18F4420(PDIP40)	MPU / MCU	NONE
Microchip	PIC18F4420(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18F448(PDIP40)	MPU / MCU	LP48-PSOP-44PIN
Microchip	PIC18F448(PLCC44)	MPU / MCU	LP48-PLCC-44PIN OR LP48-PLCC-44S
Microchip	PIC18F448(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18F44K20(PDIP40)	MPU / MCU	LP-TSOP-48S
Microchip	PIC18F44K20(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18F4510(PDIP40)	MPU / MCU	NONE
Microchip	PIC18F4510(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18F452(PDIP40)	MPU / MCU	LP48-PSOP-44PIN
Microchip	PIC18F452(PLCC44)	MPU / MCU	LP48-PLCC-44PIN OR LP48-PLCC-44S
Microchip	PIC18F452(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18F4520(PDIP40)	MPU / MCU	NONE
Microchip	PIC18F4520(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18F4525(PDIP40)	MPU / MCU	NONE
Microchip	PIC18F4525(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18F4550(PDIP40)	MPU / MCU	NONE
Microchip	PIC18F4550(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18F458(PDIP40)	MPU / MCU	LP-TSOP-48S
Microchip	PIC18F458(PLCC44)	MPU / MCU	LP48-PLCC-44PIN OR LP48-PLCC-44S
Microchip	PIC18F458(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18F45J10(PDIP40)	MPU / MCU	NONE
Microchip	PIC18F45J10(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18F45K20(PDIP40)	MPU / MCU	LP-TSOP-48S
Microchip	PIC18F45K20(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18F4620(PDIP40)	MPU / MCU	NONE
Microchip	PIC18F4620(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18F46K20(PDIP40)	MPU / MCU	NONE
Microchip	PIC18F46K20(QFN44)	MPU / MCU	LP-QFN-44S-8x8
Microchip	PIC18F46K20(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18F46K22(PDIP40)	MPU / MCU	NONE
Microchip	PIC18F46K22(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18F67J60(TQFP64)	MPU / MCU	LP-VQFP-64
Microchip	PIC18F96J60(TQFP100)	MPU / MCU	LP-QFP-100PIN-12x12-PIC
Microchip	PIC18F96J65(TQFP100)	MPU / MCU	LP-QFP-100PIN-12x12-PIC
Microchip	PIC18F97J60(TQFP100)	MPU / MCU	LP-QFP-100PIN-12x12-PIC
Microchip	PIC18LF1220(DIP18)	MPU / MCU	NONE
Microchip	PIC18LF1220(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC18LF1220(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC18LF1320(DIP18)	MPU / MCU	NONE
Microchip	PIC18LF1320(SOP18)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC18LF1320(SSOP20)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC18LF2220(DIP28)	MPU / MCU	NONE
Microchip	PIC18LF2220(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC18LF2320(DIP28)	MPU / MCU	NONE
Microchip	PIC18LF2320(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC18LF242(DIP28)	MPU / MCU	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
Microchip	PIC18LF242(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC18LF248(DIP28)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC18LF248(SOP28)	MPU / MCU	None
Microchip	PIC18LF24J10(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC18LF24J10(SPDIP28)	MPU / MCU	None
Microchip	PIC18LF24J10(SSOP28)	MPU / MCU	LP-SSOP-28PIN
Microchip	PIC18LF252(DIP28)	MPU / MCU	None
Microchip	PIC18LF252(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC18LF258(DIP28)	MPU / MCU	None
Microchip	PIC18LF258(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
Microchip	PIC18LF4220(PDIP40)	MPU / MCU	NONE
Microchip	PIC18LF4220(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18LF4320(PDIP40)	MPU / MCU	NONE
Microchip	PIC18LF4320(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18LF442(PLCC44)	MPU / MCU	LP48-PLCC-44PIN OR LP48-PLCC-44S
Microchip	PIC18LF442(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18LF4420(PDIP40)	MPU / MCU	NONE
Microchip	PIC18LF4420(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18LF448(PDIP40)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC18LF448(PLCC44)	MPU / MCU	LP48-PLCC-44PIN OR LP48-PLCC-44S
Microchip	PIC18LF448(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18LF4510(PDIP40)	MPU / MCU	NONE
Microchip	PIC18LF4510(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18LF452(PDIP40)	MPU / MCU	LP-SOP-16PIN(150mil)
Microchip	PIC18LF452(PLCC44)	MPU / MCU	LP48-PLCC-44PIN OR LP48-PLCC-44S
Microchip	PIC18LF452(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18LF4520(PDIP40)	MPU / MCU	NONE
Microchip	PIC18LF4520(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18LF4525(PDIP40)	MPU / MCU	NONE
Microchip	PIC18LF4525(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18LF4550(PDIP40)	MPU / MCU	NONE
Microchip	PIC18LF4550(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18LF458(PDIP40)	MPU / MCU	LP-TSSOP-8PIN
Microchip	PIC18LF458(PLCC44)	MPU / MCU	LP48-PLCC-44PIN OR LP48-PLCC-44S
Microchip	PIC18LF458(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18LF45J10(PDIP40)	MPU / MCU	NONE
Microchip	PIC18LF45J10(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18LF4620(PDIP40)	MPU / MCU	NONE
Microchip	PIC18LF4620(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip	PIC18LF46K22(PDIP40)	MPU / MCU	NONE
Microchip	PIC18LF46K22(TQFP44)	MPU / MCU	LP48-VQFP-44S
Microchip (SST)	SST29EE010(DIP32)	FLASH	NONE
Microchip (SST)	SST29EE010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29EE010(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST29EE010(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Microchip (SST)	SST29EE010A(DIP32)	FLASH	NONE
Microchip (SST)	SST29EE010A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29EE010A(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST29EE010A(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Microchip (SST)	SST29EE020(DIP32)	FLASH	NONE
Microchip (SST)	SST29EE020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29EE020(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST29EE020(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Microchip (SST)	SST29EE020A(DIP32)	FLASH	NONE
Microchip (SST)	SST29EE020A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29EE020A(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST29EE020A(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Microchip (SST)	SST29EE512(DIP32)	FLASH	NONE

Manufacturer	Parts Number	Type	ADAPTER
Microchip (SST)	SST29EE512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29EE512(TSOP32)	FLASH	LP48-TSOP-32S
Microchip (SST)	SST29EE512A(DIP32)	FLASH	NONE
Microchip (SST)	SST29EE512A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29EE512A(TSOP32)	FLASH	LP48-TSOP-32S
Microchip (SST)	SST29LE010(DIP32)	FLASH	NONE
Microchip (SST)	SST29LE010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29LE010(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST29LE010(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Microchip (SST)	SST29LE010A(DIP32)	FLASH	NONE
Microchip (SST)	SST29LE010A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29LE010A(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST29LE010A(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Microchip (SST)	SST29LE020(DIP32)	FLASH	NONE
Microchip (SST)	SST29LE020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29LE020(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST29LE020(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Microchip (SST)	SST29LE020A(DIP32)	FLASH	NONE
Microchip (SST)	SST29LE020A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29LE020A(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST29LE020A(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Microchip (SST)	SST29LE512(DIP32)	FLASH	NONE
Microchip (SST)	SST29LE512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29LE512(TSOP32)	FLASH	LP48-TSOP-32S
Microchip (SST)	SST29LE512A(DIP32)	FLASH	NONE
Microchip (SST)	SST29LE512A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29LE512A(TSOP32)	FLASH	LP48-TSOP-32S
Microchip (SST)	SST29SF010(DIP32)	FLASH	NONE
Microchip (SST)	SST29SF010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29SF010(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST29SF020(DIP32)	FLASH	NONE
Microchip (SST)	SST29SF020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29SF020(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST29SF040(DIP32)	FLASH	NONE
Microchip (SST)	SST29SF040(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29SF040(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST29SF512(DIP32)	FLASH	NONE
Microchip (SST)	SST29SF512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29SF512(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST29VE010(DIP32)	FLASH	NONE
Microchip (SST)	SST29VE010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29VE010(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST29VE010(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Microchip (SST)	SST29VE010A(DIP32)	FLASH	NONE
Microchip (SST)	SST29VE010A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29VE010A(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST29VE010A(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Microchip (SST)	SST29VE020(DIP32)	FLASH	NONE
Microchip (SST)	SST29VE020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29VE020(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST29VE020(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Microchip (SST)	SST29VE020A(DIP32)	FLASH	NONE
Microchip (SST)	SST29VE020A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29VE020A(TSOP32 8X14)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST29VE020A(TSOP32 8X20)	FLASH	LP48-TSOP-32S
Microchip (SST)	SST29VE512(DIP32)	FLASH	NONE
Microchip (SST)	SST29VE512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29VE512(TSOP32)	FLASH	LP48-TSOP-32S

Manufacturer	Parts Number	Type	ADAPTER
Microchip (SST)	SST29VE512A(DIP32)	FLASH	NONE
Microchip (SST)	SST29VE512A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29VE512A(TSOP32)	FLASH	LP48-TSOP-32S
Microchip (SST)	SST29VF010(DIP32)	FLASH	NONE
Microchip (SST)	SST29VF010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29VF010(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST29VF020(DIP32)	FLASH	NONE
Microchip (SST)	SST29VF020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29VF020(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST29VF040(DIP32)	FLASH	NONE
Microchip (SST)	SST29VF040(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29VF040(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST29VF512(DIP32)	FLASH	NONE
Microchip (SST)	SST29VF512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST29VF512(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST37VF010(DIP32)	FLASH	NONE
Microchip (SST)	SST37VF010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST37VF010(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST37VF020(DIP32)	FLASH	NONE
Microchip (SST)	SST37VF020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST37VF020(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST37VF040(DIP32)	FLASH	NONE
Microchip (SST)	SST37VF040(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST37VF040(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST37VF512(DIP32)	FLASH	NONE
Microchip (SST)	SST37VF512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST37VF512(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39LF010(DIP32)	FLASH	NONE
Microchip (SST)	SST39LF010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39LF010(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39LF016(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
Microchip (SST)	SST39LF020(DIP32)	FLASH	NONE
Microchip (SST)	SST39LF020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39LF020(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39LF040(DIP32)	FLASH	NONE
Microchip (SST)	SST39LF040(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39LF040(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39LF080(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
Microchip (SST)	SST39LF200A(TSOP48)	FLASH	LP-TSOP-48S
Microchip (SST)	SST39LF400A(TSOP48)	FLASH	LP-TSOP-48S
Microchip (SST)	SST39LF512(DIP32)	FLASH	NONE
Microchip (SST)	SST39LF512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39LF512(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39LF800A(TSOP48)	FLASH	LP-TSOP-48S
Microchip (SST)	SST39LH010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39LH010(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39LH020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39LH020(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39LH040(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39LH040(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39LH512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39LH512(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39SF010(DIP32)	FLASH	NONE
Microchip (SST)	SST39SF010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39SF010(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39SF010A(DIP32)	FLASH	NONE
Microchip (SST)	SST39SF010A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39SF010A(TSOP32)	FLASH	LP48-VSOP-32S

Manufacturer	Parts Number	Type	ADAPTER
Microchip (SST)	SST39SF020(DIP32)	FLASH	NONE
Microchip (SST)	SST39SF020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39SF020(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39SF020A(DIP32)	FLASH	NONE
Microchip (SST)	SST39SF020A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39SF020A(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39SF020P(DIP32)	FLASH	NONE
Microchip (SST)	SST39SF020P(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39SF020P(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39SF040(DIP32)	FLASH	NONE
Microchip (SST)	SST39SF040(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39SF040(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39SF040P(DIP32)	FLASH	NONE
Microchip (SST)	SST39SF040P(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39SF040P(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39SF512(DIP32)	FLASH	NONE
Microchip (SST)	SST39SF512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39SF512(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39VF010(DIP32)	FLASH	NONE
Microchip (SST)	SST39VF010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39VF010(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39VF016(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
Microchip (SST)	SST39VF016Q(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
Microchip (SST)	SST39VF020(DIP32)	FLASH	NONE
Microchip (SST)	SST39VF020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39VF020(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39VF020P(DIP32)	FLASH	NONE
Microchip (SST)	SST39VF020P(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39VF020P(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39VF040(DIP32)	FLASH	NONE
Microchip (SST)	SST39VF040(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39VF040(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39VF040P(DIP32)	FLASH	NONE
Microchip (SST)	SST39VF040P(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39VF040P(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39VF080(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
Microchip (SST)	SST39VF080Q(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
Microchip (SST)	SST39VF200A(TSOP48)	FLASH	LP-TSOP-48S
Microchip (SST)	SST39VF3201C(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
Microchip (SST)	SST39VF3201C(TSOP48)	FLASH	LP-TSOP-48S
Microchip (SST)	SST39VF3202C(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
Microchip (SST)	SST39VF3202C(TSOP48)	FLASH	LP-TSOP-48S
Microchip (SST)	SST39VF400A(TSOP48)	FLASH	LP-TSOP-48S
Microchip (SST)	SST39VF512(DIP32)	FLASH	NONE
Microchip (SST)	SST39VF512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Microchip (SST)	SST39VF512(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST39VF800A(TSOP48)	FLASH	LP-TSOP-48S
Microchip (SST)	SST49LF004A(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
Microchip (SST)	SST49LF004A(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST49LF004B(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
Microchip (SST)	SST49LF004B(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST49LF040(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
Microchip (SST)	SST49LF040(TSOP32)	FLASH	LP48-VSOP-32S
Microchip (SST)	SST49LF080A(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
Microchip (SST)	SST49LF080A(TSOP32)	FLASH	LP48-VSOP-32S
Micron	JS28F00AM29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
Micron	JS28F00AM29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
Micron	JS28F00BM29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)

Manufacturer	Parts Number	Type	ADAPTER
Micron	JS28F00BM29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
Micron	JS28F128M29EWB(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
Micron	JS28F128M29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
Micron	JS28F128M29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
Micron	JS28F128M29EWT(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
Micron	JS28F256M29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
Micron	JS28F256M29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
Micron	JS28F512M29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
Micron	JS28F512M29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
Micron	M25P10-AMB(MLP8)	FLASH	LP48-MLP8-2x3
Micron	M25P10-AMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Micron	M25P10-AMP(MLP8)	FLASH	LP48-MLP8-2x3
Micron	M25P16VME(WSON8)	FLASH	LP48-WSON8-6x8
Micron	M25P16VMF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Micron	M25P16VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Micron	M25P16VMP(WSON8)	FLASH	LP48-WSON8-5x6
Micron	M25P16VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Micron	M25P80VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Micron	M25P80VMP(WSON8)	FLASH	LP48-WSON8-5x6
Micron	M25P80VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Micron	M25PE16VMP(MLP8)	FLASH	LP48-WSON8-5x6
Micron	M25PE16VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Micron	M25PX16VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Micron	M25PX16VMP(WSON8)	FLASH	LP48-WSON8-6x8
Micron	M25PX16VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Micron	M25PX80VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Micron	M25PX80VMP(WSON8)	FLASH	LP48-WSON8-5x6
Micron	M25PX80VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Micron	M45PE10-VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Micron	M45PE10-VMP(MLP8)	FLASH	LP48-WSON8-5x6
Micron	M45PE16-VMP(MLP8)	FLASH	LP48-WSON8-5x6
Micron	M45PE16-VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Micron	M45PE20-VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Micron	M45PE20-VMP(MLP8)	FLASH	LP48-WSON8-5x6
Micron	M45PE40-VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Micron	M45PE40-VMP(MLP8)	FLASH	LP48-WSON8-5x6
Micron	M45PE40-VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Micron	M45PE80-VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Micron	M45PE80-VMP(MLP8)	FLASH	LP48-WSON8-5x6
Micron	M45PE80-VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Micron	N25Q008A11EF6(MLP8)	FLASH	LP48-WSON8-5x6
Micron	N25Q008A11ESC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Micron	N25Q016A11ESC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Micron	N25Q032A11E12(BGA24)	FLASH	LP-BGA-24PIN-5x5B
Micron	N25Q032A11EF6(MLP8)	FLASH	LP48-WSON8-5x6
Micron	N25Q032A11EF8(MLP8)	FLASH	LP48-WSON8-6x8
Micron	N25Q032A11ESC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Micron	N25Q032A11ESE(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Micron	N25Q032A11ESF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Micron	N25Q032A13E12(BGA24)	FLASH	LP-BGA-24PIN-5x5B
Micron	N25Q032A13EF6(MLP8)	FLASH	LP48-WSON8-5x6
Micron	N25Q032A13EF8(MLP8)	FLASH	LP48-WSON8-6x8
Micron	N25Q032A13ESC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Micron	N25Q032A13ESE(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Micron	N25Q032A13ESF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Micron	N25Q064A11E12(BGA24)	FLASH	LP-BGA-24PIN-5x5B
Micron	N25Q064A11EF6(MLP8)	FLASH	LP48-WSON8-5x6
Micron	N25Q064A11EF8(MLP8)	FLASH	LP48-WSON8-6x8

Manufacturer	Parts Number	Type	ADAPTER
Micron	N25Q064A11ESC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Micron	N25Q064A11ESE(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Micron	N25Q064A11ESF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Micron	N25Q064A13E12(BGA24)	FLASH	LP-BGA-24PIN-5x5B
Micron	N25Q064A13EF6(MLP8)	FLASH	LP48-WSON8-5x6
Micron	N25Q064A13EF8(MLP8)	FLASH	LP48-WSON8-6x8
Micron	N25Q064A13ESC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Micron	N25Q064A13ESE(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Micron	N25Q064A13ESF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Micron	N25Q128A11E12(BGA24)	FLASH	LP-BGA-24PIN-5x5B
Micron	N25Q128A11EF6(MLP8)	FLASH	LP48-WSON8-5x6
Micron	N25Q128A11EF6(SOP8)	FLASH	LP48-WSON8-5x6
Micron	N25Q128A11EF8(MLP8)	FLASH	LP48-WSON8-6x8
Micron	N25Q128A11EF8(SOP8)	FLASH	LP48-WSON8-6x8
Micron	N25Q128A11ESC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Micron	N25Q128A11ESE(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Micron	N25Q128A11ESF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Micron	N25Q128A13E12(BGA24)	FLASH	LP-BGA-24PIN-5x5B
Micron	N25Q128A13EF6(MLP8)	FLASH	LP48-WSON8-5x6
Micron	N25Q128A13EF6(SOP8)	FLASH	LP48-WSON8-5x6
Micron	N25Q128A13EF8(MLP8)	FLASH	LP48-WSON8-6x8
Micron	N25Q128A13EF8(SOP8)	FLASH	LP48-WSON8-6x8
Micron	N25Q128A13ESC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Micron	N25Q128A13ESE(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Micron	N25Q128A13ESF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Micron	N25Q256A13E12(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
Micron	N25Q256A13EF8(WSON8)	FLASH	LP48-WSON8-6x8
Micron	N25Q256A13ESF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Micron	PC28F00AM29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
Micron	PC28F00AM29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
Micron	PC28F00BM29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
Micron	PC28F00BM29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
Micron	PC28F128M29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
Micron	PC28F128M29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
Micron	PC28F128P30B(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	PC28F128P30BF(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	PC28F128P30T(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	PC28F128P30TF(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	PC28F256M29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
Micron	PC28F256M29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
Micron	PC28F256P30B(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	PC28F256P30BF(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	PC28F256P30T(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	PC28F256P30TF(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	PC28F512M29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
Micron	PC28F512M29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
Micron	PC28F640P30B(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	PC28F640P30BF(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	PC28F640P30T(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	PC28F640P30TF(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	RC28F00AM29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
Micron	RC28F00AM29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
Micron	RC28F00BM29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
Micron	RC28F00BM29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
Micron	RC28F128M29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
Micron	RC28F128M29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
Micron	RC28F128P30B(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	RC28F128P30BF(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)

Manufacturer	Parts Number	Type	ADAPTER
Micron	RC28F128P30T(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	RC28F128P30TF(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	RC28F256M29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
Micron	RC28F256M29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
Micron	RC28F256P30B(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	RC28F256P30BF(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	RC28F256P30T(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	RC28F256P30TF(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	RC28F512M29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
Micron	RC28F512M29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
Micron	RC28F640P30B(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	RC28F640P30BF(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	RC28F640P30T(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Micron	RC28F640P30TF(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
Mitsubishi	M5L27256K(DIP28)	EPROM	NONE
Mitsubishi	M5L27512K(DIP28)	EPROM	NONE
Mitsubishi	M5L27C127(DIP28)	EPROM	NONE
Mitsubishi	M5M27256P(DIP28)	EPROM	NONE
Mitsubishi	M5M27512P(DIP28)	EPROM	NONE
Mitsubishi	M5M27C256AK(DIP28)	EPROM	NONE
Mitsubishi	M5M28C64A(DIP28)	EEPROM	NONE
Mitsubishi	M5M28C64A(SOP28)	EEPROM	LP-SOP-28PIN-B(300mil)
MSHINE	MS25X10(PDIP8)	FLASH	NONE
MSHINE	MS25X10(SOP8-150)	FLASH	LP-SOP-16PIN(150mil)
MSHINE	MS25X10(SOP8-209)	FLASH	LP-SOP-8PIN-B(207mil)
MSHINE	MS25X10(TSSOP8)	FLASH	LP-TSSOP-8PIN
MSHINE	MS25X16(PDIP8)	FLASH	NONE
MSHINE	MS25X16(SOP16-300)	FLASH	LP-SOP-28PIN-B(300mil)
MSHINE	MS25X16(SOP8-209)	FLASH	LP-SOP-8PIN-B(207mil)
MSHINE	MS25X20(PDIP8)	FLASH	NONE
MSHINE	MS25X20(SOP8-150)	FLASH	LP-SOP-16PIN(150mil)
MSHINE	MS25X20(SOP8-209)	FLASH	LP-SOP-8PIN-B(207mil)
MSHINE	MS25X32(PDIP8)	FLASH	NONE
MSHINE	MS25X32(SOP16-300)	FLASH	LP-SOP-28PIN-B(300mil)
MSHINE	MS25X32(SOP8-209)	FLASH	LP-SOP-8PIN-B(207mil)
MSHINE	MS25X40(PDIP8)	FLASH	NONE
MSHINE	MS25X40(SOP8-150)	FLASH	LP-SOP-16PIN(150mil)
MSHINE	MS25X40(SOP8-209)	FLASH	LP-SOP-8PIN-B(207mil)
MSHINE	MS25X512(PDIP8)	FLASH	NONE
MSHINE	MS25X512(SOP8-150)	FLASH	LP-SOP-16PIN(150mil)
MSHINE	MS25X512(SOP8-209)	FLASH	LP-SOP-8PIN-B(207mil)
MSHINE	MS25X512(TSSOP8)	FLASH	LP-TSSOP-8PIN
MSHINE	MS25X80(PDIP8)	FLASH	NONE
MSHINE	MS25X80(SOP8-150)	FLASH	LP-SOP-16PIN(150mil)
MSHINE	MS25X80(SOP8-209)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	KH25L1006AMC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	KH25L1006MI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	KH25L1006ZMC(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	KH25L1006ZMI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	KH25L1006ZUI(USON8)	FLASH	LP48-MLP8-2x3
MXIC	KH25L12835FM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	KH25L12835FMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	KH25L12835FZ2I(WSON6x8)	FLASH	LP48-WSON8-6x8
MXIC	KH25L12835FZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	KH25L12845EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	KH25L12855FXCI(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
MXIC	KH25L12855FXDI(TFBGA24)	FLASH	LP-BGA-24PIN-5x5B
MXIC	KH25L12873FM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)

Manufacturer	Parts Number	Type	ADAPTER
MXIC	KH25L12873FMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	KH25L12873FZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	KH25L1606EM1C(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	KH25L1633EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	KH25L1633EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	KH25L1673EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	KH25L1673EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	KH25L3206EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	KH25L3206EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	KH25L3206EPI(DIP8)	FLASH	NONE
MXIC	KH25L3206EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	KH25L3206EZUI(USON4x4)	FLASH	LP-USON8-4x4
MXIC	KH25L3254EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	KH25L3254EXCI(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
MXIC	KH25L3254EXDI(TFBGA24)	FLASH	LP-BGA-24PIN-5x5B
MXIC	KH25L3255EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	KH25L3255EXCI(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
MXIC	KH25L3255EXDI(TFBGA24)	FLASH	LP-BGA-24PIN-5x5B
MXIC	KH25L3273EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	KH25L3273EMBI(VSOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	KH25L3273EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	KH25L3273EPI(DIP8)	FLASH	NONE
MXIC	KH25L3273EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	KH25L4006EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	KH25L4006EMI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	KH25L4006EPI(DIP8)	FLASH	NONE
MXIC	KH25L4006EZMI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	KH25L4006EZU(USON8)	FLASH	LP48-MLP8-2x3
MXIC	KH25L512EMI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	KH25L512EOI(TSSOP8)	FLASH	LP-TSSOP-8PIN
MXIC	KH25L512EZVI(USON2x3)	FLASH	LP48-MLP8-2x3
MXIC	KH25L512MI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	KH25L512ZMI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	KH25L8006EM1I(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	KH25L8006EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	KH25L8006EPI(DIP8)	FLASH	NONE
MXIC	KH25L8006EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	KH25L8006EZUI(USON4x4)	FLASH	LP-USON8-4x4
MXIC	KH25L8073EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	KH29LV320DB(TSOP48)	FLASH	LP-TSOP-48S
MXIC	KH29LV320DT(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX25L1005AMC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L1005CMI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L1005MC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L1005MI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L1005ZMC(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L1005ZMI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L1021EMC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L1025CMI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L1026EM(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L12801FM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L12801FMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L12801FZ2I(WSON6x8)	FLASH	LP48-WSON8-6x8
MXIC	MX25L12801FZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L12805DMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L12835EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L12835EZNI(WSON6x8)	FLASH	LP48-WSON8-6x8
MXIC	MX25L12835FM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)

Manufacturer	Parts Number	Type	ADAPTER
MXIC	MX25L12835FMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L12835FMJ(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L12835FZ2I(WSON6x8)	FLASH	LP48-WSON8-6x8
MXIC	MX25L12835FZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L12836EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L12836EZNI(WSON6x8)	FLASH	LP48-WSON8-6x8
MXIC	MX25L12839FZNW(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L12845EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L12845EZNI(WSON6x8)	FLASH	LP48-WSON8-6x8
MXIC	MX25L12855EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L12855EXCI(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
MXIC	MX25L12855FMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L12855FXCI(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
MXIC	MX25L12855FXDI(TFBGA24)	FLASH	LP-BGA-24PIN-5x5B
MXIC	MX25L12865EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L12865EZNI(WSON6x8)	FLASH	LP48-WSON8-6x8
MXIC	MX25L12873FM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L12873FMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L12873FZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L12875FM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L12875FMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L12875FZ2I(WSON6x8)	FLASH	LP48-WSON8-6x8
MXIC	MX25L12875FZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L1605AM2C(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L1605AZMC(WSON6x8)	FLASH	LP48-WSON8-6x8
MXIC	MX25L1605DM1I(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L1605DM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L1605DPI(DIP8)	FLASH	NONE
MXIC	MX25L1605DZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L1605DZUI(USON4x4)	FLASH	LP-USON8-4x4
MXIC	MX25L1606EM1I(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L1606EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L1606EPI(DIP8)	FLASH	NONE
MXIC	MX25L1606EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L1606EZUI(USON4x4)	FLASH	LP-USON8-4x4
MXIC	MX25L1608EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L1633EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L1633EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L1633EZUI(USON4x4)	FLASH	LP-USON8-4x4
MXIC	MX25L1635DM1I(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L1635DM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L1635DZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L1635EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L1636DM1I(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L1636DM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L1636DZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L1636EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L1655DM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L1655DXCI(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
MXIC	MX25L1673EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L1673EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L1675EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L1675EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L2005MC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L2005MI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L2005ZMC(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L2005ZMI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L2006EM1I(SOP8)	FLASH	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
MXIC	MX25L2006EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L2025MC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L2025MI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L2025ZMC(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L2025ZMI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L2026DM1I(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L2026EM1I(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L25635EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L25635EZNI(WSON6x8)	FLASH	LP48-WSON8-6x8
MXIC	MX25L25635FMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L25635FMJ(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L25635FZ2I(WSON6x8)	FLASH	LP48-WSON8-6x8
MXIC	MX25L25639FZ4W(WSON6x8)	FLASH	LP48-WSON8-6x8
MXIC	MX25L25655EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L25655EXCI(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
MXIC	MX25L25655FMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L25655FXCI(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
MXIC	MX25L25655FXDI(TFBGA24)	FLASH	LP-BGA-24PIN-5x5B
MXIC	MX25L25735EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L25735EZNI(WSON6x8)	FLASH	LP48-WSON8-6x8
MXIC	MX25L25735FMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L25735FZ2I(WSON6x8)	FLASH	LP48-WSON8-6x8
MXIC	MX25L3205AZMC(WSON6x8)	FLASH	LP48-WSON8-6x8
MXIC	MX25L3205AZMI(WSON6x8)	FLASH	LP48-WSON8-6x8
MXIC	MX25L3205DM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L3205DMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L3205DPI(DIP8)	FLASH	NONE
MXIC	MX25L3205DZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L3205DZUI(USON4x4)	FLASH	LP-USON8-4x4
MXIC	MX25L3206DM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L3206DPI(DIP8)	FLASH	NONE
MXIC	MX25L3206DZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L3206DZUI(USON4x4)	FLASH	LP-USON8-4x4
MXIC	MX25L3206EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L3206EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L3206EPI(DIP8)	FLASH	NONE
MXIC	MX25L3206EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L3206EZUI(USON4x4)	FLASH	LP-USON8-4x4
MXIC	MX25L3208EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L3208EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L3225DM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L3235DM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L3235DMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L3235DZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L3235EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L3235EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L3235EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L3236DM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L3237DZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L3239EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L3239EMBI(VSOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L3239EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L3254EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L3254EXCI(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
MXIC	MX25L3254EXDI(TFBGA24)	FLASH	LP-BGA-24PIN-5x5B
MXIC	MX25L3255DM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L3255DMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L3255DXCI(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B

Manufacturer	Parts Number	Type	ADAPTER
MXIC	MX25L3255EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L3255EXCI(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
MXIC	MX25L3255EXDI(TFBGA24)	FLASH	LP-BGA-24PIN-5x5B
MXIC	MX25L3273EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L3273EMBI(VSOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L3273EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L3273EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L3275EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L3275EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L3275EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L4005(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L4005AM2C(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L4005AM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L4005AMC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L4005AMI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L4005AZMC(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L4005AZMI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L4005AZNC(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L4005AZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L4005AZUC(USON4x4)	FLASH	LP-USON8-4x4
MXIC	MX25L4005AZUI(USON4x4)	FLASH	LP-USON8-4x4
MXIC	MX25L4005M2C(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L4005M2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L4005MC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L4005MI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L4005ZMC(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L4005ZMI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L4006EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L4006EMI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L4006EPI(DIP8)	FLASH	NONE
MXIC	MX25L4006EZMI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L4006EZU(USON8)	FLASH	LP48-MLP8-2x3
MXIC	MX25L4025AM2C(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L4025AM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L4025AMC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L4025AMI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L4025AZMC(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L4025AZMI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L4026EM1I(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L5121EMC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L5121EOC(TSSOP8)	FLASH	LP-TSSOP-8PIN
MXIC	MX25L512CMI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L512COI(TSSOP8)	FLASH	LP-TSSOP-8PIN
MXIC	MX25L512CUI(USON2x3)	FLASH	LP48-MLP8-2x3
MXIC	MX25L512EMI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L512EOI(TSSOP8)	FLASH	LP-TSSOP-8PIN
MXIC	MX25L512EZUI(USON8)	FLASH	LP48-MLP8-2x3
MXIC	MX25L512MC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L512MI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L512ZMC(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L512ZMI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L6405DZNI(WSON6x8)	FLASH	LP48-WSON8-6x8
MXIC	MX25L6406EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L6406EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L6406EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L6408EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L6408EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L6408EZNI(WSON6x8)	FLASH	LP48-WSON8-6x8

Manufacturer	Parts Number	Type	ADAPTER
MXIC	MX25L6435EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L6435EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L6435EXCI(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
MXIC	MX25L6435EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L6436EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L6436EZNI(WSON6x8)	FLASH	LP48-WSON8-6x8
MXIC	MX25L6445EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L6445EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L6445EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L6455EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L6455EXCI(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
MXIC	MX25L6465EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L6465EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L6473EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L6473EMBI(VSOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L6473EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L6473EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L6475EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L6475EMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25L6475EZNI(WSON8)	FLASH	LP48-WSON8-5x6
MXIC	MX25L8005M2C(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L8005M2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L8005MC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L8005MI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L8005PC(SOP8)	FLASH	NONE
MXIC	MX25L8005PI(SOP8)	FLASH	NONE
MXIC	MX25L8005ZMC(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L8005ZMI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L8006EM1I(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L8006EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L8006EPI(DIP8)	FLASH	NONE
MXIC	MX25L8006EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L8006EZUI(USON4x4)	FLASH	LP-USON8-4x4
MXIC	MX25L8008EM1I(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L8008EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L8008EPI(DIP8)	FLASH	NONE
MXIC	MX25L8008EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L8008EZUI(USON4x4)	FLASH	LP-USON8-4x4
MXIC	MX25L8025M2C(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L8025M2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L8025MC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L8025MI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25L8025ZMC(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L8025ZMI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25L8035EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L8036EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L8073EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25L8075EM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25U12833FZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25U12835FMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25U12835FZ2I(WSON6x8)	FLASH	LP48-WSON8-6x8
MXIC	MX25U12835FZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25U1635EM1(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25U1635EM2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25U1635EZN(WSON8)	FLASH	LP48-WSON8-5x6
MXIC	MX25U1635FM2I(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25U1635MI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25U2032EMI(SOP8)	FLASH	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
MXIC	MX25U25635FMI(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
MXIC	MX25U25635FZ2I(WSON6x8)	FLASH	LP48-WSON8-6x8
MXIC	MX25U25635FZ4I(WSON6x8)	FLASH	LP48-WSON8-6x8
MXIC	MX25U3235EM1(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25U3235EM2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25U3235EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25U3235FM2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25U3235FZN(WSON8)	FLASH	LP48-WSON8-5x6
MXIC	MX25U4032EM1I(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25U4032EMI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25U4032EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25U4032EZUI(USON4x4)	FLASH	LP-USON8-4x4
MXIC	MX25U4033EM1I(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25U4033EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25U4033EZUI(USON4x4)	FLASH	LP-USON8-4x4
MXIC	MX25U4035MI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25U4035ZUI(USON4x4)	FLASH	LP-USON8-4x4
MXIC	MX25U6435FM2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
MXIC	MX25U6435FZN(WSON8)	FLASH	LP48-WSON8-5x6
MXIC	MX25U8032EM1(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25U8032EZNI(WSON8)	FLASH	LP48-WSON8-5x6
MXIC	MX25U8032EZU(USON8)	FLASH	LP-USON8-4x4
MXIC	MX25U8035MI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25V4006EM1I(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25V4006EZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25V4006EZVI(USON8)	FLASH	LP48-MLP8-2x3
MXIC	MX25V4035MI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25V4035ZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX25V8035MI(SOP8)	FLASH	LP-SOP-16PIN(150mil)
MXIC	MX25V8035ZNI(WSON5x6)	FLASH	LP48-WSON8-5x6
MXIC	MX26LV400BTC(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX26LV400TTC(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX27C1000(DIP32)	EPROM	NONE
MXIC	MX27C1000(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
MXIC	MX27C1000(SOP32)	EPROM	LP48-SOP-32PIN
MXIC	MX27C1000(TSOP32)	EPROM	LP48-TSOP-32S
MXIC	MX27C1000A(DIP32)	EPROM	NONE
MXIC	MX27C1000A(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
MXIC	MX27C1000A(SOP32)	EPROM	LP48-SOP-32PIN
MXIC	MX27C1000A(TSOP32)	EPROM	LP48-TSOP-32S
MXIC	MX27C1000DC(DIP32)	EPROM	NONE
MXIC	MX27C1001(DIP32)	EPROM	NONE
MXIC	MX27C1001(SOP32)	EPROM	LP48-SOP-32PIN
MXIC	MX27C1024(DIP40)	EPROM	NONE
MXIC	MX27C1024(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
MXIC	MX27C1024(TSOP40)	EPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
MXIC	MX27C1100(DIP40)	EPROM	NONE
MXIC	MX27C1100(SOP40)	EPROM	LP48-PSOP-44PIN
MXIC	MX27C1610(DIP42)	EPROM	NONE
MXIC	MX27C2000(DIP32)	EPROM	NONE
MXIC	MX27C2000(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
MXIC	MX27C2000(SOP32)	EPROM	LP48-SOP-32PIN
MXIC	MX27C2000(TSOP32)	EPROM	LP48-TSOP-32S
MXIC	MX27C2000A(DIP32)	EPROM	NONE
MXIC	MX27C2000A(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
MXIC	MX27C2000A(SOP32)	EPROM	LP48-SOP-32PIN
MXIC	MX27C2000A(TSOP32)	EPROM	LP48-TSOP-32S
MXIC	MX27C2048(DIP40)	EPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
MXIC	MX27C2048(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
MXIC	MX27C2048(TSOP40)	EPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
MXIC	MX27C2100(DIP40)	EPROM	NONE
MXIC	MX27C2100(SOP40)	EPROM	LP48-PSOP-44PIN
MXIC	MX27C256(DIP28)	EPROM	NONE
MXIC	MX27C256(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
MXIC	MX27C256(TSOP28)	EPROM	LP48-TSOP-28PIN
MXIC	MX27C4000(DIP32)	EPROM	NONE
MXIC	MX27C4000(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
MXIC	MX27C4000(SOP32)	EPROM	LP48-SOP-32PIN
MXIC	MX27C4000(TSOP32)	EPROM	LP48-TSOP-32S
MXIC	MX27C4000A(DIP32)	EPROM	NONE
MXIC	MX27C4000A(SOP32)	EPROM	LP48-SOP-32PIN
MXIC	MX27C4000A(TSOP32)	EPROM	LP48-TSOP-32S
MXIC	MX27C4000AQC(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
MXIC	MX27C4096(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
MXIC	MX27C4096(TSOP40)	EPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
MXIC	MX27C4100(DIP40)	EPROM	NONE
MXIC	MX27C4100(SOP40)	EPROM	LP48-PSOP-44PIN
MXIC	MX27C4111(DIP40)	EPROM	NONE
MXIC	MX27C512(DIP28)	EPROM	NONE
MXIC	MX27C512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
MXIC	MX27C512(TSOP28)	EPROM	LP-TSOP-28PIN
MXIC	MX27C8000(DIP32)	EPROM	NONE
MXIC	MX27C8000(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
MXIC	MX27C8000(SOP32)	EPROM	LP48-PSOP-44PIN
MXIC	MX27C8000(TSOP32)	EPROM	LP48-TSOP-32S
MXIC	MX27C8100(DIP42)	EPROM	NONE
MXIC	MX27C8100(SOP42)	EPROM	LP48-PSOP-44PIN
MXIC	MX27C8111(DIP42)	EPROM	NONE
MXIC	MX27C8111(SOP42)	EPROM	LP48-PSOP-44PIN
MXIC	MX27L1000(DIP32)	EPROM	NONE
MXIC	MX27L1000(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
MXIC	MX27L1000(SOP32)	EPROM	LP48-SOP-32PIN
MXIC	MX27L1000(TSOP32)	EPROM	LP48-TSOP-32S
MXIC	MX27L2000(DIP32)	EPROM	NONE
MXIC	MX27L2000(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
MXIC	MX27L2000(SOP32)	EPROM	LP48-PSOP-44PIN
MXIC	MX27L2000(TSOP32)	EPROM	LP48-TSOP-32S
MXIC	MX27L256(DIP28)	EPROM	NONE
MXIC	MX27L256(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
MXIC	MX27L256(TSOP28)	EPROM	LP48-TSOP-28PIN
MXIC	MX27L4000(DIP32)	EPROM	NONE
MXIC	MX27L4000(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
MXIC	MX27L4000(SOP32)	EPROM	LP48-SOP-32PIN
MXIC	MX27L4000(TSOP32)	EPROM	LP48-TSOP-32S
MXIC	MX27L512(DIP28)	EPROM	NONE
MXIC	MX27L512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
MXIC	MX27L512(TSOP28)	EPROM	LP48-TSOP-28PIN
MXIC	MX29F002B(DIP32)	FLASH	NONE
MXIC	MX29F002B(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
MXIC	MX29F002B(TSOP32)	FLASH	LP48-TSOP-32S
MXIC	MX29F002NB(DIP32)	FLASH	NONE
MXIC	MX29F002NB(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
MXIC	MX29F002NB(TSOP32)	FLASH	LP48-TSOP-32S
MXIC	MX29F002NT(DIP32)	FLASH	NONE
MXIC	MX29F002NT(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
MXIC	MX29F002NT(TSOP32)	FLASH	LP48-TSOP-32S

Manufacturer	Parts Number	Type	ADAPTER
MXIC	MX29F002T(DIP32)	FLASH	NONE
MXIC	MX29F002T(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
MXIC	MX29F002T(TSOP32)	FLASH	LP48-TSOP-32S
MXIC	MX29F004B(DIP32)	FLASH	NONE
MXIC	MX29F004B(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
MXIC	MX29F004B(TSOP32)	FLASH	LP48-TSOP-32S
MXIC	MX29F004T(DIP32)	FLASH	NONE
MXIC	MX29F004T(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
MXIC	MX29F004T(TSOP32)	FLASH	LP48-TSOP-32S
MXIC	MX29F016(SOP44)	FLASH	LP-SOP-44PIN
MXIC	MX29F016(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
MXIC	MX29F016(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29F022B(DIP32)	FLASH	NONE
MXIC	MX29F022B(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
MXIC	MX29F022B(TSOP32)	FLASH	LP48-TSOP-32S
MXIC	MX29F022NB(DIP32)	FLASH	NONE
MXIC	MX29F022NB(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
MXIC	MX29F022NB(TSOP32)	FLASH	LP48-TSOP-32S
MXIC	MX29F022NT(DIP32)	FLASH	NONE
MXIC	MX29F022NT(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
MXIC	MX29F022NT(TSOP32)	FLASH	LP48-TSOP-32S
MXIC	MX29F022T(DIP32)	FLASH	NONE
MXIC	MX29F022T(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
MXIC	MX29F022T(TSOP32)	FLASH	LP48-TSOP-32S
MXIC	MX29F040(DIP32)	FLASH	NONE
MXIC	MX29F040(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
MXIC	MX29F040(TSOP32)	FLASH	LP48-TSOP-32S
MXIC	MX29F040C(DIP32)	FLASH	NONE
MXIC	MX29F040C(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
MXIC	MX29F040C(TSOP32)	FLASH	LP48-TSOP-32S
MXIC	MX29F080(SOP44)	FLASH	LP-SOP-44PIN
MXIC	MX29F080(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
MXIC	MX29F100B(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29F100B(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29F100T(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29F100T(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29F200B(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29F200B(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29F200CB(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29F200CB(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29F200CT(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29F200CT(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29F200T(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29F200T(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29F400B(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29F400B(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29F400CB(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29F400CB(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29F400CT(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29F400CT(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29F400T(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29F400T(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29F800B(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29F800B(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29F800CB(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29F800CT(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29F800T(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29F800T(TSOP48)	FLASH	LP-TSOP-48S

[illegible]

Manufacturer	Parts Number	Type	ADAPTER
MXIC	MX29GL512FLT2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
MXIC	MX29GL512FLXF(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
MXIC	MX29GL512FUT2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
MXIC	MX29GL512FUXF(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
MXIC	MX29GL640EHFX(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
MXIC	MX29GL640EHT2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
MXIC	MX29GL640ELFX(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
MXIC	MX29GL640ELT2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
MXIC	MX29LA128MBT(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
MXIC	MX29LA128MTT(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
MXIC	MX29LV040(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
MXIC	MX29LV040(TSOP32)	FLASH	LP48-TSOP-32S
MXIC	MX29LV128DB(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV128DB(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
MXIC	MX29LV128DBT2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
MXIC	MX29LV128DT(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV128DT(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
MXIC	MX29LV128DTT2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
MXIC	MX29LV128MHT(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
MXIC	MX29LV128MLT(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
MXIC	MX29LV160AB(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29LV160AB(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV160AT(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29LV160AT(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV160B(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29LV160B(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV160BB(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29LV160BB(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV160BT(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29LV160BT(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV160CB(CSP48)	FLASH	LP-TFBGA-48PIN-6x8
MXIC	MX29LV160CB(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV160CT(CSP48)	FLASH	LP-TFBGA-48PIN-6x8
MXIC	MX29LV160CT(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV160DBTI(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV160DTTI(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV160T(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29LV160T(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV160TTC(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV161B(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29LV161T(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29LV320CBX(CSP48)	FLASH	LP-TFBGA-48PIN-6x8
MXIC	MX29LV320CTX(CSP48)	FLASH	LP-TFBGA-48PIN-6x8
MXIC	MX29LV320DB(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV320DT(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV320EBT(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV320ETT(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV400B(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29LV400BTC(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV400CB(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV400CBXB(CSP48)	FLASH	LP-TFBGA-48PIN-6x8
MXIC	MX29LV400CBXE(CSP48)	FLASH	LP-TFBGA-48PIN-6x8
MXIC	MX29LV400CT(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV400CTXB(CSP48)	FLASH	LP-TFBGA-48PIN-6x8
MXIC	MX29LV400CTXE(CSP48)	FLASH	LP-TFBGA-48PIN-6x8
MXIC	MX29LV400T(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29LV400TTC(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV640BB(TSOP48)	FLASH	LP-TSOP-48S

Manufacturer	Parts Number	Type	ADAPTER
MXIC	MX29LV640BT(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV640EB(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV640ET(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV640MHT(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
MXIC	MX29LV640MLT(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
MXIC	MX29LV641MH(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV800AB(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29LV800AB(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV800ABXB(CSP48)	FLASH	LP-TFBGA-48PIN-6x8
MXIC	MX29LV800ABXE(CSP48)	FLASH	LP-TFBGA-48PIN-6x8
MXIC	MX29LV800AT(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29LV800AT(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV800ATXB(CSP48)	FLASH	LP-TFBGA-48PIN-6x8
MXIC	MX29LV800ATXE(CSP48)	FLASH	LP-TFBGA-48PIN-6x8
MXIC	MX29LV800B(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29LV800B(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV800BB(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29LV800BT(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29LV800BTC(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV800CB(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29LV800CBT(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV800CBXB(CSP48)	FLASH	LP-TFBGA-48PIN-6x8
MXIC	MX29LV800CBXE(CSP48)	FLASH	LP-TFBGA-48PIN-6x8
MXIC	MX29LV800CT(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29LV800CTT(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV800CTXB(CSP48)	FLASH	LP-TFBGA-48PIN-6x8
MXIC	MX29LV800CTXE(CSP48)	FLASH	LP-TFBGA-48PIN-6x8
MXIC	MX29LV800T(PSOP44)	FLASH	LP48-PSOP-44PIN
MXIC	MX29LV800T(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX29LV800TTC(TSOP48)	FLASH	LP-TSOP-48S
MXIC	MX68GA1G0FHXF(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
MXIC	MX68GA1G0FLXF(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
MXIC	MX68GL1G0FDT2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
MXIC	MX68GL1G0FDXF(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
MXIC	MX68GL1G0FHT2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
MXIC	MX68GL1G0FHXF(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
MXIC	MX68GL1G0FLT2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
MXIC	MX68GL1G0FLXF(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
MXIC	MX68GL1G0FUT2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
MXIC	MX68GL1G0FUXF(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
My-MS	MM24C01-3(DIP8)	EEPROM	NONE
My-MS	MM24C01-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
My-MS	MM24C02-3(DIP8)	EEPROM	NONE
My-MS	MM24C02-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
My-MS	MM24C04-3(DIP8)	EEPROM	NONE
My-MS	MM24C04-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
My-MS	MM24C08(DIP8)	EEPROM	NONE
My-MS	MM24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
My-MS	MM24C08-2(DIP8)	EEPROM	NONE
My-MS	MM24C08-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
My-MS	MM24C08-3(DIP8)	EEPROM	NONE
My-MS	MM24C08-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
My-MS	MM24C16(DIP8)	EEPROM	NONE
My-MS	MM24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
My-MS	MM24C16-2(DIP8)	EEPROM	NONE
My-MS	MM24C16-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
My-MS	MM24C16-3(DIP8)	EEPROM	NONE
My-MS	MM24C16-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
My-MS	MM24C32(DIP8)	EEPROM	NONE
My-MS	MM24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
My-MS	MM24C32-2(DIP8)	EEPROM	NONE
My-MS	MM24C32-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
My-MS	MM24C32-3(DIP8)	EEPROM	NONE
My-MS	MM24C32-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
My-MS	MM24C64(DIP8)	EEPROM	NONE
My-MS	MM24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
My-MS	MM24C64-2(DIP8)	EEPROM	NONE
My-MS	MM24C64-2(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
My-MS	MM24C64-3(DIP8)	EEPROM	NONE
My-MS	MM24C64-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
My-MS	MM93C46-3(DIP8)	EEPROM	NONE
My-MS	MM93C46-3G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
My-MS	MM93C46-3GR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
My-MS	MM93C56-3(DIP8)	EEPROM	NONE
My-MS	MM93C56-3G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
My-MS	MM93C56-3GR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
My-MS	MM93C66-3(DIP8)	EEPROM	NONE
My-MS	MM93C66-3G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
My-MS	MM93C66-3GR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
MySON	CS8966-A0(LQFP48)	MPU / MCU	LP-LQFP-48PIN
MySON	CS8966-A1(LQFP48)	MPU / MCU	LP-LQFP-48PIN
MySON	MTV24C02(DIP8)	EEPROM	NONE
MySON	MTV24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
MySON	MTV24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
MySON	MTV24C04(DIP8)	EEPROM	NONE
MySON	MTV24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
MySON	MTV24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
MySON	MTV24C08(DIP8)	EEPROM	NONE
MySON	MTV24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
MySON	MTV24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
MySON	MTV24C16(DIP8)	EEPROM	NONE
MySON	MTV24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
MySON	MTV24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
MySON	MTV24LC02(DIP8)	EEPROM	NONE
MySON	MTV24LC02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
MySON	MTV24LC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
MySON	MTV24LC04(DIP8)	EEPROM	NONE
MySON	MTV24LC04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
MySON	MTV24LC04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
MySON	MTV24LC08(DIP8)	EEPROM	NONE
MySON	MTV24LC08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
MySON	MTV24LC08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
MySON	MTV24LC16(DIP8)	EEPROM	NONE
MySON	MTV24LC16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
MySON	MTV24LC16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NANTRONICS	N25S10(DIP8)	FLASH	NONE
NANTRONICS	N25S10(SOP8-150mil)	FLASH	LP-SOP-16PIN(150mil)
NANTRONICS	N25S10(SOP8-207mil)	FLASH	LP-SOP-8PIN-B(207mil)
NANTRONICS	N25S10(WSON8)	FLASH	LP48-WSON8-5x6
NANTRONICS	N25S16(DIP8)	FLASH	NONE
NANTRONICS	N25S16(SOP8-150mil)	FLASH	LP-SOP-16PIN(150mil)
NANTRONICS	N25S16(SOP8-207mil)	FLASH	LP-SOP-8PIN-B(207mil)
NANTRONICS	N25S16(WSON8)	FLASH	LP48-WSON8-5x6
NANTRONICS	N25S20(DIP8)	FLASH	NONE
NANTRONICS	N25S20(SOP8-150mil)	FLASH	LP-SOP-16PIN(150mil)
NANTRONICS	N25S20(SOP8-207mil)	FLASH	LP-SOP-8PIN-B(207mil)

Manufacturer	Parts Number	Type	ADAPTER
NANTRONICS	N25S20(WSON8)	FLASH	LP48-WSON8-5x6
NANTRONICS	N25S40(DIP8)	FLASH	NONE
NANTRONICS	N25S40(SOP8-150mil)	FLASH	LP-SOP-16PIN(150mil)
NANTRONICS	N25S40(SOP8-207mil)	FLASH	LP-SOP-8PIN-B(207mil)
NANTRONICS	N25S40(WSON8)	FLASH	LP48-WSON8-5x6
NANTRONICS	N25S80(DIP8)	FLASH	NONE
NANTRONICS	N25S80(SOP8-150mil)	FLASH	LP-SOP-16PIN(150mil)
NANTRONICS	N25S80(SOP8-207mil)	FLASH	LP-SOP-8PIN-B(207mil)
NANTRONICS	N25S80(WSON8)	FLASH	LP48-WSON8-5x6
NEC	UPD2732B(DIP24)	EPROM	NONE
NEC	uPD27C1000(DIP40)	EPROM	NONE
NEC	uPD27C1000(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
NEC	uPD27C1000A(DIP40)	EPROM	NONE
NEC	uPD27C1001A(DIP32)	EPROM	NONE
NEC	uPD27C1024(DIP40)	EPROM	NONE
NEC	uPD27C1024(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
NEC	uPD27C2001(DIP32)	EPROM	NONE
NEC	uPD27C256A(DIP28)	EPROM	NONE
NEC	uPD27C4000(DIP40)	EPROM	NONE
NEC	uPD27C4001(DIP32)	EPROM	NONE
NEC	uPD27C512(DIP28)	EPROM	NONE
NEC	uPD27C64C(DIP28)	EPROM	NONE
NEC	uPD27C64D(DIP28)	EPROM	NONE
NEC	uPD2804(DIP24)	EEPROM	NONE
NEC	uPD28C256(DIP28)	EEPROM	NONE
NEC	uPD28C64(DIP28)	EEPROM	NONE
NEC	uPD28C64(SOP28)	EEPROM	LP-SOP-28PIN-B(300mil)
NEC	uPD28C64A(DIP28)	EEPROM	NONE
NEC	uPD28C64A(SOP28)	EEPROM	LP-SOP-28PIN-B(300mil)
NEC	uPD28C64A(TSOP32)	EEPROM	LP48-TSOP-32S
Nik Microelectr	24LC02(DIP8)	EEPROM	NONE
Nik Microelectr	24LC02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C01(DIP8)	EEPROM	NONE
NS	NM24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C02(DIP8)	EEPROM	NONE
NS	NM24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C02F(DIP8)	EEPROM	NONE
NS	NM24C02F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C02F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C02FL(DIP8)	EEPROM	NONE
NS	NM24C02FL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C02FL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C02L(DIP8)	EEPROM	NONE
NS	NM24C02L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C02L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C03(DIP8)	EEPROM	NONE
NS	NM24C03(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C03(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C03F(DIP8)	EEPROM	NONE
NS	NM24C03F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C03F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C03FL(DIP8)	EEPROM	NONE
NS	NM24C03FL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C03FL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C03L(DIP8)	EEPROM	NONE
NS	NM24C03L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
NS	NM24C03L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C04(DIP8)	EEPROM	NONE
NS	NM24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C04F(DIP8)	EEPROM	NONE
NS	NM24C04F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C04F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C04FL(DIP8)	EEPROM	NONE
NS	NM24C04FL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C04FL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C04L(DIP8)	EEPROM	NONE
NS	NM24C04L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C04L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C05(DIP8)	EEPROM	NONE
NS	NM24C05(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C05(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C05F(DIP8)	EEPROM	NONE
NS	NM24C05F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C05F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C05FL(DIP8)	EEPROM	NONE
NS	NM24C05FL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C05FL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C05L(DIP8)	EEPROM	NONE
NS	NM24C05L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C05L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C08(DIP8)	EEPROM	NONE
NS	NM24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C08F(DIP8)	EEPROM	NONE
NS	NM24C08F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C08F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C08FL(DIP8)	EEPROM	NONE
NS	NM24C08FL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C08FL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C08L(DIP8)	EEPROM	NONE
NS	NM24C08L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C08L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C09(DIP8)	EEPROM	NONE
NS	NM24C09(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C09(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C09F(DIP8)	EEPROM	NONE
NS	NM24C09F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C09F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C09FL(DIP8)	EEPROM	NONE
NS	NM24C09FL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C09FL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C09L(DIP8)	EEPROM	NONE
NS	NM24C09L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C09L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C16(DIP8)	EEPROM	NONE
NS	NM24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C16F(DIP8)	EEPROM	NONE
NS	NM24C16F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C16F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C16FL(DIP8)	EEPROM	NONE
NS	NM24C16FL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C16FL(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
NS	NM24C16L(DIP8)	EEPROM	NONE
NS	NM24C16L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C16L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C17(DIP8)	EEPROM	NONE
NS	NM24C17(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C17(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C17F(DIP8)	EEPROM	NONE
NS	NM24C17F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C17F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C17FL(DIP8)	EEPROM	NONE
NS	NM24C17FL(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C17FL(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C17L(DIP8)	EEPROM	NONE
NS	NM24C17L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C17L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C32(DIP8)	EEPROM	NONE
NS	NM24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C65(DIP8)	EEPROM	NONE
NS	NM24C65(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C65(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C65L(DIP8)	EEPROM	NONE
NS	NM24C65L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C65L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24C65XLZ(DIP8)	EEPROM	NONE
NS	NM24C65XLZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24C65XLZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24W02(DIP8)	EEPROM	NONE
NS	NM24W02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24W02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24W02L(DIP8)	EEPROM	NONE
NS	NM24W02L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24W02L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24W02LZ(DIP8)	EEPROM	NONE
NS	NM24W02LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24W02LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24W04(DIP8)	EEPROM	NONE
NS	NM24W04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24W04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24W04L(DIP8)	EEPROM	NONE
NS	NM24W04L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24W04L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24W04LZ(DIP8)	EEPROM	NONE
NS	NM24W04LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24W04LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24W08(DIP8)	EEPROM	NONE
NS	NM24W08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24W08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24W08L(DIP8)	EEPROM	NONE
NS	NM24W08L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24W08L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24W08LZ(DIP8)	EEPROM	NONE
NS	NM24W08LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24W08LZ(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24W16(DIP8)	EEPROM	NONE
NS	NM24W16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24W16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24W16L(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
NS	NM24W16L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM24W16L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM24W16LZ(DIP8)	EEPROM	NONE
NS	NM24W16LZ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM27BV010(TSOP32)	EPROM	LP48-TSOP-32S
NS	NM27C010(DIP32)	EPROM	NONE
NS	NM27C010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
NS	NM27C020(DIP32)	EPROM	NONE
NS	NM27C020(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
NS	NM27C040(DIP32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
NS	NM27C128(DIP28)	EPROM	NONE
NS	NM27C256(DIP28)	EPROM	NONE
NS	NM27C256(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
NS	NM27C512(DIP28)	EPROM	NONE
NS	NM27C512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
NS	NM27LV010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
NS	NM28C64-A(DIP28)	EEPROM	NONE
NS	NM28C64-A(TSOP28)	EEPROM	LP-TSOP-28PIN
NS	NM28C64L(DIP28)	EEPROM	NONE
NS	NM28C64L(TSOP28)	EEPROM	LP-TSOP-28PIN
NS	NM93C06(DIP8)	EEPROM	NONE
NS	NM93C06(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93C06(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93C06L(DIP8)	EEPROM	NONE
NS	NM93C06L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93C06L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93C13(DIP8)	EEPROM	NONE
NS	NM93C13(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93C14(DIP8)	EEPROM	NONE
NS	NM93C14(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93C46(DIP8)	EEPROM	NONE
NS	NM93C46(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93C46(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93C46A-X16(DIP8)	EEPROM	NONE
NS	NM93C46A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93C46A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93C46A-X8(DIP8)	EEPROM	NONE
NS	NM93C46A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93C46A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93C46L(DIP8)	EEPROM	NONE
NS	NM93C46L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93C46L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93C56(DIP8)	EEPROM	NONE
NS	NM93C56(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93C56(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93C56A-X16(DIP8)	EEPROM	NONE
NS	NM93C56A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93C56A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93C56A-X8(DIP8)	EEPROM	NONE
NS	NM93C56A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93C56A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93C56L(DIP8)	EEPROM	NONE
NS	NM93C56L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93C56L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93C66(DIP8)	EEPROM	NONE
NS	NM93C66(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93C66(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93C66A-X16(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
NS	NM93C66A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93C66A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93C66A-X8(DIP8)	EEPROM	NONE
NS	NM93C66A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93C66A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93C66L(DIP8)	EEPROM	NONE
NS	NM93C66L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93C66L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93C86A-X16(DIP8)	EEPROM	NONE
NS	NM93C86A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93C86A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93C86A-X8(DIP8)	EEPROM	NONE
NS	NM93C86A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93C86A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93CS06(DIP8)	EEPROM	NONE
NS	NM93CS06(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93CS06(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93CS06L(DIP8)	EEPROM	NONE
NS	NM93CS06L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93CS06L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93CS46(DIP8)	EEPROM	NONE
NS	NM93CS46(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93CS46(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93CS46L(DIP8)	EEPROM	NONE
NS	NM93CS46L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93CS46L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93CS56(DIP8)	EEPROM	NONE
NS	NM93CS56(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93CS56(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93CS56L(DIP8)	EEPROM	NONE
NS	NM93CS56L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93CS56L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93CS66(DIP8)	EEPROM	NONE
NS	NM93CS66(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93CS66(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93CS66L(DIP8)	EEPROM	NONE
NS	NM93CS66L(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NM93CS66L(TSSOP8)	EEPROM	LP-TSSOP-8PIN
NS	NM93S06(DIP8)	EEPROM	NONE
NS	NM93S46(DIP8)	EEPROM	NONE
NS	NM93S56(DIP8)	EEPROM	NONE
NS	NM93S66(DIP8)	EEPROM	NONE
NS	NMC27C010(DIP32)	EPROM	NONE
NS	NMC27C128(DIP28)	EPROM	NONE
NS	NMC27C128B(DIP28)	EPROM	NONE
NS	NMC27C16B(DIP24)	EPROM	NONE
NS	NMC27C256(DIP28)	EPROM	NONE
NS	NMC27C256(SOP28)	EPROM	LP-SOP-28PIN-B(300mil)
NS	NMC27C256B(DIP28)	EPROM	NONE
NS	NMC27C32B(DIP24)	EPROM	NONE
NS	NMC27C512(DIP28)	EPROM	NONE
NS	NMC27C512A(DIP28)	EPROM	NONE
NS	NMC27C64(DIP28)	EPROM	NONE
NS	NMC27CP128(DIP28)	EPROM	NONE
NS	NMC27LC64(DIP28)	EPROM	NONE
NS	NMC9306(DIP8)	EEPROM	NONE
NS	NMC9306(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
NS	NMC9307(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
NS	NMC9313B(DIP8)	EEPROM	NONE
NS	NMC9314B(DIP8)	EEPROM	NONE
NS	NMC9345(DIP8)	EEPROM	NONE
NS	NMC9346(DIP8)	EEPROM	NONE
NS	NMC93C06(DIP8)	EEPROM	NONE
NS	NMC93C46(DIP8)	EEPROM	NONE
NS	NMC93C56(DIP8)	EEPROM	NONE
NS	NMC93C66(DIP8)	EEPROM	NONE
NS	NMC93CS06(DIP8)	EEPROM	NONE
NS	NMC93CS46(DIP8)	EEPROM	NONE
NS	NMC93CS56(DIP8)	EEPROM	NONE
NS	NMC93CS66(DIP8)	EEPROM	NONE
NUMONYX	E28F128J3A(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
NUMONYX	E28F256J3A(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
NUMONYX	E28F320J3A(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
NUMONYX	E28F640J3A(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
NUMONYX	JR28F032M29EWB(TSOP48)	FLASH	LP-TSOP-48S
NUMONYX	JR28F032M29EWH(TSOP48)	FLASH	LP-TSOP-48S
NUMONYX	JR28F032M29EWL(TSOP48)	FLASH	LP-TSOP-48S
NUMONYX	JR28F032M29EWT(TSOP48)	FLASH	LP-TSOP-48S
NUMONYX	JR28F064M29EWB(TSOP48)	FLASH	LP-TSOP-48S
NUMONYX	JR28F064M29EWH(TSOP48)	FLASH	LP-TSOP-48S
NUMONYX	JR28F064M29EWL(TSOP48)	FLASH	LP-TSOP-48S
NUMONYX	JR28F064M29EWT(TSOP48)	FLASH	LP-TSOP-48S
NUMONYX	JS28F00AM29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	JS28F00AM29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	JS28F00BM29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	JS28F00BM29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	JS28F032M29EWB(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	JS28F032M29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	JS28F032M29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	JS28F032M29EWT(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	JS28F064M29EWB(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	JS28F064M29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	JS28F064M29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	JS28F064M29EWT(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	JS28F128J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
NUMONYX	JS28F128J3D(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
NUMONYX	JS28F128J3F(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
NUMONYX	JS28F128M29EWB(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	JS28F128M29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	JS28F128M29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	JS28F128M29EWT(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	JS28F128P30B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	JS28F128P30BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	JS28F128P30T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	JS28F128P30TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	JS28F256J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
NUMONYX	JS28F256J3F(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
NUMONYX	JS28F256M29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	JS28F256M29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	JS28F256P30B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	JS28F256P30BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	JS28F256P30T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	JS28F256P30TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	JS28F256P33BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	JS28F256P33TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	JS28F320J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)

Manufacturer	Parts Number	Type	ADAPTER
NUMONYX	JS28F320J3D(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
NUMONYX	JS28F320J3F(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
NUMONYX	JS28F512M29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	JS28F512M29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	JS28F640J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
NUMONYX	JS28F640J3D(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
NUMONYX	JS28F640J3F(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
NUMONYX	JS28F640P30B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	JS28F640P30BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	JS28F640P30T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	JS28F640P30TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	JS28F640P33B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	JS28F640P33T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	M25P05-AVDW(TSSOP8)	FLASH	LP-TSSOP-8PIN
NUMONYX	M25P05-AVMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	M25P05-AVMP(WSON8)	FLASH	LP48-WSON8-5x6
NUMONYX	M25P10-AVMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	M25P10-AVMP(WSON8)	FLASH	LP48-WSON8-5x6
NUMONYX	M25P128VME(WSON8)	FLASH	LP48-WSON8-6x8
NUMONYX	M25P128VMF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
NUMONYX	M25P16VME(WSON8)	FLASH	LP48-WSON8-6x8
NUMONYX	M25P16VMF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
NUMONYX	M25P16VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	M25P16VMP(WSON8)	FLASH	LP48-WSON8-5x6
NUMONYX	M25P16VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
NUMONYX	M25P20VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	M25P20VMP(WSON8)	FLASH	LP48-WSON8-5x6
NUMONYX	M25P32VME(WSON8)	FLASH	LP48-WSON8-6x8
NUMONYX	M25P32VMF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
NUMONYX	M25P32VMP(WSON8)	FLASH	LP48-WSON8-5x6
NUMONYX	M25P32VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
NUMONYX	M25P40VME(WSON8)	FLASH	LP48-WSON8-6x8
NUMONYX	M25P40VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	M25P40VMP(WSON8)	FLASH	LP48-WSON8-5x6
NUMONYX	M25P64VME(WSON8)	FLASH	LP48-WSON8-6x8
NUMONYX	M25P64VMF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
NUMONYX	M25P80VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	M25P80VMP(WSON8)	FLASH	LP48-WSON8-5x6
NUMONYX	M25P80VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
NUMONYX	M25PE10VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	M25PE10VMP(WSON8)	FLASH	LP48-WSON8-5x6
NUMONYX	M25PE16VMP(SOP8)	FLASH	LP48-WSON8-5x6
NUMONYX	M25PE16VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
NUMONYX	M25PE20VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	M25PE20VMP(WSON8)	FLASH	LP48-WSON8-5x6
NUMONYX	M25PE40VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	M25PE40VMP(WSON8)	FLASH	LP48-WSON8-5x6
NUMONYX	M25PE40VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
NUMONYX	M25PE80VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	M25PE80VMP(WSON8)	FLASH	LP48-WSON8-6x8
NUMONYX	M25PE80VMS(WSON8)	FLASH	LP48-WSON8-5x6
NUMONYX	M25PE80VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
NUMONYX	M25PX16VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	M25PX16VMP(WSON8)	FLASH	LP48-WSON8-6x8
NUMONYX	M25PX16VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
NUMONYX	M25PX32VMF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
NUMONYX	M25PX32VMP(WSON8)	FLASH	LP48-WSON8-5x6
NUMONYX	M25PX32VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)

Manufacturer	Parts Number	Type	ADAPTER
NUMONYX	M25PX64VME(WSON8)	FLASH	LP48-WSON8-6x8
NUMONYX	M25PX64VMF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
NUMONYX	M25PX80VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	M25PX80VMP(WSON8)	FLASH	LP48-WSON8-5x6
NUMONYX	M25PX80VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
NUMONYX	M29DW128F(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	M29DW128G(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	M29DW256G(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	M29DW640D(TSOP48)	FLASH	LP-TSOP-48S
NUMONYX	M29W128FH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	M29W128FL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	M29W128GH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	M29W128GL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	M29W160EB-N(TSOP48)	FLASH	LP-TSOP-48S
NUMONYX	M29W160EB-ZA(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
NUMONYX	M29W160ET-N(TSOP48)	FLASH	LP-TSOP-48S
NUMONYX	M29W160ET-ZA(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
NUMONYX	M29W256GH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	M29W256GL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	M29W320EB-N(TSOP48)	FLASH	LP-TSOP-48S
NUMONYX	M29W320EB-ZE(BGA48)	FLASH	LP-TFBGA-48PIN-6x8
NUMONYX	M29W320ET-N(TSOP48)	FLASH	LP-TSOP-48S
NUMONYX	M29W320ET-ZE(BGA48)	FLASH	LP-TFBGA-48PIN-6x8
NUMONYX	M29W640DB(TSOP48)	FLASH	LP-TSOP-48S
NUMONYX	M29W640DT(TSOP48)	FLASH	LP-TSOP-48S
NUMONYX	M29W640FB(TSOP48)	FLASH	LP-TSOP-48S
NUMONYX	M29W640FT(TSOP48)	FLASH	LP-TSOP-48S
NUMONYX	M29W640GB(BGA48)	FLASH	LP-TFBGA-48PIN-6x8
NUMONYX	M29W640GB(TSOP48)	FLASH	LP-TSOP-48S
NUMONYX	M29W640GB(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	M29W640GH(TSOP48)	FLASH	LP-TSOP-48S
NUMONYX	M29W640GH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	M29W640GL(TSOP48)	FLASH	LP-TSOP-48S
NUMONYX	M29W640GL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	M29W640GT(TSOP48)	FLASH	LP-TSOP-48S
NUMONYX	M29W640GT(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
NUMONYX	M45PE10-VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	M45PE10-VMP(MLP8)	FLASH	LP48-WSON8-5x6
NUMONYX	M45PE16-VMP(MLP8)	FLASH	LP48-WSON8-5x6
NUMONYX	M45PE16-VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
NUMONYX	M45PE20-VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	M45PE20-VMP(MLP8)	FLASH	LP48-WSON8-5x6
NUMONYX	M45PE40-VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	M45PE40-VMP(MLP8)	FLASH	LP48-WSON8-5x6
NUMONYX	M45PE40-VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
NUMONYX	M45PE80-VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	M45PE80-VMP(MLP8)	FLASH	LP48-WSON8-5x6
NUMONYX	M45PE80-VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
NUMONYX	N25Q008A11EF6(MLP8)	FLASH	LP48-WSON8-5x6
NUMONYX	N25Q008A11ESC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	N25Q016A11ESC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	N25Q032A11E12(BGA24)	FLASH	LP-BGA-24PIN-5x5B
NUMONYX	N25Q032A11EF6(MLP8)	FLASH	LP48-WSON8-5x6
NUMONYX	N25Q032A11EF8(MLP8)	FLASH	LP48-WSON8-6x8
NUMONYX	N25Q032A11ESC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	N25Q032A11ESE(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
NUMONYX	N25Q032A11ESF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
NUMONYX	N25Q032A13E12(BGA24)	FLASH	LP-BGA-24PIN-5x5B

Manufacturer	Parts Number	Type	ADAPTER
NUMONYX	N25Q032A13EF6(MLP8)	FLASH	LP48-WSON8-5x6
NUMONYX	N25Q032A13EF8(MLP8)	FLASH	LP48-WSON8-6x8
NUMONYX	N25Q032A13ESC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	N25Q032A13ESE(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
NUMONYX	N25Q032A13ESF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
NUMONYX	N25Q064A11E12(BGA24)	FLASH	LP-BGA-24PIN-5x5B
NUMONYX	N25Q064A11EF6(MLP8)	FLASH	LP48-WSON8-5x6
NUMONYX	N25Q064A11EF8(MLP8)	FLASH	LP48-WSON8-6x8
NUMONYX	N25Q064A11ESC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	N25Q064A11ESE(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
NUMONYX	N25Q064A11ESF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
NUMONYX	N25Q064A13E12(BGA24)	FLASH	LP-BGA-24PIN-5x5B
NUMONYX	N25Q064A13EF6(MLP8)	FLASH	LP48-WSON8-5x6
NUMONYX	N25Q064A13EF8(MLP8)	FLASH	LP48-WSON8-6x8
NUMONYX	N25Q064A13ESC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	N25Q064A13ESE(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
NUMONYX	N25Q064A13ESF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
NUMONYX	N25Q128A11E12(BGA24)	FLASH	LP-BGA-24PIN-5x5B
NUMONYX	N25Q128A11EF6(MLP8)	FLASH	LP48-WSON8-5x6
NUMONYX	N25Q128A11EF6(SOP8)	FLASH	LP48-WSON8-5x6
NUMONYX	N25Q128A11EF8(MLP8)	FLASH	LP48-WSON8-6x8
NUMONYX	N25Q128A11EF8(SOP8)	FLASH	LP48-WSON8-6x8
NUMONYX	N25Q128A11ESC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	N25Q128A11ESE(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
NUMONYX	N25Q128A11ESF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
NUMONYX	N25Q128A13E12(BGA24)	FLASH	LP-BGA-24PIN-5x5B
NUMONYX	N25Q128A13EF6(MLP8)	FLASH	LP48-WSON8-5x6
NUMONYX	N25Q128A13EF6(SOP8)	FLASH	LP48-WSON8-5x6
NUMONYX	N25Q128A13EF8(MLP8)	FLASH	LP48-WSON8-6x8
NUMONYX	N25Q128A13EF8(SOP8)	FLASH	LP48-WSON8-6x8
NUMONYX	N25Q128A13ESC(SOP8)	FLASH	LP-SOP-16PIN(150mil)
NUMONYX	N25Q128A13ESE(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
NUMONYX	N25Q128A13ESF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
NUMONYX	PC28F00AM29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
NUMONYX	PC28F00AM29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
NUMONYX	PC28F00BM29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
NUMONYX	PC28F00BM29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
NUMONYX	PC28F128J3C(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
NUMONYX	PC28F128J3D(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
NUMONYX	PC28F128J3F(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
NUMONYX	PC28F128M29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
NUMONYX	PC28F128M29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
NUMONYX	PC28F128P30B(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
NUMONYX	PC28F128P30BF(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
NUMONYX	PC28F128P30T(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
NUMONYX	PC28F128P30TF(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
NUMONYX	PC28F256J3C(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
NUMONYX	PC28F256J3D(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
NUMONYX	PC28F256J3F(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
NUMONYX	PC28F256M29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
NUMONYX	PC28F256M29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
NUMONYX	PC28F256P30B(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
NUMONYX	PC28F256P30BF(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
NUMONYX	PC28F256P30T(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
NUMONYX	PC28F256P30TF(EBGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
NUMONYX	PC28F320J3C(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
NUMONYX	PC28F320J3D(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
NUMONYX	PC28F320J3F(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)

[illegible]

Manufacturer	Parts Number	Type	ADAPTER
NUMONYX	TE28F256P30TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	TE28F256P33BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	TE28F256P33TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	TE28F320J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
NUMONYX	TE28F320J3D(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
NUMONYX	TE28F640J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
NUMONYX	TE28F640J3D(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
NUMONYX	TE28F640P30B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	TE28F640P30BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	TE28F640P30T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	TE28F640P30TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	TE28F640P33B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUMONYX	TE28F640P33T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
NUVOTON	M0516LAN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	M0516LBN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	M0516ZAN(QFN33)	MPU / MCU	LP-QFN-32PIN
NUVOTON	M0516ZBN(QFN33)	MPU / MCU	LP-QFN-32PIN
NUVOTON	M052LAN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	M052LBN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	M052ZAN(QFN33)	MPU / MCU	LP-QFN-32PIN
NUVOTON	M052ZBN(QFN33)	MPU / MCU	LP-QFN-32PIN
NUVOTON	M054LAN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	M054LBN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	M054ZAN(QFN33)	MPU / MCU	LP-QFN-32PIN
NUVOTON	M054ZBN(QFN33)	MPU / MCU	LP-QFN-32PIN
NUVOTON	M058LAN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	M058LBN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	M058ZAN(QFN33)	MPU / MCU	LP-QFN-32PIN
NUVOTON	M058ZBN(QFN33)	MPU / MCU	LP-QFN-32PIN
NUVOTON	MINI51LAN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	MINI52LAN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	MINI54LAN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	NUC100LC1AN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	NUC100LD1AN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	NUC100LD2AN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	NUC100LD3AN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	NUC100LE3AN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	NUC120LC1AN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	NUC120LD1AN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	NUC120LD2AN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	NUC120LD3AN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	NUC120LE3AN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	NUC130LC1CN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	NUC130LD2CN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	NUC130LE3CN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	NUC140LC1CN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	NUC140LD2CN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	NUC140LE3CN(LQFP48)	MPU / MCU	LP-LQFP-48PIN
NUVOTON	W77E58(DIP40)	MPU / MCU	NONE
NUVOTON	W77E58(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W77E58(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78E051C(DIP40)	MPU / MCU	NONE
NUVOTON	W78E051C(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78E051C(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78E051DDG(DIP40)	MPU / MCU	NONE
NUVOTON	W78E051DFG(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78E051DPG(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78E052C(DIP40)	MPU / MCU	NONE

Manufacturer	Parts Number	Type	ADAPTER
NUVOTON	W78E052C(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78E052C(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78E052DDG(DIP40)	MPU / MCU	NONE
NUVOTON	W78E052DFG(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78E052DPG(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78E054C(DIP40)	MPU / MCU	NONE
NUVOTON	W78E054C(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78E054C(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78E054DDG(DIP40)	MPU / MCU	NONE
NUVOTON	W78E054DFG(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78E054DPG(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78E058DDG(DIP40)	MPU / MCU	NONE
NUVOTON	W78E058DFG(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78E058DPG(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78E065A(DIP40)	MPU / MCU	NONE
NUVOTON	W78E065A(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78E065A(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78E365(DIP40)	MPU / MCU	NONE
NUVOTON	W78E365(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78E365(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78E365A(DIP40)	MPU / MCU	NONE
NUVOTON	W78E365A(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78E365A(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78E516B(DIP40)	MPU / MCU	NONE
NUVOTON	W78E516B(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78E516B(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78E516DDG(DIP40)	MPU / MCU	NONE
NUVOTON	W78E516DFG(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78E516DPG(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78E51B(DIP40)	MPU / MCU	NONE
NUVOTON	W78E51B(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78E51B(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78E52B(DIP40)	MPU / MCU	NONE
NUVOTON	W78E52B(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78E52B(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78E54B(DIP40)	MPU / MCU	NONE
NUVOTON	W78E54B(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78E54B(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78E62(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78E62B(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78E65(DIP40)	MPU / MCU	NONE
NUVOTON	W78E65(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78E65(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78IE52(DIP40)	MPU / MCU	NONE
NUVOTON	W78IE52(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78IE52(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78IE54(DIP40)	MPU / MCU	NONE
NUVOTON	W78IE54(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78IE54(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78IE58(DIP40)	MPU / MCU	NONE
NUVOTON	W78IE58(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78IE58(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78L365(DIP40)	MPU / MCU	NONE
NUVOTON	W78L365(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78L365(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78L365A(DIP40)	MPU / MCU	NONE
NUVOTON	W78L365A(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78L365A(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S

Manufacturer	Parts Number	Type	ADAPTER
NUVOTON	W78L516A(DIP40)	MPU / MCU	NONE
NUVOTON	W78L516A(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78L516A(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78LE051C(DIP40)	MPU / MCU	NONE
NUVOTON	W78LE051C(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78LE051C(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78LE052C(DIP40)	MPU / MCU	NONE
NUVOTON	W78LE052C(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78LE052C(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78LE054C(DIP40)	MPU / MCU	NONE
NUVOTON	W78LE054C(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78LE054C(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78LE365(DIP40)	MPU / MCU	NONE
NUVOTON	W78LE365(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78LE365(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78LE365A(DIP40)	MPU / MCU	NONE
NUVOTON	W78LE365A(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78LE365A(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78LE51(DIP40)	MPU / MCU	NONE
NUVOTON	W78LE51(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78LE51(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78LE516(DIP40)	MPU / MCU	NONE
NUVOTON	W78LE516(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78LE516(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78LE52(DIP40)	MPU / MCU	NONE
NUVOTON	W78LE52(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78LE52(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78LE54(DIP40)	MPU / MCU	NONE
NUVOTON	W78LE54(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78LE54(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78LE58(DIP40)	MPU / MCU	NONE
NUVOTON	W78LE58(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78LE58(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W78LE812(DIP40)	MPU / MCU	NONE
NUVOTON	W78LE812(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NUVOTON	W78LE812(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
NUVOTON	W79E632A(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89C51RA+(DIP40)	MPU / MCU	NONE
NXP	P89C51RA+(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89C51RA+(QFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89C51RA2(DIP40)	MPU / MCU	NONE
NXP	P89C51RA2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89C51RA2(QFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89C51RB+(DIP40)	MPU / MCU	NONE
NXP	P89C51RB+(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89C51RB+(QFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89C51RB2(DIP40)	MPU / MCU	NONE
NXP	P89C51RB2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89C51RB2(QFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89C51RC+(DIP40)	MPU / MCU	NONE
NXP	P89C51RC+(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89C51RC+(QFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89C51RC2(DIP40)	MPU / MCU	NONE
NXP	P89C51RC2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89C51RC2(QFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89C51RD+(DIP40)	MPU / MCU	NONE
NXP	P89C51RD+(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89C51RD+(QFP44)	MPU / MCU	LP48-VQFP-44S

Manufacturer	Parts Number	Type	ADAPTER
NXP	P89C51RD2(DIP40)	MPU / MCU	NONE
NXP	P89C51RD2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89C51RD2(QFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89C51UB(DIP40)	MPU / MCU	NONE
NXP	P89C51UB(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89C51UB(QFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89C52UB(DIP40)	MPU / MCU	NONE
NXP	P89C52UB(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89C52UB(QFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89C54UB(DIP40)	MPU / MCU	NONE
NXP	P89C54UB(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89C54UB(QFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89C58UB(DIP40)	MPU / MCU	NONE
NXP	P89C58UB(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89C58UB(QFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89C60X2(DIP40)	MPU / MCU	NONE
NXP	P89C60X2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89C60X2(QFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89C61X2(DIP40)	MPU / MCU	NONE
NXP	P89C61X2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89C61X2(QFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89C660(DIP40)	MPU / MCU	NONE
NXP	P89C660(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89C660(QFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89C662(DIP40)	MPU / MCU	NONE
NXP	P89C662(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89C662(QFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89C664(DIP40)	MPU / MCU	NONE
NXP	P89C664(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89C664(QFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89C668(DIP40)	MPU / MCU	NONE
NXP	P89C668(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89C668(QFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89C669(DIP40)	MPU / MCU	NONE
NXP	P89C669(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89C669(QFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89LPC901(DIP8)	MPU / MCU	NONE
NXP	P89LPC901(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
NXP	P89LPC902(DIP8)	MPU / MCU	NONE
NXP	P89LPC902(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
NXP	P89LPC903(DIP8)	MPU / MCU	NONE
NXP	P89LPC903(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
NXP	P89LPC904(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
NXP	P89LPC906(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
NXP	P89LPC907(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
NXP	P89LPC908(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
NXP	P89LPC9102(HVSON10)	MPU / MCU	HVSON10-3X3-0.5mm
NXP	P89LPC9103(HVSON10)	MPU / MCU	HVSON10-3X3-0.5mm
NXP	P89LPC9107(DIP14)	MPU / MCU	NONE
NXP	P89LPC9107(TSSOP14)	MPU / MCU	LP48-TSSOP-20PIN
NXP	P89LPC912(TSSOP14)	MPU / MCU	LP48-TSSOP-20PIN
NXP	P89LPC913(TSSOP14)	MPU / MCU	LP48-TSSOP-20PIN
NXP	P89LPC914(TSSOP14)	MPU / MCU	LP48-TSSOP-20PIN
NXP	P89LPC915(TSSOP14)	MPU / MCU	LP48-TSSOP-20PIN
NXP	P89LPC916(TSSOP16)	MPU / MCU	LP48-TSSOP-20PIN
NXP	P89LPC917(TSSOP16)	MPU / MCU	LP48-TSSOP-20PIN
NXP	P89LPC920(DIP20)	MPU / MCU	NONE
NXP	P89LPC920(SOP20)	MPU / MCU	LP48-SOP-20PIN

Manufacturer	Parts Number	Type	ADAPTER
NXP	P89LPC920(SSOP20)	MPU / MCU	LP48-SSOP-28PIN
NXP	P89LPC920(TSSOP20)	MPU / MCU	LP48-TSSOP-20PIN
NXP	P89LPC921(DIP20)	MPU / MCU	NONE
NXP	P89LPC921(SOP20)	MPU / MCU	LP48-SOP-20PIN
NXP	P89LPC921(SSOP20)	MPU / MCU	LP48-SSOP-28PIN
NXP	P89LPC921(TSSOP20)	MPU / MCU	LP48-TSSOP-20PIN
NXP	P89LPC922(DIP20)	MPU / MCU	NONE
NXP	P89LPC922(SOP20)	MPU / MCU	LP48-SOP-20PIN
NXP	P89LPC922(SSOP20)	MPU / MCU	LP48-SSOP-28PIN
NXP	P89LPC922(TSSOP20)	MPU / MCU	LP48-TSSOP-20PIN
NXP	P89LPC9221(DIP20)	MPU / MCU	NONE
NXP	P89LPC9221(TSSOP20)	MPU / MCU	LP48-TSSOP-20PIN
NXP	P89LPC924(DIP20)	MPU / MCU	NONE
NXP	P89LPC924(TSSOP20)	MPU / MCU	LP48-TSSOP-20PIN
NXP	P89LPC925(DIP20)	MPU / MCU	NONE
NXP	P89LV51RB2(DIP40)	MPU / MCU	NONE
NXP	P89LV51RB2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89LV51RB2(TQFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89LV51RC2(DIP40)	MPU / MCU	NONE
NXP	P89LV51RC2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89LV51RC2(TQFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89LV51RD2(DIP40)	MPU / MCU	NONE
NXP	P89LV51RD2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89LV51RD2(TQFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89V51RB2(DIP40)	MPU / MCU	NONE
NXP	P89V51RB2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89V51RB2(TQFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89V51RC2(DIP40)	MPU / MCU	NONE
NXP	P89V51RC2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89V51RC2(TQFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89V51RD2(TQFP44)	MPU / MCU	LP48-VQFP-44S
NXP	P89V51RD2BA(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89V51RD2BN(DIP40)	MPU / MCU	NONE
NXP	P89V51RD2FA(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
NXP	P89V51RD2FN(DIP40)	MPU / MCU	NONE
NXP	PCA24S08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
OKI	MR27V1602EMA(SOP44)	EPROM	LP48-PSOP-44PIN
OKI	MR27V1602ETN(TSOP48)	EPROM	LP-TSOP-48S
OKI	MR27V1602ETP(TSOP44)	EPROM	LP-TSOP-44PIN*
OKI	MR27V1652DMA(SOP44)	EPROM	LP48-PSOP-44PIN
OKI	MR27V1652DRA(DIP42)	EPROM	NONE
OKI	MR27V1652DTA(TSOP48)	EPROM	LP-TSOP-48S
OKI	MR27V1652DTP(TSOP44)	EPROM	LP-TSOP-44PIN*
OKI	MR27V3202EMA(SOP44)	EPROM	LP48-PSOP-44PIN
OKI	MR27V3202ETMA(SOP44)	EPROM	LP48-PSOP-44PIN
OKI	MR27V3202ETP(TSOP44)	EPROM	LP-TSOP-44PIN*
OKI	MR27V3202FMA(SOP44)	EPROM	LP48-PSOP-44PIN(1536)
OKI	MR27V3202FTN(TSOP48)	EPROM	LP-TSOP-48S
OKI	MR27V3202FTP(TSOP44)	EPROM	LP-TSOP-44PIN*
OKI	MR27V3252D(SOP44)	EPROM	LP48-PSOP-44PIN
OKI	MR27V3252D(TSOP48)	EPROM	LP-TSOP-48S
OKI	MR27V401D(DIP32)	EPROM	NONE
OKI	MR27V401D(SOP32)	EPROM	LP48-SOP-32PIN
OKI	MR27V401D(TSOP32)	EPROM	LP48-TSOP-32S
OKI	MR27V401EMA(VSOP)	EPROM	LP48-VSOP-32S
OKI	MR27V401ETA(TSOP32)	EPROM	LP48-TSOP-32S
OKI	MR27V402EJA(SOP42)	EPROM	LP48-SOP-44PIN
OKI	MR27V402EMP(SOP40)	EPROM	LP48-SOP-40PIN

Manufacturer	Parts Number	Type	ADAPTER
OKI	MR27V402ERP(DIP40)	EPROM	NONE
OKI	MR27V402ETP(TSOP44)	EPROM	LP-TSOP-44PIN*
OKI	MR27V402FJA(SOP42)	EPROM	LP48-SOP-44PIN
OKI	MR27V6402GMA(SOP44)	EPROM	LP48-PSOP-44PIN
OKI	MR27V6402GTN(TSOP48)	EPROM	LP-TSOP-48S
OKI	MR27V6402GTP(TSOP44)	EPROM	LP-TSOP-44PIN*
OKI	MR27V6452D(SOP44)	EPROM	LP48-PSOP-44PIN
OKI	MR27V6452G(SOP44)	EPROM	LP48-PSOP-44PIN
OKI	MR27V6452G(TSOP48)	EPROM	LP-TSOP-48S
OKI	MR27V801D(DIP32)	EPROM	NONE
OKI	MR27V801D(SOP32)	EPROM	LP48-SOP-32PIN
OKI	MR27V802D(DIP42)	EPROM	NONE
OKI	MR27V802D(SOP44)	EPROM	LP48-PSOP-44PIN
OKI	MR27V802DMA(SOP44)	EPROM	LP48-PSOP-44PIN
OKI	MR27V852D(DIP42)	EPROM	NONE
OKI	MR27V852D(SOP44)	EPROM	LP48-PSOP-44PIN
OKI	MR27V852EJA(SOJ42)	EPROM	NONE
OKI	MR27V852ERA(DIP42)	EPROM	NONE
OKI	MSM271024(DIP40)	EPROM	NONE
OKI	MSM27128A(DIP28)	EPROM	NONE
OKI	MSM27256(DIP28)	EPROM	NONE
OKI	MSM27512(DIP28)	EPROM	NONE
OKI	MSM2764A(DIP28)	EPROM	NONE
OKI	MSM2764Z(DIP28)	EPROM	NONE
OKI	MSM27C1000(DIP32)	EPROM	NONE
OKI	MSM27C1024(DIP40)	EPROM	NONE
OKI	MSM27C128(DIP28)	EPROM	NONE
OKI	MSM27C201CZ(DIP32)	EPROM	NONE
OKI	MSM27C201CZ(SOP32)	EPROM	LP48-SOP-32PIN
OKI	MSM27C401CZ(DIP32)	EPROM	NONE
OKI	MSM27C401CZ(SOP32)	EPROM	LP48-SOP-32PIN
OKI	MSM27C401CZ(TSOP32)	EPROM	LP48-TSOP-32S
OKI	MSM27C64(DIP28)	EPROM	NONE
OKI	MSM27C802CZ(DIP42)	EPROM	NONE
OKI	MSM27C802CZ(SOP44)	EPROM	LP48-PSOP-44PIN
OKI	MSM27C852CZ(DIP42)	EPROM	NONE
OKI	MSM27C852CZ(SOP44)	EPROM	LP48-PSOP-44PIN
OKI	MSM2816A(DIP24)	EEPROM	NONE
OKI	MSM28C16A(DIP24)	EEPROM	NONE
OKI	MSM28C256(DIP28)	EEPROM	NONE
OKI	MSM28C256(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
OKI	MSM28C64A(DIP28)	EEPROM	NONE
ON Semiconductor	CAT1021(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT1022(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT1023(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT1024(DIP8)	EEPROM	NONE
ON Semiconductor	CAT1024(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT1024(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT1025(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT1026(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT1027(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24AA01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24AA02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24AA04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24AA08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24AA16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24C00(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C00(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
ON Semiconductor	CAT24C00(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24C01(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24C01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24C01B(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C01B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24C01B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24C02(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24C021(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C022(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C023(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C02AI(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C02AI(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24C03(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C03(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24C03(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24C04(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24C041(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C042(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C043(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C05(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C05(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24C05(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24C08(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24C081(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C082(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C083(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C128(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24C128(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24C16(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24C161(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C162(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C163(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C164(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C164(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24C164(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24C208W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24C256(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C256(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT24C256(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24C32(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24C321(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C321(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24C321(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24C322(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C322(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24C322(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
ON Semiconductor	CAT24C323(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C323(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24C323(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24C64(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C64(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT24C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24C641(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C641(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT24C641(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24C642(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C642(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT24C642(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24C643(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24C643(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT24C643(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24FC17(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24FC17(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24FC17(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24FC512(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24FC512W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT24FC512X(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT24FC65(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24FC65(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT24FC65(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24FC66(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24FC66(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT24FC66(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24LC02I(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24LC04I(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24LC08I(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24LC16I(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24WC03(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24WC03(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24WC03(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24WC05(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24WC05(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24WC05(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24WC09(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24WC09(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24WC09(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24WC129(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24WC129(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24WC17(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24WC17(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24WC17(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT24WC257(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24WC257J(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24WC33(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24WC33J(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24WC65(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24WC65J(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT24WC66(DIP8)	EEPROM	NONE
ON Semiconductor	CAT24WC66W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT24WC66X(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT93C46-X16(DIP8)	EEPROM	NONE
ON Semiconductor	CAT93C46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT93C46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT93C46-X8(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
ON Semiconductor	CAT93C46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT93C46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT93C46R-X16(DIP8)	EEPROM	NONE
ON Semiconductor	CAT93C46R-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT93C46R-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT93C46R-X8(DIP8)	EEPROM	NONE
ON Semiconductor	CAT93C46R-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT93C46R-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT93C46RW-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT93C46RW-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT93C46W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT93C46W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT93C56-X16(DIP8)	EEPROM	NONE
ON Semiconductor	CAT93C56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT93C56-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT93C56-X8(DIP8)	EEPROM	NONE
ON Semiconductor	CAT93C56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT93C56-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT93C56W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT93C56W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT93C57-X16(DIP8)	EEPROM	NONE
ON Semiconductor	CAT93C57-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT93C57-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT93C57-X8(DIP8)	EEPROM	NONE
ON Semiconductor	CAT93C57-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT93C57-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT93C57W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT93C57W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT93C66-X16(DIP8)	EEPROM	NONE
ON Semiconductor	CAT93C66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT93C66-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT93C66-X8(DIP8)	EEPROM	NONE
ON Semiconductor	CAT93C66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT93C66-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT93C66W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT93C66W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT93C76-X16(DIP8)	EEPROM	NONE
ON Semiconductor	CAT93C76-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT93C76-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT93C76-X8(DIP8)	EEPROM	NONE
ON Semiconductor	CAT93C76-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT93C76-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT93C86-X16(DIP8)	EEPROM	NONE
ON Semiconductor	CAT93C86-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT93C86-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT93C86-X8(DIP8)	EEPROM	NONE
ON Semiconductor	CAT93C86-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil) or LP-SOP-8PIN-B(207mil)
ON Semiconductor	CAT93C86-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ON Semiconductor	CAT93C86W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT93C86W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT93HC46J-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT93HC46J-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT93HC46W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ON Semiconductor	CAT93HC46W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
PCT	PCT25VF010A-Q(WSON8)	FLASH	LP48-WSON8-5x6
PCT	PCT25VF010A-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PCT	PCT25VF016-Q(WSON8)	FLASH	LP48-WSON8-5x6
PCT	PCT25VF016-S2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)

Manufacturer	Parts Number	Type	ADAPTER
PCT	PCT25VF016B-Q(WSON8)	FLASH	LP48-WSON8-5x6
PCT	PCT25VF016B-S2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PCT	PCT25VF020-Q(WSON8)	FLASH	LP48-WSON8-5x6
PCT	PCT25VF020-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PCT	PCT25VF020A-Q(WSON8)	FLASH	LP48-WSON8-5x6
PCT	PCT25VF020A-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PCT	PCT25VF020B-Q(WSON8)	FLASH	LP48-WSON8-5x6
PCT	PCT25VF020B-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PCT	PCT25VF032-Q(WSON8)	FLASH	LP48-WSON8-5x6
PCT	PCT25VF032-S2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PCT	PCT25VF032B-Q(WSON8)	FLASH	LP48-WSON8-5x6
PCT	PCT25VF032B-S2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PCT	PCT25VF040B-50-Q(WSON8)	FLASH	LP48-WSON8-5x6
PCT	PCT25VF040B-50-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PCT	PCT25VF040B-50-S2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PCT	PCT25VF040B-80-Q(WSON8)	FLASH	LP48-WSON8-5x6
PCT	PCT25VF040B-80-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PCT	PCT25VF040B-80-S2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PCT	PCT25VF064C-Q2(WSON8)	FLASH	LP48-WSON8-6x8
PCT	PCT25VF064C-S(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
PCT	PCT25VF064C-S3(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PCT	PCT25VF080B-50-P(PDIP8)	FLASH	NONE
PCT	PCT25VF080B-50-Q(WSON8)	FLASH	LP48-WSON8-5x6
PCT	PCT25VF080B-50-S2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PCT	PCT25VF080B-80-P(PDIP8)	FLASH	NONE
PCT	PCT25VF080B-80-Q(WSON8)	FLASH	LP48-WSON8-5x6
PCT	PCT25VF080B-80-S2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PCT	PCT25VF512A-Q(WSON8)	FLASH	LP48-WSON8-5x6
PCT	PCT25VF512A-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PCT	PCT26VF016-Q(WSON8)	FLASH	LP48-WSON8-5x6
PCT	PCT26VF016-S2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PCT	PCT26VF032-Q(WSON8)	FLASH	LP48-WSON8-5x6
PCT	PCT26VF032-S2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PHILIPS	27C010(DIP32)	EPROM	NONE
PHILIPS	27C010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
PHILIPS	27C256(DIP28)	EPROM	NONE
PHILIPS	27C512(DIP28)	EPROM	NONE
PHILIPS	27C512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
PHILIPS	P87C52(DIP40)	MPU / MCU	NONE
PHILIPS	P87C52(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P87C52(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P87C54(DIP40)	MPU / MCU	NONE
PHILIPS	P87C54(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P87C54(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P87C58(DIP40)	MPU / MCU	NONE
PHILIPS	P87C58(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P87C58(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89C51RA+(DIP40)	MPU / MCU	NONE
PHILIPS	P89C51RA+(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89C51RA+(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89C51RA2(DIP40)	MPU / MCU	NONE
PHILIPS	P89C51RA2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89C51RA2(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89C51RB+(DIP40)	MPU / MCU	NONE
PHILIPS	P89C51RB+(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89C51RB+(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89C51RB2(DIP40)	MPU / MCU	NONE
PHILIPS	P89C51RB2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S

Manufacturer	Parts Number	Type	ADAPTER
PHILIPS	P89C51RB2(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89C51RC+(DIP40)	MPU / MCU	NONE
PHILIPS	P89C51RC+(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89C51RC+(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89C51RC2(DIP40)	MPU / MCU	NONE
PHILIPS	P89C51RC2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89C51RC2(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89C51RD+(DIP40)	MPU / MCU	NONE
PHILIPS	P89C51RD+(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89C51RD+(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89C51RD2(DIP40)	MPU / MCU	NONE
PHILIPS	P89C51RD2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89C51RD2(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89C51UB(DIP40)	MPU / MCU	NONE
PHILIPS	P89C51UB(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89C51UB(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89C52UB(DIP40)	MPU / MCU	NONE
PHILIPS	P89C52UB(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89C52UB(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89C54UB(DIP40)	MPU / MCU	NONE
PHILIPS	P89C54UB(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89C54UB(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89C58UB(DIP40)	MPU / MCU	NONE
PHILIPS	P89C58UB(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89C58UB(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89C60X2(DIP40)	MPU / MCU	NONE
PHILIPS	P89C60X2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89C60X2(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89C61X2(DIP40)	MPU / MCU	NONE
PHILIPS	P89C61X2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89C61X2(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89C660(DIP40)	MPU / MCU	NONE
PHILIPS	P89C660(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89C660(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89C662(DIP40)	MPU / MCU	NONE
PHILIPS	P89C662(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89C662(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89C664(DIP40)	MPU / MCU	NONE
PHILIPS	P89C664(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89C664(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89C668(DIP40)	MPU / MCU	NONE
PHILIPS	P89C668(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89C668(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89C669(DIP40)	MPU / MCU	NONE
PHILIPS	P89C669(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89C669(QFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89LPC901(DIP8)	MPU / MCU	NONE
PHILIPS	P89LPC901(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
PHILIPS	P89LPC902(DIP8)	MPU / MCU	NONE
PHILIPS	P89LPC902(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
PHILIPS	P89LPC903(DIP8)	MPU / MCU	NONE
PHILIPS	P89LPC903(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
PHILIPS	P89LPC904(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
PHILIPS	P89LPC906(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
PHILIPS	P89LPC907(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
PHILIPS	P89LPC908(SOP8)	MPU / MCU	LP-SOP-16PIN(150mil)
PHILIPS	P89LPC9102(HVSON10)	MPU / MCU	HVSON10-3X3-0.5mm
PHILIPS	P89LPC9103(HVSON10)	MPU / MCU	HVSON10-3X3-0.5mm

Manufacturer	Parts Number	Type	ADAPTER
PHILIPS	P89LPC9107(DIP14)	MPU / MCU	NONE
PHILIPS	P89LPC9107(TSSOP14)	MPU / MCU	LP48-TSSOP-20PIN
PHILIPS	P89LPC912(TSSOP14)	MPU / MCU	LP48-TSSOP-20PIN
PHILIPS	P89LPC913(TSSOP14)	MPU / MCU	LP48-TSSOP-20PIN
PHILIPS	P89LPC914(TSSOP14)	MPU / MCU	LP48-TSSOP-20PIN
PHILIPS	P89LPC915(TSSOP14)	MPU / MCU	LP48-TSSOP-20PIN
PHILIPS	P89LPC916(TSSOP16)	MPU / MCU	LP48-TSSOP-20PIN
PHILIPS	P89LPC917(TSSOP16)	MPU / MCU	LP48-TSSOP-20PIN
PHILIPS	P89LPC920(DIP20)	MPU / MCU	NONE
PHILIPS	P89LPC920(SOP20)	MPU / MCU	LP48-SOP-20PIN
PHILIPS	P89LPC920(SSOP20)	MPU / MCU	LP48-SSOP-28PIN
PHILIPS	P89LPC920(TSSOP20)	MPU / MCU	LP48-TSSOP-20PIN
PHILIPS	P89LPC921(DIP20)	MPU / MCU	NONE
PHILIPS	P89LPC921(SOP20)	MPU / MCU	LP48-SOP-20PIN
PHILIPS	P89LPC921(SSOP20)	MPU / MCU	LP48-SSOP-28PIN
PHILIPS	P89LPC921(TSSOP20)	MPU / MCU	LP48-TSSOP-20PIN
PHILIPS	P89LPC922(DIP20)	MPU / MCU	NONE
PHILIPS	P89LPC922(SOP20)	MPU / MCU	LP48-SOP-20PIN
PHILIPS	P89LPC922(SSOP20)	MPU / MCU	LP48-SSOP-28PIN
PHILIPS	P89LPC922(TSSOP20)	MPU / MCU	LP48-TSSOP-20PIN
PHILIPS	P89LPC9221(DIP20)	MPU / MCU	NONE
PHILIPS	P89LPC9221(TSSOP20)	MPU / MCU	LP48-TSSOP-20PIN
PHILIPS	P89LPC924(DIP20)	MPU / MCU	NONE
PHILIPS	P89LPC924(TSSOP20)	MPU / MCU	LP48-TSSOP-20PIN
PHILIPS	P89LPC925(DIP20)	MPU / MCU	NONE
PHILIPS	P89LPC925(TSSOP20)	MPU / MCU	LP48-TSSOP-20PIN
PHILIPS	P89LV51RB2(DIP40)	MPU / MCU	NONE
PHILIPS	P89LV51RB2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89LV51RB2(TQFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89LV51RC2(DIP40)	MPU / MCU	NONE
PHILIPS	P89LV51RC2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89LV51RC2(TQFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89LV51RD2(DIP40)	MPU / MCU	NONE
PHILIPS	P89LV51RD2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89LV51RD2(TQFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89V51RB2(DIP40)	MPU / MCU	NONE
PHILIPS	P89V51RB2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89V51RB2(TQFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89V51RC2(DIP40)	MPU / MCU	NONE
PHILIPS	P89V51RC2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89V51RC2(TQFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89V51RD2(TQFP44)	MPU / MCU	LP48-VQFP-44S
PHILIPS	P89V51RD2BA(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89V51RD2BN(DIP40)	MPU / MCU	NONE
PHILIPS	P89V51RD2FA(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
PHILIPS	P89V51RD2FN(DIP40)	MPU / MCU	NONE
PHILIPS	PCA24S08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
PMC	PM25LD010-B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PMC	PM25LD010-D(TSSOP8)	FLASH	LP-TSSOP-8PIN
PMC	PM25LD010-K(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25LD010-P(DIP8)	FLASH	NONE
PMC	PM25LD010-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PMC	PM25LD010C-B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PMC	PM25LD010C-D(TSSOP8)	FLASH	LP-TSSOP-8PIN
PMC	PM25LD010C-K(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25LD010C-P(DIP8)	FLASH	NONE
PMC	PM25LD010C-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PMC	PM25LD020-B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)

Manufacturer	Parts Number	Type	ADAPTER
PMC	PM25LD020-D(TSSOP8)	FLASH	LP-TSSOP-8PIN
PMC	PM25LD020-K(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25LD020-P(PDIP8)	FLASH	NONE
PMC	PM25LD020-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PMC	PM25LD020C-B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PMC	PM25LD020C-D(TSSOP8)	FLASH	LP-TSSOP-8PIN
PMC	PM25LD020C-K(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25LD020C-P(PDIP8)	FLASH	NONE
PMC	PM25LD020C-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PMC	PM25LD040-B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PMC	PM25LD040-K(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25LD040-P(DIP8)	FLASH	NONE
PMC	PM25LD040-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PMC	PM25LD040C-B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PMC	PM25LD040C-K(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25LD040C-P(PDIP8)	FLASH	NONE
PMC	PM25LD040C-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PMC	PM25LD256C-D(TSSOP8)	FLASH	LP-TSSOP-8PIN
PMC	PM25LD256C-K(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25LD256C-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PMC	PM25LD512C-D(TSSOP8)	FLASH	LP-TSSOP-8PIN
PMC	PM25LD512C-K(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25LD512C-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PMC	PM25LQ016C-B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PMC	PM25LQ016C-K(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25LQ016C-M(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
PMC	PM25LQ016C-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PMC	PM25LQ032C-B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PMC	PM25LQ032C-K(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25LQ032C-M(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
PMC	PM25LQ032C-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PMC	PM25LQ040-B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PMC	PM25LQ040-K(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25LQ040-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PMC	PM25LQ080C-B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PMC	PM25LQ080C-K(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25LQ080C-M(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
PMC	PM25LQ080C-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PMC	PM25LV010-Q(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25LV010-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PMC	PM25LV010A-K(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25LV010A-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PMC	PM25LV016B-B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PMC	PM25LV016B-Q(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25LV020-Q(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25LV020-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PMC	PM25LV040-P(PDIP8)	FLASH	NONE
PMC	PM25LV040-Q(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25LV040-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PMC	PM25LV080B-B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PMC	PM25LV080B-Q(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25LV512-P(PDIP8)	FLASH	NONE
PMC	PM25LV512-Q(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25LV512A-D(TSSOP8)	FLASH	LP-TSSOP-8PIN
PMC	PM25LV512A-K(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25LV512A-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PMC	PM25W020-K(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25W020-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
PMC	PM25WD020-K(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25WD020-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PMC	PM25WD040-B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
PMC	PM25WD040-K(WSON8)	FLASH	LP48-WSON8-5x6
PMC	PM25WD040-P(PDIP8)	FLASH	NONE
PMC	PM25WD040-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
PMC	PM28LV64(DIP28)	EEPROM	NONE
PMC	PM28LV64(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
PMC	PM28LV64(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
PMC	PM28LV64(TSOP28)	EEPROM	LP-TSOP-28PIN
PMC	PM39LV010(DIP32)	FLASH	NONE
PMC	PM39LV010(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
PMC	PM39LV010(VSOP32)	FLASH	LP48-VSOP-32S
PMC	PM39LV020(DIP32)	FLASH	NONE
PMC	PM39LV020(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
PMC	PM39LV020(VSOP32)	FLASH	LP48-VSOP-32S
PMC	PM39LV040(DIP32)	FLASH	NONE
PMC	PM39LV040(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
PMC	PM39LV040(VSOP32)	FLASH	LP48-VSOP-32S
PMC	PM39LV512(DIP32)	FLASH	NONE
PMC	PM39LV512(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
PMC	PM39LV512(VSOP32)	FLASH	LP48-VSOP-32S
PMC	PM49FL002T(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
PMC	PM49FL002T(VSOP32)	FLASH	LP48-VSOP-32S
PMC	PM49FL004T(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
PMC	PM49FL004T(VSOP32)	FLASH	LP48-VSOP-32S
Portek	PTK24A02T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Portek	PTK24A08T(DIP8)	EEPROM	NONE
Portek	PTK24A08T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Portek	PTK24A16T(DIP8)	EEPROM	NONE
Portek	PTK24A16T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Portek	PTK24A32T(DIP8)	EEPROM	NONE
Portek	PTK24A32T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Portek	PTK24A64T(DIP8)	EEPROM	NONE
Portek	PTK24A64T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Portek	PTK93LC46-X16(DIP8)	EEPROM	NONE
Portek	PTK93LC46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Portek	PTK93LC46-X8(DIP8)	EEPROM	NONE
Portek	PTK93LC46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Portek	PTK93LC56-X16(DIP8)	EEPROM	NONE
Portek	PTK93LC56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Portek	PTK93LC56-X8(DIP8)	EEPROM	NONE
Portek	PTK93LC56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Portek	PTK93LC66-X16(DIP8)	EEPROM	NONE
Portek	PTK93LC66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Portek	PTK93LC66-X8(DIP8)	EEPROM	NONE
Portek	PTK93LC66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Princeton	PT28C010(DIP32)	EEPROM	NONE
Princeton	PT28C010(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Ramtron	FM24C04(DIP8)	EEPROM	NONE
Ramtron	FM24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24C04A(DIP8)	EEPROM	NONE
Ramtron	FM24C04A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24C04B(DIP8)	EEPROM	NONE
Ramtron	FM24C04B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24C04C(DIP8)	EEPROM	NONE
Ramtron	FM24C04C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24C16(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
Ramtron	FM24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24C16A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24C16B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24C16C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24C256(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Ramtron	FM24C512(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Ramtron	FM24C64(DIP8)	EEPROM	NONE
Ramtron	FM24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24C64B(DIP8)	EEPROM	NONE
Ramtron	FM24C64B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24C64C(DIP8)	EEPROM	NONE
Ramtron	FM24C64C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24CL04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24CL04B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24CL16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24CL16B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24CL32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24CL64(DIP8)	EEPROM	NONE
Ramtron	FM24CL64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24CL64B(DIP8)	EEPROM	NONE
Ramtron	FM24CL64B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24L256(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Ramtron	FM24V01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24V02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24V05(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24V10(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24VN01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24VN02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24VN05(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24VN10(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM24W256-EG(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Ramtron	FM24W256-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25040-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25040-S(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25040A-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25040A-GA(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25040A-S(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25040B-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25040B-GA(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25160-P(PDIP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25160-S(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25256-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25256B-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25640-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25640-GA(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25640-S(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25640B-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25640B-GA(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25C160-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25C160-GA(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25C160-S(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25C160B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25C160B-GA(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25CL64-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25CL64-GA(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25CL64-S(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25CL64B-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25CL64B-GA(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
Ramtron	FM25H20-DG(WSON8)	EEPROM	LP48-WSON8-5x6
Ramtron	FM25H20-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25L04-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25L04-GA(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25L04-S(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25L04B-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25L04B-GA(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25L16-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25L16-GA(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25L16B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25L256-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25L256-S(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25L256B-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25L512-DG(WSON8)	EEPROM	LP48-WSON8-5x6
Ramtron	FM25V01-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25V02-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25V05-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25V10-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25VN01-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25VN02-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25VN05-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25VN10-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM25W256-G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Ramtron	FM28V020(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
Rato	RT24A02(DIP8)	EEPROM	NONE
Rato	RT24A02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Rato	RT24A02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Rato	RT93LC46-X16(DIP8)	EEPROM	NONE
Rato	RT93LC46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Rato	RT93LC46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Rato	RT93LC46-X8(DIP8)	EEPROM	NONE
Rato	RT93LC46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Rato	RT93LC46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
RAYDIUM	RM24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RAYDIUM	RM24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
RAYDIUM	RM24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RAYDIUM	RM24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
RAYDIUM	RM24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RAYDIUM	RM24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
RAYDIUM	RM24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RAYDIUM	RM24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
RAYDIUM	RM24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RAYDIUM	RM24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
RAYDIUM	RM24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RAYDIUM	RM24C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
REALTEK	RTD2120L(LQFP48)	MPU / MCU	LP-LQFP-48PIN
REALTEK	RTD2120S(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
RENESAS	HD6477043F28(TQFP144)	MPU / MCU	LP-QFP-144PIN-SH7043
RENESAS	R1EX24002A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RENESAS	R1EX24002A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
RENESAS	R1EX24004A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RENESAS	R1EX24004A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
RENESAS	R1EX24008A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RENESAS	R1EX24008A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
RENESAS	R1EX24016A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RENESAS	R1EX24016A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
RENESAS	R1EX24032A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RENESAS	R1EX24032A(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
RENESAS	R1EX24064A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RENESAS	R1EX24064A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
RENESAS	R1EX24128A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RENESAS	R1EX24128A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
RENESAS	R1EX24256A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RENESAS	R1EX24256A(SOP8-207)	EEPROM	LP-SOP-8PIN-B(207mil)
RENESAS	R1EX24256B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RENESAS	R1EX24256B(SOP8-207)	EEPROM	LP-SOP-8PIN-B(207mil)
RENESAS	R1EX24512A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RENESAS	R1EX24512A(SOP8-207)	EEPROM	LP-SOP-8PIN-B(207mil)
RENESAS	R1EX24512A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
RENESAS	R1EX24512B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RENESAS	R1EX24512B(SOP8-207)	EEPROM	LP-SOP-8PIN-B(207mil)
RENESAS	R1EX24512B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
RENESAS	R1EX25016A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RENESAS	R1EX25016A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
RENESAS	R1EX25020A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RENESAS	R1EX25020A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
RENESAS	R1EX25032A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RENESAS	R1EX25032A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
RENESAS	R1EX25040A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RENESAS	R1EX25040A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
RENESAS	R1EX25064A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RENESAS	R1EX25064A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
RENESAS	R1EX25080A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RENESAS	R1EX25080A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
RENESAS	R1EX25512A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
RENESAS	R1EX25512A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
RENESAS	R5F21324CDSP(LSSOP20)	MPU / MCU	LP-LSSOP20
RICOH	RD27C128(DIP28)	EPROM	NONE
RICOH	RD27C64(DIP28)	EPROM	NONE
Rockwell	R2816A(DIP24)	EEPROM	NONE
ROHM	BR24A01AFJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24A02FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24A04F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24A04FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24A08FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24A16FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24A32FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24A64FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24C01A(DIP8)	EEPROM	NONE
ROHM	BR24C01AF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24C01AFV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24C02(DIP8)	EEPROM	NONE
ROHM	BR24C02F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24C04(DIP8)	EEPROM	NONE
ROHM	BR24C04F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24C04FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24C08(DIP8)	EEPROM	NONE
ROHM	BR24C08F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24C08FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24C16(DIP8)	EEPROM	NONE
ROHM	BR24C16F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24C16FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24C32(DIP8)	EEPROM	NONE
ROHM	BR24C64(DIP8)	EEPROM	NONE
ROHM	BR24E16(DIP8)	EEPROM	NONE
ROHM	BR24G01(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
ROHM	BR24G01FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24G01FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24G01FVT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24G02(DIP8)	EEPROM	NONE
ROHM	BR24G02FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24G04(DIP8)	EEPROM	NONE
ROHM	BR24G04F(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24G04FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24G04FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24G04FVT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24G08(DIP8)	EEPROM	NONE
ROHM	BR24G08FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24G08FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24G08FVT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24G128FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24G128FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24G128FVT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24G16(DIP8)	EEPROM	NONE
ROHM	BR24G16FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24G16FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24G16FVT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24G256FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24G32(DIP8)	EEPROM	NONE
ROHM	BR24G32FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24G32FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24G32FVT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24G64(DIP8)	EEPROM	NONE
ROHM	BR24G64FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24G64FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24G64FVT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24L01A(DIP8)	EEPROM	NONE
ROHM	BR24L01AFJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24L01AFV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24L02(DIP8)	EEPROM	NONE
ROHM	BR24L02FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24L02FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24L04(DIP8)	EEPROM	NONE
ROHM	BR24L04FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24L04FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24L08(DIP8)	EEPROM	NONE
ROHM	BR24L08FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24L08FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24L16(DIP8)	EEPROM	NONE
ROHM	BR24L16FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24L16FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24L32(DIP8)	EEPROM	NONE
ROHM	BR24L32FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24L32FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24L64(DIP8)	EEPROM	NONE
ROHM	BR24L64FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24L64FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24S08FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24S08FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24S08FVT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24S128FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24S128FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24S128FVT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24S16FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
ROHM	BR24S16FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24S16FVT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24S256FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24S32FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24S32FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24S32FVT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24S64FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24S64FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24S64FVT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24T02(DIP8)	EEPROM	NONE
ROHM	BR24T02FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR24T02FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24T02FVT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR24T08(DIP8)	EEPROM	NONE
ROHM	BR34E02FVT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR34E02NUX(VSON8)	EEPROM	LP48-MLP8-2x3
ROHM	BR93A46FJ-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93A46RFJ-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93A56FJ-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93A56RFJ-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93A66FJ-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93A66RFJ-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93A76FJ-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93A76RFJ-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93A86FJ-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93A86RFJ-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93C46(DIP8)	EEPROM	NONE
ROHM	BR93C46(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93C46(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR93C46-T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93C46R(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93C56(DIP8)	EEPROM	NONE
ROHM	BR93C56(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93C56(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR93C56-T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93C66(DIP8)	EEPROM	NONE
ROHM	BR93C66(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93C66(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR93C66-T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93C76(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93C76(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR93C76-T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93C86(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93C86(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR93C86-T(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93H56-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93H66-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93H76-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93H86-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93L46-W(DIP8)	EEPROM	NONE
ROHM	BR93L46FJ-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93L46FV-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR93L46RFJ-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93L46RFV-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR93L56-W(DIP8)	EEPROM	NONE
ROHM	BR93L56FJ-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93L56FV-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR93L56RFJ-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
ROHM	BR93L56RFV-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR93L66-W(DIP8)	EEPROM	NONE
ROHM	BR93L66FJ-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93L66FV-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR93L66RFJ-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93L66RFV-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR93L76-W(DIP8)	EEPROM	NONE
ROHM	BR93L76FJ-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93L76RFJ-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93L76RFV-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR93L76RFVT-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR93L86-W(DIP8)	EEPROM	NONE
ROHM	BR93L86FJ-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93L86RFJ-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93L86RFV-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR93L86RFVT-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR93LC46(DIP8)	EEPROM	NONE
ROHM	BR93LC46FJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93LC46FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR93LC46RFJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ROHM	BR93LC56(DIP8)	EEPROM	NONE
ROHM	BR93LC56FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR93LC66(DIP8)	EEPROM	NONE
ROHM	BR93LC66FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ROHM	BR93LL46FV(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Saifun	SA24C1024(DIP8)	EEPROM	NONE
Saifun	SA24C1024(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Saifun	SA24C512(DIP8)	EEPROM	NONE
Saifun	SA24C512(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
Saifun	SA25C020LEMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Saifun	SA25C020LEN(PDIP8)	FLASH	NONE
Saifun	SA25F005LEM8(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Saifun	SA25F005LEN(PDIP8)	FLASH	NONE
Saifun	SA25F010LEM8(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Saifun	SA25F010LEN(PDIP8)	FLASH	NONE
Saifun	SA25F020LEM8(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Saifun	SA25F020LEN(PDIP8)	FLASH	NONE
Saifun	SA25F040LEM8(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Saifun	SA25F040LEN(PDIP8)	FLASH	NONE
Samsung	K8D1716UBC(TSOP48)	FLASH	LP-TSOP-48S
Samsung	K8D1716UTC(TSOP48)	FLASH	LP-TSOP-48S
Samsung	K8D3216UBC(TSOP48)	FLASH	LP-TSOP-48S
Samsung	K8D3216UTC(TSOP48)	FLASH	LP-TSOP-48S
Samsung	K8P1615UQB(BGA48)	FLASH	LP-TFBGA-48PIN-6x8
Samsung	K8P1615UQB(TSOP48)	FLASH	LP-TSOP-48S
Samsung	K8P3215UQB(BGA48)	FLASH	LP-TFBGA-48PIN-6x8
Samsung	K8P3215UQB(TSOP48)	FLASH	LP-TSOP-48S
Samsung	K8P5615UQA(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
Samsung	K8P5616UZB(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
Samsung	K8P6415UQB(BGA48)	FLASH	LP-TFBGA-48PIN-6x8
Samsung	K8P6415UQB(TSOP48)	FLASH	LP-TSOP-48S
Samsung	K8Q2815UQB(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
Samsung	KM2816(DIP24)	EEPROM	NONE
Samsung	KM2816A(DIP24)	EEPROM	NONE
Samsung	KM2817(DIP28)	EEPROM	NONE
Samsung	KM2817A(DIP28)	EEPROM	NONE
Samsung	KM2864A-H(DIP28)	EEPROM	NONE
Samsung	KM2865A-H(DIP28)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
Samsung	KM28C16(DIP24)	EEPROM	NONE
Samsung	KM28C17(DIP28)	EEPROM	NONE
Samsung	KM28C17(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Samsung	KM28C256(DIP28)	EEPROM	NONE
Samsung	KM28C256(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Samsung	KM28C256A(DIP28)	EEPROM	NONE
Samsung	KM28C256A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Samsung	KM28C64(DIP28)	EEPROM	NONE
Samsung	KM28C64(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Samsung	KM28C64A(DIP28)	EEPROM	NONE
Samsung	KM28C64A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Samsung	KM28C65(DIP28)	EEPROM	NONE
Samsung	KM28C65(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Samsung	KM28C65A(DIP28)	EEPROM	NONE
Samsung	KM28C65A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Samsung	KM93C06(DIP8)	EEPROM	NONE
Samsung	KM93C06G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C06GD(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C07(DIP8)	EEPROM	NONE
Samsung	KM93C07G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C07GD(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C46(DIP8)	EEPROM	NONE
Samsung	KM93C46G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C46GD(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C46V(DIP8)	EEPROM	NONE
Samsung	KM93C46VG(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C46VGD(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C56(DIP8)	EEPROM	NONE
Samsung	KM93C56G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C56GD(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C56V(DIP8)	EEPROM	NONE
Samsung	KM93C56VG(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C56VGD(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C57-X16(DIP8)	EEPROM	NONE
Samsung	KM93C57-X8(DIP8)	EEPROM	NONE
Samsung	KM93C57G-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C57G-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C57GD-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C57GD-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C57V-X16(DIP8)	EEPROM	NONE
Samsung	KM93C57V-X8(DIP8)	EEPROM	NONE
Samsung	KM93C57VG-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C57VG-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C57VGD-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C57VGD-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C66(DIP8)	EEPROM	NONE
Samsung	KM93C66G(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C66GD(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C66V(DIP8)	EEPROM	NONE
Samsung	KM93C66VG(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C66VGD(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C67-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C67-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C67G-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C67G-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C67GD-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C67GD-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C67V-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
Samsung	KM93C67V-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C67VG-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C67VG-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C67VGD-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93C67VGD-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93CS56(DIP8)	EEPROM	NONE
Samsung	KM93CS56GD(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93CS66(DIP8)	EEPROM	NONE
Samsung	KM93CS66GD(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93S56D(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KM93S66D(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KS24A010(DIP8)	EEPROM	NONE
Samsung	KS24A011(DIP8)	EEPROM	NONE
Samsung	KS24A020(DIP8)	EEPROM	NONE
Samsung	KS24A021(DIP8)	EEPROM	NONE
Samsung	KS24A021(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KS24A040(DIP8)	EEPROM	NONE
Samsung	KS24A040(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KS24A041(DIP8)	EEPROM	NONE
Samsung	KS24A041(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KS24A081(DIP8)	EEPROM	NONE
Samsung	KS24A081(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KS24A1281(DIP8)	EEPROM	NONE
Samsung	KS24A161(DIP8)	EEPROM	NONE
Samsung	KS24A2561(DIP8)	EEPROM	NONE
Samsung	KS24A321(DIP8)	EEPROM	NONE
Samsung	KS24A641(DIP8)	EEPROM	NONE
Samsung	KS24C010(DIP8)	EEPROM	NONE
Samsung	KS24C010(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KS24C010(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Samsung	KS24C011(DIP8)	EEPROM	NONE
Samsung	KS24C011(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KS24C011(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Samsung	KS24C020(DIP8)	EEPROM	NONE
Samsung	KS24C020(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KS24C020(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Samsung	KS24C021(DIP8)	EEPROM	NONE
Samsung	KS24C021(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KS24C021(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Samsung	KS24C040(DIP8)	EEPROM	NONE
Samsung	KS24C040(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KS24C040(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Samsung	KS24C041(DIP8)	EEPROM	NONE
Samsung	KS24C041(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KS24C041(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Samsung	KS24C080(DIP8)	EEPROM	NONE
Samsung	KS24C080(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KS24C080(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Samsung	KS24C081(DIP8)	EEPROM	NONE
Samsung	KS24C081(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Samsung	KS24C081(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Samsung	KS24L161(DIP8)	EEPROM	NONE
Samsung	KS24L321(DIP8)	EEPROM	NONE
Samsung	KS24L641(DIP8)	EEPROM	NONE
SANYO	24C01A(DIP8)	EEPROM	NONE
SANYO	LE24C0411(DIP8)	EEPROM	NONE
SANYO	LE24C042(DIP8)	EEPROM	NONE
SANYO	LE24C081(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
SANYO	LE24C082(DIP8)	EEPROM	NONE
SANYO	LE24C161(DIP8)	EEPROM	NONE
SANYO	LE24C162(DIP8)	EEPROM	NONE
SANYO	LE24C322(DIP8)	EEPROM	NONE
SANYO	LE25FS406LF(WSON5x6)	FLASH	LP48-WSON8-5x6
SANYO	LE25FS406MA(MFP8)	FLASH	LP-SOP-16PIN(150mil)
SANYO	LE25FS406TT(SOP8)	FLASH	LP-SOP-16PIN(150mil)
SEEQ	27256(DIP28)	EPROM	NONE
SEEQ	27256(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SEEQ	27256(TSOP28)	EPROM	LP48-TSOP-28PIN
SEEQ	27C256(DIP28)	EPROM	NONE
SEEQ	27C256(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SEEQ	27C256(TSOP28)	EPROM	LP48-TSOP-28PIN
SEEQ	2816A-H(DIP24)	EEPROM	NONE
SEEQ	2816A-H(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
SEEQ	2864-H(DIP28)	EEPROM	NONE
SEEQ	2864-H(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
SEEQ	28C010-H(DIP32)	EEPROM	NONE
SEEQ	28C256(DIP28)	EEPROM	NONE
SEEQ	28C256(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
SEEQ	28C256A-H(DIP28)	EEPROM	NONE
SEEQ	28C256A-H(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
SEEQ	28C64(DIP28)	EEPROM	NONE
SEEQ	28C64(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
SEEQ	28HC64-H(DIP28)	EEPROM	NONE
SEEQ	28HC64-H(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
SEEQ	DQ2804A(DIP24)	EEPROM	NONE
SEEQ	DQ2817A(DIP28)	EEPROM	NONE
SEEQ	DQ2817A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
SEIKO	S-24C01A(DIP8)	EEPROM	NONE
SEIKO	S-24C01A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-24C01B(DIP8)	EEPROM	NONE
SEIKO	S-24C01B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-24C01C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-24C01C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-24C02A(DIP8)	EEPROM	NONE
SEIKO	S-24C02A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-24C02B(DIP8)	EEPROM	NONE
SEIKO	S-24C02B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-24C02C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-24C02C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-24C04A(DIP8)	EEPROM	NONE
SEIKO	S-24C04A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-24C04B(DIP8)	EEPROM	NONE
SEIKO	S-24C04B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-24C08A(DIP8)	EEPROM	NONE
SEIKO	S-24C08A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-24C08C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-24C08C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-24C128C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-24C128C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-24C16A(DIP8)	EEPROM	NONE
SEIKO	S-24C16A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-24C16C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-24C16C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-24C32C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-24C32C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-24C64C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
SEIKO	S-24C64C(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-24CS01A(DIP8)	EEPROM	NONE
SEIKO	S-24CS01A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-24CS01A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-24CS02A(DIP8)	EEPROM	NONE
SEIKO	S-24CS02A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-24CS02A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-24CS04A(DIP8)	EEPROM	NONE
SEIKO	S-24CS04A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-24CS04A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-24CS08A(DIP8)	EEPROM	NONE
SEIKO	S-24CS08A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-24CS08A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-24CS16A(DIP8)	EEPROM	NONE
SEIKO	S-24CS16A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-24CS16A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-24CS64A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-24CS64A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-2812A(DIP24)	EEPROM	NONE
SEIKO	S-2812A[SOP28]	EEPROM	LP-SOP-28PIN-B(300mil)
SEIKO	S-2817A(DIP24)	EEPROM	NONE
SEIKO	S-2817A[SOP28]	EEPROM	LP-SOP-28PIN-B(300mil)
SEIKO	S-2860B(DIP28)	EEPROM	NONE
SEIKO	S-2860B(SOP28)	EEPROM	LP-SOP-28PIN-B(300mil)
SEIKO	S-2864B(DIP28)	EEPROM	NONE
SEIKO	S-2864B(SOP28)	EEPROM	LP-SOP-28PIN-B(300mil)
SEIKO	S-29190AD(DIP8)	EEPROM	NONE
SEIKO	S-29190AF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-29290AD(DIP8)	EEPROM	NONE
SEIKO	S-29290AF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-2934A(DIP8)	EEPROM	NONE
SEIKO	S-2934A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-29355AD(DIP8)	EEPROM	NONE
SEIKO	S-29355AF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-29390AD(DIP8)	EEPROM	NONE
SEIKO	S-29390AF(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-34C02A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-93A46A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93A56A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93A66A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93A86A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93C46AD(DIP8)	EEPROM	NONE
SEIKO	S-93C46ADFJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93C46AFJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93C46AFT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-93C46BD(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93C46BD(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-93C46BR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93C56AD(DIP8)	EEPROM	NONE
SEIKO	S-93C56ADFJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93C56AFJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93C56AFT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-93C56BD(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93C56BD(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-93C56BR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93C66AD(DIP8)	EEPROM	NONE
SEIKO	S-93C66ADFJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93C66AFJ(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
SEIKO	S-93C66AFT(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-93C66BD(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93C66BD(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-93C66BR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93C76A(DIP8)	EEPROM	NONE
SEIKO	S-93C76A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93C76A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-93C86B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93C86B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-93L46AD(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93L46AD(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-93L46AR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93L56AD(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93L56AD(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-93L56AR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93L66AD(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93L66AD(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SEIKO	S-93L66AR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93L76A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SEIKO	S-93L76A(TSSOP8)	EEPROM	LP-TSSOP-8PIN
SHARP	LH28F008BJT-BTLZ1(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
SHARP	LH28F008BJT-TTLZ2(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
SHARP	LH28F008SAT(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
Siemens	SLA24C01(DIP8)	EEPROM	NONE
Siemens	SLA24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLA24C01-3(DIP8)	EEPROM	NONE
Siemens	SLA24C01-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLA24C02(DIP8)	EEPROM	NONE
Siemens	SLA24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLA24C02-3(DIP8)	EEPROM	NONE
Siemens	SLA24C02-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLA24C04(DIP8)	EEPROM	NONE
Siemens	SLA24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLA24C04-3(DIP8)	EEPROM	NONE
Siemens	SLA24C04-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLA24C08(DIP8)	EEPROM	NONE
Siemens	SLA24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLA24C08-3(DIP8)	EEPROM	NONE
Siemens	SLA24C08-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLA24C16(DIP8)	EEPROM	NONE
Siemens	SLA24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLA24C16-3(DIP8)	EEPROM	NONE
Siemens	SLA24C16-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLA24C164(DIP8)	EEPROM	NONE
Siemens	SLA24C164(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLA24C164-3(DIP8)	EEPROM	NONE
Siemens	SLA24C164-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLA24C32(DIP8)	EEPROM	NONE
Siemens	SLA24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLA24C32-3(DIP8)	EEPROM	NONE
Siemens	SLA24C32-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLA24C64(DIP8)	EEPROM	NONE
Siemens	SLA24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLA24C64-3(DIP8)	EEPROM	NONE
Siemens	SLA24C64-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLE24C01(DIP8)	EEPROM	NONE
Siemens	SLE24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLE24C02(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
Siemens	SLE24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLE24C04(DIP8)	EEPROM	NONE
Siemens	SLE24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLE24C08(DIP8)	EEPROM	NONE
Siemens	SLE24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLE24C16(DIP8)	EEPROM	NONE
Siemens	SLE24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLE24C164(DIP8)	EEPROM	NONE
Siemens	SLE24C164(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLE24C32(DIP8)	EEPROM	NONE
Siemens	SLE24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Siemens	SLE24C64(DIP8)	EEPROM	NONE
Siemens	SLE24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SIGNETICS	27128(DIP28)	EPROM	NONE
SIGNETICS	27C128(DIP28)	EPROM	NONE
SIGNETICS	27C64(DIP28)	EPROM	NONE
SIGNETICS	27C64A(DIP28)	EPROM	NONE
Silicon Labs	C8051F310(LQFP32)	MPU / MCU	LP-TQFP32
Silicon Labs	C8051F320(LQFP32)	MPU / MCU	LP-TQFP32
Silicon Labs	C8051F321(QFN28)	MPU / MCU	LP-QFN-28PIN-5x5
Silicon Labs	C8051F330-GM(QFN20)	MPU / MCU	LP-QFN-20PIN-4x4
Silicon Labs	C8051F331-GM(QFN20)	MPU / MCU	LP-QFN-20PIN-4x4
Silicon Labs	C8051F332-GM(QFN20)	MPU / MCU	LP-QFN-20PIN-4x4
Silicon Labs	C8051F333-GM(QFN20)	MPU / MCU	LP-QFN-20PIN-4x4
Silicon Labs	C8051F334-GM(QFN20)	MPU / MCU	LP-QFN-20PIN-4x4
Silicon Labs	C8051F335-GM(QFN20)	MPU / MCU	LP-QFN-20PIN-4x4
Silicon Labs	C8051F336-GM(QFN20)	MPU / MCU	LP-QFN-20PIN-4x4
Silicon Labs	C8051F337-GM(QFN20)	MPU / MCU	LP-QFN-20PIN-4x4
Silicon Labs	C8051F338-GM(QFN24)	MPU / MCU	LP-QFN-24PIN-4x4
Silicon Labs	C8051F339-GM(QFN24)	MPU / MCU	LP-QFN-24PIN-4x4
Silicon Labs	C8051F340-GQ(TQFP48)	MPU / MCU	LP-LQFP-48PIN
Silicon Labs	C8051F341-GQ(TQFP48)	MPU / MCU	LP-LQFP-48PIN
Silicon Labs	C8051F342-GM(QFN32)	MPU / MCU	LP-QFN-32PIN
Silicon Labs	C8051F342-GQ(LQFP32)	MPU / MCU	LP-TQFP32
Silicon Labs	C8051F343-GM(QFN32)	MPU / MCU	LP-QFN-32PIN
Silicon Labs	C8051F343-GQ(LQFP32)	MPU / MCU	LP-TQFP32
Silicon Labs	C8051F344-GQ(TQFP48)	MPU / MCU	LP-LQFP-48PIN
Silicon Labs	C8051F345-GQ(TQFP48)	MPU / MCU	LP-LQFP-48PIN
Silicon Labs	C8051F346-GM(QFN32)	MPU / MCU	LP-QFN-32PIN
Silicon Labs	C8051F346-GQ(LQFP32)	MPU / MCU	LP-TQFP32
Silicon Labs	C8051F347-GM(QFN32)	MPU / MCU	LP-QFN-32PIN
Silicon Labs	C8051F347-GQ(LQFP32)	MPU / MCU	LP-TQFP32
Silicon Labs	C8051F348-GQ(TQFP48)	MPU / MCU	LP-LQFP-48PIN
Silicon Labs	C8051F349-GM(QFN32)	MPU / MCU	LP-QFN-32PIN
Silicon Labs	C8051F349-GQ(LQFP32)	MPU / MCU	LP-TQFP32
Silicon Labs	C8051F34A-GM(QFN32)	MPU / MCU	LP-QFN-32PIN
Silicon Labs	C8051F34A-GQ(LQFP32)	MPU / MCU	LP-TQFP32
Silicon Labs	C8051F34B-GM(QFN32)	MPU / MCU	LP-QFN-32PIN
Silicon Labs	C8051F34B-GQ(LQFP32)	MPU / MCU	LP-TQFP32
Silicon Labs	C8051F34C-GQ(TQFP48)	MPU / MCU	LP-LQFP-48PIN
Silicon Labs	C8051F34D-GQ(LQFP32)	MPU / MCU	LP-TQFP32
Silicon Labs	C8051F380-GQ(TQFP48)	MPU / MCU	LP-LQFP-48PIN
Silicon Labs	C8051F410-GQ(LQFP32)	MPU / MCU	LP-TQFP32
Silicon Labs	C8051F412-GQ(LQFP32)	MPU / MCU	LP-TQFP32
Silicon Labs	C8051F706-GM(QFN48)	MPU / MCU	LP-QFN-48S-7x7
Silicon Labs	C8051F706-GQ(TQFP48)	MPU / MCU	LP-TQFP48
Silicon Labs	C8051F707-GM(QFN48)	MPU / MCU	LP-QFN-48S-7x7
Silicon Labs	C8051F707-GQ(TQFP48)	MPU / MCU	LP-TQFP48

Manufacturer	Parts Number	Type	ADAPTER
Silicon Labs	C8051F715-GQ(TQFP48)	MPU / MCU	LP-LQFP-48PIN
Silicon Labs	C8051F920-GM(QFN32)	MPU / MCU	LP-QFN-32PIN
Silicon Labs	C8051F920-GQ(LQFP32)	MPU / MCU	LP-TQFP32
SMOS	27128H(DIP28)	EPROM	NONE
SMOS	27C64H(DIP28)	EPROM	NONE
SONY	CXK27C1000(DIP32)	EPROM	NONE
SONY	CXK27C1000(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SONY	CXK27C1000(TSOP32)	EPROM	LP48-TSOP-32S
SONY	CXK27C1001(DIP40)	EPROM	NONE
SONY	CXK27C1001(SOP40)	EPROM	LP48-PSOP-44PIN
SONY	CXK27C1001(TSOP48)	EPROM	LP-TSOP-48S
SONY	CXK27C256(DIP28)	EPROM	NONE
SONY	CXK27C256(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SONY	CXK27C256(TSOP28)	EPROM	LP48-TSOP-28PIN
SONY	CXK27C512(DIP28)	EPROM	NONE
SONY	CXK27C512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SONY	CXK27C512(TSOP32)	EPROM	LP48-TSOP-32S
SPANSION	AM29F010(DIP32)	FLASH	NONE
SPANSION	AM29F010(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
SPANSION	AM29F010(TSOP32)	FLASH	LP48-TSOP-32S
SPANSION	AM29F010A(DIP32)	FLASH	NONE
SPANSION	AM29F010A(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
SPANSION	AM29F010A(TSOP32)	FLASH	LP48-TSOP-32S
SPANSION	AM29F010B(DIP32)	FLASH	NONE
SPANSION	AM29F010B(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
SPANSION	AM29F010B(TSOP32)	FLASH	LP48-TSOP-32S
SPANSION	AM29F040(DIP32)	FLASH	NONE
SPANSION	AM29F040(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
SPANSION	AM29F040(TSOP32)	FLASH	LP48-TSOP-32S
SPANSION	AM29F040B(DIP32)	FLASH	NONE
SPANSION	AM29F040B(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
SPANSION	AM29F040B(TSOP32)	FLASH	LP48-TSOP-32S
SPANSION	AM29F200AB(SO44)	FLASH	LP48-PSOP-44PIN
SPANSION	AM29F200AB(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	AM29F200AT(SO44)	FLASH	LP48-PSOP-44PIN
SPANSION	AM29F200AT(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	AM29F200B(SO44)	FLASH	LP48-PSOP-44PIN
SPANSION	AM29F200B(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	AM29F200BB(SO44)	FLASH	LP48-PSOP-44PIN
SPANSION	AM29F200BB(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	AM29F200BT(SO44)	FLASH	LP48-PSOP-44PIN
SPANSION	AM29F200BT(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	AM29F200CB(SO44)	FLASH	LP48-PSOP-44PIN
SPANSION	AM29F200CB(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	AM29F200CT(SO44)	FLASH	LP48-PSOP-44PIN
SPANSION	AM29F200CT(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	AM29F200T(SO44)	FLASH	LP48-PSOP-44PIN
SPANSION	AM29F200T(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	AM29F400AB(SO44)	FLASH	LP48-PSOP-44PIN
SPANSION	AM29F400AB(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	AM29F400AT(SO44)	FLASH	LP48-PSOP-44PIN
SPANSION	AM29F400AT(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	AM29F400B(SO44)	FLASH	LP48-PSOP-44PIN
SPANSION	AM29F400B(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	AM29F400BB(SO44)	FLASH	LP48-PSOP-44PIN
SPANSION	AM29F400BB(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	AM29F400BT(SO44)	FLASH	LP48-PSOP-44PIN
SPANSION	AM29F400BT(TSOP48)	FLASH	LP-TSOP-48S

Manufacturer	Parts Number	Type	ADAPTER
SPANSION	AM29F400T(SO44)	FLASH	LP48-PSOP-44PIN
SPANSION	AM29F400T(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	AM29F800B(SO44)	FLASH	LP48-PSOP-44PIN
SPANSION	AM29F800B(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	AM29F800BB(SO44)	FLASH	LP48-PSOP-44PIN
SPANSION	AM29F800BB(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	AM29F800BT(SO44)	FLASH	LP48-PSOP-44PIN
SPANSION	AM29F800BT(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	AM29F800T(SO44)	FLASH	LP48-PSOP-44PIN
SPANSION	AM29F800T(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S25FL004DOLM(SOP8-207)	FLASH	LP-SOP-8PIN-B(207mil)
SPANSION	S25FL004DOLN(WSON-5x6)	FLASH	LP48-WSON8-5x6
SPANSION	S25FL004KOXM(SOP8-150)	FLASH	LP-SOP-16PIN(150mil)
SPANSION	S25FL004KOXM(SOP8-207)	FLASH	LP-SOP-8PIN-B(207mil)
SPANSION	S25FL008AOLM(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
SPANSION	S25FL008KOXM(SOP8-150)	FLASH	LP-SOP-16PIN(150mil)
SPANSION	S25FL008KOXM(SOP8-207)	FLASH	LP-SOP-8PIN-B(207mil)
SPANSION	S25FL016AOLM(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
SPANSION	S25FL016AOLM(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
SPANSION	S25FL016AOLN(WSON8)	FLASH	LP48-WSON8-6x8
SPANSION	S25FL016KOXM(SOP8-150)	FLASH	LP-SOP-16PIN(150mil)
SPANSION	S25FL016KOXM(SOP8-207)	FLASH	LP-SOP-8PIN-B(207mil)
SPANSION	S25FL032AOLM(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
SPANSION	S25FL032KOXM(SOP8-207)	FLASH	LP-SOP-8PIN-B(207mil)
SPANSION	S25FL032POXM(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
SPANSION	S25FL032POXM(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
SPANSION	S25FL032POXN(WSON8-5x6)	FLASH	LP48-WSON8-5x6
SPANSION	S25FL032POXN(WSON8-6x8)	FLASH	LP48-WSON8-6x8
SPANSION	S25FL040AOLM-Bottom(SOP8-207)	FLASH	LP-SOP-8PIN-B(207mil)
SPANSION	S25FL040AOLM-Top(SOP8-207)	FLASH	LP-SOP-8PIN-B(207mil)
SPANSION	S25FL040AOLM-Uniform(SOP8-207)	FLASH	LP-SOP-8PIN-B(207mil)
SPANSION	S25FL040AOLN-Bottom(WSON-5x6)	FLASH	LP48-WSON8-5x6
SPANSION	S25FL040AOLN-Top(WSON-5x6)	FLASH	LP48-WSON8-5x6
SPANSION	S25FL040AOLN-Uniform(WSON-5x6)	FLASH	LP48-WSON8-5x6
SPANSION	S25FL040AOLV-Bottom(SOP8-150)	FLASH	LP-SOP-16PIN(150mil)
SPANSION	S25FL040AOLV-Top(SOP8-150)	FLASH	LP-SOP-16PIN(150mil)
SPANSION	S25FL040AOLV-Uniform(SOP8-150)	FLASH	LP-SOP-16PIN(150mil)
SPANSION	S25FL064AOLM(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
SPANSION	S25FL064KOSM(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
SPANSION	S25FL064KOSM(SOP8-207)	FLASH	LP-SOP-8PIN-B(207mil)
SPANSION	S25FL064POXM(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
SPANSION	S25FL064POXN(WSON-6x8)	FLASH	LP48-WSON8-6x8
SPANSION	S25FL128KOXM(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
SPANSION	S25FL128POXM(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
SPANSION	S25FL128POXN(WSON8)	FLASH	LP48-WSON8-6x8
SPANSION	S25FL128S(BGA24)	FLASH	LP-BGA-24PIN-4x6B or LP-BGA-24PIN-5x5B
SPANSION	S25FL128S(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
SPANSION	S25FL128S(WSON-6x8)	FLASH	LP48-WSON8-6x8
SPANSION	S25FL128SAG(BGA24)	FLASH	LP-BGA-24PIN-4x6B or LP-BGA-24PIN-5x5B
SPANSION	S25FL128SAG(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
SPANSION	S25FL128SAG(WSON-6x8)	FLASH	LP48-WSON8-6x8
SPANSION	S25FL128SBH-30(BGA24)	FLASH	LP-BGA-24PIN-4x6B or LP-BGA-24PIN-5x5B
SPANSION	S25FL128SBH-30(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
SPANSION	S25FL128SBH-30(WSON-6x8)	FLASH	LP48-WSON8-6x8
SPANSION	S25FL129POXM(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
SPANSION	S25FL129POXN(WSON-6x8)	FLASH	LP48-WSON8-6x8
SPANSION	S25FL204KOXM(SOP8-150)	FLASH	LP-SOP-16PIN(150mil)
SPANSION	S25FL204KOXM(SOP8-207)	FLASH	LP-SOP-8PIN-B(207mil)

Manufacturer	Parts Number	Type	ADAPTER
SPANSION	S25FL208KOXM(SOP8-150)	FLASH	LP-SOP-16PIN(150mil)
SPANSION	S25FL208KOXM(SOP8-207)	FLASH	LP-SOP-8PIN-B(207mil)
SPANSION	S25FL216KOXM(SOP8-150)	FLASH	LP-SOP-16PIN(150mil)
SPANSION	S25FL216KOXM(SOP8-207)	FLASH	LP-SOP-8PIN-B(207mil)
SPANSION	S25FL256S(BGA24)	FLASH	LP-BGA-24PIN-4x6B or LP-BGA-24PIN-5x5B
SPANSION	S25FL256S(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
SPANSION	S25FL256S(WSON-6x8)	FLASH	LP48-WSON8-6x8
SPANSION	S25FL256SAG(BGA24)	FLASH	LP-BGA-24PIN-4x6B or LP-BGA-24PIN-5x5B
SPANSION	S25FL256SAG(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
SPANSION	S25FL256SAG(WSON-6x8)	FLASH	LP48-WSON8-6x8
SPANSION	S25FL256SAG-00(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
SPANSION	S29AL004D-T-01(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AL004D-T-02(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AL008D-T-01(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AL008D-T-02(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AL008D-T-R1(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AL008D-T-R2(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AL016D-T-01(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AL016D-T-02(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AL016J-T-01(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AL016J-T-02(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AL016J-T-03(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AL016J-T-04(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AL016J-T-R1(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AL016J-T-R2(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AL016M-T-01(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AL016M-T-02(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AL016M-T-R1(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AL016M-T-R2(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AL032D-T-03(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AL032D-T-04(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AS016J-T-01(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AS016J-T-02(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AS016J-T-03(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29AS016J-T-04(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29GL01GP-F-01(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL01GP-F-02(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL01GP-F-R1(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL01GP-F-R2(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL01GP-F-S0(BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL01GP-F-S1(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL01GP-F-S2(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL01GP-F-S3(BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL01GP-F-S4(BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL01GP-F-S5(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL01GP-F-S6(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL01GP-F-S7(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL01GP-F-S8(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL01GP-F-S9(BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL01GP-F-V1(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL01GP-F-V2(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL01GP-T-01(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL01GP-T-02(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL01GP-T-R1(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL01GP-T-R2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL01GP-T-V1(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL01GP-T-V2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL01GS-DH-02(FBGA64)	FLASH	LP-BGA64-SOCKET-9x9 + LP-BGA64-A (For 29xxx)

Manufacturer	Parts Number	Type	ADAPTER
SPANSION	S29GL01GS-TF-01(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL01GS-TF-02(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL01GS-TF-V1(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL01GS-TF-V2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL032M90TAIR3(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29GL032M90TAIR4(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29GL032N-B-03(FBGA48)	FLASH	LP-TFBGA-48PIN-6x8
SPANSION	S29GL032N-D-01(FBGA64)	FLASH	LP-BGA64-SOCKET-9x9 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL032N-D-02(FBGA64)	FLASH	LP-BGA64-SOCKET-9x9 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL032N-D-03(FBGA64)	FLASH	LP-BGA64-SOCKET-9x9 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL032N-F-03(FBGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL032N-F-04(FBGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL032N-F-S2(FBGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL032N-T-03(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29GL032N-T-04(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29GL032N-T-R3(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29GL032N-T-R4(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29GL064M-T-R6(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29GL064M-T-R7(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29GL064N-F-01(FBGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL064N-F-01(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL064N-F-02(FBGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL064N-F-02(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL064N-F-S2(FBGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL064N-F-V1(FBGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL064N-F-V1(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL064N-F-V2(FBGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL064N-F-V2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL064N-T-03(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29GL064N-T-04(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29GL064N-T-04(TSOP48_X4)	FLASH	SU-3280-NOR-TSOP48-X4
SPANSION	S29GL064N-T-R3(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29GL064N-T-R4(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S29GL128N-T-01(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL128N-T-02(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL128N-T-R1(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL128N-T-R2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL128N-T-V1(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL128N-T-V2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL128P-F-01(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL128P-F-02(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL128P-F-R1(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL128P-F-R2(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL128P-F-V1(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL128P-F-V2(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL128P-T-01(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL128P-T-02(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL128P-T-R1(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL128P-T-R2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL128P-T-V1(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL128P-T-V2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL128S-F-01(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL128S-F-02(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL128S-F-V1(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL128S-F-V2(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL128S-TF-01(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL128S-TF-02(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL128S-TF-V1(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)

Manufacturer	Parts Number	Type	ADAPTER
SPANSION	S29GL128S-TF-V2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL256N-T-01(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL256N-T-02(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL256N-T-R1(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL256N-T-R2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL256N-T-V1(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL256N-T-V2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL256P-T-01(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL256P-T-02(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL256P-T-R1(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL256P-T-R2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL256P-T-V1(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL256P-T-V2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL512N-T-01(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL512N-T-02(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL512N-T-R1(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL512N-T-R2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL512N-T-V1(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL512N-T-V2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL512P-T-01(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL512P-T-02(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL512P-T-R1(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL512P-T-R2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL512P-T-V1(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL512P-T-V2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL512S-DH-S5(FBGA64)	FLASH	LP-BGA64-SOCKET-9x9 + LP-BGA64-A (For 29xxx)
SPANSION	S29GL512S-T-01(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL512S-T-02(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL512S-T-V1(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29GL512S-T-V2(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
SPANSION	S29JL064J(TSOP48)	FLASH	LP-TSOP-48S
SPANSION	S70FL256POXM(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
SST	27SF010(DIP32)	EPROM	NONE
SST	27SF010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	27SF010(TSOP32)	EPROM	LP48-TSOP-32S
SST	27SF020(DIP32)	EPROM	NONE
SST	27SF020(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	27SF020(TSOP32)	EPROM	LP48-TSOP-32S
SST	27SF256(DIP28)	EPROM	NONE
SST	27SF512(DIP28)	EPROM	NONE
SST	27SF512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	27SF512(TSOP32)	EPROM	LP48-VSOP-32S
SST	27VF010(DIP32)	EPROM	NONE
SST	27VF010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	27VF010(TSOP32)	EPROM	LP48-TSOP-32S
SST	27VF020(DIP32)	EPROM	NONE
SST	27VF020(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	27VF020(TSOP32)	EPROM	LP48-TSOP-32S
SST	SST25LF020A-Q(WSON8)	FLASH	LP48-WSON8-5x6
SST	SST25LF020A-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
SST	SST25LF040A-Q(WSON8)	FLASH	LP48-WSON8-5x6
SST	SST25LF040A-S2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
SST	SST25LF080A-Q(WSON8)	FLASH	LP48-WSON8-5x6
SST	SST25LF080A-S2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
SST	SST25PF020B-Q(WSON8)	FLASH	LP48-WSON8-5x6
SST	SST25PF020B-Q3(USON8)	FLASH	LP48-MLP8-2x3
SST	SST25PF020B-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
SST	SST25PF040B-Q(WSON8)	FLASH	LP48-WSON8-5x6

Manufacturer	Parts Number	Type	ADAPTER
SST	SST25PF040B-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
SST	SST25PF040B-S2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
SST	SST25PF080B-Q(WSON8)	FLASH	LP48-WSON8-5x6
SST	SST25PF080B-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
SST	SST25PF080B-S2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
SST	SST25VF010(SOP8)	FLASH	None
SST	SST25VF010(WSON5x6)	FLASH	LP48-PLCC-44PIN or LP48-PLCC-44S
SST	SST25VF010-Q(WSON8)	FLASH	LP48-WSON8-5x6
SST	SST25VF010-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
SST	SST25VF010A-Q(WSON8)	FLASH	LP48-WSON8-5x6
SST	SST25VF010A-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
SST	SST25VF016B(SOP8)	FLASH	None
SST	SST25VF016B(WSON5x6)	FLASH	LP48-PLCC-44PIN or LP48-PLCC-44S
SST	SST25VF016B-Q(WSON8)	FLASH	LP48-WSON8-5x6
SST	SST25VF016B-S2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
SST	SST25VF020(SOP8)	FLASH	LP48-PLCC-44PIN or LP48-PLCC-44S
SST	SST25VF020(WSON5x6)	FLASH	LP48-QFP-44PIN or LP48-QFP-44S
SST	SST25VF020-Q(WSON8)	FLASH	LP48-WSON8-5x6
SST	SST25VF020-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
SST	SST25VF020B(SOP8)	FLASH	LP48-QFP-44PIN or LP48-QFP-44S
SST	SST25VF020B(WSON5x6)	FLASH	None
SST	SST25VF020B-Q(WSON8)	FLASH	LP48-WSON8-5x6
SST	SST25VF020B-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
SST	SST25VF032B(SOP8)	FLASH	NONE
SST	SST25VF032B(WSON5x6)	FLASH	NONE
SST	SST25VF032B-S2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
SST	SST25VF032B-S2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
SST	SST25VF040(SOP8)	FLASH	LP48-PLCC-44PIN or LP48-PLCC-44S
SST	SST25VF040(WSON5x6)	FLASH	LP48-QFP-44PIN or LP48-QFP-44S
SST	SST25VF040-Q(WSON8)	FLASH	LP48-WSON8-5x6
SST	SST25VF040-S2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
SST	SST25VF040B(SOP8)	FLASH	LP48-QFP-44PIN or LP48-QFP-44S
SST	SST25VF040B(WSON5x6)	FLASH	None
SST	SST25VF040B-Q(WSON8)	FLASH	LP48-WSON8-5x6
SST	SST25VF040B-S2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
SST	SST25VF064C-Q2(WSON8)	FLASH	LP48-WSON8-6x8
SST	SST25VF064C-S2(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
SST	SST25VF064C-S3(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
SST	SST25VF080B(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
SST	SST25VF080B(WSON5x6)	FLASH	LP48-WSON8-5x6
SST	SST25VF080B-Q(WSON8)	FLASH	LP48-WSON8-5x6
SST	SST25VF080B-S2(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
SST	SST25VF512(SOP8)	FLASH	LP48-PLCC-44PIN or LP48-PLCC-44S
SST	SST25VF512(WSON5x6)	FLASH	LP48-QFP-44PIN or LP48-QFP-44S
SST	SST25VF512-Q(WSON8)	FLASH	LP48-WSON8-5x6
SST	SST25VF512-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
SST	SST25VF512A-Q(WSON8)	FLASH	LP48-WSON8-5x6
SST	SST25VF512A-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
SST	SST25WF010-Q(WSON8)	FLASH	LP48-WSON8-5x6
SST	SST25WF010-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
SST	SST25WF020-Q(WSON8)	FLASH	LP48-WSON8-5x6
SST	SST25WF020-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
SST	SST25WF040-Q(WSON8)	FLASH	LP48-WSON8-5x6
SST	SST25WF040-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
SST	SST25WF080-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
SST	SST25WF512-Q(WSON8)	FLASH	LP48-WSON8-5x6
SST	SST25WF512-S(SOP8)	FLASH	LP-SOP-16PIN(150mil)
SST	SST27SF010(DIP32)	EPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
SST	SST27SF010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST27SF010(TSOP32)	EPROM	LP48-TSOP-32S
SST	SST27SF020(DIP32)	EPROM	NONE
SST	SST27SF020(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST27SF020(TSOP32)	EPROM	LP48-TSOP-32S
SST	SST27SF256(DIP28)	EPROM	NONE
SST	SST27SF512(DIP28)	EPROM	NONE
SST	SST27SF512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST27SF512(TSOP32)	EPROM	LP48-VSOP-32S
SST	SST27VF010(DIP32)	EPROM	NONE
SST	SST27VF010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST27VF010(TSOP32)	EPROM	LP48-TSOP-32S
SST	SST27VF020(DIP32)	EPROM	NONE
SST	SST27VF020(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST27VF020(TSOP32)	EPROM	LP48-TSOP-32S
SST	SST29EE010(DIP32)	FLASH	NONE
SST	SST29EE010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29EE010(TSOP32 8X14)	FLASH	LP48-VSOP-32S
SST	SST29EE010(TSOP32 8X20)	FLASH	LP48-TSOP-32S
SST	SST29EE010A(DIP32)	FLASH	NONE
SST	SST29EE010A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29EE010A(TSOP32 8X14)	FLASH	LP48-VSOP-32S
SST	SST29EE010A(TSOP32 8X20)	FLASH	LP48-TSOP-32S
SST	SST29EE020(DIP32)	FLASH	NONE
SST	SST29EE020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29EE020(TSOP32 8X14)	FLASH	LP48-VSOP-32S
SST	SST29EE020(TSOP32 8X20)	FLASH	LP48-TSOP-32S
SST	SST29EE020A(DIP32)	FLASH	NONE
SST	SST29EE020A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29EE020A(TSOP32 8X14)	FLASH	LP48-VSOP-32S
SST	SST29EE020A(TSOP32 8X20)	FLASH	LP48-TSOP-32S
SST	SST29EE512(DIP32)	FLASH	NONE
SST	SST29EE512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29EE512(TSOP32)	FLASH	LP48-TSOP-32S
SST	SST29EE512A(DIP32)	FLASH	NONE
SST	SST29EE512A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29EE512A(TSOP32)	FLASH	LP48-TSOP-32S
SST	SST29LE010(DIP32)	FLASH	NONE
SST	SST29LE010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29LE010(TSOP32 8X14)	FLASH	LP48-VSOP-32S
SST	SST29LE010(TSOP32 8X20)	FLASH	LP48-TSOP-32S
SST	SST29LE010A(DIP32)	FLASH	NONE
SST	SST29LE010A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29LE010A(TSOP32 8X14)	FLASH	LP48-VSOP-32S
SST	SST29LE010A(TSOP32 8X20)	FLASH	LP48-TSOP-32S
SST	SST29LE020(DIP32)	FLASH	NONE
SST	SST29LE020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29LE020(TSOP32 8X14)	FLASH	LP48-VSOP-32S
SST	SST29LE020(TSOP32 8X20)	FLASH	LP48-TSOP-32S
SST	SST29LE020A(DIP32)	FLASH	NONE
SST	SST29LE020A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29LE020A(TSOP32 8X14)	FLASH	LP48-VSOP-32S
SST	SST29LE020A(TSOP32 8X20)	FLASH	LP48-TSOP-32S
SST	SST29LE512(DIP32)	FLASH	NONE
SST	SST29LE512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29LE512(TSOP32)	FLASH	LP48-TSOP-32S
SST	SST29LE512A(DIP32)	FLASH	NONE
SST	SST29LE512A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S

Manufacturer	Parts Number	Type	ADAPTER
SST	SST29LE512A(TSOP32)	FLASH	LP48-TSOP-32S
SST	SST29SF010(DIP32)	FLASH	NONE
SST	SST29SF010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29SF010(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST29SF020(DIP32)	FLASH	NONE
SST	SST29SF020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29SF020(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST29SF040(DIP32)	FLASH	NONE
SST	SST29SF040(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29SF040(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST29SF512(DIP32)	FLASH	NONE
SST	SST29SF512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29SF512(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST29VE010(DIP32)	FLASH	NONE
SST	SST29VE010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29VE010(TSOP32 8X14)	FLASH	LP48-VSOP-32S
SST	SST29VE010(TSOP32 8X20)	FLASH	LP48-TSOP-32S
SST	SST29VE010A(DIP32)	FLASH	NONE
SST	SST29VE010A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29VE010A(TSOP32 8X14)	FLASH	LP48-VSOP-32S
SST	SST29VE010A(TSOP32 8X20)	FLASH	LP48-TSOP-32S
SST	SST29VE020(DIP32)	FLASH	NONE
SST	SST29VE020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29VE020(TSOP32 8X14)	FLASH	LP48-VSOP-32S
SST	SST29VE020(TSOP32 8X20)	FLASH	LP48-TSOP-32S
SST	SST29VE020A(DIP32)	FLASH	NONE
SST	SST29VE020A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29VE020A(TSOP32 8X14)	FLASH	LP48-VSOP-32S
SST	SST29VE020A(TSOP32 8X20)	FLASH	LP48-TSOP-32S
SST	SST29VE512(DIP32)	FLASH	NONE
SST	SST29VE512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29VE512(TSOP32)	FLASH	LP48-TSOP-32S
SST	SST29VE512A(DIP32)	FLASH	NONE
SST	SST29VE512A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29VE512A(TSOP32)	FLASH	LP48-TSOP-32S
SST	SST29VF010(DIP32)	FLASH	NONE
SST	SST29VF010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29VF010(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST29VF020(DIP32)	FLASH	NONE
SST	SST29VF020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29VF020(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST29VF040(DIP32)	FLASH	NONE
SST	SST29VF040(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29VF040(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST29VF512(DIP32)	FLASH	NONE
SST	SST29VF512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST29VF512(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST36VF320(TSOP48)	FLASH	LP-TSOP-48S
SST	SST36VF3203(TSOP48)	FLASH	LP-TSOP-48S
SST	SST36VF3204(TSOP48)	FLASH	LP-TSOP-48S
SST	SST37VF010(DIP32)	FLASH	NONE
SST	SST37VF010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST37VF010(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST37VF020(DIP32)	FLASH	NONE
SST	SST37VF020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST37VF020(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST37VF040(DIP32)	FLASH	NONE
SST	SST37VF040(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S

Manufacturer	Parts Number	Type	ADAPTER
SST	SST37VF040(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST37VF512(DIP32)	FLASH	NONE
SST	SST37VF512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST37VF512(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST38VF6402(TSOP48)	FLASH	LP-TSOP-48S
SST	SST38VF6403(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39LF010(DIP32)	FLASH	NONE
SST	SST39LF010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39LF010(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39LF016(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
SST	SST39LF020(DIP32)	FLASH	NONE
SST	SST39LF020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39LF020(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39LF040(DIP32)	FLASH	NONE
SST	SST39LF040(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39LF040(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39LF080(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
SST	SST39LF100(VSOP40)	FLASH	LP48-VSOP-40PIN
SST	SST39LF200A(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39LF400A(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39LF512(DIP32)	FLASH	NONE
SST	SST39LF512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39LF512(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39LF800A(BGA48)	FLASH	LP-TFBGA-48PIN-6x8
SST	SST39LF800A(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39LH010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39LH010(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39LH020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39LH020(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39LH040(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39LH040(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39LH512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39LH512(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39SF010(DIP32)	FLASH	NONE
SST	SST39SF010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39SF010(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39SF010A(DIP32)	FLASH	NONE
SST	SST39SF010A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39SF010A(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39SF020(DIP32)	FLASH	NONE
SST	SST39SF020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39SF020(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39SF020A(DIP32)	FLASH	NONE
SST	SST39SF020A(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39SF020A(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39SF020P(DIP32)	FLASH	NONE
SST	SST39SF020P(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39SF020P(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39SF040(DIP32)	FLASH	NONE
SST	SST39SF040(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39SF040(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39SF040P(DIP32)	FLASH	NONE
SST	SST39SF040P(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39SF040P(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39SF512(DIP32)	FLASH	NONE
SST	SST39SF512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39SF512(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39VF010(DIP32)	FLASH	NONE

Manufacturer	Parts Number	Type	ADAPTER
SST	SST39VF010(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39VF010(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39VF016(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
SST	SST39VF016Q(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
SST	SST39VF020(DIP32)	FLASH	NONE
SST	SST39VF020(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39VF020(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39VF020P(DIP32)	FLASH	NONE
SST	SST39VF020P(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39VF020P(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39VF040(DIP32)	FLASH	NONE
SST	SST39VF040(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39VF040(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39VF040P(DIP32)	FLASH	NONE
SST	SST39VF040P(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39VF040P(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39VF080(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
SST	SST39VF080Q(TSOP40)	FLASH	LP48-TSOP-40PIN or LP48-TSOP-40S
SST	SST39VF088(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF100(VSOP40)	FLASH	LP48-VSOP-40PIN
SST	SST39VF160(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF1601C(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF1602(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF1602C(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF160Q(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF1681(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF1682(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF200(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF200A(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF320(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF3201(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF3201B(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF3201C(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
SST	SST39VF3201C(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF3202(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF3202B(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF3202C(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
SST	SST39VF3202C(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF400(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF400A(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF512(DIP32)	FLASH	NONE
SST	SST39VF512(PLCC32)	FLASH	LP48-PLCC-1M32 or LP48-PLCC-1M32S
SST	SST39VF512(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST39VF6401(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF6401B(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF6402(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF6402B(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF800(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF800A(TSOP48)	FLASH	LP-TSOP-48S
SST	SST39VF800Q(TSOP48)	FLASH	LP-TSOP-48S
SST	SST49LF002(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
SST	SST49LF002(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST49LF002A(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
SST	SST49LF002A(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST49LF002B(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
SST	SST49LF002B(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST49LF003A(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
SST	SST49LF003A(TSOP32)	FLASH	LP48-VSOP-32S

Manufacturer	Parts Number	Type	ADAPTER
SST	SST49LF003B(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
SST	SST49LF003B(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST49LF004A(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
SST	SST49LF004A(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST49LF004B(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
SST	SST49LF004B(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST49LF008A(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
SST	SST49LF008A(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST49LF040(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
SST	SST49LF040(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST49LF080A(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
SST	SST49LF080A(TSOP32)	FLASH	LP48-VSOP-32S
SST	SST89E516RD(DIP40)	MPU / MCU	NONE
SST	SST89E516RD(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SST	SST89E516RD(TQFP44)	MPU / MCU	LP48-VQFP-44S (pinsize=12*12)
SST	SST89E516RD2(DIP40)	MPU / MCU	NONE
SST	SST89E516RD2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SST	SST89E516RD2(TQFP44)	MPU / MCU	LP48-VQFP-44S (pinsize=12*12)
SST	SST89E52RD(DIP40)	MPU / MCU	NONE
SST	SST89E52RD(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SST	SST89E52RD(TQFP44)	MPU / MCU	LP48-VQFP-44S
SST	SST89E52RD2(DIP40)	MPU / MCU	NONE
SST	SST89E52RD2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SST	SST89E52RD2(TQFP44)	MPU / MCU	LP48-VQFP-44S
SST	SST89E54RD(DIP40)	MPU / MCU	NONE
SST	SST89E54RD(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SST	SST89E54RD(TQFP44)	MPU / MCU	LP48-VQFP-44S
SST	SST89E54RD2(DIP40)	MPU / MCU	NONE
SST	SST89E54RD2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SST	SST89E54RD2(TQFP44)	MPU / MCU	LP48-VQFP-44S
SST	SST89E58RD(DIP40)	MPU / MCU	NONE
SST	SST89E58RD(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SST	SST89E58RD(TQFP44)	MPU / MCU	LP48-VQFP-44S
SST	SST89E58RD2(DIP40)	MPU / MCU	NONE
SST	SST89E58RD2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SST	SST89E58RD2(TQFP44)	MPU / MCU	LP48-VQFP-44S
SST	SST89V52RD(DIP40)	MPU / MCU	NONE
SST	SST89V52RD(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SST	SST89V52RD(TQFP44)	MPU / MCU	LP48-VQFP-44S
SST	SST89V52RD2(DIP40)	MPU / MCU	NONE
SST	SST89V52RD2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SST	SST89V52RD2(TQFP44)	MPU / MCU	LP48-VQFP-44S
SST	SST89V54RD(DIP40)	MPU / MCU	NONE
SST	SST89V54RD(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SST	SST89V54RD(TQFP44)	MPU / MCU	LP48-VQFP-44S
SST	SST89V54RD2(DIP40)	MPU / MCU	NONE
SST	SST89V54RD2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SST	SST89V54RD2(TQFP44)	MPU / MCU	LP48-VQFP-44S
SST	SST89V58RD(DIP40)	MPU / MCU	NONE
SST	SST89V58RD(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SST	SST89V58RD(TQFP44)	MPU / MCU	LP48-VQFP-44S
SST	SST89V58RD2(DIP40)	MPU / MCU	NONE
SST	SST89V58RD2(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SST	SST89V58RD2(TQFP44)	MPU / MCU	LP48-VQFP-44S
ST	E28F128J3A(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	E28F256J3A(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	E28F320J3A(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	E28F640J3A(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)

Manufacturer	Parts Number	Type	ADAPTER
ST	JR28F032M29EWB(TSOP48)	FLASH	LP-TSOP-48S
ST	JR28F032M29EWH(TSOP48)	FLASH	LP-TSOP-48S
ST	JR28F032M29EWL(TSOP48)	FLASH	LP-TSOP-48S
ST	JR28F032M29EWT(TSOP48)	FLASH	LP-TSOP-48S
ST	JR28F064M29EWB(TSOP48)	FLASH	LP-TSOP-48S
ST	JR28F064M29EWH(TSOP48)	FLASH	LP-TSOP-48S
ST	JR28F064M29EWL(TSOP48)	FLASH	LP-TSOP-48S
ST	JR28F064M29EWT(TSOP48)	FLASH	LP-TSOP-48S
ST	JS28F00AM29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	JS28F00AM29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	JS28F00BM29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	JS28F00BM29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	JS28F032M29EWB(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	JS28F032M29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	JS28F032M29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	JS28F032M29EWT(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	JS28F064M29EWB(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	JS28F064M29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	JS28F064M29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	JS28F064M29EWT(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	JS28F128J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	JS28F128J3D(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	JS28F128J3F(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	JS28F128M29EWB(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	JS28F128M29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	JS28F128M29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	JS28F128M29EWT(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	JS28F128P30B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	JS28F128P30BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	JS28F128P30T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	JS28F128P30TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	JS28F256J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	JS28F256J3F(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	JS28F256M29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	JS28F256M29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	JS28F256P30B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	JS28F256P30BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	JS28F256P30T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	JS28F256P30TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	JS28F256P33BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	JS28F256P33TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	JS28F320J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	JS28F320J3D(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	JS28F320J3F(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	JS28F512M29EWH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	JS28F512M29EWL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	JS28F640J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	JS28F640J3D(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	JS28F640J3F(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	JS28F640P30B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	JS28F640P30BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	JS28F640P30T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	JS28F640P30TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	JS28F640P33B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	JS28F640P33T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	M24128(DIP8)	EEPROM	NONE
ST	M24128(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ST	M24128-B(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
ST	M24128-B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24128-B(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24128-BR(DIP8)	EEPROM	NONE
ST	M24128-BR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24128-BR(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24128-BW(DIP8)	EEPROM	NONE
ST	M24128-BW(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24128-BW(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24128-R(DIP8)	EEPROM	NONE
ST	M24128-R(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ST	M24256(DIP8)	EEPROM	NONE
ST	M24256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24256(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24256-BF(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24256-BHR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24256-BHR(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24256-BR(DIP8)	EEPROM	NONE
ST	M24256-BR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24256-BR(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24256-DR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24256-DR(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24256-R(DIP8)	EEPROM	NONE
ST	M24256-R(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ST	M24512-DR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24512-DR(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24512-HR(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24512-R(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ST	M24512-R(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24512-S(DIP8)	EEPROM	NONE
ST	M24512-S(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ST	M24512-W(DIP8)	EEPROM	NONE
ST	M24512-W(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ST	M24512-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C01(DIP8)	EEPROM	NONE
ST	M24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24C01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C01-R(DIP8)	EEPROM	NONE
ST	M24C01-R(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24C01-R(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C01-W(DIP8)	EEPROM	NONE
ST	M24C01-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24C01-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C02(DIP8)	EEPROM	NONE
ST	M24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C02-R(DIP8)	EEPROM	NONE
ST	M24C02-R(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24C02-R(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C02-W(DIP8)	EEPROM	NONE
ST	M24C02-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24C02-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C04(DIP8)	EEPROM	NONE
ST	M24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C04-R(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24C04-R(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C04-W(DIP8)	EEPROM	NONE
ST	M24C04-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
ST	M24C04-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C08(DIP8)	EEPROM	NONE
ST	M24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C08-F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C08-R(DIP8)	EEPROM	NONE
ST	M24C08-R(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24C08-R(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C08-W(DIP8)	EEPROM	NONE
ST	M24C08-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24C08-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C16(DIP8)	EEPROM	NONE
ST	M24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C16-F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C16-R(DIP8)	EEPROM	NONE
ST	M24C16-R(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24C16-R(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C16-W(DIP8)	EEPROM	NONE
ST	M24C16-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24C16-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C32(DIP8)	EEPROM	NONE
ST	M24C32(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ST	M24C32(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C32-F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C32-R(DIP8)	EEPROM	NONE
ST	M24C32-R(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24C32-R(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C32-S(DIP8)	EEPROM	NONE
ST	M24C32-S(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24C32-S(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C32-W(DIP8)	EEPROM	NONE
ST	M24C32-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24C32-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C64(DIP8)	EEPROM	NONE
ST	M24C64(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ST	M24C64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C64-F(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C64-R(DIP8)	EEPROM	NONE
ST	M24C64-R(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24C64-R(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C64-S(DIP8)	EEPROM	NONE
ST	M24C64-S(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24C64-S(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24C64-W(DIP8)	EEPROM	NONE
ST	M24C64-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24C64-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M24M01(SOP8-150)	EEPROM	LP-SOP-16PIN(150mil)
ST	M24M01(SOP8-207)	EEPROM	LP-SOP-8PIN-B(207mil)
ST	M24M02(SOP8-150)	EEPROM	LP-SOP-16PIN(150mil)
ST	M25P05-AVDW(SOP8)	FLASH	LP-TSSOP-8PIN
ST	M25P05-AVME(WSON8)	FLASH	LP48-WSON8-6x8
ST	M25P05-AVMF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ST	M25P05-AVMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ST	M25P05-AVMP(WSON8)	FLASH	LP48-WSON8-5x6
ST	M25P05VDA(PDIP8)	FLASH	NONE
ST	M25P05VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ST	M25P10-AVME(WSON8)	FLASH	LP48-WSON8-6x8

Manufacturer	Parts Number	Type	ADAPTER
ST	M25P10-AVMF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ST	M25P10-AVMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ST	M25P10-AVMP(WSON8)	FLASH	LP48-WSON8-5x6
ST	M25P10VDA(PDIP8)	FLASH	NONE
ST	M25P10VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ST	M25P10VMP(WSON8)	FLASH	LP48-WSON8-5x6
ST	M25P128VME(WSON8)	FLASH	LP48-WSON8-6x8
ST	M25P128VMF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ST	M25P16VMF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ST	M25P16VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ST	M25P16VMP(SOP8)	FLASH	LP48-WSON8-5x6
ST	M25P16VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ST	M25P20VME(WSON8)	FLASH	LP48-WSON8-6x8
ST	M25P20VMF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ST	M25P20VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ST	M25P20VMP(WSON8)	FLASH	LP48-WSON8-5x6
ST	M25P32VMF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ST	M25P32VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ST	M25P32VMP(SOP8)	FLASH	LP48-WSON8-5x6
ST	M25P32VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ST	M25P40VMF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ST	M25P40VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ST	M25P40VMP(SOP8)	FLASH	LP48-WSON8-5x6
ST	M25P40VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ST	M25P64VME(WSON8)	FLASH	LP48-WSON8-6x8
ST	M25P64VMF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ST	M25P80VME(WSON8)	FLASH	LP48-WSON8-6x8
ST	M25P80VMF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ST	M25P80VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ST	M25P80VMP(WSON8)	FLASH	LP48-WSON8-5x6
ST	M25P80VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ST	M25PE10VME(WSON8)	FLASH	LP48-WSON8-6x8
ST	M25PE10VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ST	M25PE16VMP(WSON8)	FLASH	LP48-WSON8-5x6
ST	M25PE16VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ST	M25PE20VME(WSON8)	FLASH	LP48-WSON8-6x8
ST	M25PE20VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ST	M25PE40VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ST	M25PE40VMP(WSON8)	FLASH	LP48-WSON8-5x6
ST	M25PE40VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ST	M25PE80VMP(WSON8)	FLASH	LP48-WSON8-5x6
ST	M25PE80VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ST	M25PX32VMF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ST	M25PX32VMP(SOP8)	FLASH	LP48-WSON8-5x6
ST	M25PX32VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ST	M25PX64VME(WSON8)	FLASH	LP48-WSON8-6x8
ST	M25PX64VMF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
ST	M27128A(DIP28)	EPROM	NONE
ST	M27256(DIP28)	EPROM	NONE
ST	M27512(DIP28)	EPROM	NONE
ST	M2764A(DIP28)	EPROM	NONE
ST	M2764AP(DIP28)	EPROM	NONE
ST	M27C1001(DIP32)	EPROM	NONE
ST	M27C1001(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ST	M27C1024(DIP40)	EPROM	NONE
ST	M27C1024(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
ST	M27C160(DIP42)	EPROM	NONE
ST	M27C160(SOP44)	EPROM	LP48-PSOP-44PIN

Manufacturer	Parts Number	Type	ADAPTER
ST	M27C2001(DIP32)	EPROM	NONE
ST	M27C2001(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ST	M27C202(DIP40)	EPROM	NONE
ST	M27C202(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
ST	M27C202(TSOP40)	EPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
ST	M27C256B(DIP28)	EPROM	NONE
ST	M27C256B-12F1(DIP28)	EPROM	NONE
ST	M27C322(DIP42)	EPROM	NONE
ST	M27C4001(DIP32)	EPROM	NONE
ST	M27C4002(DIP40)	EPROM	NONE
ST	M27C512(DIP28)	EPROM	NONE
ST	M27C512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ST	M27C512(TSOP28)	EPROM	LP-TSOP-28PIN
ST	M27C64A(DIP28)	EPROM	NONE
ST	M27C800(DIP42)	EPROM	NONE
ST	M27C800(SOP44)	EPROM	LP48-PSOP-44PIN
ST	M27C801(DIP32)	EPROM	NONE
ST	M27C801(PLCC32)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
ST	M27V101(DIP32)	EPROM	NONE
ST	M27V101(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ST	M27V102(DIP40)	EPROM	NONE
ST	M27V102(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
ST	M27V160(DIP42)	EPROM	NONE
ST	M27V160(SOP44)	EPROM	LP48-PSOP-44PIN
ST	M27V201(DIP32)	EPROM	NONE
ST	M27V201(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ST	M27V202(DIP40)	EPROM	NONE
ST	M27V202(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
ST	M27V400(DIP40)	EPROM	NONE
ST	M27V400(SOP40)	EPROM	LP48-SOP-40PIN
ST	M27V401(DIP32)	EPROM	NONE
ST	M27V401(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ST	M27V800(DIP42)	EPROM	NONE
ST	M27V800(SOP44)	EPROM	LP48-PSOP-44PIN
ST	M27V801(DIP32)	EPROM	NONE
ST	M27V801(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ST	M27W016(SO44)	EPROM	LP48-PSOP-44PIN
ST	M27W016(TSOP48)	EPROM	LP-TSOP-48S
ST	M27W032(SO44)	EPROM	LP48-PSOP-44PIN
ST	M27W032(TSOP48)	EPROM	LP-TSOP-48S
ST	M27W064(SO44)	EPROM	LP48-PSOP-44PIN
ST	M27W064(TSOP48)	EPROM	LP-TSOP-48S
ST	M27W101(DIP32)	EPROM	NONE
ST	M27W101(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ST	M27W102(DIP40)	EPROM	NONE
ST	M27W102(PLCC44)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ST	M27W201(DIP32)	EPROM	NONE
ST	M27W201(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ST	M27W202(DIP40)	EPROM	NONE
ST	M27W202(PLCC44)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ST	M27W400(DIP40)	EPROM	NONE
ST	M27W400(SOP40)	EPROM	LP48-SOP-40PIN
ST	M27W401(DIP32)	EPROM	NONE
ST	M27W401(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ST	M27W512(DIP28)	EPROM	NONE
ST	M27W512(PLCC32)	EPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ST	M27W512(TSOP28)	EPROM	LP-TSOP-28PIN
ST	M27W800(DIP42)	EPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
ST	M27W801(DIP32)	EPROM	NONE
ST	M27W801(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
ST	M27W801(TSOP32)	EPROM	LP48-TSOP-32S
ST	M28010(DIP32)	EEPROM	NONE
ST	M28010(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ST	M28010(TSOP32)	EEPROM	LP48-TSOP-32S
ST	M28010-R(DIP32)	EEPROM	NONE
ST	M28010-R(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ST	M28010-R(TSOP32)	EEPROM	LP48-TSOP-32S
ST	M28010-W(DIP32)	EEPROM	NONE
ST	M28010-W(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ST	M28010-W(TSOP32)	EEPROM	LP48-TSOP-32S
ST	M28256(DIP28)	EEPROM	NONE
ST	M28256(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ST	M28256(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ST	M28256(TSOP28)	EEPROM	LP-TSOP-28PIN
ST	M28256-W(DIP28)	EEPROM	NONE
ST	M28256-W(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ST	M28256-W(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ST	M28256-W(TSOP28)	EEPROM	LP-TSOP-28PIN
ST	M28C17(DIP28)	EEPROM	NONE
ST	M28C17(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ST	M28C17(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ST	M28C64(DIP28)	EEPROM	NONE
ST	M28C64(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ST	M28C64(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ST	M28C64(TSOP28)	EEPROM	LP-TSOP-28PIN
ST	M28C64C(DIP28)	EEPROM	NONE
ST	M28C64C(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ST	M28C64C(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ST	M28C64C(TSOP28)	EEPROM	LP-TSOP-28PIN
ST	M28C64X(DIP28)	EEPROM	NONE
ST	M28C64X(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ST	M28C64X(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ST	M28C64X(TSOP28)	EEPROM	LP-TSOP-28PIN
ST	M28LV64C(DIP28)	EEPROM	NONE
ST	M28LV64C(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ST	M28LV64C(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ST	M28LV64C(TSOP28)	EEPROM	LP-TSOP-28PIN
ST	M28LV64X(DIP28)	EEPROM	NONE
ST	M28LV64X(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
ST	M28LV64X(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
ST	M28LV64X(TSOP28)	EEPROM	LP-TSOP-28PIN
ST	M28W160BB(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W160BT(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W160CB(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W160CT(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W160ECB(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W160ECT(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W320BB(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W320BT(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W320CB(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W320CT(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W320EBB(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W320EBT(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W320FCB(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W320FCT(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W640CB(TSOP48)	FLASH	LP-TSOP-48S

Manufacturer	Parts Number	Type	ADAPTER
ST	M28W640CT(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W640ECB(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W640ECT(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W640FCB(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W640FCT(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W800BB(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W800BT(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W800CB(TSOP48)	FLASH	LP-TSOP-48S
ST	M28W800CT(TSOP48)	FLASH	LP-TSOP-48S
ST	M29DW128F(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	M29DW128G(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	M29DW256G(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	M29DW640D(TSOP48)	FLASH	LP-TSOP-48S
ST	M29DW640F(TSOP48)	FLASH	LP-TSOP-48S
ST	M29DW641F(TSOP48)	FLASH	LP-TSOP-48S
ST	M29F010B(DIP32)	FLASH	NONE
ST	M29F010B(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
ST	M29F010B(TSOP32)	FLASH	LP48-TSOP-32S
ST	M29F400B(TSOP48)	FLASH	LP-TSOP-48S
ST	M29F400T(TSOP48)	FLASH	LP-TSOP-48S
ST	M29W040B(PLCC32)	FLASH	LP-PLCC-1M32 or LP-PLCC-1M32S
ST	M29W040B(TSOP32)	FLASH	LP48-TSOP-32S
ST	M29W128FH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	M29W128FL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	M29W128GH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	M29W128GL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	M29W160EB-N(TSOP48)	FLASH	LP-TSOP-48S
ST	M29W160EB-ZA(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
ST	M29W160ET-N(TSOP48)	FLASH	LP-TSOP-48S
ST	M29W160ET-ZA(TFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
ST	M29W256GH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	M29W256GL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	M29W320EB-N(TSOP48)	FLASH	LP-TSOP-48S
ST	M29W320EB-ZE(BGA48)	FLASH	LP-TFBGA-48PIN-6x8
ST	M29W320ET-N(TSOP48)	FLASH	LP-TSOP-48S
ST	M29W320ET-ZE(BGA48)	FLASH	LP-TFBGA-48PIN-6x8
ST	M29W400BB(TSOP48)	FLASH	LP-TSOP-48S
ST	M29W400BT(TSOP48)	FLASH	LP-TSOP-48S
ST	M29W400DB(TSOP48)	FLASH	LP-TSOP-48S
ST	M29W400DT(TSOP48)	FLASH	LP-TSOP-48S
ST	M29W640DB(TSOP48)	FLASH	LP-TSOP-48S
ST	M29W640DT(TSOP48)	FLASH	LP-TSOP-48S
ST	M29W640FB(TSOP48)	FLASH	LP-TSOP-48S
ST	M29W640FT(TSOP48)	FLASH	LP-TSOP-48S
ST	M29W640GB(BGA48)	FLASH	LP-TFBGA-48PIN-6x8
ST	M29W640GB(TSOP48)	FLASH	LP-TSOP-48S
ST	M29W640GB(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	M29W640GH(TSOP48)	FLASH	LP-TSOP-48S
ST	M29W640GH(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	M29W640GL(TSOP48)	FLASH	LP-TSOP-48S
ST	M29W640GL(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	M29W640GT(TSOP48)	FLASH	LP-TSOP-48S
ST	M29W640GT(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
ST	M29W800AB(TSOP48)	FLASH	LP-TSOP-48S
ST	M29W800AT(TSOP48)	FLASH	LP-TSOP-48S
ST	M29W800B(TSOP48)	FLASH	LP-TSOP-48S
ST	M29W800DB(TSOP48)	FLASH	LP-TSOP-48S
ST	M29W800DT(TSOP48)	FLASH	LP-TSOP-48S

Manufacturer	Parts Number	Type	ADAPTER
ST	M29W800T(TSOP48)	FLASH	LP-TSOP-48S
ST	M34A02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M34C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M34D64(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M34E02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M45PE10-VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ST	M45PE10-VMP(MLP8)	FLASH	LP48-WSON8-5x6
ST	M45PE16-VMP(MLP8)	FLASH	LP48-WSON8-5x6
ST	M45PE16-VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ST	M45PE20-VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ST	M45PE20-VMP(MLP8)	FLASH	LP48-WSON8-5x6
ST	M45PE40-VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ST	M45PE40-VMP(MLP8)	FLASH	LP48-WSON8-5x6
ST	M45PE40-VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ST	M45PE80-VMN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
ST	M45PE80-VMP(MLP8)	FLASH	LP48-WSON8-5x6
ST	M45PE80-VMW(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
ST	M48T59(DIP28)	NV RAM	NONE
ST	M9306(DIP8)	EEPROM	NONE
ST	M9306(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M9346(DIP8)	EEPROM	NONE
ST	M93C06-R-X16(DIP8)	EEPROM	NONE
ST	M93C06-R-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C06-R-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C06-R-X8(DIP8)	EEPROM	NONE
ST	M93C06-R-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C06-R-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C06-T-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C06-T-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C06-T-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C06-T-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C06-TR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C06-TR-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C06-TR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C06-TR-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C06-X16(DIP8)	EEPROM	NONE
ST	M93C06-X8(DIP8)	EEPROM	NONE
ST	M93C46-R-X16(DIP8)	EEPROM	NONE
ST	M93C46-R-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C46-R-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C46-R-X8(DIP8)	EEPROM	NONE
ST	M93C46-R-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C46-R-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C46-T-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C46-T-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C46-T-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C46-T-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C46-TR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C46-TR-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C46-TR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C46-TR-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C46-W-X16(DIP8)	EEPROM	NONE
ST	M93C46-W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C46-W-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C46-W-X8(DIP8)	EEPROM	NONE
ST	M93C46-W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C46-W-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C46-X16(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
ST	M93C46-X8(DIP8)	EEPROM	NONE
ST	M93C56-R-X16(DIP8)	EEPROM	NONE
ST	M93C56-R-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C56-R-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C56-R-X8(DIP8)	EEPROM	NONE
ST	M93C56-R-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C56-R-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C56-T-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C56-T-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C56-T-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C56-T-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C56-TR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C56-TR-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C56-TR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C56-TR-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C56-W-X16(DIP8)	EEPROM	NONE
ST	M93C56-W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C56-W-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C56-W-X8(DIP8)	EEPROM	NONE
ST	M93C56-W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C56-W-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C56-X16(DIP8)	EEPROM	NONE
ST	M93C56-X8(DIP8)	EEPROM	NONE
ST	M93C66-R-X16(DIP8)	EEPROM	NONE
ST	M93C66-R-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C66-R-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C66-R-X8(DIP8)	EEPROM	NONE
ST	M93C66-R-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C66-R-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C66-T-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C66-T-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C66-T-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C66-T-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C66-TR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C66-TR-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C66-TR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C66-TR-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C66-W-X16(DIP8)	EEPROM	NONE
ST	M93C66-W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C66-W-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C66-W-X8(DIP8)	EEPROM	NONE
ST	M93C66-W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C66-W-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C66-X16(DIP8)	EEPROM	NONE
ST	M93C66-X8(DIP8)	EEPROM	NONE
ST	M93C76-R-X16(DIP8)	EEPROM	NONE
ST	M93C76-R-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C76-R-X8(DIP8)	EEPROM	NONE
ST	M93C76-R-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C76-T-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C76-T-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C76-TR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C76-TR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C76-W-X16(DIP8)	EEPROM	NONE
ST	M93C76-W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C76-W-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C76-W-X8(DIP8)	EEPROM	NONE
ST	M93C76-W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
ST	M93C76-W-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C76-X16(DIP8)	EEPROM	NONE
ST	M93C76-X8(DIP8)	EEPROM	NONE
ST	M93C86-R-X16(DIP8)	EEPROM	NONE
ST	M93C86-R-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C86-R-X8(DIP8)	EEPROM	NONE
ST	M93C86-R-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C86-T-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C86-T-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C86-TR-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C86-TR-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C86-W-X16(DIP8)	EEPROM	NONE
ST	M93C86-W-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C86-W-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C86-W-X8(DIP8)	EEPROM	NONE
ST	M93C86-W-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93C86-W-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93C86-X16(DIP8)	EEPROM	NONE
ST	M93C86-X8(DIP8)	EEPROM	NONE
ST	M93S46(DIP8)	EEPROM	NONE
ST	M93S46(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93S46(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93S46-R(DIP8)	EEPROM	NONE
ST	M93S46-R(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93S46-R(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93S56(DIP8)	EEPROM	NONE
ST	M93S56(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93S56(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93S56-R(DIP8)	EEPROM	NONE
ST	M93S56-R(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93S56-R(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93S66(DIP8)	EEPROM	NONE
ST	M93S66(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93S66(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M93S66-R(DIP8)	EEPROM	NONE
ST	M93S66-R(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M93S66-R(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95010(DIP8)	EEPROM	NONE
ST	M95010(MLP8)	EEPROM	LP48-MLP8-2x3
ST	M95010(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95010(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95010-R(DIP8)	EEPROM	NONE
ST	M95010-R(MLP8)	EEPROM	LP48-MLP8-2x3
ST	M95010-R(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95010-R(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95010-W(DIP8)	EEPROM	NONE
ST	M95010-W(MLP8)	EEPROM	LP48-MLP8-2x3
ST	M95010-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95010-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95020(DIP8)	EEPROM	NONE
ST	M95020(MLP8)	EEPROM	LP48-MLP8-2x3
ST	M95020(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95020(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95020-R(DIP8)	EEPROM	NONE
ST	M95020-R(MLP8)	EEPROM	LP48-MLP8-2x3
ST	M95020-R(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95020-R(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95020-W(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
ST	M95020-W(MLP8)	EEPROM	LP48-MLP8-2x3
ST	M95020-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95020-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95040(DIP8)	EEPROM	NONE
ST	M95040(MLP8)	EEPROM	LP48-MLP8-2x3
ST	M95040(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95040(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95040-R(DIP8)	EEPROM	NONE
ST	M95040-R(MLP8)	EEPROM	LP48-MLP8-2x3
ST	M95040-R(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95040-R(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95040-W(DIP8)	EEPROM	NONE
ST	M95040-W(MLP8)	EEPROM	LP48-MLP8-2x3
ST	M95040-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95040-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95080(DIP8)	EEPROM	NONE
ST	M95080(MLP8)	EEPROM	LP48-MLP8-2x3
ST	M95080(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95080(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95080-R(DIP8)	EEPROM	NONE
ST	M95080-R(MLP8)	EEPROM	LP48-MLP8-2x3
ST	M95080-R(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95080-R(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95080-W(DIP8)	EEPROM	NONE
ST	M95080-W(MLP8)	EEPROM	LP48-MLP8-2x3
ST	M95080-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95080-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95128-BN(DIP8)	EEPROM	NONE
ST	M95128-DW(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95128-MN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95128-MW(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ST	M95128-RBN(DIP8)	EEPROM	NONE
ST	M95128-RDW(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95128-RMN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95128-RMW(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ST	M95128-WBN(DIP8)	EEPROM	NONE
ST	M95128-WDW(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95128-WMN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95128-WMW(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ST	M95160(DIP8)	EEPROM	NONE
ST	M95160(MLP8)	EEPROM	LP48-MLP8-2x3
ST	M95160(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95160(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95160-R(DIP8)	EEPROM	NONE
ST	M95160-R(MLP8)	EEPROM	LP48-MLP8-2x3
ST	M95160-R(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95160-R(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95160-W(DIP8)	EEPROM	NONE
ST	M95160-W(MLP8)	EEPROM	LP48-MLP8-2x3
ST	M95160-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95160-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95256-BN(DIP8)	EEPROM	NONE
ST	M95256-DW(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95256-MN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95256-MW(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ST	M95256-RBN(DIP8)	EEPROM	NONE
ST	M95256-RDW(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95256-RMN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
ST	M95256-RMW(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ST	M95256-WBN(DIP8)	EEPROM	NONE
ST	M95256-WDW(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95256-WMN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95256-WMW(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
ST	M95320(DIP8)	EEPROM	NONE
ST	M95320(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95320(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95320-R(DIP8)	EEPROM	NONE
ST	M95320-R(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95320-R(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95320-W(DIP8)	EEPROM	NONE
ST	M95320-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95320-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95640(DIP8)	EEPROM	NONE
ST	M95640(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95640(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95640-R(DIP8)	EEPROM	NONE
ST	M95640-R(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95640-R(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95640-W(DIP8)	EEPROM	NONE
ST	M95640-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	M95640-W(TSSOP8)	EEPROM	LP-TSSOP-8PIN
ST	M95M02MN(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	PC28F128J3C(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	PC28F128J3D(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	PC28F128J3F(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	PC28F128M29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
ST	PC28F128M29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
ST	PC28F256J3C(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	PC28F256J3D(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	PC28F256J3F(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	PC28F256M29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
ST	PC28F256M29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
ST	PC28F320J3C(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	PC28F320J3D(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	PC28F320J3F(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	PC28F640J3C(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	PC28F640J3D(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	PC28F640J3F(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	RC28F128J3A(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	RC28F128J3C(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	RC28F128J3D(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	RC28F128J3F(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	RC28F128M29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
ST	RC28F128M29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
ST	RC28F256J3A(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	RC28F256J3C(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	RC28F256J3D(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	RC28F256J3F(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	RC28F256M29EWH(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
ST	RC28F256M29EWL(BGA64)	FLASH	LP-BGA64-SOCKET-11x13 + LP-BGA64-A (For 29xxx)
ST	RC28F320J3A(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	RC28F320J3C(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	RC28F320J3D(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	RC28F320J3F(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	RC28F640J3A(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	RC28F640J3C(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)

Manufacturer	Parts Number	Type	ADAPTER
ST	RC28F640J3D(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	RC28F640J3F(Easy BGA64)	FLASH	LP-BGA64-SOCKET-10x13 + LP-BGA64-B (For J3x,P3x)
ST	ST24164(DIP8)	EEPROM	NONE
ST	ST24C01(DIP8)	EEPROM	NONE
ST	ST24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST24C016(DIP8)	EEPROM	NONE
ST	ST24C02(DIP8)	EEPROM	NONE
ST	ST24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST24C026(DIP8)	EEPROM	NONE
ST	ST24C04(DIP8)	EEPROM	NONE
ST	ST24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST24C046(DIP8)	EEPROM	NONE
ST	ST24C08(DIP8)	EEPROM	NONE
ST	ST24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST24C086(DIP8)	EEPROM	NONE
ST	ST24C16(DIP8)	EEPROM	NONE
ST	ST24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST24C166(DIP8)	EEPROM	NONE
ST	ST24C32(DIP8)	EEPROM	NONE
ST	ST24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST24C326(DIP8)	EEPROM	NONE
ST	ST24C64(DIP8)	EEPROM	NONE
ST	ST24C64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST24C646(DIP8)	EEPROM	NONE
ST	ST24E128(DIP8)	EEPROM	NONE
ST	ST24E128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST24E16(DIP8)	EEPROM	NONE
ST	ST24E16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST24E166(DIP8)	EEPROM	NONE
ST	ST24E166(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST24E256(DIP8)	EEPROM	NONE
ST	ST24E256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST24E32(DIP8)	EEPROM	NONE
ST	ST24E32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST24E64(DIP8)	EEPROM	NONE
ST	ST24E64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST24W01(DIP8)	EEPROM	NONE
ST	ST24W01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST24W016(DIP8)	EEPROM	NONE
ST	ST24W02(DIP8)	EEPROM	NONE
ST	ST24W02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST24W026(DIP8)	EEPROM	NONE
ST	ST24W04(DIP8)	EEPROM	NONE
ST	ST24W04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST24W046(DIP8)	EEPROM	NONE
ST	ST24W08(DIP8)	EEPROM	NONE
ST	ST24W08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST24W086(DIP8)	EEPROM	NONE
ST	ST24W16(DIP8)	EEPROM	NONE
ST	ST24W16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST24W166(DIP8)	EEPROM	NONE
ST	ST24W32(DIP8)	EEPROM	NONE
ST	ST24W32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST24W326(DIP8)	EEPROM	NONE
ST	ST24W64(DIP8)	EEPROM	NONE
ST	ST24W646(DIP8)	EEPROM	NONE
ST	ST93C06-X16(DIP8)	EEPROM	NONE
ST	ST93C06-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
ST	ST93C06-X8(DIP8)	EEPROM	NONE
ST	ST93C06-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C06C-X16(DIP8)	EEPROM	NONE
ST	ST93C06C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C06C-X8(DIP8)	EEPROM	NONE
ST	ST93C06C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C46A-X16(DIP8)	EEPROM	NONE
ST	ST93C46A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C46A-X8(DIP8)	EEPROM	NONE
ST	ST93C46A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C46C-X16(DIP8)	EEPROM	NONE
ST	ST93C46C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C46C-X8(DIP8)	EEPROM	NONE
ST	ST93C46C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C46T-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C46T-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C47C-X16(DIP8)	EEPROM	NONE
ST	ST93C47C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C47C-X8(DIP8)	EEPROM	NONE
ST	ST93C47C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C47T-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C47T-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C56-X16(DIP8)	EEPROM	NONE
ST	ST93C56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C56-X8(DIP8)	EEPROM	NONE
ST	ST93C56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C56C-X16(DIP8)	EEPROM	NONE
ST	ST93C56C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C56C-X8(DIP8)	EEPROM	NONE
ST	ST93C56C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C57C-X16(DIP8)	EEPROM	NONE
ST	ST93C57C-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C57C-X8(DIP8)	EEPROM	NONE
ST	ST93C57C-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C66-X16(DIP8)	EEPROM	NONE
ST	ST93C66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C66-X8(DIP8)	EEPROM	NONE
ST	ST93C66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C67-X16(DIP8)	EEPROM	NONE
ST	ST93C67-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93C67-X8(DIP8)	EEPROM	NONE
ST	ST93C67-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93CS46(DIP8)	EEPROM	NONE
ST	ST93CS46(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93CS47(DIP8)	EEPROM	NONE
ST	ST93CS47(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93CS56(DIP8)	EEPROM	NONE
ST	ST93CS56(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93CS57(DIP8)	EEPROM	NONE
ST	ST93CS57(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93CS66(DIP8)	EEPROM	NONE
ST	ST93CS66(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST93CS67(DIP8)	EEPROM	NONE
ST	ST93CS67(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST95010(DIP8)	EEPROM	NONE
ST	ST95010(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST95010-W(DIP8)	EEPROM	NONE
ST	ST95010-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
ST	ST95020(DIP8)	EEPROM	NONE
ST	ST95020(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST95020-W(DIP8)	EEPROM	NONE
ST	ST95020-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST95040(DIP8)	EEPROM	NONE
ST	ST95040(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST95040-W(DIP8)	EEPROM	NONE
ST	ST95040-W(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST95080(DIP8)	EEPROM	NONE
ST	ST95080(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
ST	ST95128(DIP8)	EEPROM	NONE
ST	ST95160(DIP8)	EEPROM	NONE
ST	ST95320(DIP8)	EEPROM	NONE
ST	ST95640(DIP8)	EEPROM	NONE
ST	TE28F128J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	TE28F128J3D(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	TE28F128P30B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	TE28F128P30BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	TE28F128P30T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	TE28F128P30TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	TE28F256J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	TE28F256J3F(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	TE28F256P30B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	TE28F256P30BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	TE28F256P30T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	TE28F256P30TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	TE28F256P33BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	TE28F256P33TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	TE28F320J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	TE28F320J3D(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	TE28F640J3C(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	TE28F640J3D(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-B (For J3X)
ST	TE28F640P30B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	TE28F640P30BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	TE28F640P30T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	TE28F640P30TF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	TE28F640P33B(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	TE28F640P33T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
ST	TES28F256P33BF(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-C (For P3X)
Summit	S24022(DIP8)	EEPROM	NONE
Summit	S24022(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Summit	S24023(DIP8)	EEPROM	NONE
Summit	S24023(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Summit	S24042(DIP8)	EEPROM	NONE
Summit	S24042(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Summit	S24043(DIP8)	EEPROM	NONE
Summit	S24043(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Summit	S24162(DIP8)	EEPROM	NONE
Summit	S24162(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Summit	S24163(DIP8)	EEPROM	NONE
Summit	S24163(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Summit	S24VP02(DIP8)	EEPROM	NONE
Summit	S24VP02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Summit	S24VP04(DIP8)	EEPROM	NONE
Summit	S24VP04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Summit	S24VP16(DIP8)	EEPROM	NONE
Summit	S24VP16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Summit	S93462(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
Summit	S93463(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Summit	S93662(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Summit	S93663(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Summit	S93VP462(DIP8)	EEPROM	NONE
Summit	S93VP462(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Summit	S93VP463(DIP8)	EEPROM	NONE
Summit	S93VP463(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Summit	S93VP662(DIP8)	EEPROM	NONE
Summit	S93VP662(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Summit	S93VP663(DIP8)	EEPROM	NONE
Summit	S93VP663(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Summit	S93WD462(DIP8)	EEPROM	NONE
Summit	S93WD462(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Summit	S93WD463(DIP8)	EEPROM	NONE
Summit	S93WD463(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Summit	S93WD662(DIP8)	EEPROM	NONE
Summit	S93WD662(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Summit	S93WD663(DIP8)	EEPROM	NONE
Summit	S93WD663(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Sunmoon	SM24C02(DIP8)	EEPROM	NONE
Sunmoon	SM24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Sunmoon	SM24C08(DIP8)	EEPROM	NONE
Sunmoon	SM24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Sunmoon	SM24M64(DIP8)	EEPROM	NONE
Sunmoon	SM24M64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
SyncMos	SM39R08A2(DIP20)	MPU / MCU	NONE
SyncMos	SM39R08A2(DIP24)	MPU / MCU	NONE
SyncMos	SM39R08A2(DIP28)	MPU / MCU	NONE
SyncMos	SM39R08A2(SOP20)	MPU / MCU	LP-SOP-20PIN(300mil) or LP-SOP-28PIN-B(300mil)
SyncMos	SM39R08A2(SOP24)	MPU / MCU	LP-SOP-28PIN-B(300mil)
SyncMos	SM39R08A2(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
SyncMos	SM39R12A2(DIP20)	MPU / MCU	NONE
SyncMos	SM39R12A2(DIP24)	MPU / MCU	NONE
SyncMos	SM39R12A2(DIP28)	MPU / MCU	NONE
SyncMos	SM39R12A2(SOP20)	MPU / MCU	LP-SOP-20PIN(300mil) or LP-SOP-28PIN-B(300mil)
SyncMos	SM39R12A2(SOP24)	MPU / MCU	LP-SOP-28PIN-B(300mil)
SyncMos	SM39R12A2(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
SyncMos	SM39R16A2(DIP20)	MPU / MCU	NONE
SyncMos	SM39R16A2(DIP24)	MPU / MCU	NONE
SyncMos	SM39R16A2(DIP28)	MPU / MCU	NONE
SyncMos	SM39R16A2(SOP20)	MPU / MCU	LP-SOP-20PIN(300mil) or LP-SOP-28PIN-B(300mil)
SyncMos	SM39R16A2(SOP24)	MPU / MCU	LP-SOP-28PIN-B(300mil)
SyncMos	SM39R16A2(SOP28)	MPU / MCU	LP-SOP-28PIN-B(300mil)
SyncMos	SM5964(DIP40)	MPU / MCU	NONE
SyncMos	SM5964(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SyncMos	SM5964(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
SyncMos	SM5964AC(DIP40)	MPU / MCU	NONE
SyncMos	SM5964AC(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SyncMos	SM5964AC(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
SyncMos	SM5964AL(DIP40)	MPU / MCU	NONE
SyncMos	SM5964AL(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SyncMos	SM5964AL(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
SyncMos	SM59R02A1C(DIP40)	MPU / MCU	NONE
SyncMos	SM59R02A1C(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SyncMos	SM59R02A1C(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
SyncMos	SM59R02A1L(DIP40)	MPU / MCU	NONE
SyncMos	SM59R02A1L(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SyncMos	SM59R02A1L(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S

[illegible]

Manufacturer	Parts Number	Type	ADAPTER
SyncMos	SM59R16A5L(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SyncMos	SM59R16A5L(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
SyncMos	SM59R16G6(DIP40)	MPU / MCU	NONE
SyncMos	SM59R16G6(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SyncMos	SM59R16G6(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
SyncMos	SM894051(DIP20)	MPU / MCU	NONE
SyncMos	SM894051(SOP20)	MPU / MCU	LP-SOP-28PIN-B(300mil)
SyncMos	SM8951(DIP40)	MPU / MCU	NONE
SyncMos	SM8951(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SyncMos	SM8951(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
SyncMos	SM89516(DIP40)	MPU / MCU	NONE
SyncMos	SM89516(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SyncMos	SM89516(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
SyncMos	SM89516A(DIP40)	MPU / MCU	NONE
SyncMos	SM89516A(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SyncMos	SM89516A(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
SyncMos	SM89516C(DIP40)	MPU / MCU	NONE
SyncMos	SM89516C(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SyncMos	SM89516C(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
SyncMos	SM89516L(DIP40)	MPU / MCU	NONE
SyncMos	SM89516L(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SyncMos	SM89516L(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
SyncMos	SM8951A(DIP40)	MPU / MCU	NONE
SyncMos	SM8951A(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SyncMos	SM8951A(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
SyncMos	SM8952(DIP40)	MPU / MCU	NONE
SyncMos	SM8952(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SyncMos	SM8952(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
SyncMos	SM8952A(DIP40)	MPU / MCU	NONE
SyncMos	SM8952A(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SyncMos	SM8952A(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
SyncMos	SM8954(DIP40)	MPU / MCU	NONE
SyncMos	SM8954(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SyncMos	SM8954(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
SyncMos	SM8954A(DIP40)	MPU / MCU	NONE
SyncMos	SM8954A(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SyncMos	SM8954A(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
SyncMos	SM8958(DIP40)	MPU / MCU	NONE
SyncMos	SM8958(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SyncMos	SM8958(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
SyncMos	SM8958A(DIP40)	MPU / MCU	NONE
SyncMos	SM8958A(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
SyncMos	SM8958A(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
TI	bq4010(DIP28)	NV RAM	NONE
TI	bq4822YMA(DIP28)	NV RAM	NONE
TI	MSP430F2001(DIP14)	MPU / MCU	NONE
TI	MSP430F2001(QFN16)	MPU / MCU	LP-QFN-16PIN
TI	MSP430F2001(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
TI	MSP430F2002(DIP14)	MPU / MCU	NONE
TI	MSP430F2002(QFN16)	MPU / MCU	LP-QFN-16PIN
TI	MSP430F2002(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
TI	MSP430F2003(DIP14)	MPU / MCU	NONE
TI	MSP430F2003(QFN16)	MPU / MCU	LP-QFN-16PIN
TI	MSP430F2003(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
TI	MSP430F2011(DIP14)	MPU / MCU	NONE
TI	MSP430F2011(QFN16)	MPU / MCU	LP-QFN-16PIN
TI	MSP430F2011(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
TI	MSP430F2012(DIP14)	MPU / MCU	NONE

Manufacturer	Parts Number	Type	ADAPTER
TI	MSP430F2012(QFN16)	MPU / MCU	LP-QFN-16PIN
TI	MSP430F2012(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
TI	MSP430F2013(DIP14)	MPU / MCU	NONE
TI	MSP430F2013(QFN16)	MPU / MCU	LP-QFN-16PIN
TI	MSP430F2013(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
TI	MSP430G2112(DIP20)	MPU / MCU	NONE
TI	MSP430G2112(QFN16)	MPU / MCU	LP-QFN-16PIN-4x4
TI	MSP430G2112(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
TI	MSP430G2112(TSSOP20)	MPU / MCU	LP-TSSOP-20PIN
TI	MSP430G2152(DIP20)	MPU / MCU	NONE
TI	MSP430G2152(QFN16)	MPU / MCU	LP-QFN-16PIN-4x4
TI	MSP430G2152(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
TI	MSP430G2152(TSSOP20)	MPU / MCU	LP-TSSOP-20PIN
TI	MSP430G2212(DIP20)	MPU / MCU	NONE
TI	MSP430G2212(QFN16)	MPU / MCU	LP-QFN-16PIN-4x4
TI	MSP430G2212(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
TI	MSP430G2212(TSSOP20)	MPU / MCU	LP-TSSOP-20PIN
TI	MSP430G2252(DIP20)	MPU / MCU	NONE
TI	MSP430G2252(QFN16)	MPU / MCU	LP-QFN-16PIN-4x4
TI	MSP430G2252(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
TI	MSP430G2252(TSSOP20)	MPU / MCU	LP-TSSOP-20PIN
TI	MSP430G2312(DIP20)	MPU / MCU	NONE
TI	MSP430G2312(QFN16)	MPU / MCU	LP-QFN-16PIN-4x4
TI	MSP430G2312(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
TI	MSP430G2312(TSSOP20)	MPU / MCU	LP-TSSOP-20PIN
TI	MSP430G2352(DIP20)	MPU / MCU	NONE
TI	MSP430G2352(QFN16)	MPU / MCU	LP-QFN-16PIN-4x4
TI	MSP430G2352(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
TI	MSP430G2352(TSSOP20)	MPU / MCU	LP-TSSOP-20PIN
TI	MSP430G2412(DIP20)	MPU / MCU	NONE
TI	MSP430G2412(QFN16)	MPU / MCU	LP-QFN-16PIN-4x4
TI	MSP430G2412(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
TI	MSP430G2412(TSSOP20)	MPU / MCU	LP-TSSOP-20PIN
TI	MSP430G2452(DIP20)	MPU / MCU	NONE
TI	MSP430G2452(QFN16)	MPU / MCU	LP-QFN-16PIN-4x4
TI	MSP430G2452(TSSOP14)	MPU / MCU	LP-TSSOP-20PIN
TI	MSP430G2452(TSSOP20)	MPU / MCU	LP-TSSOP-20PIN
TI	TMS27C010A(DIP32)	EPROM	NONE
TI	TMS27C010A(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
TI	TMS27C020(DIP32)	EPROM	NONE
TI	TMS27C020(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
TI	TMS27C040(DIP32)	EPROM	NONE
TI	TMS27C040(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
TI	TMS27C128(DIP28)	EPROM	NONE
TI	TMS27C210(DIP40)	EPROM	NONE
TI	TMS27C210(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
TI	TMS27C210A(DIP40)	EPROM	NONE
TI	TMS27C210A(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
TI	TMS27C240(DIP40)	EPROM	NONE
TI	TMS27C240(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
TI	TMS27C256(DIP28)	EPROM	NONE
TI	TMS27C256(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
TI	TMS27C512(DIP28)	EPROM	NONE
TI	TMS27C512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
TI	TMS27C64(DIP28)	EPROM	NONE
TI	TMS27PC010A(DIP32)	EPROM	NONE
TI	TMS27PC010A(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
TI	TMS27PC020(DIP32)	EPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
TI	TMS27PC020(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
TI	TMS27PC040(DIP32)	EPROM	NONE
TI	TMS27PC040(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
TI	TMS27PC128(DIP28)	EPROM	NONE
TI	TMS27PC210(DIP40)	EPROM	NONE
TI	TMS27PC210(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
TI	TMS27PC210A(DIP40)	EPROM	NONE
TI	TMS27PC210A(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
TI	TMS27PC240(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
TI	TMS27PC256(DIP28)	EPROM	NONE
TI	TMS27PC256(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
TI	TMS27PC512(DIP28)	EPROM	NONE
TI	TMS27PC512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
TI	TMS28C64(DIP28)	EEPROM	NONE
TMC	24A01(DIP8)	EEPROM	NONE
TMC	24A01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
TMC	24A01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
TMC	24A02(DIP8)	EEPROM	NONE
TMC	24A02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
TMC	24A02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
TMC	24A04(DIP8)	EEPROM	NONE
TMC	24A04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
TMC	24A04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
TMC	24A08(DIP8)	EEPROM	NONE
TMC	24A08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
TMC	24A08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
TMC	24A16(DIP8)	EEPROM	NONE
TMC	24A16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
TMC	24A16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
TMC	93LC46-X16(DIP8)	EEPROM	NONE
TMC	93LC46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
TMC	93LC46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
TMC	93LC46-X8(DIP8)	EEPROM	NONE
TMC	93LC46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
TMC	93LC46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
TMC	93LC56-X16(DIP8)	EEPROM	NONE
TMC	93LC56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
TMC	93LC56-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
TMC	93LC56-X8(DIP8)	EEPROM	NONE
TMC	93LC56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
TMC	93LC56-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
TMC	93LC57-X16(DIP8)	EEPROM	NONE
TMC	93LC57-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
TMC	93LC57-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
TMC	93LC57-X8(DIP8)	EEPROM	NONE
TMC	93LC57-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
TMC	93LC57-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
TMC	93LC66-X16(DIP8)	EEPROM	NONE
TMC	93LC66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
TMC	93LC66-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
TMC	93LC66-X8(DIP8)	EEPROM	NONE
TMC	93LC66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
TMC	93LC66-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
TMC	93LC86-X16(DIP8)	EEPROM	NONE
TMC	93LC86-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
TMC	93LC86-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
TMC	93LC86-X8(DIP8)	EEPROM	NONE
TMC	93LC86-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
TMC	93LC86-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
TOSHIBA	TC57256AD(DIP28)	EPROM	NONE
TOSHIBA	TC58FVB160AFT(TSOP48)	FLASH	LP-TSOP-48S
TOSHIBA	TC58FVB160FT(TSOP48)	FLASH	LP-TSOP-48S
TOSHIBA	TC58FVB321FT(TSOP48)	FLASH	LP-TSOP-48S
TOSHIBA	TC58FVB641FT(TSOP48)	FLASH	LP-TSOP-48S
TOSHIBA	TC58FVM6B2A(TSOP48)	FLASH	LP-TSOP-48S
TOSHIBA	TC58FVM6T2A(TSOP48)	FLASH	LP-TSOP-48S
TOSHIBA	TC58FVT160AFT(TSOP48)	FLASH	LP-TSOP-48S
TOSHIBA	TC58FVT160FT(TSOP48)	FLASH	LP-TSOP-48S
TOSHIBA	TC58FVT321FT(TSOP48)	FLASH	LP-TSOP-48S
TOSHIBA	TC58FVT641FT(TSOP48)	FLASH	LP-TSOP-48S
TOSHIBA	TMM27128AD(DIP28)	EPROM	NONE
TOSHIBA	TMM27128ADI(DIP28)	EPROM	NONE
TOSHIBA	TMM27128AP(DIP28)	EPROM	NONE
TOSHIBA	TMM27256BD(DIP28)	EPROM	NONE
TOSHIBA	TMM27512AD(DIP28)	EPROM	NONE
TOSHIBA	TMM2764AD(DIP28)	EPROM	NONE
TOSHIBA	TMM2764ADI(DIP28)	EPROM	NONE
TOSHIBA	TMM2764AP(DIP28)	EPROM	NONE
TOSHIBA	TMP89FH42LUG(TQFP44)	MPU / MCU	LP48-VQFP-44S
TOSHIBA	TMP89FH42UG(TQFP44)	MPU / MCU	LP48-VQFP-44S
TOSHIBA	TMP89FM42LUG(TQFP44)	MPU / MCU	LP48-VQFP-44S
TOSHIBA	TMP89FM42UG(TQFP44)	MPU / MCU	LP48-VQFP-44S
TSI	TS25L010A-P(PDIP8)	FLASH	NONE
TSI	TS25L010A-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
TSI	TS25L010A-V(SOP8)	FLASH	LP-SOP-16PIN(150mil)
TSI	TS25L020A-P(PDIP8)	FLASH	NONE
TSI	TS25L020A-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
TSI	TS25L020A-V(SOP8)	FLASH	LP-SOP-16PIN(150mil)
TSI	TS25L032A-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
TSI	TS25L032A-V(WSON8)	FLASH	LP48-WSON8-5x6
TSI	TS25L16-P(PDIP8)	FLASH	NONE
TSI	TS25L16-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
TSI	TS25L16-V(SOP8)	FLASH	LP-SOP-16PIN(150mil)
TSI	TS25L16PE-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
TSI	TS25L16PE-V(WSON8)	FLASH	LP48-WSON8-5x6
TSI	TS25L20-P(PDIP8)	FLASH	NONE
TSI	TS25L20-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
TSI	TS25L20-V(SOP8)	FLASH	LP-SOP-16PIN(150mil)
TSI	TS25L40-P(PDIP8)	FLASH	NONE
TSI	TS25L40-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
TSI	TS25L40-V(SOP8)	FLASH	LP-SOP-16PIN(150mil)
TSI	TS25L512A-V(SOP8)	FLASH	LP-SOP-16PIN(150mil)
TSI	TS25L80-P(PDIP8)	FLASH	NONE
TSI	TS25L80-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
TSI	TS25L80-V(SOP8)	FLASH	LP-SOP-16PIN(150mil)
TSI	TS25L80PE-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
TSI	TS25L80PE-V(WSON8)	FLASH	LP48-WSON8-5x6
Turbo IC	28C256A(DIP28)	EEPROM	NONE
Turbo IC	28C256A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Turbo IC	28C256A(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
Turbo IC	28C256A(TSOP28)	EEPROM	LP-TSOP-28PIN
Turbo IC	28C64A(DIP28)	EEPROM	NONE
Turbo IC	28C64A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Turbo IC	28C64A(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
Turbo IC	28C64A(TSOP28)	EEPROM	LP-TSOP-28PIN
Turbo IC	28LV256(DIP28)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
Turbo IC	28LV256(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Turbo IC	28LV256(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
Turbo IC	28LV256(TSOP28)	EEPROM	LP-TSOP-28PIN
Turbo IC	28LV64(DIP28)	EEPROM	NONE
Turbo IC	28LV64(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
Turbo IC	28LV64(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
Turbo IC	28LV64(TSOP28)	EEPROM	LP-TSOP-28PIN
Turbo IC	TU24C01B(DIP8)	EEPROM	NONE
Turbo IC	TU24C01B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Turbo IC	TU24C02B(DIP8)	EEPROM	NONE
Turbo IC	TU24C02B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Turbo IC	TU24C04B(DIP8)	EEPROM	NONE
Turbo IC	TU24C04B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Turbo IC	TU24C08B(DIP8)	EEPROM	NONE
Turbo IC	TU24C08B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Turbo IC	TU24C128(DIP8)	EEPROM	NONE
Turbo IC	TU24C128(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Turbo IC	TU24C16B(DIP8)	EEPROM	NONE
Turbo IC	TU24C16B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Turbo IC	TU24C256(DIP8)	EEPROM	NONE
Turbo IC	TU24C256(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Turbo IC	TU24C32(DIP8)	EEPROM	NONE
Turbo IC	TU24C32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Turbo IC	TU24C64B(DIP8)	EEPROM	NONE
Turbo IC	TU24C64B(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Turbo IC	TU93C46-X16(DIP8)	EEPROM	NONE
Turbo IC	TU93C46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Turbo IC	TU93C46-X8(DIP8)	EEPROM	NONE
Turbo IC	TU93C46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Turbo IC	TU93C56-X16(DIP8)	EEPROM	NONE
Turbo IC	TU93C56-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Turbo IC	TU93C56-X8(DIP8)	EEPROM	NONE
Turbo IC	TU93C56-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Turbo IC	TU93C66-X16(DIP8)	EEPROM	NONE
Turbo IC	TU93C66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Turbo IC	TU93C66-X8(DIP8)	EEPROM	NONE
Turbo IC	TU93C66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Unigen	UG24C01(DIP8)	EEPROM	NONE
Unigen	UG24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Unigen	UG24C01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Unigen	UG24C02(DIP8)	EEPROM	NONE
Unigen	UG24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Unigen	UG24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Unigen	UG24C04(DIP8)	EEPROM	NONE
Unigen	UG24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Unigen	UG24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Unigen	UG24C08(DIP8)	EEPROM	NONE
Unigen	UG24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Unigen	UG24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Unigen	UG24C16(DIP8)	EEPROM	NONE
Unigen	UG24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Unigen	UG24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Unigen	UG93C46-A-X16(DIP8)	EEPROM	NONE
Unigen	UG93C46-A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Unigen	UG93C46-A-X8(DIP8)	EEPROM	NONE
Unigen	UG93C46-A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Unigen	UG93C46-B-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Unigen	UG93C46-B-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
Unigen	UG93C56-A-X16(DIP8)	EEPROM	NONE
Unigen	UG93C56-A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Unigen	UG93C56-A-X8(DIP8)	EEPROM	NONE
Unigen	UG93C56-A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Unigen	UG93C56-B-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Unigen	UG93C56-B-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Unigen	UG93C56-C(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Unigen	UG93C66-A-X16(DIP8)	EEPROM	NONE
Unigen	UG93C66-A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Unigen	UG93C66-A-X8(DIP8)	EEPROM	NONE
Unigen	UG93C66-A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Unigen	UG93C66-B-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Unigen	UG93C66-B-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Wave Systems	W93C46(DIP8)	EEPROM	NONE
Wave Systems	W93C46(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Wave Systems	W93C46(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Wave Systems	W93C46A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Wave Systems	W93C56(DIP8)	EEPROM	NONE
Wave Systems	W93C56(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Wave Systems	W93C56(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Wave Systems	W93C56A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Wave Systems	W93C66(DIP8)	EEPROM	NONE
Wave Systems	W93C66(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Wave Systems	W93C66(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Wave Systems	W93C66A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Wave Systems	W93C86(DIP8)	EEPROM	NONE
Wave Systems	W93C86(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Wave Systems	W93C86(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Wave Systems	W93C86A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Winbond	W25B40AVSN(Bottom)(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25B40AVSN(Top)(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25B40VSN(Bottom)(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25B40VSN(Top)(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25D10VDA(PDIP8)	FLASH	NONE
Winbond	W25D10VSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25D10VZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25D20VDA(PDIP8)	FLASH	NONE
Winbond	W25D20VSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25D20VZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25D40VDA(PDIP8)	FLASH	NONE
Winbond	W25D40VSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25D40VSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25D40VZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25D80VDA(PDIP8)	FLASH	NONE
Winbond	W25D80VSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25D80VZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25P10VSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25P16VSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25P16VSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25P20VSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25P32VSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25P32VSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25P40VSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25P80VSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25P80VSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q05CLSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q05CLSV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q05CLUX(USON8)	FLASH	LP48-MLP8-2x3

Manufacturer	Parts Number	Type	ADAPTER
Winbond	W25Q05CLZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q05CVSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q05CVSV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q05CVUX(USON8)	FLASH	LP48-MLP8-2x3
Winbond	W25Q05CVZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q10CLSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q10CLSV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q10CLUX(USON8)	FLASH	LP48-MLP8-2x3
Winbond	W25Q10CLZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q10CVSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q10CVSV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q10CVUX(USON8)	FLASH	LP48-MLP8-2x3
Winbond	W25Q10CVZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q128BVB(TFBGA24)	FLASH	LP-BGA-24PIN-5x5B
Winbond	W25Q128BVC(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
Winbond	W25Q128BVE(WSON8)	FLASH	LP48-WSON8-6x8
Winbond	W25Q128BVF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25Q128FVA(DIP8)	FLASH	NONE
Winbond	W25Q128FVB(TFBGA24)	FLASH	LP-BGA-24PIN-5x5B
Winbond	W25Q128FVC(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
Winbond	W25Q128FVE(WSON8)	FLASH	LP48-WSON8-6x8
Winbond	W25Q128FVF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25Q128FVP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q128FVS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q128FVT(VSOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q128FWB(TFBGA24)	FLASH	LP-BGA-24PIN-5x5B
Winbond	W25Q128FWC(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
Winbond	W25Q128FWE(WSON8)	FLASH	LP48-WSON8-6*8
Winbond	W25Q128FWF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25Q128FWP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q128FWS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q16BVDA(PDIP8)	FLASH	NONE
Winbond	W25Q16BVSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25Q16BVSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q16BVSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q16BVZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q16CLDA(PDIP8)	FLASH	NONE
Winbond	W25Q16CLSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25Q16CLSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q16CLSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q16CLZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q16CVDA(PDIP8)	FLASH	NONE
Winbond	W25Q16CVSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25Q16CVSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q16CVSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q16CVZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q16DVDA(DIP8)	FLASH	NONE
Winbond	W25Q16DVSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25Q16DVSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q16DVSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q16DVST(VSOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q16DVSV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q16DVTB(BGA24)	FLASH	LP-BGA-24PIN-5x5B
Winbond	W25Q16DVTC(BGA24)	FLASH	LP-BGA-24PIN-4x6B
Winbond	W25Q16DVZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q16DWSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25Q16DWSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q16DWSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)

Manufacturer	Parts Number	Type	ADAPTER
Winbond	W25Q16DWZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q16VSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25Q16VSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q16VZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q20BVDA(DIP8)	FLASH	NONE
Winbond	W25Q20BVSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25Q20BVSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q20BWSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q20BWZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q20CLSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q20CLSV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q20CLUX(USON8)	FLASH	LP48-MLP8-2x3
Winbond	W25Q20CLZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q256FVB(TFBGA24)	FLASH	LP-BGA-24PIN-5x5B
Winbond	W25Q256FVC(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
Winbond	W25Q256FVE(WSON8)	FLASH	LP48-WSON8-6x8
Winbond	W25Q256FVF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25Q32BVDA(DIP8)	FLASH	NONE
Winbond	W25Q32BVSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25Q32BVSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q32BVZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q32BWSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25Q32BWSS(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q32BWZE(WSON8)	FLASH	LP48-WSON8-6x8
Winbond	W25Q32BWZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q32DWSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25Q32DWSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q32DWZE(WSON8)	FLASH	LP48-WSON8-6x8
Winbond	W25Q32DWZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q32FVDA(DIP8)	FLASH	NONE
Winbond	W25Q32FVSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25Q32FVSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q32FVST(VSOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q32FVTB(TFBGA24)	FLASH	LP-BGA-24PIN-5x5B
Winbond	W25Q32FVTC(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
Winbond	W25Q32FVZE(WSON8)	FLASH	LP48-WSON8-6x8
Winbond	W25Q32FVZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q32VSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25Q32VSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q40BLSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q40BLSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q40BLZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q40BVSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q40BVSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q40BVZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q40BWSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q40BWZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q40CLSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q64BVDA(PDIP8)	FLASH	NONE
Winbond	W25Q64BVSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25Q64BVSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q64BVZE(WSON8)	FLASH	LP48-WSON8-6x8
Winbond	W25Q64CVDA(PDIP8)	FLASH	NONE
Winbond	W25Q64CVSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25Q64CVSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q64CVZE(WSON8)	FLASH	LP48-WSON8-6x8
Winbond	W25Q64CVZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q64DWSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)

Manufacturer	Parts Number	Type	ADAPTER
Winbond	W25Q64DWSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q64DWZE(WSON8)	FLASH	LP48-WSON8-6x8
Winbond	W25Q64DWZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q64FVSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25Q64FVSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q64FVTB(TFBGA24)	FLASH	LP-BGA-24PIN-5x5B
Winbond	W25Q64FVTC(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
Winbond	W25Q64FVZE(WSON8)	FLASH	LP48-WSON8-6x8
Winbond	W25Q64FVZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q64FWSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25Q64FWSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q64FWTB(TFBGA24)	FLASH	LP-BGA-24PIN-5x5B
Winbond	W25Q64FWTC(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
Winbond	W25Q64FWZE(WSON8)	FLASH	LP48-WSON8-6x8
Winbond	W25Q64FWZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q80BLSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q80BLSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q80BLZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q80BVDA(PDIP8)	FLASH	NONE
Winbond	W25Q80BVSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25Q80BVSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q80BVSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q80BVUX(USON8)	FLASH	LP48-MLP8-2x3
Winbond	W25Q80BVZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q80BWSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25Q80BWSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q80BWZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25Q80VSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25Q80VZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25R128FVA(DIP8)	FLASH	NONE
Winbond	W25R128FVB(TFBGA24)	FLASH	LP-BGA-24PIN-5x5B
Winbond	W25R128FVC(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
Winbond	W25R128FVE(WSON8)	FLASH	LP48-WSON8-6x8
Winbond	W25R128FVF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25R128FVP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25R128FVS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25R128FVT(VSOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25R64FVSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25R64FVSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25R64FVTB(TFBGA24)	FLASH	LP-BGA-24PIN-5x5B
Winbond	W25R64FVTC(TFBGA24)	FLASH	LP-BGA-24PIN-4x6B
Winbond	W25R64FVZE(WSON8)	FLASH	LP48-WSON8-6x8
Winbond	W25R64FVZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X05CLD(TSSOP8)	FLASH	LP-TSSOP-8PIN
Winbond	W25X05CLSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X05CLSV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X05CLUX(USON8)	FLASH	LP48-MLP8-2x3
Winbond	W25X05CLZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X10ALDA(PDIP8)	FLASH	NONE
Winbond	W25X10ALSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X10ALZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X10AVDA(PDIP8)	FLASH	NONE
Winbond	W25X10AVSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X10AVZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X10BLDA(PDIP8)	FLASH	NONE
Winbond	W25X10BLSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X10BLSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25X10BLZP(WSON8)	FLASH	LP48-WSON8-5x6

Manufacturer	Parts Number	Type	ADAPTER
Winbond	W25X10BVDA(PDIP8)	FLASH	NONE
Winbond	W25X10BVSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X10BVSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25X10BVZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X10CLD(TSSOP8)	FLASH	LP-TSSOP-8PIN
Winbond	W25X10CLSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X10CLSV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X10CLUX(USON8)	FLASH	LP48-MLP8-2x3
Winbond	W25X10CLZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X10LSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X10LZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X10VDA(DIP8)	FLASH	NONE
Winbond	W25X10VSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X10VZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X16AVDA(PDIP8)	FLASH	NONE
Winbond	W25X16AVSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25X16AVSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X16AVSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25X16AVZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X16VDA(PDIP8)	FLASH	NONE
Winbond	W25X16VSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25X16VSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25X16VZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X20ALDA(PDIP8)	FLASH	NONE
Winbond	W25X20ALSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X20ALZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X20AVDA(PDIP8)	FLASH	NONE
Winbond	W25X20AVSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X20AVSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25X20AVZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X20BLDA(PDIP8)	FLASH	NONE
Winbond	W25X20BLSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X20BLSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25X20BLZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X20BVDA(DIP8)	FLASH	NONE
Winbond	W25X20BVSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X20BVSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25X20BVZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X20CLSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X20CLSV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X20CLUX(USON8)	FLASH	LP48-MLP8-2x3
Winbond	W25X20CLZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X20LSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X20LZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X20VDA(DIP8)	FLASH	NONE
Winbond	W25X20VSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X20VZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X21CLSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X21CLSV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X21CLUX(USON8)	FLASH	LP48-MLP8-2x3
Winbond	W25X21CLZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X32AVSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25X32AVSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X32AVSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25X32AVZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X32VDA(PDIP8)	FLASH	NONE
Winbond	W25X32VSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25X32VSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)

Manufacturer	Parts Number	Type	ADAPTER
Winbond	W25X32VZE(WSON8)	FLASH	LP48-WSON8-6x8
Winbond	W25X40ALDA(PDIP8)	FLASH	NONE
Winbond	W25X40ALSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X40ALSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25X40ALZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X40AVDA(DIP8)	FLASH	NONE
Winbond	W25X40AVSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X40AVZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X40BLDA(PDIP8)	FLASH	NONE
Winbond	W25X40BLSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X40BLSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25X40BLZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X40BVDA(PDIP8)	FLASH	NONE
Winbond	W25X40BVSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X40BVSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25X40BVZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X40CLSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X40CLSV(VSOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X40CLUX(USON8)	FLASH	LP48-MLP8-2x3
Winbond	W25X40CLZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X40LSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X40LSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25X40LZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X40VDA(DIP8)	FLASH	NONE
Winbond	W25X40VSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X40VSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25X40VZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X41CLSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X64VDA(PDIP8)	FLASH	NONE
Winbond	W25X64VSF(SOP16)	FLASH	LP-SOP-28PIN-B(300mil)
Winbond	W25X64VSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25X64VZE(WSON8)	FLASH	LP48-WSON8-6x8
Winbond	W25X80ALDA(PDIP8)	FLASH	NONE
Winbond	W25X80ALSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X80ALSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25X80ALZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X80AVDA(PDIP8)	FLASH	NONE
Winbond	W25X80AVSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X80AVSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25X80AVZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X80BLDA(PDIP8)	FLASH	NONE
Winbond	W25X80BLSN(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Winbond	W25X80BLSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25X80BLZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X80LSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25X80LZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W25X80VDA(DIP8)	FLASH	NONE
Winbond	W25X80VSS(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Winbond	W25X80VZP(WSON8)	FLASH	LP48-WSON8-5x6
Winbond	W27C01(DIP32)	EPROM	NONE
Winbond	W27C01(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Winbond	W27C010(DIP32)	EPROM	NONE
Winbond	W27C010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Winbond	W27C010(SOP32)	EPROM	LP48-SOP-32PIN
Winbond	W27C02(DIP32)	EPROM	NONE
Winbond	W27C02(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Winbond	W27C020(DIP32)	EPROM	NONE
Winbond	W27C020(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S

Manufacturer	Parts Number	Type	ADAPTER
Winbond	W27C020(SOP32)	EPROM	LP48-SOP-32PIN
Winbond	W27C020M(DIP32)	EPROM	NONE
Winbond	W27C020M(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Winbond	W27C257(DIP28)	EPROM	NONE
Winbond	W27C257(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Winbond	W27C4096(DIP40)	EPROM	NONE
Winbond	W27C4096(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W27C4096(TSOP40)	EPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
Winbond	W27C512(DIP28)	EPROM	NONE
Winbond	W27C512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Winbond	W27C520(SOP20)	EPROM	LP-SOP-28PIN-B(300mil)
Winbond	W27C520(TSSOP20)	EPROM	LP48-TSSOP-20PIN
Winbond	W27E01(DIP32)	EPROM	NONE
Winbond	W27E01(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Winbond	W27E010(DIP32)	EPROM	NONE
Winbond	W27E010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Winbond	W27E010(SOP32)	EPROM	LP48-SOP-32PIN
Winbond	W27E02(DIP32)	EPROM	NONE
Winbond	W27E02(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Winbond	W27E020(DIP32)	EPROM	NONE
Winbond	W27E020(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Winbond	W27E020(SOP32)	EPROM	LP48-SOP-32PIN
Winbond	W27E040(DIP32)	EPROM	NONE
Winbond	W27E040(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Winbond	W27E040(SOP32)	EPROM	LP48-SOP-32PIN
Winbond	W27E257(DIP28)	EPROM	NONE
Winbond	W27E257(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Winbond	W27E4096(DIP40)	EPROM	NONE
Winbond	W27E4096(PLCC44)	EPROM	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W27E4096(TSOP40)	EPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
Winbond	W27E512(DIP28)	EPROM	NONE
Winbond	W27E512(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Winbond	W27E512(TSOP28)	EPROM	LP-TSOP-28PIN
Winbond	W27E520(SOP20)	EPROM	LP-SOP-28PIN-B(300mil)
Winbond	W27E520(TSSOP20)	EPROM	LP48-TSSOP-20PIN
Winbond	W27F256(DIP28)	EPROM	NONE
Winbond	W27L01(DIP32)	EPROM	NONE
Winbond	W27L01(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Winbond	W27L010(DIP32)	EPROM	NONE
Winbond	W27L010(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Winbond	W27L010(SOP32)	EPROM	LP48-SOP-32PIN
Winbond	W27L02(DIP32)	EPROM	NONE
Winbond	W27L02(PLCC32)	EPROM	LP48-PLCC-1M32 or LP48-PLCC-1M32S
Winbond	W28J160BT(TSOP48)	FLASH	LP-TSOP-48S
Winbond	W28J160TT(TSOP48)	FLASH	LP-TSOP-48S
Winbond	W28J320BT(TSOP48)	FLASH	LP-TSOP-48S
Winbond	W28J320TT(TSOP48)	FLASH	LP-TSOP-48S
Winbond	W28J800BT(TSOP48)	FLASH	LP-TSOP-48S
Winbond	W28J800TT(TSOP48)	FLASH	LP-TSOP-48S
Winbond	W29EE011(DIP32)	EEPROM	NONE
Winbond	W29EE011(PLCC32)	EEPROM	NONE
Winbond	W29GL032CB(TSOP48)	FLASH	LP48-TSOP-48PIN
Winbond	W29GL032CB(VFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
Winbond	W29GL032CT(TSOP48)	FLASH	LP48-TSOP-48PIN
Winbond	W29GL032CT(VFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
Winbond	W29GL064CB(TSOP48)	FLASH	LP-TSOP-48S
Winbond	W29GL064CB(VFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
Winbond	W29GL064CH(TSOP48)	FLASH	LP-TSOP-48S

Manufacturer	Parts Number	Type	ADAPTER
Winbond	W29GL064CL(TSOP48)	FLASH	LP-TSOP-48S
Winbond	W29GL064CT(TSOP48)	FLASH	LP-TSOP-48S
Winbond	W29GL064CT(VFBGA48)	FLASH	LP-TFBGA-48PIN-6x8
Winbond	W29GL128CH9T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
Winbond	W29GL128CL9T(TSOP56)	FLASH	LP-TSOP56-SOCKET + LP-TSOP56-A (For 29xxx)
Winbond	W77E516(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W77E58(DIP40)	MPU / MCU	NONE
Winbond	W77E58(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W77E58(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78E051C(DIP40)	MPU / MCU	NONE
Winbond	W78E051C(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78E051C(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78E051DDG(DIP40)	MPU / MCU	NONE
Winbond	W78E051DFG(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78E051DPG(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78E052C(DIP40)	MPU / MCU	NONE
Winbond	W78E052C(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78E052C(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78E052DDG(DIP40)	MPU / MCU	NONE
Winbond	W78E052DFG(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78E052DPG(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78E054C(DIP40)	MPU / MCU	NONE
Winbond	W78E054C(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78E054C(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78E054DDG(DIP40)	MPU / MCU	NONE
Winbond	W78E054DFG(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78E054DPG(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78E058DDG(DIP40)	MPU / MCU	NONE
Winbond	W78E058DFG(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78E058DPG(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78E065A(DIP40)	MPU / MCU	NONE
Winbond	W78E065A(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78E065A(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78E365(DIP40)	MPU / MCU	NONE
Winbond	W78E365(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78E365(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78E365A(DIP40)	MPU / MCU	NONE
Winbond	W78E365A(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78E365A(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78E516B(DIP40)	MPU / MCU	NONE
Winbond	W78E516B(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78E516B(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78E516DDG(DIP40)	MPU / MCU	NONE
Winbond	W78E516DFG(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78E516DPG(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78E51B(DIP40)	MPU / MCU	NONE
Winbond	W78E51B(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78E51B(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78E52B(DIP40)	MPU / MCU	NONE
Winbond	W78E52B(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78E52B(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78E54B(DIP40)	MPU / MCU	NONE
Winbond	W78E54B(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78E54B(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78E62(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78E62B(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78E65(DIP40)	MPU / MCU	NONE
Winbond	W78E65(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S

Manufacturer	Parts Number	Type	ADAPTER
Winbond	W78E65(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78IE52(DIP40)	MPU / MCU	NONE
Winbond	W78IE52(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78IE52(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78IE54(DIP40)	MPU / MCU	NONE
Winbond	W78IE54(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78IE54(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78IE58(DIP40)	MPU / MCU	NONE
Winbond	W78IE58(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78IE58(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78L365(DIP40)	MPU / MCU	NONE
Winbond	W78L365(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78L365(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78L365A(DIP40)	MPU / MCU	NONE
Winbond	W78L365A(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78L365A(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78L516A(DIP40)	MPU / MCU	NONE
Winbond	W78L516A(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78L516A(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78LE051C(DIP40)	MPU / MCU	NONE
Winbond	W78LE051C(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78LE051C(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78LE052C(DIP40)	MPU / MCU	NONE
Winbond	W78LE052C(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78LE052C(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78LE054C(DIP40)	MPU / MCU	NONE
Winbond	W78LE054C(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78LE054C(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78LE365(DIP40)	MPU / MCU	NONE
Winbond	W78LE365(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78LE365(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78LE365A(DIP40)	MPU / MCU	NONE
Winbond	W78LE365A(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78LE365A(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78LE51(DIP40)	MPU / MCU	NONE
Winbond	W78LE51(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78LE51(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78LE516(DIP40)	MPU / MCU	NONE
Winbond	W78LE516(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78LE516(QFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78LE52(DIP40)	MPU / MCU	NONE
Winbond	W78LE52(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78LE52(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78LE54(DIP40)	MPU / MCU	NONE
Winbond	W78LE54(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78LE54(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78LE58(DIP40)	MPU / MCU	NONE
Winbond	W78LE58(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78LE58(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Winbond	W78LE812(DIP40)	MPU / MCU	NONE
Winbond	W78LE812(PLCC44)	MPU / MCU	LP48-PLCC-44PIN or LP48-PLCC-44S
Winbond	W78LE812(PQFP44)	MPU / MCU	LP48-QFP-44PIN or LP48-QFP-44S
Wing Shing	WS24C02(DIP8)	EEPROM	NONE
Wing Shing	WS24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Wing Shing	WS24W04(DIP8)	EEPROM	NONE
Wing Shing	WS24W04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Wing Shing	WS24W08(DIP8)	EEPROM	NONE
Wing Shing	WS24W08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
Wing Shing	WS24W16(DIP8)	EEPROM	NONE
Wing Shing	WS24W16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Wing Shing	WS24W32(DIP8)	EEPROM	NONE
Wing Shing	WS24W32(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Wing Shing	WS24W64(DIP8)	EEPROM	NONE
Wing Shing	WS24W64(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
WSI	WS27C128FM(DIP28)	EPROM	NONE
WSI	WS27C64FM(DIP28)	EPROM	NONE
XICOR	X24001(DIP8)	EEPROM	NONE
XICOR	X24001(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24001-2.7(DIP8)	EEPROM	NONE
XICOR	X24001-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24001-3(DIP8)	EEPROM	NONE
XICOR	X24001-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24012(DIP8)	EEPROM	NONE
XICOR	X24012(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24012-2.7(DIP8)	EEPROM	NONE
XICOR	X24012-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24012-3(DIP8)	EEPROM	NONE
XICOR	X24012-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X2402(DIP8)	EEPROM	NONE
XICOR	X24022(DIP8)	EEPROM	NONE
XICOR	X24022(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24022(TSSOP8)	EEPROM	LP-TSSOP-8PIN
XICOR	X24022-2.7(DIP8)	EEPROM	NONE
XICOR	X24022-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24022-2.7(TSSOP8)	EEPROM	LP-TSSOP-8PIN
XICOR	X24022-3(DIP8)	EEPROM	NONE
XICOR	X24022-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24022-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
XICOR	X2404(DIP8)	EEPROM	NONE
XICOR	X24042(DIP8)	EEPROM	NONE
XICOR	X24042(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24042-2.7(DIP8)	EEPROM	NONE
XICOR	X24042-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24042-3(DIP8)	EEPROM	NONE
XICOR	X24042-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24164(DIP8)	EEPROM	NONE
XICOR	X24164(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24164-2.7(DIP8)	EEPROM	NONE
XICOR	X24164-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24164-3(DIP8)	EEPROM	NONE
XICOR	X24164-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24165(DIP8)	EEPROM	NONE
XICOR	X24165(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24165-2.7(DIP8)	EEPROM	NONE
XICOR	X24165-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24257-1.8(TSSOP8)	EEPROM	LP-TSSOP-20PIN
XICOR	X24257-A8(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
XICOR	X24257-A8-1.8(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
XICOR	X24257-A8-2.5(SOP8)	EEPROM	LP-SOP-8PIN-B(207mil)
XICOR	X24257-S8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24257-S8-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24257-S8-2.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24320(DIP8)	EEPROM	NONE
XICOR	X24320(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24320-1.8(DIP8)	EEPROM	NONE
XICOR	X24320-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)

Manufacturer	Parts Number	Type	ADAPTER
XICOR	X24320-2.5(DIP8)	EEPROM	NONE
XICOR	X24320-2.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24320-2.5(TSSOP8)	EEPROM	LP-TSSOP-20PIN
XICOR	X24321(DIP8)	EEPROM	NONE
XICOR	X24321(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24321-1.8(DIP8)	EEPROM	NONE
XICOR	X24321-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24321-2.5(DIP8)	EEPROM	NONE
XICOR	X24321-2.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24325(DIP8)	EEPROM	NONE
XICOR	X24325(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24325-2.7(DIP8)	EEPROM	NONE
XICOR	X24325-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24640(DIP8)	EEPROM	NONE
XICOR	X24640(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24640-1.8(DIP8)	EEPROM	NONE
XICOR	X24640-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24640-18(DIP8)	EEPROM	NONE
XICOR	X24640-18(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24640-2.7(DIP8)	EEPROM	NONE
XICOR	X24640-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24641(DIP8)	EEPROM	NONE
XICOR	X24641(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24641-1.8(DIP8)	EEPROM	NONE
XICOR	X24641-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24641-2.5(DIP8)	EEPROM	NONE
XICOR	X24641-2.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24645(DIP8)	EEPROM	NONE
XICOR	X24645(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24645-1.8(DIP8)	EEPROM	NONE
XICOR	X24645-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24645-2.5(DIP8)	EEPROM	NONE
XICOR	X24645-2.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C00(DIP8)	EEPROM	NONE
XICOR	X24C00(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C00-2.7(DIP8)	EEPROM	NONE
XICOR	X24C00-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C00-3(DIP8)	EEPROM	NONE
XICOR	X24C00-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C01(DIP8)	EEPROM	NONE
XICOR	X24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C01-2.7(DIP8)	EEPROM	NONE
XICOR	X24C01-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C01-3(DIP8)	EEPROM	NONE
XICOR	X24C01-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C01-3.5(DIP8)	EEPROM	NONE
XICOR	X24C01-3.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C01A(DIP8)	EEPROM	NONE
XICOR	X24C01A(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C01A-3(DIP8)	EEPROM	NONE
XICOR	X24C01A-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C01A-3.5(DIP8)	EEPROM	NONE
XICOR	X24C01A-3.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C02(DIP8)	EEPROM	NONE
XICOR	X24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C02-2.7(DIP8)	EEPROM	NONE
XICOR	X24C02-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C02-3(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
XICOR	X24C02-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C02-3.5(DIP8)	EEPROM	NONE
XICOR	X24C02-3.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C04(DIP8)	EEPROM	NONE
XICOR	X24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN
XICOR	X24C04-1.8(DIP8)	EEPROM	NONE
XICOR	X24C04-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C04-1.8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
XICOR	X24C04-2.7(DIP8)	EEPROM	NONE
XICOR	X24C04-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C04-2.7(TSSOP8)	EEPROM	LP-TSSOP-8PIN
XICOR	X24C04-3(DIP8)	EEPROM	NONE
XICOR	X24C04-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C04-3(TSSOP8)	EEPROM	LP-TSSOP-8PIN
XICOR	X24C04-3.5(DIP8)	EEPROM	NONE
XICOR	X24C04-3.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C04-3.5(TSSOP8)	EEPROM	LP-TSSOP-8PIN
XICOR	X24C08(DIP8)	EEPROM	NONE
XICOR	X24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C08-2.7(DIP8)	EEPROM	NONE
XICOR	X24C08-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C08-3(DIP8)	EEPROM	NONE
XICOR	X24C08-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C08-3.5(DIP8)	EEPROM	NONE
XICOR	X24C08-3.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C16(DIP8)	EEPROM	NONE
XICOR	X24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C16-1.8(DIP8)	EEPROM	NONE
XICOR	X24C16-1.8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C16-2.7(DIP8)	EEPROM	NONE
XICOR	X24C16-2.7(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C16-3(DIP8)	EEPROM	NONE
XICOR	X24C16-3(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24C16-3.5(DIP8)	EEPROM	NONE
XICOR	X24C16-3.5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24F016(DIP8)	EEPROM	NONE
XICOR	X24F016(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24F016-5(DIP8)	EEPROM	NONE
XICOR	X24F016-5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24F032(DIP8)	EEPROM	NONE
XICOR	X24F032(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24F032-5(DIP8)	EEPROM	NONE
XICOR	X24F032-5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24F064(DIP8)	EEPROM	NONE
XICOR	X24F064(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24F064-5(DIP8)	EEPROM	NONE
XICOR	X24F064-5(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X24F128(DIP8)	EEPROM	NONE
XICOR	X24F128-5(DIP8)	EEPROM	NONE
XICOR	X25020P(DIP8)	EEPROM	NONE
XICOR	X25020P-2.7V(DIP8)	EEPROM	NONE
XICOR	X25020P-3V(DIP8)	EEPROM	NONE
XICOR	X25020S(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X25020S-2.7V(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X25020S-3V(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X25040P(DIP8)	EEPROM	NONE
XICOR	X25040P-2.7V(DIP8)	EEPROM	NONE

Manufacturer	Parts Number	Type	ADAPTER
XICOR	X25040P-3V(DIP8)	EEPROM	NONE
XICOR	X25040S(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X25040S-2.7V(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X25040S-3V(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
XICOR	X2804A(DIP24)	EEPROM	NONE
XICOR	X2804C(DIP24)	EEPROM	NONE
XICOR	X2816A(DIP24)	EEPROM	NONE
XICOR	X2816A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
XICOR	X2816B(DIP24)	EEPROM	NONE
XICOR	X2816B(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
XICOR	X2816C(DIP24)	EEPROM	NONE
XICOR	X2816C(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
XICOR	X2816C(SOIC24)	EEPROM	LP-SOP-28PIN-B(300mil)
XICOR	X28256(DIP28)	EEPROM	NONE
XICOR	X28256(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
XICOR	X2864A(DIP28)	EEPROM	NONE
XICOR	X2864A(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
XICOR	X2864B(DIP28)	EEPROM	NONE
XICOR	X2864B(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
XICOR	X2864H(DIP28)	EEPROM	NONE
XICOR	X2864H(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
XICOR	X28C010(DIP32)	EEPROM	NONE
XICOR	X28C010(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
XICOR	X28C010(TSOP40)	EEPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
XICOR	X28C16(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
XICOR	X28C256(DIP28)	EEPROM	NONE
XICOR	X28C256(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
XICOR	X28C256(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
XICOR	X28C256(TSOP32)	EEPROM	LP48-TSOP-32S
XICOR	X28C256B(DIP28)	EEPROM	NONE
XICOR	X28C256B(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
XICOR	X28C512(DIP32)	EEPROM	NONE
XICOR	X28C512(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
XICOR	X28C512(TSOP40)	EEPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
XICOR	X28C513(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
XICOR	X28C64(DIP28)	EEPROM	NONE
XICOR	X28C64(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
XICOR	X28C64(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
XICOR	X28C64(TSOP32)	EEPROM	LP48-TSOP-32S
XICOR	X28HC16(DIP24)	EEPROM	NONE
XICOR	X28HC16(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
XICOR	X28HC16(SOIC24)	EEPROM	LP-SOP-28PIN-B(300mil)
XICOR	X28HC256(DIP28)	EEPROM	NONE
XICOR	X28HC256(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
XICOR	X28HC256(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
XICOR	X28HC256(TSOP32)	EEPROM	LP48-TSOP-32S
XICOR	X28HC64(DIP28)	EEPROM	NONE
XICOR	X28HC64(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
XICOR	X28HC64(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
XICOR	X28HC64(TSOP32)	EEPROM	LP48-TSOP-32S
XICOR	X28HT010(DIP32)	EEPROM	NONE
XICOR	X28HT512(DIP32)	EEPROM	NONE
XICOR	X28LC512(DIP32)	EEPROM	NONE
XICOR	X28LC512(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
XICOR	X28LC512(TSOP40)	EEPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
XICOR	X28LC513(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
XICOR	X28LV010(DIP32)	EEPROM	NONE
XICOR	X28LV010(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S

Manufacturer	Parts Number	Type	ADAPTER
XICOR	X28LV010(TSOP40)	EEPROM	LP48-TSOP-40PIN or LP48-TSOP-40S
XICOR	X28VC256(DIP28)	EEPROM	NONE
XICOR	X28VC256(PLCC32)	EEPROM	LP-PLCC-1M32 or LP-PLCC-1M32S
XICOR	X28VC256(SOIC28)	EEPROM	LP-SOP-28PIN-B(300mil)
XICOR	X28VC256(TSOP32)	EEPROM	LP48-TSOP-32S
YMC	Y24LC02(DIP8)	EEPROM	NONE
YMC	Y24LC02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
YMC	Y24LC02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
YMC	Y93LC46-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
YMC	Y93LC46-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
YMC	Y93LC46-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
YMC	Y93LC46-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
YMC	Y93LC46A-X16(DIP8)	EEPROM	NONE
YMC	Y93LC46A-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
YMC	Y93LC46A-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
YMC	Y93LC46A-X8(DIP8)	EEPROM	NONE
YMC	Y93LC46A-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
YMC	Y93LC46A-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
YMC	Y93LC46B-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
YMC	Y93LC46B-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
YMC	Y93LC66-X16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
YMC	Y93LC66-X16(TSSOP8)	EEPROM	LP-TSSOP-8PIN
YMC	Y93LC66-X8(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
YMC	Y93LC66-X8(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Zempro	MS25X16(SOP8-209)	FLASH	LP-SOP-8PIN-B(207mil)
Zempro	TS25L010A-P(PDIP8)	FLASH	NONE
Zempro	TS25L010A-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Zempro	TS25L010A-V(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Zempro	TS25L020A-P(PDIP8)	FLASH	NONE
Zempro	TS25L020A-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Zempro	TS25L020A-V(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Zempro	TS25L032A-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Zempro	TS25L16-P(PDIP8)	FLASH	NONE
Zempro	TS25L16-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Zempro	TS25L16-V(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Zempro	TS25L16PE-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Zempro	TS25L16PE-V(WSON8)	FLASH	LP48-WSON8-5x6
Zempro	TS25L20-P(PDIP8)	FLASH	NONE
Zempro	TS25L20-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Zempro	TS25L20-V(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Zempro	TS25L40-P(PDIP8)	FLASH	NONE
Zempro	TS25L40-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Zempro	TS25L40-V(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Zempro	TS25L512A-V(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Zempro	TS25L80-P(PDIP8)	FLASH	NONE
Zempro	TS25L80-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Zempro	TS25L80-V(SOP8)	FLASH	LP-SOP-16PIN(150mil)
Zempro	TS25L80PE-S(SOP8)	FLASH	LP-SOP-8PIN-B(207mil)
Zempro	TS25L80PE-V(WSON8)	FLASH	LP48-WSON8-5x6
Zhengxin	LX24C01(DIP8)	EEPROM	NONE
Zhengxin	LX24C01(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Zhengxin	LX24C01(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Zhengxin	LX24C02(DIP8)	EEPROM	NONE
Zhengxin	LX24C02(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Zhengxin	LX24C02(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Zhengxin	LX24C04(DIP8)	EEPROM	NONE
Zhengxin	LX24C04(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Zhengxin	LX24C04(TSSOP8)	EEPROM	LP-TSSOP-8PIN

Manufacturer	Parts Number	Type	ADAPTER
Zhengxin	LX24C08(DIP8)	EEPROM	NONE
Zhengxin	LX24C08(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Zhengxin	LX24C08(TSSOP8)	EEPROM	LP-TSSOP-8PIN
Zhengxin	LX24C16(DIP8)	EEPROM	NONE
Zhengxin	LX24C16(SOP8)	EEPROM	LP-SOP-16PIN(150mil)
Zhengxin	LX24C16(TSSOP8)	EEPROM	LP-TSSOP-8PIN