





LEAD FINISH:		SOLDER				
BUSHING FINISH:		SILVER				
CAPACITANCE		27nF GMV				
TEMP. RANGE		-55°C TO 125°C				
CURRENT		5 AMP MAX.				
WORKING VOLTAGE		125°C 100VDC MAX.				
D.C. RESISTANCE		.03ohms MAX.				
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD						
FREQ. MHZ	1	10	100	1GHz	10GHz	
I.L. (db)	10	30	50	70	70	

SCHEMATIC



MARKING:

PART: SCI002
BAG: SCI-3112-002
DATE CODE
LOT NO.
QTY./BAG (200 MAX.)

REV. NO.	06	05	04
CHANGE NOTICE	CN 214618	CN 202420	CN 169175 REDRAWN
TOLERANCES UNLESS OTHERWISE SPECIFIED			
Fractions ± 1/64			
Dec. .xx±			
Dec. .xxx±.010			
Angles ±0° 30'			
CODE IDENT. NO. DLSP2			



SPECTRUM CONTROL INC.

ERIE, FAIRVIEW
PENNSYLVANIA

Dwn. M.KEVERLINE

Date 2-17-04

Engr. T. Taylor

Scale NONE

Description FEED THRU
RESIN SEAL FILTER

SCI-3112-002