


3.5mm 4 Cond Plug

171-7435-EX

KOBI CONN

3.5mm 4 Cond Plug



DIMENSIONS: mm (in.)

SPECIFICATIONS	
Handle:	Polyethylene
Contacts:	Nickel plated brass
Color:	Black
Insulator:	PBT G15%
Recommended Wire:	28 AWG
Insulation resistance:	100 Megaohm min. @ 500VDC
Dielectric Strenght:	500VAC (for one minute)
Mating jacks:	161-6435-EX
	161-5435-EX
	161-7900-EX
RoHS Compliant by Exemption	

	Part Name	Material	Finish
1	Metal	BS	NI
2	Chip Terminal	BS	NI
3	Terminal 1	BS	NI
4	Terminal 2	BS	NI
5	Terminal 3	ST	NI
6	Plug Insulattor	POM	-
7	Insulator	PBT G15%	-
8	Handol	PE	-

Date Last Revised: 8-4-10

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300914

171-7435-EX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[171-7435-EX](#)