

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0015876022](#)
Status: **Obsolete**
Description: 1.27mm (.050") Pitch SCSI+ Receptacle, Shielded, Right Angle with Latches, 68 Circuits, Screw Hole, 4-40 Thread
Replacement Part Number: NONE

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	I/O Connectors
Series	79059
Application	Wire-to-Board
Comments	For Automatic Placement of Screw Hardware
Component Type	Receptacle
Obsolete Date	2004/09/01
Product Name	SCSI+
Replacement Part Number	NONE
Type	N/A

Physical

Circuits (Loaded)	68
Circuits (maximum)	68
Color - Resin	Black
Durability (mating cycles max)	500
Flammability	94V-0
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Number of Rows	2
Orientation	Right Angle
PC Tail Length	3.18mm (.125"), 4.19mm (.165")
PCB Retention	Yes
PCB Thickness - Recommended	3.20mm (.126")
Packaging Type	Tube
Panel Mount	Yes
Pitch - Mating Interface	1.27mm (.050")
Plating min - Mating	0.762µm (30µ")
Plating min - Termination	1.905µm (75µ")
Polarized to Mating Part	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-55°C to +105°C
Termination Interface: Style	Through Hole
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	1A
Shielded	Yes
Voltage - Maximum	30V

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[79059Series](#)

Mates With
[79058](#) , [71295](#)

Material Info
Old Part Number

790592202

This document was generated on 02/23/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION