





JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
7732	2.5	.100	.100	1.25	10,000	C-2R
7022	5.0	.021	.034	0.43	10,000	C-2R
7263	5.0	.030	.030	.038	16,000	C-2R
7680	5.0	.060	.030	0.38	100,000	C-2R
7683	5.0	.060	.050	0.63	100,000	C-2R
7265	5.0	.060	.150	1.89	5,000	C-2R
7714	5.0	.075	.090	1.13	25,000	C-2R
7715	5.0	.115	.150	1.89	40,000	C-2R
7268	5.0	.125	.220	2.77	5,000	C-2R
8095	10.0	.027	.100	1.26	10,000	C-2F
CB44	12.0	.040	.090	1.13	10,000	C-2F
8097	12.0	.060	.150	1.89	16,000	C-2F
8098	14.0	.065	.150	1.89	16,000	C-2F
8099	18.0	.026	.150	1.89	16,000	C-2F
7839	28.0	.024	.150	1.89	16,000	CC-2F

NOTES:

- GLASS ENVELOPE TO BE TIPLESS AND SEAMLESS.
- BASE MATERIAL: NYLON OR EQUIVALENT.
- BASE COLOR: WHITE.
- PIN MATERIAL: NICKEL PLATED.
- LAMPS TO BE 100% AGED FOR AN EQUIVALENT TO A MINIMUM OF TEN HOURS AT RATED VOLTAGES.
- FINAL INSPECTION ON ALL LAMPS TO BE PER: MIL. STD. 105E TO AN AQL OF 2.5.
- DIMENSIONS NOT PROVIDING TOLERANCES ARE REFERENCE DIMENSIONS ONLY.



DIMENSIONS ARE
IN MILLIMETERS

TOLERANCE UNLESS
OTHERWISE SPECIFIED

1 PL +/- 0.2
2 PL +/- 0
ANGLE +/- 0

JKL

COMPONENTS CORPORATION

TITLE

T-1 STANDARD BI-PIN BASED LAMPS

REV.
NO.

CHANGE PIN MATERIAL NOTE
RELEASED - CANCEL SM-STDBP-T 1, CB81, 7255,
7260, 7261, CB23, CB43, 7264, CB45, CB48

7/28/08
3/13/00
APPVD
DATE

DRAWN BY
L. WENGSTROM

APPVD BY
L.R.

DATE
7/28/08

- CAD DRAWING -
MANUAL REVISIONS NOT PERMITTED

SIZE
A

FSCM NO.
55335

DRAWING
NO.

BI-PIN T-1

SCALE
NONE

RELEASED
DATE
3/13/00

REVISION
DATE
7/28/08

REV.
NO. A

SHEET
1 OF 1