



NRZ

28
G b p s

(0.80 mm) .0315" PITCH • QTE/QSE SERIES

**QTE**
Board Mates:
QSE**QSE**
Board Mates:
QTE**QTE/QSE**
Cable Mates:
EQCD, EQDP**Standoffs:**
SO

QTE	PINS PER ROW NO. OF PAIRS	LEAD STYLE	PLATING OPTION	TYPE	A	OTHER OPTIONS	"X"R
	-020, -040, -060 (40 total pins per bank = -D)	Specify LEAD STYLE from Chart	-F = Gold flash on contact, Matte Tin on tail	-D = Single- Ended		-K = (7.00 mm) .275" DIA Polyimide film Pick & Place Pad	Leave blank for Tray Packaging
	-014, -028, -042 (14 pairs per bank = -D-DP)		-L = 10 μ" (0.25 μm) Gold on contact, Matte Tin on tail	-D-DP = Differential Pair (-01 only)		-L = Latching Option (N/A on -042 & -060 positions)	-TR = Tape & Reel (Not available with -05 & -07 lead style)

SPECIFICATIONS**Insulator Material:**

Liquid Crystal Polymer

Contact Material:

Phosphor Bronze

Plating:Au or Sn over
50 μ" (1.27 μm) Ni**Operating Temp Range:**

-55 °C to +125 °C

Current Rating:

Contact:

2 A per pin (2 pins powered)

Ground Plane:


23 A per ground plane
(1 ground plane powered)**Voltage Rating:**

225 VAC/318 VDC

Max Cycles:

100


QTE LEAD STYLE	A	HEIGHT WITH QSE*
-01	(4.27) .168	(5.00) .197
-02	(7.26) .286	(8.00) .315
-03	(10.27) .404	(11.00) .433
-04	(15.25) .600	(16.00) .630
-05	(18.26) .718	(19.00) .748
-07	(24.24) .954	(25.00) .984
-09	(13.26) .522	(14.00) .551

*Processing conditions will affect mated
height. See SO Series for board space
tolerances.**PROCESSING****Lead-Free Solderable:**

Yes

SMT Lead Coplanarity:(0.10 mm) .004" max
(020-060)**Board Stacking:**For applications requiring
more than two connectors
contact ipg@samtec.comView complete specifications at: samtec.com?QTE

QSE	PINS PER ROW NO. OF PAIRS	01	PLATING OPTION	TYPE	A	OTHER OPTIONS	"X"R
	-020, -040, -060 (40 total pins per bank = -D)		-F = Gold flash on contact, Matte Tin on tail	-D = Single- Ended		-GP = Guide Post	Leave blank for Tray Packaging
	-014, -028, -042 (14 pairs per bank = -D-DP)		-L = 10 μ" (0.25 μm) Gold on contact, Matte Tin on tail	-D-DP = Differential Pair		-K = (8.25 mm) .325" DIA Polyimide Film Pick & Place Pad	-TR = Tape & Reel (40 positions max. with -GP)

**Note:**
Some lengths, styles and
options are non-standard,
non-returnable.View complete specifications at: samtec.com?QSE